



[Alcoswitch](#) | [Alcoswitch TRD](#)

TE Internal #: 1825423-1

Alcoswitch TRD, Rocker Switches, Power, Panel Cutout Size .445 x .475 in [11.3 x 12.06 mm], Silver

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **Power**

Rocker Switch Mounting Type: **15/32" (Round Hole)**

Indicator/Imprint Legend: **None**

Panel Cutout Size: **11.3 x 12.06 mm [.445 x .475 in]**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Product Type	Switch
Rocker Switch Type	Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Top
Actuator Style	Rocker

Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	11.3 x 12.06 mm [.445 x .475 in]
Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On None On

Electrical Characteristics

Rocker Switch Voltage Rating	28 VDC
------------------------------	--------

Body Features

Actuator Color	Black
----------------	-------

Contact Features

Switch Contact Plating Material	Silver
Rocker Switch Contact Current Rating	3 A



Termination Features

Termination Type	Quick Connect
------------------	---------------

Mechanical Attachment

Mounting Angle	Vertical
Rocker Switch Mounting Type	15/32" (Round Hole)

Housing Features

Process Sealed	No
----------------	----

Industry Standards

VDE Tested	No
------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 4-1437595-1
TRD11D10WL=SPDT ROCKER BLACK



TE Part # 5-1437595-6
TRD11G10WL=ROCKER SW SPDT (ON)



TE Part # 1825426-1
TRD13D10WLLR204 rocker switch (ON)




TE Part # 5-1437595-9
TRD11H10WL=ROCKER GOLD ON OFF



TE Part # 4-1437595-2
TRD11D10WLLR5=SP ROCKER LIGHTE

Also in the Series | Alcoswitch TRD



Rocker Switches(42)

Customers Also Bought



TE Part #1393127-9
PRD-11AG0-120=PRD



TE Part #W4SB
WEDGE LOCK, 4P, PLG, BLK, STD, DT, B



TE Part #5-1393122-5
KHAU-17D12-12=KH



TE Part #1969805-1
04P UMNL HDR ASSY R/A, PIN V0 GW



TE Part #640309-3
UMNL PIN 12-10 PTPPHBZ




TE Part #1355541-2
UMGEH M.SCHIEBER32P



TE Part #6-1393127-1
PRD-11DY0-12=PRD



TE Part #1-968873-3
AMP MCP 2.8, CONTACT (LP)



Documents

Product Drawings

[TRD23N10QC04 rocker switch](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1825423-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825423-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825423-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English