

Product information

35 41 115

Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Soft transitions; no sharp edges
 Low-friction double spring for gentle and
- Low-friction double spring for gentle and even opening
 The polish or mirror polish together with a fine film of oil offer effective rust protection no circuit faults caused by peeling chrome from plated
- tools
 Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened

MM <u>√4</u> 5°	0
-----------------	---

••••••

General		
Article No.	35 41 115	
EAN	4003773082248	
Head	mirror polished	
Handles	with multi-component grips	
Weight	55 g	
Dimensions	115 x 66 x 14 mm	
Standard	DIN ISO 9655	
Reach	no	
RohS	no	
Technical details		
Jaw length (B)	22.5 mm	
Jaw thickness (joint) (D)	6.5 mm	
Tips width (E)	2.0 mm	
Tips thickness (F)	1.0 mm	
Head width (A)	11.0 mm	
Dimensions angle	45 °	
Classification		
eCl@ss 5.1.4	21040301	
proficl@ss 6.0	EAA840c015	
UNSPSC 13.1	27112149	
Spare Parts		
35 99 01	Spare spring for electronics pliers, (2x)	

technical change and errors excepted

KNIPEX Quality – Made in Germany





