

Product information

48 41 J11

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 D



90°



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- With overexpansion guard (adjustable using end stop)
- Adjustment using hexagonal screw
- Ideal for series production as excessive expansion of rings is effectively prevented
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- 90° angled tips
- With overstretching limiter for standardised assembly in accordance with DIN 472
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

General

Article No.	48 41 J11
EAN	4003773079576
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	105 g
Dimensions	130 x 52 x 12 mm
Standard	DIN 5256 D
Reach	no
RohS	no

Technical details

Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted

