

Product information

79 42 125 Z ESD

Precision Electronics Side Cutter ESD

DIN ISO 9654 DIN EN 61 340-5




- For an optimised flush cutting result of soft materials
- For installations with tight tolerances, for precise configuration of wire ends
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened

General

Article No.	79 42 125 Z ESD
EAN	4003773078456
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	58 g
Dimensions	125 x 61 x 19 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
Reach	no
RohS	no

Technical details

Cutting capacities soft wire (diameter)	Ø 0.1 – 1.3 mm
Jaw length (B)	11 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	11 mm
ESD	yes



Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

