

## Product information

# 92 21 05

## Mini Precision Tweezers




- For particularly demanding precision work: tough and highly resistant to corrosion
- Handcrafted: polished edges and an excellent matt, scratch-free and non-reflective surface
- For the electronics industry, watchmakers, jewellers, laboratories with biological and medical applications in moderately aggressive chemical environments
- High-quality premium stainless steel: high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Extra short and lightweight tweezers with narrow tips
- Ideal for working in confined spaces, under the microscope and for precision close work.
- Ideal for sample handling, microscopy preparation, sorting, precision manufacturing, electronic assembly, rework and repair
- Premium stainless steel

### General

Article No.	92 21 05
EAN	4003773086703
Material	premium stainless steel
Gripping surfaces	smooth gripping surfaces
Weight	7 g
Dimensions	70 x 7 x 7.5 mm
Reach	no
RohS	no

### Technical details

Tips width (A)	0.1 mm
Tips width (B)	0.2 mm
Corrosion-resistant	yes
	no
VDE tested	no
sectors	Industry electronics



### Classification

eCl@ss 5.1.4	21040500
ETIM 5.0	EC000182
ETIM 6.0	EC000182
proficl@ss 6.0	EAB696c019

technical change and errors excepted