

### **Product information**

## 95 36 315 A

#### **Cable Cutter**

(ratchet action)

For steel wire armoured cables (SWA cable)

IEC 60900 DIN EN 60900



**☆1000V ///// <b>③** 

General
Article No.

#### Robust, handy, stable: for steel-armoured cables (SWA cables)

- Cuts through steel wire armoured cables up to Ø 45 mm / 380 mm<sup>2</sup> (e.g. 4 x 95 mm<sup>2</sup>) using one or two-handed operation
- Sturdy. Easy to use. Stable.
- Simple handling due to low weight (800 g) and compact design (315 mm length) can also be used in confined areas
- Precision-ground blades and induction-hardened cutting edges cut smoothly and neatly without crushing
- Innovative high leverage three-stage ratchet-drive
- Support area for putting down the pliers when cutting
- Not suitable for cutting ACSR cable and wire rope!
- Cutter head: special high-grade tool steel, forged, oil-hardened

EAN	4003773078579
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Weight	800 g
Dimensions	315 x 140 x 30 mm
Standard	IEC 60900 DIN EN 60900
Reach	no
RohS	no
Technical details	
Cutting capacity copper cable, multiple- stranded	380 mm²
Cutting capacity copper cable, multiple- stranded	Ø 45 mm
MCM	750
VDE tested	yes
Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616
Accessories	
95 39 315 A01	Pivot cutter repair kit for 95 32 315 A and 95 36 315 A,
95 39 315 A02	Fixed cutter repair kit for 95 32 315 A and 95 36 315 A,

Pivot cutter repair kit for 95 32 315 A and 95 36 315 A,

95 36 315 A

technical change and errors excepted

**Spare Parts** 95 39 315 A01

# **KNIPEX** Quality – Made in Germany







Precision-milled and induction-hardened cutting edge