

Product information

97 53 14

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access



- Narrow handle width and improved ergonomics
- Expanded capacity of hexagonal crimping up to 10 mm²
- Hexagonal compression for confined connection dimensions
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 53 14
EAN	4003773041474
Pliers	burnished
Handles	with multi-component grips
Weight	445 g
Dimensions	180 x 75 x 21 mm
Reach	yes
RohS	no

Technical details



Applications	Wire ferrules
Capacity in square millimetres	0.08 — 10 mm ²
Number of crimping positions	1
AWG	28 — 8

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts	
97 59 30	Extension spring for 97 53 4/5/8/9/14, thin (Handle)
97 59 31	Extension spring for 97 53 4/5/8/9/14, thick (Head)

KNIPEX Quality – Made in Germany



Spare Parts	
97 59 32	Circlips for model 97 53 for 97 53 XX,

technical change and errors excepted