cannon

High Temperature Micro-MDM Connector Series

Features & Benefits



Reliable. Durable. Versatile.

cannon

ITT Cannon's High Temperature Micro-MDM Connectors are designed to perform in the harshest and most demanding environments

With the increasing demand for ruggedized interconnect solutions that can withstand extreme temperatures and operating conditions, ITT Cannon's **High Temperature Microminiature Connector Series** continues to lead the industry with high reliability products and customized solutions for multiple markets and applications.



Aerospace & Defense UAVs, Satellites, Military Electronics, Missile Systems



Space & Satellites Rocket Boosters, Launch Systems, Data Transmission



Oil & Gas Oil Exploration, Down-Hole Drilling, Offshore Drilling



Transportation & Industrial High-Speed Rail, Instrumentation, Test Equipment

From Standard to Ultra, ITT Cannon Offers a Full Range of Ruggedized, High Temp Microminiature Connectors

Drawing on 100 years of interconnect excellence and more than two decades of industry-leading innovation with High Temp Micro-MDM Connectors, ITT Cannon is committed to delivering solutions that are truly Engineered for Life.

Our family of reliable and versatile Micro-MDM Connectors withstand temperatures ranging from -55°C to 230°C and are designed to MIL-DTL-83513 specifications.

The Cannon Difference:

200

- 20+ years of experience in the design and manufacture of High Temp Micro-MDM connectors
- Highly engineered Micro-MDM interconnects offer exceptional durability, reliability and versatility in high temperature applications
- Designed to MIL-DTL-83513 specifications
- A commitment to delivering the best solution for standard and custom design requirements



Cannon Standard Micro-MDM

- Designed to MIL-DTL-83513 specifications
- Micro Twist Pin recessed into plug insulators
- Current rating: 3A
- Durability: 500 mating cycles
- Contacts: copper alloy; gold plated
- Low profile configurations available
- Operating temperature: -55°C to +150°C



Cannon High Temp Micro-MDM F222

150

- Designed to MIL-DTL-83513 specifications
- Standard or low profile, cable-to-cable and board mount configurations
- Micro Twist Pin recessed into plug insulators
- Current rating: 3A
- Durability: 500 mating cycles
- Contacts: copper alloy; gold plated
- Low profile configurations available
- Operating temperature: -55°C to +200°C



NEW Cannon Ultra-High Temp Micro-MDM F300



- Withstands 230° Celsius continuous operating temperature for 500 hours
- Stainless steel shells (passivation only)
- High temp Liquid Crystal Polymer insulator material
- Nickel plated copper wire PTFE jacket per M22759/87
- Designed for critical cable-to-cable applications
- High reliability Micro Twist Pin and Socket contacts
- Durability: 500 mating cycles
- Operating temperature: -55°C to 230°C

Specifications and Options

For Standard MDM and High Temp MDM / MDLM



Specifications

Configurations

- Terminations
- Stranded wire
- Solid wire
- Solder pots
- PCB
 - Straight
 - Right angle
 - Condensed right angle
- Signal contacts: 9, 15, 21, 25, 31, 37, 51, 100

Electrical Wire Size

- Stranded wire:
 24 AWG thru 32 AWG
 - 24 AVVG tillu 32 AVV
- Solid wire: - 25 AWG
- Solder pots:
- 26 AWG or smaller
- PC tails: - 24 AWG

Material and Finishes

- Shell material
- Aluminum alloy
- Shell plating
- Electroless nickel
- Yellow chromate /cadmium over nickel
- Insulator
 - Liquid crystal polymer per MIL-M-24519, type GLCP-30F
- At temperatures above 175°C, yellow chromate over cadmium can cause shell discoloration and deterioration of the chromate conversion coating.

Hardware Configurations

	Commercial		MIL-DTL-83513
Code	Description	Code	Description
А	No hardware (.125 dia. hole for sizes 9-51 &.166 dia. hole for size 100")		Size 9-51
В	No hardware (standard) (.091 dia. hole for size 9-51 & .120 dia. hole for size 100)	M2	Jackscrew-low profile (allen head)
B1	No hardware (.1475 dia. hole for size 100)		Jackscrew-standard profile (allen head)
F	Float mount		Jackscrew-low profile (slotted head)
К	Jackscrew-standard profile	M6	Jackscrew-standard profile (slotted head)
L	Jackscrew-low profile		Jackpost
Р	Jackpost		
			Size 100
	PCB Only	M12	Jackscrew-low profile (allen head)
R1	Rear Panel Mount Jackpost, .032" Panel	M13	Jackscrew-standard profile (allen head)
R2	Rear Panel Mount Jackpost, .047" Panel	M15	Jackscrew-low profile (slotted head)
R3	Rear Panel Mount Jackpost, .062" Panel	M16	Jackscrew-standard profile (slotted head)
R4	Rear Panel Mount Jackpost, .093" Panel	M17	Jackpost
R5	Rear Panel Mount Jackpost, .125" Panel		

Termination Modification Codes

Stranded 1	feflon [®] Wire per MIL-W-	16878/4 (H)	Solid Uninsulated Wire (L)						
Length	All Yellow	Color Coded	Termination Code	Length					
3 (76.2)	H020	H027	L61	.125 (3.18)					
6 (152.4)	H019	H016	L56	.150 (3.81)					
8 (203.2)	H026	H034	L57	.190 (4.83)					
10 (254.0)	H029	H025	L39	.250 (6.35)					
12 (304.8)	H028	H002	L58	.375 (9.52)					
18 (457.2)	H001	H003	L1	.500 (12.70)					
20 (508.0)	H038	H023	L14	.750 (19.05)					
24 (609.6)	H009	H004	L2	1.000 (25.40)					
30 (762.0)	H010	H005	L7	1.500 (38.10)					
36 (914.4)	H011	H006	L6	2.000 (50.80)					
48 (1219.2)	H013	H048	L16	2.500 (63.50)					
72 (1828.8)	H017	H046	L10	3.000 (76.20)					
120 (3048.0)	H042	H041							

200°C High Temp Micro-MDM F222

How to Order | Part Number Configurator



Wired & Solder Pot	R	- MDM	25	Р	Н	003	M2	A174	- F222
RoHS Compliance									
Series									
MDM - Micro-D Metal Shell									
Contact Arrangement									
9, 15, 21, 25, 31, 37, 51 & 100									
Contract Type									
P - Pin S - Socket									
Termination Type									
H - Insulated Stranded Wire L - Uninsulated Stranded Wire S - S - Solderpot									
Termination Modified Code									
See Termination Modification table for Harness Types (H) & Solid Uninsulated	Types (L)								
Hardware									
Commercial A - No hardware (.125 dia. hole for sizes 9-51 & .166 dia. hole for size 1 B - No hardware (standard) (.091 dia. hole for size 9-51 & .120 dia. hole B1 - No hardware (.1475 dia. hole for size 100) F - Float mount K - Jackscrew-standard profile L - Jackscrew-low profile M7 Jackpost P - Jackpost		00)							
Military Size 9-51M2-Size Jackscrew-low profile (allen head)M3-Jackscrew-standard profile (allen head)M5-Jackscrew-low profile (slotted head)M6-Jackscrew-standard profile (slotted head)M7-Jackpost									
Military Size 100M12-Jackscrew-low profile (allen head)M13-Jackscrew-standard profile (allen head)M14-Jackscrew-low profile (slotted head)M16-Jackscrew-standard profile (slotted head)M17-Jackpost									
Shell Finish									
BlankYellow Chromate/Cadmium (Not RoHS Compliant)A174Electroless Nickel (RoHS Compliant)								-	
Mod Code									
E222 High Tomporature 2009C									

F222 - High Temperature 200°C

200°C High Temp Micro-MDM F222

How to Order | Part Number Configurator



Board Mount, PCB	R - MDM	25	P BR	Р	Т	L39	A714	- F222
RoHS Compliance								
Series								
MDM - Micro-D Metal Shell								
Contact Arrangement								
9, 15, 21, 25, 31, 37, 51 & 100								
Contract Type								
P - Pin S - Socket								
Termination Type								
BS - Straight BR - Right Angle CBR - Condensed Right Angle								
Hardware								
CommercialA-No hardware (.125 dia. hole for sizes 9-51 &.166 dialB-No hardware (standard) (.091 dia. hole for size 9-B1-No hardware (.1475 dia. hole for size 100)P-JackpostR1-Rear Panel Mount Jackpost, .032" PanelR2-Rear Panel Mount Jackpost, .047" PanelR3-Rear Panel Mount Jackpost, .062" PanelR4-Rear Panel Mount Jackpost, .093" PanelR5-Rear Panel Mount Jackpost, .125" Panel								
Military Size 9-51 M7 - Jackpost								
Military Size 100 M17 - Jackpost								
Mounting Hardware for PCB								
T - Threaded Insert - Thru-Hole								
Termination Modified Code								
See Termination Modification table for Harness Types (H) & S	olid Uninsulated Types (L)							
Shell Finish								
Blank Yellow Chromate/Cadmium (Not RoHS Compliant A174 - Electroless Nickel (RoHS Compliant)	t)							
Mod Code								

F222 - High Temperature 200°C

200°C Low Profile Micro-MDLM F222

How to Order | Part Number Nomenclature



200 °C

Wired	MDLM	- 25	Р	6	Р	Y	18	L	- A174	F222
Series										
MDLM - MDM Low Profile / RMDLM - MDM Low Profile RoHS										
Contact Arrangement										
9, 15, 21, 25, 31, 37 & 51										
Contact Type										
P Pin / S Socket										
Wire Gauge (AWG)										
4 #24 Gauge / 6 #26 Gauge (Standard) / 8 #28 Gauge / 0 #	30 Gauge									
Wire Type										
P Teflon (PTFE Insulated) Wire Per MIL-W-16878/4 (Standard) / T - E Cross-Linked Tefzel (ETFE Insulated) Wire Per MIL-W-22759/33	Teflon (TFE) W	/ire Per MIL	-W-22759/1	1						
Wire Colour										
W White / Y Yellow (Standard) / S Color Coded pet MIL-STD-68	1, System 1 /	T Ten Colo	or Repeat /	C Custon	n Wire Co	loring				
Overall Wire Length (Inches)										
1 Inch Minimum Rounded to the Nearest Whole Inch Examples: 5 -	5 inches, 18 - 1	8 inches, 5	0 - 50 inche	s, 120 - 12	0 inches					
Hardware										
Commerical B, A, P, K, L, F / Military M2, M3, M5, M6, M7										
Shell Finish										
Blank Standard Shell Finish Electroless Nickel (RoHS Compliant) / A141 Irridite/Alodine (RoHS Compliant) / A30 Black Anodize (RoH		er Nickel (R	oHS Compli	ant)						
Mod Code										

F222 High Temperature 200°C (Consult Factory for all other Mod Codes)

200°C Low Profile Micro-MDLM F222

How to Order | Part Number Configurator

Board Mount PCB	MDLM	- 25	Р	CBR	Р	Т	L67	A172	- F222
Series									
MDLM - MDM Low Profile / RMDLM - MDM Low Profile RoHS									
Contact Arrangement									
9, 15, 21, 25, 31, 37 & 51									
Contact Type									
P Pin / S Socket									
Termination Type									
CBR Right Angle Narrow Profile PCB Termination									
Hardware									
Blank No hardware, Ø.092 Hole / M* Military Specification Hardwar *There will be a threaded nut behind flange as to allow later optional		/5 / <mark>M7</mark> Ja	ckpost						
Mounting Hardware for PCB									
Blank Thru-Hole / T Threaded Insert (Future Offering)									
Termination Tail Length (Gold plated Solid 24 AW	G Wire)								
Blank .109 Inch (Standard) / L67 .140 inch / L66 .172 inch									
Shell Finish/Mod Codes									
Blank Electroless Nickel (RoHS Compliant) / A172 Gold over Nickel (RoHS Compliant)								
Mod Code									
E222 High Temperature 200°C									

F222 High Temperature 200°C (Consult Factory for all other Mod Codes)

230oC Ultra-High Temp Micro-MDM F300



How to Order | Part Number Configurator

Μ	DM -	25	Р	R	003	L	-	F300	Hi	gh-Tem	o Wires	Callou	ıts _
Series										M22	2759/87-	26-9	
MDM - MD Metal Shell									Length	Yellow	White	10-Color Repeat	System 1
Contact Arrangement									1	030	R30	Т30	U30
									2	024	R24	T24	U24
9, 15, 21, 25, 31 & 37									3	020	R20	T20	U20
Contact Type									4	-	R33	T33	U33
									5	031	R31	T31	U31
P - Pin / S - Socket									6	019	R65	T19	072
Termination Type									8	026	R26	T26	U26
R - Insulated Standards Wire / S - S	Solder Pot								9	015	R15	T15	U15
n - Insuidleu Stanuarus Wife / 3									10	029	R29	T29	U29
Termination Modifier Co	de								12	028	R66	T28	073
(Consult Factory for all 'R', 'T' and 'U'	Mod Codes fo	r Lead Mat	erial and Le	anath)					16	029	R39 R36	T39 T36	U39
				ingunj					17 18	036	R36	T01	U36 074
									20	038	R38	T38	U38
Hardware									20	055	R55	T55	U55
P - Jackpost	K - Jacks	crew-Stand	lard Profile	•	Hardware p	er			24	009	R68	T09	075
R1 - Rear Panel Mount Jackpost	L - Jackso	rew-Low F	rofile		83513/5				30	010	R10	T10	U10
.032" Panel	F - Float	Mount			Size 9-25:				35	018	R18	T18	U18
R2 - Rear Panel Mount Jackpost	B - No ha	ardware (S	tandard)		M2 - Jackso (Allen Head		rofile		36	011	R69	T11	076
.047" Panel		dia. hole fo		1	M3 - Jackso	rew-stand	ard		40	037	R37	T37	U37
R3 - Rear Panel Mount Jackpost .062" Panel		dia. hole fo	or size 100		profile (Alle	n Head)			42	012	R12	T12	U12
R4 - Rear Panel Mount Jackpost	A - No ha 125 (ardware dia. hole fo	r sizes 9-5	1	M5 - Jackso	rew-low p	rofile		48	013	R70	T13	077
.093" Panel		dia. hole fo			(Slotted He	ad)			50	040	R40	T40	U40
R5 - Rear Panel Mount Jackpost	B1 - No l	nardware			M6 - Jackso		ard		60	014	R14	T14	U14
.125" Panel		dia. hole f	or size 10	,	profile (Slot	-			72	017	R71	T17	078
K - Jackscrew-Standard Profile		3513)			M7 - Jackpo	ost			80	032	R32	T32	U32
L - Jackscrew-Low Profile	S - Clinch	n Nut							92	022	R22	T22	U22
Chall Finish (MOD Casta	_								96	035	R35	T35	U35
Shell Finish / MOD Code	S								120	042	R42	T42	U42
F300 - Stainless Steel Passivated Only	у								180	043	R43	T43	U43

Specifications & Options for 230°C Ultra-High Temp Micro

Configurations

- Terminations
- Stranded wire
- Solid wire
- Solder pots
- PCB
 - StraightRight angle
 - Condensed right angle
- Signal contacts: 9, 15, 21, 25, 37, 37

Electrical Wire Size

- Solid wire:
 - Nickel plated copper wire PTFE jacket per M22759/87
 26 AWG
 - - -
- Solder pots: – 26 AWG or smaller

Material and Finishes

- Shell material
 - Stainless steel shells (passivation only)
- Insulator

 High temp Liquid Crystal Polymer insulator material
- Durability - 500 mating cycles
- Operating temperature -55°C to 230°C

Connect with your ITT Cannon representative today or visit us at www.ittcannon.com

Connect with the experts

From aerospace and defense systems, to specialized solutions for the oil and gas industry, we connect data, signal and power with those who need it most.



CHINA - Shenzhen City +86.755.2726.7888 FRANCE +33.1.60.04.93.93 GERMANY - Weinstadt +49.7151.699.0 HONG KONG +852.2732.2720 ITALY - Lainate +39.02938721 JAPAN - Kanagawa +81.462.57.2010 KOREA +82.2.702.7111 MEXICO - Nogales +52.631.311005 SHANGHAI + 86.21.2231.2222.2 SINGAPORE +65 66974205 UK - Basingstoke +44.1256.347400

USA - Irvine, CA +1.800.854.3028

The "ITT Engineered Blocks" symbol, "Engineered for life," "ITT" and "Cannon" are registered trademarks of ITT Inc. Specification and other data are based on information available at the time of printing, and are subject to change without notice.

