# **Darlington Transistor**



## **Description**

Designed for use in automotive ignition, switching and motor control applications.

RoHS Compliant



#### **Features**

- Collector–Emitter Breakdown Voltage
- V(BR)CEO = 400V(Min.)
- · Collector Saturation Voltage
- V<sub>CE(sat)</sub> = 2.0V(Max) @ IC= 5.0A
- · Minimum Lot-to-Lot variations for robust device performance and reliable operation

### **Maximum Ratings**

Parameter	Symbol	Value	Unit	
Collector-Base Voltage	Vсво	400		
Collector-Emitter Voltage	Vceo	400	V	
Emitter-Base Voltage	VEBO	8		
Collector Current-Continuous	lc	7		
Collector Current-Peak	Ісм	10	A	
Base Current- Continuous	lв	1.5		
Total Power Dissipation @Tc = 25°C	Pc	80	Watts	
Junction Temperature	TJ	150	°C	
Storage Temperature	Тѕтс	-65 to +150		

### **Thermal Characteristics**

Characteristic	Symbol	Value	Unit
Thermal Resistance Junction to Case	Rth j-c	1.56	°C/W

### Electrical Characteristics (Tc = 25°C unless otherwise specified

Characteristic	Symbol	Min.	Max.	Unit
Off Characteristics				
Collector-Emitter Breakdown Voltage (Ic= 10mA, Iв=0)	Vceo	400	-	V
Collector-Base Breakdown Voltage (Ic= 1mA, I <sub>E</sub> =0)	Vсво	400	-	V
Collector Cut-off Current (VCE= 400V, IB=0)	ICEO		0.25	A
Emitter Cut-off Current VEB=8V, IC=0	Ієво		15	mA

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




# Darlington Transistor



Characteristic	Symbol	Min.	Max.	Unit
On Characteristics	•		•	
DC Current Gain (Ic= 2.5A, Vc=5A) (Ic= 5A, Vc=5A) (Ic= 7A, Vc=5A)	hfe	150 50 15		
Collector-Emitter Saturation Voltage (Ic= 1A, V <sub>B</sub> =10mA) (Ic= 2A, V <sub>B</sub> =100mA) (Ic= 5A, V <sub>B</sub> =250mA)	Vce(sat)	-	1.5 1.5 2.0	
Base-Emitter Saturation Voltage (Ic= 2A, Iв=100mA) (Ic= 5A, Iв=250mA)	VBE(SAT)	-	2.2 2.3	V
Diode Forward Voltage (IF= 7A)	VF		3.5	
DYNAMIC CHARATERISTICS				
Collector Output Capacitance (Vcb=10 V, IE =0, f = 1.0 MHz)	Cob		150	pF

#### **Dimensions**



PIN 1. Base 2. Collector

3. Emitter

Dim	Min.	Max.
Α	15.5	15.9
В	9.8	10.2
С	4.2	4.5
D	0.7	0.9
F	3.4	3.7
G	4.98	5.18
Н	2.68	2.9
J	0.44	0.6
K	12.8	13.4
L	1.2	1.45
0	2.7	2.9
R	2.3	2.7
S	1.29	1.35
U	6.45	6.65
V	8.66	8.86

#### **Part Number Table**

Description	Part Number	
Darlington Transistor, NPN, 400V, 7A, 80W, TO-220	TIP152.	

Dimensions : Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

