

RoHS
Compliant




Description

MP010827 is a 4.3 (16:9) inch diagonally measured active display with high resolution WXGA 800x480 display and high brightness. This model is composed of a TFT LCD panel, backlight system, and HDMI interface. It is designed to make Raspberry Pi usage easy. You can simply use this TFT display with your Raspberry Pi, or also you can use this as computer display with any device which has HDMI output. This 4.3" TFT model comes in 800x480 resolution that would be great for embedded computing usage too.

Features

| No. | Item | Specification | Unit |
|-----|--------------------------------|-------------------------------------|-------------------|
| 1 | Panel Size | 4.3" | Inch |
| 2 | Number of Pixels | 800 (W) × RGB × 480 (H) | Pixels |
| 3 | Active Area | 95.04 (W) × 53.856 (H) | mm |
| 4 | Pixel Pitch | 0.1188 (W) × 0.1122 (H) | mm |
| 5 | Outline Dimension | 105.5 (W) × 67.2 (H) × 16.9 (T) | mm |
| 6 | Number of Colors | 16.7M | -- |
| 7 | Display Mode | IPS / Normally Black / Transmissive | -- |
| 8 | View Direction | Free direction | -- |
| 9 | Display Format | RGB vertical stripe | -- |
| 10 | Surface Treatment | Anti-Glare | -- |
| 11 | Contrast Ratio | 800 (Typ.) | -- |
| 12 | Luminance (cd/m ²) | 1100 (Typ.) | cd/m ² |
| 13 | Video Input Interface | HDMI (Compliance HDMI V1.4) | -- |
| 14 | Backlight | White LED | -- |
| 15 | Operation Temperature | -30 to 70 | °C |
| 16 | Storage Temperature | -30 to 80 | °C |
| 17 | Weight | (60) | g |

Mechanical Specification



Pin Description

HDMI (CN1) [HDMI A TYPE: A111974-2-01-R or compatible]

| Pin No. | Symbol | I/O | Function |
|---------|-----------|-----|---------------------|
| 1 | TMDS 2+ | I | TMDS Data2+ |
| 2 | GND | P | TMDS Data2 Shield |
| 3 | TMDS 2- | I | TMDS Data2- |
| 4 | TMDS 1+ | I | TMDS Data1+ |
| 5 | GND | P | TMDS Data1 Shield |
| 6 | TMDS 1- | I | TMDS Data1- |
| 7 | TMDS 0+ | I | TMDS Data0+ |
| 8 | GND | P | TMDS Data0 Shield |
| 9 | TMDS 0- | I | TMDS Data0- |
| 10 | TMDS CLK+ | I | TMDS Clock+ |
| 11 | GND | P | TMDS Clock Shield |
| 12 | TMDS CLK- | I | TMDS Clock- |
| 13 | CEC | I | CEC |
| 14 | N.C. | - | N.C. |
| 15 | DDC_SCL | I | IIC SCL to EDID ROM |
| 16 | DDC_SDA | I/O | IIC SDA to EDID ROM |
| 17 | GND | P | DDC/CEC Ground |
| 18 | HD_5V | P | +5V Power |
| 19 | HPD | O | Hot Plug Detect |

Power Input(CN2) [WAFER P2.0mm:2001S-02-RTE or compatible]

| Pin No. | Symbol | I/O | Function |
|---------|--------|-----|------------------|
| 1 | 5V | P | Power Supply +5V |
| 2 | GND | P | Ground |

Back-light Control(CN3) [WAFER P1.25mm:1251-03-ST-SE or compatible]

| Pin No. | Symbol | I/O | Function | Note |
|---------|--------|-----|---|------|
| 1 | GND | P | Ground | |
| 2 | PWM | I | Back-light Dimming control (internal pull up to 3.3V) | *1 |
| 3 | NC | - | No connection. | |

Absolute Maximum Ratings

Electrical Absolute Rating HDMI TFT LCD Module


| Item | Symbol | Values | | Unit |
|----------------------|--------|--------|------|------|
| | | Min | Max. | |
| Power supply voltage | 5V | 4.5 | 5.5 | V |

Environment Absolute Rating

| Item | Symbol | Values | | Unit | Note |
|-----------------------|--------|--------|------|------|---------------------|
| | | Min | Max. | | |
| Operating Temperature | Top | -30 | 70 | °C | Ambient temperature |
| Storage Temperature | Tst | | 80 | | |

Block Diagram

5.2 TFT LCD Module



Electrical Characteristics

HDMI TFT LCD Module

| Item | Symbol | Values | | | Unit | Note |
|---------------------|---------------------|--------|-------|------|------|------|
| | | Min | Typ. | Max. | | |
| Supply Voltage | 5V | 4.5 | 5 | 5.5 | V | |
| PWM frequency | | 200 | - | 200K | Hz | |
| PWM Dimming Voltage | V _{PWM-IH} | 2 | 3.3 | 5 | V | |
| | V _{PWM-IL} | - | - | 0.8 | | |
| Supply Current | ICC(5V) | - | 375 | 405 | mA | |
| LED life time | | - | 50000 | - | Hr | (1) |

Note


The "LED life time" is defined as the module brightness decrease to 50% original brightness that the ambient temperature is 25°C 60% RH.

Optical Characteristics

| Item | | Symbol | Condition | Min. | Typ. | Max. | Unit | | |
|---------------------|------------|---------|--|--------------|------|------|-------|----|----|
| Brightness | | -- | Note1, Note 3, (θ= 0°, Normal Viewing Angle) | 880 | 1100 | -- | cd/m2 | | |
| Uniformity | | B-uni | | 70 | 75 | - | % | | |
| Contrast Ratio | | CR | | 640 | 800 | -- | -- | | |
| Response Time | | Tr + Tf | | -- | 30 | 40 | ms | | |
| Colour Chromaticity | White | Wx | Center CR≥10 | 0.26 | 0.31 | 0.36 | -- | | |
| | | Wy | | 0.28 | 0.33 | 0.38 | | | |
| View angle | Horizontal | θx+ | | Center CR≥10 | 70 | 80 | | -- | -- |
| | | θx- | | | | | | | |
| | Vertical | θY+ | | | | | | | |
| | | θY- | | | | | | | |

Note: The following optical specifications shall be measured in a darkroom or equivalent state (ambient luminance ≤1 lux, and at room temperature). The operation temperature is 25°C±2°C. The measurement method is shown in Note1.

Note1: The method of optical measurement




Note2: Measured at the center area of the panel and at the viewing angle of the $\theta_x = \theta_y = 0^\circ$


Note3: Definition of Contrast Ratio (CR):

CR = Luminance with all pixels in white state ÷ Luminance with all pixels in Black state

Definition of Viewing Angle




Definition of Brightness Uniformity (B-uni)



$$B\text{-uni} = (\text{Minimum luminance of 9 points} \div \text{Maximum luminance of 9 points}) \times 100\%$$

Note 6: Definition of Response Time:

The Response Time is set initially by defining the "Rising Time (Tr)" and the "Falling Time (Tf)" respectively. Tr and Tf are defined as following figure



Note 7: Definition of Chromaticity:

The color coordinates (Wx,Wy),(Rx,Ry),(Gx,Gy),and (Bx,By) are obtained with all pixels in the viewing field at white, red, green, and blue states, respectively.

Part Number Table

| Description | Part Number |
|--------------------------------|-------------|
| TFT LCD, 4.3", HDMI, 800 × 480 | MP010827 |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.