# High Power Dry SIL/SIP Reed Relays


## Series 100HC

- Up to 3 Amps continuous carry current
- 1 A switching at up to 40 W
- Highest quality instrumentation grade switches
- High coil resistance of up to  $6000~\Omega$  for low power consumption
- Thermal EMF levels less than 10  $\mu$ V
- Stacking on 0.40 Inches pitch
- Internal mu-metal magnetic screen
- One or two switches in a single package
- Form A (energise to make) or Form B (energise to break) configurations
- 5, 12 or 24 V coils with optional internal diode
- Additional build options are available
- Many benefits compared to industry standard relays (see last page)
- Suitable for high power applications and in many cases, may be used as an alternative to mercury wetted reed relays

The Series 100HC Form A versions offer higher coil resistances than the similar specification Series 114, the greater winding space allowing for the use of switches rated to 3 Amps continuous carry current and even higher levels in pulsed current applications.

Featuring sputtered ruthenium contacts, this also makes them suitable for low level or 'dry' switching applications and the reduced heating effect from the higher coil resistances gives them thermal EMF performance less than 10  $\mu$ V. The range features an internal mu-metal screen to minimize problems that would otherwise be experienced due to magnetic interaction when they are closely stacked. Form A versions may be stacked side-by-side. Due to the fact that the

Form B types feature an internal biasing magnet, a gap of 0.4 inches minimum should be left between adjacent relays.







## Switch Ratings - Dry Switches

1 Form A (energize to make)	1 Form B (energize to break)	2 Form A (energize to make)		
200 VDC or 240 VAC at 40 W	200 VDC or 240 VAC at 40 W	200 VDC or 240 VAC at 40 W		
500 V min stand-off	500 V min stand-off	500 V min stand-off		

## Dry Reed: Series 100HC switch ratings - contact ratings for each switch type

vitch No	Switch form	Power rating	Max. switch current	Max. carry current (see Note <sup>2</sup> )	Max. switching volts	Min. stand-off volts	Life expectancy ops typical (see Note <sup>1</sup> )	Operate time inc bounce (max)	Release time	Special features
1	A or B	40 W	1.0 A	3.0 A	200 V DC 240 V AC RMS	500	10 <sup>8</sup>	2.0 ms	1.0 ms	General purpose

#### Note<sup>1</sup>: Life Expectancy

The life of a reed relay depends upon the switch load and end of life criteria. For example, for an 'end of life' contact resistance specification of 1  $\Omega$ , switching low loads (10 V at 10 mA resistive) or when 'cold' switching, typical life is approx 10 x 10<sup>9</sup> ops. At the maximum load (resistive), typical life is 1 x 10<sup>7</sup> ops. In the event of abusive conditions, e.g. high currents due to capacitive inrushes, this figure reduces considerably. Pickering will be pleased to perform life testing with any particular load condition.

#### Note<sup>2</sup>: Carry Current

The maximum continuous carry current of 3 Amps can be increased where current pulses are used, the level being dependant on the pulse duration and the duty cycle. For advice, please contact Pickering.

## **Operating Voltages**

Coil voltage - nominal	Must operate voltage - maximum at 25°C	Must release voltage - minimum at 25°C		
5 V	3.75 V	0.5 V		
12 V	9 V	1.2 V		
24 V	18 V	2.4 V		

## **Environmental Specification/Mechanical Characteristics**

In the table below, the upper temperature limit can be extended to +125 °C if the coil drive voltage is increased to accommodate the resistance/temperature coefficient of the copper coil winding. This is approximately 0.4% per °C. This means that at 125 °C the coil drive voltage will need to be increased by approximately 40 x 0.4 =16% to maintain the required magnetic drive level. Please contact sales@pickeringrelay.com for assistance.

Operating Temperature Range	-20 °C to +85 °C
Storage Temperature Range	-35 °C to +100 °C
Shock Resistance	50 g
Vibration Resistance (10 - 2000 Hz)	20 g
Soldering Temperature (max) (10 s max)	270°C
Washability (Proper drying process is recommended)	Fully Sealed



### Dry Relay: Series 100HC Coil data and type numbers

	Type Number	Coil (V)	Coil resistance	Max. contact	Insulation resistance (minimum at 25 °C) (see Note <sup>5</sup> )		Capacitance (typical) (see Note³)	
Device Type				resistance (initial)	Switch to coil	Across switch	Closed switch to coil	Across open switch
1 Form A,	100HC-1-A-5/1D	5	500 Ω	0.20 Ω	10 <sup>12</sup> Ω		2.0 pF	
Switch No. 1	100HC-1-A-12/1D	12	2000 Ω			10 <sup>12</sup> Ω		0.1 pF
Package Type 1	100HC-1-A-24/1D	24	0000 Ω					
1 Form B,	100HC-1-B-5/1D	5	300 Ω	0.20 Ω 10 <sup>12</sup> Ω	10 <sup>12</sup> Ω		2.0 pF	0.1 pF
Switch No. 1	100HC-1-B-12/1D	12	1000 Ω			10 <sup>12</sup> Ω		
Package Type 2	100HC-1-B-24/1D	24	4000 Ω					
2 Form A,	100HC-2-A-5/1D	5	300 Ω					
Switch No. 1	100HC-2-A-12/1D	12	1000 Ω	0.25 Ω	10 <sup>12</sup> Ω	$10^{12} \Omega$	See	See Note <sup>4</sup>
Package Type 3	100HC-2-A-24/1D	24	4000 Ω				Note <sup>4</sup>	NOLE

When an internal diode is required, the suffix D is added to the part number as shown in the table.

#### Note<sup>3</sup>: Capacitance across open switch

The capacitance across the open switch was measured with other connections guarded.

#### Note<sup>4</sup>: Capacitance values

The value will depend upon on the mode of connection/guarding of unused terminals. Please contact technical sales for details.


#### Note<sup>5</sup>: Insulation resistance

Insulation resistance will reduce at higher temperatures. For more information on temperature effects **click here**, or **contact Pickering** for more in depth guidance.

The technical information shown in this data sheet could contain inaccuracies or typographical errors. This information may be periodically changed or updated and these changes will be included in future versions of this data sheet.

For FREE evaluation samples go to: pickeringrelay.com/samples





## Pin Configuration, Weights and Dimensional Data (dimensions in inches, millimeters in brackets)

**Important:** Where the optional internal diode is fitted or for all Form B types, the correct coil polarity must be observed, as shown by the + symbol on the schematics.

## Similar Relays Comparison

If the Series 100HC is unsuitable for your application, Pickering also manufactures another series of reed relays with similar characteristics, but in different package sizes.

Series Name	114-1-A	114-1-B	114-2-A	100HC-1-A	100HC-1-B	100HC-2-A		
Physical Outline		Contraction of the second			Care 2 & Total 1	Care a secon		
Depth	6.3 (0.245)	6.3 (0	).245)	10.2 (0.40)	10.2 (	0.40)		
Width (inches)	24.1 (0.95)	29.0	(1.14)	24.1 (0.95)	29.0 (	1.14)		
Height	8.2 (0.32)	12.5	(0.49)	12.7 (0.50)	15.2 (	0.60)		
Package Volume ( <b>mm</b> ³)	1245	2284	2284	<b>1</b> 3122	<b>2</b> 4496	<b>3</b> 4496		
Typical Weights ( <b>g</b> )	2.07	3.61	3.68	6.99	8.75	8.75		
Contact Configuration	1-A (SPST)	1-B (SPNC)	2-A (DPST)	1-A (SPST)	1-B (SPNC)	2-A (DPST)		
Reed Switch Type		Dry		Dry				
Stand-off Voltage ( <b>V</b> )		500			500			
Switching Voltage (V)		200 DC/240 AC RMS		200 DC/240 AC RMS				
Switching Current (A)		1			1			
Carry Current (A)		3		3				
Switch Power ( <b>W</b> )		40		40				

## **Reed Relay Selection Tool**

Because Pickering offer the largest range of high-quality reed relays, sometimes it can be difficult to find the right reed relay you require. That is why we created the Reed Relay Selector, this tool will help you narrow down our offering to get you the correct reed relay for your application. To try the tool today go to: pickeringrelay.com/reed-relay-selector-tool



## **Standard Build Options**

The Series 100HC Reed Relays are available with a number of standard build options to tailor them to your specific application. These options are detailed in the table below. If you decide to go ahead and specify one, or more, of these options you will be allocated a unique part number suffix.

Mechanical Build Options	Electrical Build Options
Special pin configurations or pin lengths	Different coil resistance
Special print with customer's own part number or logo	Different stand-off or switching voltage
Custom packaging possibility	Operate or de-operate time
	Pulse capability
	Enhanced specifications
	Non-standard coil voltages and resistance figures
	Special Life testing under customer's specific load conditions
	Specific environmental requirements
	Controlled thermal EMF

#### Customization

If your specific requirements are not met by standard relay, or any of the standard build options, please speak to us to discuss producing a customized reed relay to service your specific application: pickeringrelay.com/contact

## **3D Models**

Interactive 3D models of the complete range of Pickering relay products in STEP, IGS and SLDPRT formats can be downloaded from the website: pickeringrelay.com/3d-models

Part Number Description:	100 HC -	1 - A	- <b>5</b>	/ 2	2 D ·	- xxx
Series						
Number of reeds						
Switch form						
Coil voltage						
Switch number (see table on page	2) ———					
Diode if fitted (omit if not required)						
Unique suffix (if standard build opt	ion selected)					

## Help

If you need any technical advice or other help, please do not hesitate to contact our Technical Sales Department. We will always be pleased to discuss Pickering relays with you. email: techsales@pickeringrelay.com

## **Contact Us**

bickerind

UK Headquarters - email: sales@pickeringrelay.com   Tel. +44 1255 428141
USA - email: ussales@pickeringrelay.com   Tel. +1 781 897 1710
Germany - email: desales@pickeringtest.com   Tel. +49 89 125 953 160
France - email: frsales@pickeringtest.com   Tel. +33 9 72 58 77 00
Nordic - email: ndsales@pickeringtest.com   Tel. +46 340 69 06 69
Czech Republic: czsales@pickeringtest.com   Tel. +420 558-987-613
China - email: chinasales@pickeringtest.com   Tel. +86 4008 799 765
For a full list of agents, distributors and representatives visit: pickeringrelay.com/a



6

agents

## 10 Key Benefits of Pickering Reed Relays

Key Benefit	Pickering Reed Relays	Typical Industry Reed Relays	
1 Instrumentation Grade Reed Switches	Instrumentation Grade Reed Switches with vacuum sputtered Ruthenium plating to ensure stable, long life up to 5x10E9 operations.	Often low grade Reed Switches with electroplated Rhodium plating resulting in higher, less stable contact resistance.	-1 <sup></sup>
2 Formerless Coil Construction	Formerless coil construction increases the coil winding volume, maximizing magnetic efficiency, allowing the use of less sensitive reed switches resulting in optimal switching action and extended lifetime at operational extremes.	Use of bobbins decreases the coil winding volume, resulting in having less magnetic drive and a need to use more sensitive reed switches which are inherently less stable with greatly reduced restoring forces.	Pickering former-less coil Typical industry coil wound on bobbin
3 Magnetic Screening	Mu-metal magnetic screening (either external or internal), enables ultra-high PCB side-by-side packing densities with minimal magnetic interaction, saving significant cost and space. <b>Pickering</b> <b>Mu-Metal magnetic screen - interaction</b> <b>approx. 5%</b>	Lower cost reed relays have minimal or no magnetic screening, resulting in magnetic interaction issues causing changes in operating and release voltages, timing and contact resistance, causing switches to not operate at their nominal voltages. <b>Typical industry</b> <b>screen - interaction approx. 30%</b>	X-Ray of Pickering mu-metal magnetic screen
<b>4</b> SoftCenter™ Technology	<b>SoftCenter</b> <sup>™</sup> technology, provides maximum cushioned protection of the reed switch, minimising internal lífetime stresses and extending the working life and contact stability.	Transfer moulded reed relays (produced using high temperature/pressure), result in significant stresses to the glass reed switch which can cause the switch blades to deflect or misalign leading to changes in the operating characteristics, contact resistance stability and operating lifetime.	Pickering soft center protection of the reed switch
5 100% Dynamic Testing	100% testing for all operating parameters including dynamic contact wave-shape analysis with full data scrutiny to maintain consistency.	Simple dc testing or just batch testing which may result in non-operational devices being supplied.	Dynamic Contact Resistance Test
6 100% Inspection at Every Stage of Manufacturing	Inspection at every stage of manufacturing maintaining high levels of quality.	Often limited batch inspection.	
7 100% Thermal Cycling	Stress testing of the manufacturing processes, from -20°C to +85°C to -20°C, repeated 3 times.	Rarely included resulting in field failures.	+85°C
8 Flexible Manufacturing Process	Flexible manufacturing processes allow quick-turn manufacturing of small batches.	Mass production: Usually large batch sizes and with no quick-turn manufacturing.	FAST
9 Custom Reed Relays	Our reed relays can be customized easily, e.g. special pin configurations, enhanced specifications, non-standard coil or resistance figures, special life testing, low capacitance, and more.	Limited ability to customize.	
10 Product Longevity	Pickering are committed to product longevity; our reed relays are manufactured and supported for more than 25 years from introduction, typically much longer.	Most other manufacturers discontinue parts when they reach a low sales threshold; costing purchasing and R&D a great deal of unnecessary time and money to redesign and maintain supply.	Product 25+Years Longevity

7

For more information go to: pickeringrelay.com/10-key-benefits



© Copyright (2022) Platering Electronics. All Rights Reserved Pickering Electronics maintains a commitment to continuous product development, consequently we reserve the right to vary from the description given in this data sheet.