
**776273-1** • ACTIVE

## AMP | AMPSEAL TE Internal #: 776273-1 AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]

#### View on TE.com >

Connectors > Automotive Connectors > Connector Housings > AMPSEAL Receptacle Housings



Connector & Housing Type: Housing for Female Terminals

Mating Pin Diameter: 1.3 mm [.051 in ]

Connector System: Wire-to-Board

Number of Positions: 14

Centerline (Pitch): 4 mm [.157 in ]

All AMPSEAL Receptacle Housings (31)



## Features

### **Product Type Features**

Connector & Housing Shape	Rectangular	
Connector & Housing Type	Housing for Female Terminals	
Connector System	Wire-to-Board	
Sealable	Yes	
Hybrid Connector	No	
Primary Locking Feature	Integrated in Housing	
Configuration Features		
Number of Positions		
	14	
Number of Rows	3	
Number of Rows		

AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]



## **Body Features**

Cable Exit Angle	180°
Body Material	Other
Primary Product Color	Black
Contact Features	
Contact Size	AMPSEAL 1.3mm
Mating Pin Diameter	1.3 mm[.051 in]
Contact Current Rating (Max)	17 A
Mechanical Attachment	
Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Keyed
Mating Alignment	With
Housing Features	
Centerline (Pitch)	4 mm[.157 in]

### Dimensions

Product Width	33.6 mm[1.323 in]
Product Length	35.4 mm[1.394 in]
Product Height	34.6 mm[1.362 in]
Row-to-Row Spacing	4 mm[.157 in]
Usage Conditions	
Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Industry Standards	
Degree of Protection	IP67, IP69K
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	1
Packaging Method	Package
Other	
Serviceable	Yes

**C** For support call+1 800 522 6752

AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]



Connector Position Assurance Capable

No

### **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# **Compatible Parts**




AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]






# Also in the Series | AMPSEAL








Automotive Terminals(8)	PCB

PCB Headers & Receptacles(106)

# Customers Also Bought



AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]



TE Part #1-1768384-7 LBF-62-61485-00A TE Part #2330605-1 LBF-62-03797-13L

## Documents

## Product Drawings

### 14POS, AMPSEAL, SOC HSG ASSY, SLD, COD 1

English

### **CAD** Files

Customer View Model ENG\_CVM\_CVM\_776273-1\_E.2d\_dxf.zip

English

### 3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_776273-1\_E.3d\_igs.zip

English

Customer View Model

### ENG\_CVM\_CVM\_776273-1\_E.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages AMPSEAL Connector Catalog

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications
Application Specification

English

Instruction Sheets Instruction Sheet (U.S.)

English

Agency Approvals UL Report

**&** For support call+1 800 522 6752

AMPSEAL, Housing for Female Terminals, Wire-to-Board, 14 Position, .157 in [4 mm] Centerline, Sealable, Black, -40 – 257 °F [-40 – 125 °C]



English