

CREALITY

MPN - ENDER-2 PRO

Description - Ender-2 Pro 3D Printer



Light and Portable

Quick Assembly in Four Steps

Cantilever Structure



4-Step Assembly
90% Pre-installed



Easy Operations
User-friendly Design



Light and Portable
Only 4.65kg net weight



DIY Refit
Fashionable Colors &
Flexible Shaping



Built-in Power Supply
Safe and Reliable



Clip-on Screen
Simplified Installation
and Dismantling

Product Parameters

Molding technology:	FDM	Nozzle temperature:	≤ 260°C
Printer dimensions:	421*383*465 mm	Hotbed temperature:	≤ 80°C
Build size:	165*165*180 mm	Rated power:	150W
Net weight:	4.65 kg	Supported filament:	PLA/TPU/WOOD
Extrusion method:	Bowden extruder	Filament detector:	No
Leveling method:	Manual leveling	Printing speed:	≤ 100 mm/s. Average printing speed: 60mm/s
Resume printing:	Supported		
Display:	With a 12864 integrated screen, you can implement interactions with control knobs		