


# CO810


230VAC HARDWIRE

The Dicon CO810 Alarm monitors and detects Carbon Monoxide gas. It measures the concentration and sounds a loud alarm when a potentially harmful level is reached. The unit is easy to install in the home or office. Hardwire for extra protection against tampering. Ideal for public sector landlords' properties. No sensor or batteries to replace. Comes complete with surface mounting pattress.



## FEATURES

- 230 volt Hardwire
- Hazard Level Alarm
- Low Level Warning
- No Batteries or Replacement Sensor Required
- Advanced Semiconductor Sensing Technology
- Self Diagnosing Circuitry
- Instant Test/reset Feature
- Power/alarm Indicators
- Loud 85 Decibel Alarm
- Supplied with Surface Mounting Pattress
- 5 Year Comprehensive Guarantee
- CE



## TECHNICAL SPECIFICATIONS

Detection Method:	Semiconductor sensing technology
Sensitivity:	Low level warning Hazard level alarm
Sensor:	Continuous air quality diagnosis
Dimensions:	130mm x 68mm x 58mm
Operating Voltage:	230 volt AC (⌚) 50 Hz, 7W
Recommended Operating Temperature Range:	-5°C (23°F) to +40°C (104°F)
Alarm Sound Level:	85dB at 3m

FOR FURTHER INFORMATION OR TECHNICAL ASSISTANCE CALL OR WRITE TO:

Dicon Safety Products (UK) Ltd.  
P.O. Box 402, Gloucester, GL2 9YB  
Tel: 01452 714999  
Fax: 01452 713103  
Email: [Sales@diconsafety.co.uk](mailto:Sales@diconsafety.co.uk)  
Internet: [www.diconsafety.co.uk](http://www.diconsafety.co.uk)

**DICON™**  
**SAFETY PRODUCTS**

TOTAL P.03