

TSN 25 A

Torque wrench TSN SLIPPER

1-125 N·m / 10-1106 lbf·in / fixed setting

Code	ETIM
7092040	EC002132 Drehmomentschlüssel
EAN	UNSPSC
4002805759011	27-11-17-15 Drehmomentschlüssel
Country of Origin	eCl@ss
Great Britain	21-04-02-22 Drehmomentschlüssel
Customs tariff no.	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 5 - 25 N · m
- Serial / production-line
- Extremely long-term work
- Features:
- Pre-set production torque wrench - without scale
- 3/8" square drive with ball lock
- With integrated ratchet-function for controlled clockwise tightening
- Working accuracy: +/- 4 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Precision mechanism slips very noticeably and audibly ("click") when the pre-set value is achieved - over-tightening is not possible
- Automatic resetting to the starting position
- Lightweight, but robust and corrosion-resistant construction design
- Very convenient non-slip rubber handgrip
- The pre-setting can be made at the factory or by the user on suitable torque testers
- If ordering, please specify the N·m value - if a fixed factory pre-setting is desired (price on request)
- EPA-conformant (Electrostatic Protected Area), for use in sensitive electrostatic applications
- Scope of delivery:
- Special adjusting key for changing the pre-set torque value
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Contents (Qty of pieces)	1 tlg.	Precision +/-	+/- 4 %
Total length [mm]	216 mm	Direction of tightening	Right
Torque (min.) [N·m]	5 N·m	Fixed setting	1
Torque (max.) [N·m]	25 N·m	Test certificate	DIN EN ISO 6789-2:2017
Net weight [kg]	0,34 kg	Torque (max.) [lbf·in]	44 lbf·in
Drive connector square (male)	3/8"	Torque (min.) [lbf·in]	221 lbf·in
Drive connector square (male)	10 mm	Torque (max.) [lbf·ft]	18 lbf·ft
REACH registration available	0	Drive type/drive	Single square ratchet
Epa-/Esd-Model	1	Torque (min.) [lbf·ft]	4 lbf·ft
Trigger mechanism	Friction clutch		