

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of DFE18SANR24MG0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR24MG0%23

"#" indicates a package specification code.

DFE18SANR24MG0#

Size Code 1608 (0603) in mm (in inch), 1.0mm max. Thickness. Small and high performance type.

















< List of part numbers with package codes > DFE18SANR24MG0L




Appearance & Shape









References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	3000

Mass (typ.)		
1 piece	0.009g	



Notices

The saturation allowable DC current value is specified when the decrease of the initial inductance value at 30%. When rated current is applied to the products, the temperature rise caused by self-generated heat shall be limited to 40°C max. Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

1 of 4

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





DFE18SANR24MG0#

Note: This datasheet may be out of date.

Please download the latest datasheet of DFE18SANR24MG0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR24MG0%23

"#" indicates a package specification code.



Specifications

L size	1.6±0.2mm
W size	0.8±0.2mm
T size	1.0mm
Size code inch (mm)	0603 (1608)
Inductance	0.24µH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	4900mA
Rated current (Itemp) (Based on Temperature rise)	3500mA
Max. of DC resistance	0.03Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Metal Alloy
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 85°C
Absolute maximum voltage	20Vdc
Brand	Murata
Series	DFE18SAN_G0

2 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Product Search Data Sheet

Please download the latest datasheet of DFE18SANR24MG0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR24MG0%23

Note: This datasheet may be out of date.


"#" indicates a package specification code.


DFE18SANR24MG0#





Characteristic Data

The charts below may show another part number which shares its characteristics.









3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






DFE18SANR24MG0#

Note: This datasheet may be out of date.

Please download the latest datasheet of DFE18SANR24MG0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR24MG0%23

"#" indicates a package specification code.



4 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

