

EXG.0B.302.HLN

SUMMARY

Wires

Low voltage

2



Image is for illustrative purpose only

Series	ОВ	Download		
Termination type	Female print PCB	Request a quote		
IP rating	50	PCB Eagle Pattern		
AWG wire size	28.00 - 20.00	PCB Altium Pattern		
Cable Ø	0.00 - 0.00 mm	PCB KiCad Pattern		
Status	active	Catalog		
Matching parts	FGG.0B.302.CLAD32			

TECHNICAL DETAILS

Mechanics

Shell Style/Model	EX*: Elbow receptacle for printed circuit with two nuts (solder or screw fixing, back panel mounting)
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	PPS (Polyphenylene) shell, other pieces nickel plated [SAE AMS QQ N 290] brass
Weight	10.70 g
Performance	

Configuration	OB.302/EXG : 2 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	4.5 Amps

Specifications


Contact Type: Print (straight) Contact Dia.: 0.9 mm (0.035in) R (max): 4.8 mOhm Test voltage contact-contact : 1.45 kV rms Test voltage contact-body shell : 1.2 kV rms

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): 5000 Temp (min / max): -55°C / +250°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >144 hr 12NC part number: 4022.438.33191

DRAWINGS



Dimensions

	А	В	D	E	Н	I	К	L	Μ	Ν	\$3	e
mm.	12	12.4	14.6	4.5	6.7	12.6	13.3	25	2.5	11.7	11	M9x0.6
in.	0,47	0,49	0,57	0,18	0,26	0,50	0,52	0,98	0,10	0,46	0,43	

RECOMMENDED BY LEMO

Tools

Spanner wrench:

Socket for torque wrench DCM.0S.M09.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.