



Statement of Compliance

Requested Part

30 May 2022

FCC-325-CW9

(Part 1 of 1)

TE Internal Number: 6-1617830-2

Product Description: FCC-325-CW9=3PST W/AUX, 25 AMP RELAY

Part Status: Active

Mil-Spec Certified: No

EU RoHS Directive 2011/65/EU: Not Compliant

Substances: Pb

This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU.

EU ELV Directive: Not Yet Reviewed

2000/53/EC

China RoHS: Restricted Materials Above Threshold

MIIT Order No 32, 2016

EU REACH SvHC Compliance: Current ECHA Candidate List: JAN 2022 (223)

(EC) No. 1907/2006 Candidate List Declared Against: JAN 2022 (223)

Does not contain REACH SVHC

Halogen Content: Not Yet Reviewed for halogen content

Solder Process Capability Code: Not applicable for solder process capability

TE Connectivity Corporation  
1050 Westlakes Drive  
Berwyn, PA 19312

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change.

The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.

Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV).

Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as OSA (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.



30 May 2022

中国电子电气产品中有害物质的名称及含量  
China EEP Hazardous Substance Information



Restricted Materials Above Threshold

| 部件名称<br>(Component Name)<br>6-1617830-2   | 有害物质<br>Hazardous Substance |           |           |              |               |                 |
|---|-----------------------------|-----------|-----------|--------------|---------------|-----------------|
|   | 铅<br>(Pb)                   | 汞<br>(Hg) | 镉<br>(Cd) | 六价铬<br>(Cr6) | 多溴联苯<br>(PBB) | 多溴二苯醚<br>(PBDE) |
| 继电器<br>(Relays)   | X                           | O         | O         | O            | O             | O               |
| 本表格依据SJ/T 11364标准的规定编制。 This table is compiled according to SJ/T 11364 standard.  |                             |           |           |              |               |                 |
| O: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572标准规定的限量要求以下。<br>Indicates that the concentration of the hazardous substance in all homogeneous materials of the part is below the relevant threshold of the GB/T 26572 standard.<br><br>X: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572标准规定的限量要求。<br>Indicates that the concentration of the hazardous substance in at least one homogeneous material of the part is above the relevant threshold of the GB/T 26572 standard. |                             |           |           |              |               |                 |
| 电子电气产品的环保使用期限依据SJ/T 11388标准的规定确定。<br>The EFUP value of EEP is defined according to SJ/T 11388 standard.   |                             |           |           |              |               |                 |