TECHNICAL DATA SHEET



Models: CB19342-CB19344

RoHS Compliant

DOUBLE SIDED TAPE



Specifications: Tissue paper Adhesive: hot melt Tape Colour: Transparent Tape Type: Double Sided Tape Thickness: 80mic (0.08mm) Roll Thickness: 30mm Applications:

Thin gauge; high strength; double sided adhesive tape which is suitable for numerous applications.

Storage and shelf life:

Clean and dry in a well-ventilated area, preferably at a temperature between 10°C and 30°C. Stored under these conditions shelf life will be a minimum of 6 months.

Code	Description
ADST12X33	DOUBLE SIDED TAPE 12MMX33M
ADST25X33	DOUBLE SIDED TAPE 25MMX33M
ADST25X50	DOUBLE SIDED TAPE 25MMX50M

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

