


LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

IEC PTFE Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email sales@labfacility.com

Website www.labfacility.com

- Thermocouple types K, J & T
- Fast response, welded exposed junction 1, 2, 5 or 10 metre lengths available
- Teflon® PTFE insulated twin-twisted lead
- 1/0.2mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range -75°C to +260°C
- Tolerance to IEC 584 Class 1
- Colour code to IEC 584-3
- Ideal for test & development applications

T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	order Code
'K'	1/0.2mm	2 m	Mini plug	Green	White	XF-1202-FAR
'K'	1/0.2mm	3 m	Mini plug	Green	White	XF-1845-FAR
'K'	1/0.2mm	5 m	Mini plug	Green	White	XF-1215-FAR
'K'	1/0.2mm	10 m	Mini plug	Green	White	XF-1216-FAR
'J'	1/0.2mm	1 m	Mini plug	Black	White	XF-1203-FAR
'J'	1/0.2mm	2 m	Mini plug	Black	White	XF-1217-FAR
'J'	1/0.2mm	3 m	Mini plug	Black	White	XF-1851-FAR
'J'	1/0.2mm	5 m	Mini plug	Black	White	XF-1218-FAR
'J'	1/0.2mm	10 m	Mini plug	Black	White	XF-1219-FAR
'T'	1/0.2mm	2 m	Mini plug	Brown	White	XF-1220-FAR
'T'	1/0.2mm	3 m	Mini plug	Brown	White	XF-1834-FAR
'T'	1/0.2mm	5 m	Mini plug	Brown	White	XF-1221-FAR