Wire-Wound Resistors Power (Ribbon) Type



RoHS Compliant



Scope: This specification for approval relates to Power Ribbon Type Wire-Wound Resistors

Type designation: The type designation shall be in the following form:

Туре	Power Rating	Resistance tolerance	Nominal Resistance
MPQRZG	200W	J	1Ω

Ratings:

Туре	Rated Power at 70°C	Resistance Range	Resistance Tolerance	Operating Temp. Range		
MPQRZG 200W	200W	1Ω ~ 9.1Ω				
MPQRZG 300W	300W	102 ~ 9.102				
MPQRZG 500W	500W	1Ω ~ 20Ω				
MPQRZG 750W	750W	1Ω ~ 75Ω	± 5%	-55°C~ +155°C		
MPQRZG 1,000W	1,000W	1Ω ~ 100Ω	± 10%	-55 C~ +155 C		
MPQRZG 1,500W	1,500W					
MPQRZG 2,000W	2,000W	1Ω ~ 120Ω				
MPQRZG 2,500W	2,500W					

Power rating:

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70°C. For temperature in excess of 70°C, the load shall be derated as shown in the figure 1.

Voltage rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercialline frequency and waveform corresponding to the power rating , as determined from the following formula :

 $RCWV = \sqrt{P \times R}$

Note : Max. Working Voltage or $\sqrt{P \times R}$ whichever is lesser Max. Overload Voltage or 2.5 $\sqrt{P \times R}$ whichever is lesser

Where: RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt)

P = Power Rating (watt)

R = Nominal Resistance (ohm)


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Wire-Wound Resistors Power (Ribbon) Type

multicomp PRO

Derating Curve



Construction



No.	Name	Material	Material Generic Name			
1	Basic Body	Rod Type Ceramics	Al ₂ O ₃ , SiO ₂			
2	Terminal lead	Terminal cap plated with Tin	Fe: 73%, Mn: 21%, C: 5%			
3	Resistance Wire	Ni-Cr Alloy, Cu-Ni Alloy	Ni-Cr Alloy, Cu-Ni Alloy			
4	Coating	Insulated & Non-Flame paint (Colour : Green)	Non-Flame paint			
5	Marking	Marking Ink				

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Wire-Wound Resistors Power (Ribbon) Type



Performance specification

Characteristics	Limits	Test Methods (JIS C 5201-1)					
DC. resistance	Must be within the specified tolerance.	The limit of error of measuring apparatus shall not exceed allowable range or 5% of resistance tolerance (Sub-clause 4.5)					
Temperature coefficient	<20Ω : ± 400 PPM/°C Max. ≥20Ω : ± 300 PPM/°C Max.	Natural resistance change per temp. degree centigrade. R2-R1					
Short time overload	Resistance change rate is $\pm (2\% + 0.05\Omega)$ Max. with no evidence of mechanical damage	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds (Sub-clause 4.13)					
Terminal strength	No evidence of mechanical damage	Direct load: Resistance to a 2.5 kgs direct load for 10 secs. in the direction of the longitudinal axis of the terminal leads Twist test: Terminal leads shall be bent through 90° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about9he original axis of the bent terminal in alternating direction for a total of 3 rotations (Sub-clause 4.16)					
Solderability	95 % coverage Min.	The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temp. of solder: 245°C ± 3°C Dwell time in solder: 2 ~ 3 seconds (Sub-clause 4.17)					
Soldering temp. reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked. Wave soldering condition: (2 cycles Max.) Pre-heat: 100 ~ 120°C, 30 ± 5 sec. Suggestion solder temp.: 235 ~ 255°C, 10 sec. (Max.) Peak temp.: 260°C Hand soldering condition: Hand Soldering bit temp.: 380 ± 10°C Dwell time in solder: 3 +1/-0 sec.					
Resistance to soldering heat	Resistance change rate is ± (1% + 0.05Ω) Max. with no evidence of mechanical damage.	Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C ± 10°C solder for 3 ± 0.5 seconds. (Sub-clause 4.18)					




Wire-Wound Resistors Power (Ribbon) Type



Characteristics	Limits	Test Methods (JIS C 5201-1)				
Load life in humidity	Resistance change rate is ±(5% + 0.05Ω) Max. with no evidence of mechanical damage	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity test chamber controlled at 40°C ± 2°C and 90 to 95 % relative humidity (Sub-clause 4.24.2.1)				
Load life	Resistance change rate is ±(5% + 0.05Ω) Max. with no evidence of mechanical damage	Permanent resistance change after 1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at 70°C ± 2°C ambient (Sub-clause 4.25.1)				

Dimension




Type	Dimension												
Туре	В	E±5	F±3	D±2	H±1	H1±3	M±0.5	K±1	L±1	P±3	T±0.5	t±0.5	Ød±0.5
MPQRZG 200W	195±2	217	239	39	10 41	81	8	40		179	10	1.8	5.5
MPQRZG 300W	282±2	304	326	40						266	10		
MPQRZG 500W	316±3	338	360	50	45	101		50	3	294	16		6.5
MPQRZG 750W	316±3	338	300							29 4			
MPQRZG 1,000W	300±3	325	350	60	60	119	8.5	8.5 60		279		2	
MPQRZG 1,500W	415±3	440	465							394	15		
MPQRZG 2,000W	510±3	535	560							489			
MPQRZG 2,500W	600±3	625	650							577			

Wire-Wound Resistors Power (Ribbon) Type



Explanation of Part Number System

(Power (Ribbon) Wire-Wound Resistors)



Sample: MPQRZG 200W +/- 5% 1 Ω B/B \rightarrow MPQRZGT0J010J200

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

