# VM-61HR/61HR1/61HR2

MOS FET Relays SOP 6-pin, High-current and Low-ON-resistance Type

## MOS FET Relays in SOP 6-pin packages that achieve the low ON resistance and high switching capacitance of a mechanical relay

- Load voltage: 60 V
- 60-V Relay (61HR): Continuous load current of 2.3 A (4.6 A) max. \*
- 60-V Relay (61HR1): Continuous load current of 3.3 A (6.6 A) max. \*
- 60-V Relay (61HR2): Continuous load current of 4 A (8 A) max. \*

(Unit: mm, Average)

\* Values in parentheses are for connection C.



71

Note: The actual product is marked differently from the image shown here.

#### RoHS Compliant

## ■Application Examples

- Semiconductor test equipment
- Communication equipment
- Test & Measurement equipment
- Security equipment
- Industrial equipment
- Power circuit

## **■**Model Number Legend

G3VM-1 2 3 4 5

1. Load Voltage 2. Contact form


3. Package H: SOP 6-pin 6:60 V 1:1a (SPST-NO)

Amusement equipment

4. Additional functions 5. Other informations R: Low ON resistance

When specifications overlap, serial code is added in the recorded order.

## ■Package SOP 6-pin



Note: The actual product is marked differently from the image shown here.

## **■**Ordering Information

	Contact		Load voltage	Continuous load current (peak value) *		Stick packaging		Tape packaging	
Package	form	Terminals	(peak value) *	Connection A, B	Connection C	Model	Minimum package quantity	Model	Minimum package quantity
	SOP6 1a (SPST-NO)	Surface-mounting Terminals	60 V	2.3 A	4.6 A	G3VM-61HR	75	G3VM-61HR(TR)	2,500
SOP6				3.3 A	6.6 A	G3VM-61HR1		G3VM-61HR1(TR05)	500
				4 A	8 A	G3VM-61HR2		G3VM-61HR2(TR05)	

\* The AC peak and DC value are given for the load voltage and continuous load current.


Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR)" or "(TR05)" to the end of the model number.

## ■Absolute Maximum Ratings (Ta = 25°C)

	Item	Symbol	G3VM-61HR	G3VM-61HR1	G3VM-61HR2	Unit	Measurement conditions	
	LED forward current		lF		30		mA	
nput	LED forward current reduction rate		ΔIF/°C		-0.3		mA/°C	Ta ≥ 25°C
In	LED reverse voltage		VR	5 6		6	V	
	Connection temperature		TJ	125		°C		
	Load voltage (AC peak/DC)		Voff	60			V	
	Continuous load current	Connection A		2300	3300	4000	mA	Connection A: AC peak/DC Connection B and C: DC
		Connection B	lo					
Ħ		Connection C		4600	6600	8000		
Output	ON current reduction rate	Connection A	Δlo/°C	-30.7	-33	-40	mA/°C	G3VM-61HR: Ta ≥ 50°C G3VM-61HR1/61HR2:Ta ≥ 25°C
Ō		Connection B						
		Connection C		-61.3	-66	-80		G5VW-011111/0111112.14 2 25 0
	Pulse ON current		lop	7	10	12	Α	t=100 ms, Duty=1/10
	Connection temperature		TJ	125			°C	
Di	electric strength betw	V <sub>I-O</sub>	1500		Vrms	AC for 1 min		
Ar	nbient operating tem	Ta	-40 to +85 -40 to +110		°C	With no icing or condensation		
Ar	nbient storage tempe	Tstg	-55 to +125		°C	with no icing of condensation		
Sc	ldering temperature	-	260		°C	10 s		

<sup>\*</sup> The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.


#### **Connection Diagram**



### **■Electrical Characteristics** (Ta = 25°C)

	Item		Symbol		G3VM-61HR	G3VM-61HR1	G3VM-61HR2	Unit	Measurement conditions	
				Minimum	1.18		1.50			
	LED forward vo	LED forward voltage		Typical	1.	33	1.65	V	IF=10 mA	
				Maximum	1.48		1.80			
=	Reverse current		IR	Maximum	10		•	μΑ	V <sub>R</sub> =5 V	
Input	Capacitance be	Capacitance between terminals		Typical	70			pF	V=0, f=1 MHz	
	Trigger LED for	ward current	IFT	Typical	0.4	0.2	0.3	mA	G3VM-61HR : lo=100 mA G3VM-61HR1 : lo=2000 mA	
	Trigger LED forward current		IFI	Maximum	3			IIIA	G3VM-61HR2 : lo=1000 mA	
	Release LED fo	orward current	IFC	Minimum	0.1			mA	Ioff=10 μA	
		Connection A			0.04	0.03	0.028		G3VM-61HR2:	
	Maximum	Connection B		Typical	0.02	0.015	0.014		I <sub>F</sub> =5 mA I <sub>O</sub> =4 A (Connection A, B)	
	resistance with output ON	Connection C	Ron -		0.01	0.008	0.007		Io=8 A (C connections), t<1s	
		Connection A		Maximum	0.07	0.06	0.04	Ω	Others:	
Output		Connection B			0.04	-	0.02		I <sub>F</sub> =5 mA I <sub>O</sub> =2 A (Connection A, B)	
õ		Connection C			-	_	0.01		lo=4 A (C connections), t<1s	
	Current leakage when the relay		ILEAK	Typical		-	_		Voff= Load voltage ratings	
	is open		ILEAN	Maximum	10	20	1000	nA	VOFF LOAD VOILAGE FAILINGS	
	Canacitance be	acitance between terminals Coff		Typical	1000	700	750	pF	V=0, f=1 MHz	
	Capacitance between terminals		OOFF	Maximum	-	1500	-	ρı	V = 0, 1 = 1 1011 12	
Ca	Capacitance between I/O terminals		Cı-o	Typical	0.8			pF	f=1 MHz, Vs=0 V	
Insulation resistance between I/O		BI-O Minimum		1000			ΜΩ	V <sub>I</sub> -o=500 VDC, RoH≤60%		
te	terminals		111-0	Typical	10 <sup>8</sup>			10122	VI-0-300 VDO, ⊓011≥00/6	
Turn-ON time		ton	Typical	1.0	1.0 0.6					
	Turr-ON time		LON	Maximum	!	5	2 ms		I <sub>F</sub> =5 mA, R <sub>L</sub> =200 $\Omega$ ,	
Т	Turn-OFF time			Typical	0.15	0.2	0.15		V <sub>DD</sub> =20 V <b>*</b>	
	Tulli-OFF tillie			Maximum		1	0.5			

#### \* Turn-ON and Turn-OFF Times



## **■**Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.


Item	Symbol		G3VM-61HR	G3VM-61HR1	G3VM-61HR2	Unit
Load voltage (AC peak/DC)	VDD	Maximum	60	48		V
		Minimum	5			
Operating LED forward current	lF	Typical	7.5	10		mA
		Maximum	20	25		
Continuous load current (AC peak/DC)	lo	Maximum	1800	3300	4000	
Ambient operating temperature	Та	Minimum	-20			°C
Ambient operating temperature		Maximum	65 85		85	

## **■**Spacing and Insulation


Item	Minimum	Unit
Creepage distances	4.0	
Clearance distances	4.0	mm
Internal isolation thickness	0.1	

## **■**Engineering Data


#### LED forward current vs. Ambient temperature




# Continuous load current vs. Ambient temperature G3VM-61HR1/61HR2




#### G3VM-61HR




## LED forward current vs. LED forward voltage




## Continuous load current vs.On-state voltage




#### On-state resistance vs. Ambient temperature



#### Trigger LED forward current vs. Ambient temperature




#### Turn ON, Turn OFF time vs. LED forward current




## **■**Engineering Data

#### ● Turn ON, Turn OFF time vs. Ambient temperature




#### Current leakage vs. Load voltage

#### G3VM-61HR/61HR2




# ● Current leakage vs. Ambient temperature G3VM-61HR1/61HR2



#### Output terminal capacitance vs. Load voltage


#### G3VM-61HR/61HR2



## ■Appearance / Terminal Arrangement / Internal Connections

#### Appearance

### SOP (Small Outline Package)




Note: 1. The actual product is marked differently from the image shown here.

Note: 2. "G3VM" does not appear in the model number on the Relay.

Note: 3. The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

#### ●Terminal Arrangement/Internal Connections (Top View)




#### **■Dimensions** (Unit: mm)




#### **Surface-mounting Terminals**

Weight: 0.13 g



#### **Actual Mounting Pad Dimensions**



Note: The actual product is marked differently from the image shown here.

## ■Approved Standards

UL recognized 🔊



Approved Standards	Contact form	File No.		
UL (recognized)	1a (SPST-NO)	E80555		

## **■**Safety Precautions

• Refer to the Common Precautions for All MOS FET Relays for precautions that apply to all MOS FET Relays.

Please check each region's Terms & Conditions by region website.

#### **OMRON Corporation**

**Electronic and Mechanical Components Company** 

#### **Regional Contact**

**Americas** 

https://www.components.omron.com/

**Asia-Pacific** 

https://ecb.omron.com.sg/

Korea

https://www.omron-ecb.co.kr/

**Europe** 

http://components.omron.eu/

https://www.ecb.omron.com.cn/

Japan

https://www.omron.co.jp/ecb/

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. K318-E1-01 0120(0120)(O)