




**8151**

**Flush Precision Cut Diagonal  
Cutter with Oval Head & ESD Safe  
Handle 0.2-1.6 mm**











## PRODUCT DETAILS

- 80 Series precision diagonal and stripping cutter
- ESD safe mono-material handles with return spring
- Micro-bevel cut
- The cutting capacity given is for copper wire
- Suitable for cutting Cu
- High performance alloyed steel
- Burnished finish
- Numerically controlled machine grinding guarantees edge angle accuracy & contact, increases the tools reliability & consistency
- Precision induction hardened edges 63-65 HRC
- Screw joint that minimizes friction & maximizes alignment of cutting edges
- Ideal for wire harness work & standard printed circuit board assembly
- Also valid for stripping



PRODUCT ATTRIBUTES

Product: **8151**

	Oval		M		Flush
	0.2-1.6 mm		0.01-0.06 in		0.2-0.8 mm
	0.01-0.03 in	<b>A</b>	112.5 mm	<b>A</b>	4.43 in
<b>B</b>	13 mm	<b>B</b>	0,51 in	<b>C</b>	12,5 mm
<b>C</b>	0.50 in	<b>D</b>	6 mm	<b>D</b>	0,24 inch
<b>F</b>	1,2 mm	<b>F</b>	0,05 in		73 g
<b>Ω</b>	Dissipative				