

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200660427](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Yellow PVC Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120066](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Micro-Change (M12)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Region America  
 Taxonomy Circular Industrial Cordsets  
 Type Double Ended  
 UPC 78678836851

**Physical**

Cable Diameter 5.72mm (.225")  
 Cable Length 1.0m (3.28')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Net Weight 32.000/g  
 Orientation Straight to Straight  
 Poles 5  
 Temperature Range - Operating -20° to +105°C  
 Wire Size AWG 22  
 Wire/Cable Type UL 2661

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 885030A09M010

**Reference - Drawing Numbers**

Sales Drawing SD-120066-007-001



Series image - Reference only

**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

Not Relevant

Compliant with Exemption 3

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

Not Contained

CER\_4000410038\_00\_000.pdf

CER\_4000406014\_00\_000.pdf

**Search Parts in this Series**

120066 Series

This document was generated on 10/31/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**