

Flexible, Flame Retardant General Purpose Polyolefin Heat Shrink Tubing

multicomp^{PRO}

RoHS
Compliant



Specifications:

Shrink Ratio	: 2:1
Operating Temperature	: -55°C to 135°C
Shrink Temperature	: 100°C
Standard Colours	: Black, Clear & Yellow
Flammability Rating	: VW-1
Approval category	: UL224 (600V, 125°C)
Standard	: CSA, LR228795 (600V, 125°C)
Approval bodies	: UL

Specification Values:

Property	Test Method	Values
Tensile Strength	ISO 37	10 MPa minimum
Ultimate Elongation	ISO 37	250% minimum
Specific Gravity	ISO 1183	1.35 maximum
Heat Shock	ASTM D2671 (4hrs at 250°C)	no dripping, cracking or flowing
Heat Ageing Ultimate Elongation	ISO 188 (168hrs at 175°C) ISO 37	150% minimum
Low Temperature Flexibility	ASTM D2671 (4hrs at -55°C)	no cracking
Flammability (except Clear)	ASTM D876	pass
Electric Strength	IEC 243	20kV/mm minimum
Corrosion (Copper Contact and Copper Mirror)	ASTM D2671	no corrosion
Water Absorption	ISO 62	0.5 % maximum
Fluid Resistance Gasoline Hydraulic Fluid Lubricating Oil Tensile Strength Ultimate Elongation	ISO 1817 ISO 37	 7 MPa minimum 200% minimum
Fungus Resistance Tensile Strength Ultimate Elongation	ISO 846 ISO 37	10 MPa minimum 250% minimum

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}

Flexible, Flame Retardant

General Purpose Polyolefin Heat Shrink Tubing

multicompPRO

Specification Table:

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter (Min. Expanded Diameter - mm)	Fully Shrunk Diameter (Max. Recovered Diameter - mm)	Nominal Recovered Wall (mm)	Length (m)	Part Number	
Polyolefin	Black	20	1.6	0.8	0.45	150	SP16/RL/BLACK	
			3.2	1.6	0.5		SP32/RL/BLACK	
			4.8	2.4			SP48/RL/BLACK	
			6.4	3.2	0.65	75	SP64/RL/BLACK	
			9.5	4.8			SP95/RL/BLACK	
			12.7	6.4			SP127/RL/BLACK	
			19	9.5	0.75	60	SP190/RL/BLACK	
			1.6	0.8	0.45	1.2	SP16/1.2/BLACK	
			2.4	1.2	0.5		SP24/1.2/BLACK	
			3.2	1.6			SP32/1.2/BLACK	
			4.8	2.4			SP48/1.2BLACK	
			6.4	3.2	0.65		SP64/1.2BLACK	
			9.5	4.8			SP95/1.2/BLACK	
			12.7	6.4			SP127/1.2/BLACK	
			19	9.5	0.75		SP190/1.2/BLACK	
			38.1	19.1	1		SP381/1.2/BLACK	
			50.8	25.4	1.15		SP508/1.2/BLACK	
	9.5		4.8	0.65	5	SP95/5/BLACK		
	12.7		6.4			SP127/5/BLACK		
	25.4		12.7	0.9		SP254/5/BLACK		
	Clear		Clear	2.4	1.2	0.5	1.2	SP24/1.2/CLEAR
				6.4	3.2	0.65		SP64/1.2/CLEAR
				19	9.5	0.75		SP190/1.2/CLEAR
				6.4	3.2	0.65	5	SP64/5/CLEAR
				38.1	19.1	1		SP381/5/CLEAR
				2.4	1.2	0.5	150	SP24/RL/CLEAR
				3.2	1.6			SP32/RL/CLEAR
				4.8	2.4			SP48/RL/CLEAR
				9.5	4.8	0.65	75	SP95/RL/CLEAR
				12.7	6.4			SP127/RL/CLEAR
				19	9.5			0.75
				38.1	19.1	1	30	SP381/RL/CLEAR

Flexible, Flame Retardant

General Purpose Polyolefin Heat Shrink Tubing

multicompPRO

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter (Min. Expanded Diameter - mm)	Fully Shrunk Diameter (Max. Recovered Diameter - mm)	Nominal Recovered Wall (mm)	Length (m)	Part Number
Polyolefin	Yellow	20	1.6	0.8	0.45	1.2	SP16/1.2/YELLOW
			2.4	1.2	0.5		SP24/1.2/YELLOW
			3.2	1.6			SP32/1.2/YELLOW
			4.8	2.4			SP48/1.2/YELLOW
			6.4	3.2	0.65		SP64/1.2/YELLOW
			9.5	4.8			SP95/1.2/YELLOW
			12.7	6.4			SP127/1.2/YELLOW
			19	9.5	0.75		SP190/1.2/YELLOW
			25.4	12.7	0.9		SP254/1.2/YELLOW
			38.1	19.1	1		SP381/1.2/YELLOW
			50.8	25.4	1.15		SP508/1.2/YELLOW
			1.6	0.8	0.45		5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO