Heatshrink Adhesive Lined

RoHS

Compliant

High Shrink Ratio, Adhesive Lined, Polyolefin Heat Shrink Tubing 3X and 4X



Characteristics:

Operating Temperature Min. Shrink Temperature Shrink Ratio Approvals Standard Colour

: -55°C to +125°C
: 70°C
: 3:1 and 4:1
: UL224, 125°C 600V VW-1 (except clear)
: Black
(Other colours are also available on request)

Applications

Manufactured by co-extrusion of polyolefin and hot-melt adhesive. Designed to provide both insulation and sealing for the protected items. Typically used for the protection of automotive wires, bundled wires and metal tubes against water and moisture. The high expansion ratio makes it possible to repair most damaged cable jackets without removing connectors.

Technical Data

Property	Test Method	Typical Data
Tensile Strength	ASTM D 2671	10.4MPa
Ultimate Elongation (%)	ASTM D 2671	30
Longitudinal Shrinkage (%)	UL 224	0 to -10
Heat Aging Ultimate Elongation (%)	158°C, 168hrs.	200
Flammability	VW-1	Pass (outer jacket only)
Dielectric Strength (kv/mm)	IEC 243	20
Volume Resistivity (Ω-cm)	UL224	1 × 10 ¹⁴
Copper Stability	ASTM D 2671	Pass
Corrosion	UL224	No corrosion

Dimensions: Heat Shrinkable Tubing of 3X

Siz	ze	As supplied (mm)			After Recovered (mm)			
Inch	mm	Min. I.D.	Average W.T.	O.D.	Max. I.D.	Total W.T.	Adhesive Thickness	O.D.
1/8	3.2	3.2	0.3 ±0.08	3.6 ±0.2	1	0.95 ±0.08	0.35 ±0.08	2.9 ±0.2
3/16	4.8	4.8	0.46 ±0.08	5.7 ±0.2	1.6	1.1 ±0.08	0.4 ±0.08	3.8 ±0.2
1/4	6.4	6.4	0.5 ±0.08	7.4 ±0.2	2.2	1.2 ±0.08	0.45 ±0.08	4.6 ±0.2
5/16	7.9	7.9	0.52 ±0.08	8.9 ±0.2	2.7	1.35 ±0.08	0.5 ±0.08	5.4 ±0.2
3/8	9.5	9.5	0.55 ±0.08	10.6 ±0.2	3.2	1.45 ±0.08	0.5 ±0.08	6.1 ±0.2
1/2	12.7	12.7	0.68 ±0.08	14.1 ±0.2	4.2	1.7 ±0.08	0.5 ±0.08	7.6 ±0.2

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Heatshrink Adhesive Lined

Siz	ze	As supplied (mm)			After Recovered (mm)				
Inch	mm	Min. I.D.	Average W.T.	O.D.	Max. I.D.	Total W.T.	Adhesive Thickness	O.D.	
5/8	15	15	0.70 ±0.1	16.4 ±0.2	5.2	1.8 ±0.1	0.55 ±0.1	8.8 ±0.2	
3/4	19.1	19.1	0.76 ±0.1	20.6 ±0.2	6.3	2 ±0.1	0.55 ±0.1	10.3 ±0.2	
1	25.4	25.4	0.78 ±0.1	27.0 ±0.2	8.5	2.1 ±0.1	0.55 ±0.1	12.7 ±0.2	
1-1/4	30	30	0.80 ±0.1	31.6 ±0.2	10.2	2.2 ±0.1	0.6 ±0.1	14.6 ±0.2	
1-1/2	39	39	0.85 ±0.1	40.7 ±0.2	13.5	2.4 ±0.1	0.6 ±0.1	18.3 ±0.2	
2	50	50	0.95 ±0.1	51.9 ±0.2	17	2.7 ±0.1	0.7 ±0.1	22.4 ±0.2	

Dimensions: Heat Shrinkable Tubing of 4X

Si	ze	As	supplied (r	nm)	After Recovered (mm)					
Inch	mm	Min. I.D.	Average W.T.	O.D.	Max. I.D.	Total W.T.	Adhesive Thickness	O.D.	Part Number	
-	4	4	0.5 ±0.1	5.1 ±0.2	1	1 ±0.15	0.4 ±0.15	3 ±0.3	HS400	HS409
-	6	6	0.4 ±0.1	7.1 ±0.2	1.5	1.1 ±0.15	0.4 ±0.15	3.7 ±0.3	HS401	HS410
-	8	8	0.55 ±0.1	9.5 ±0.2	2	1.5 ±0.15	0.5 ±0.15	5 ±0.3	HS402	HS411
-	12	12	0.55 ±0.1	13.5 ±0.2	3	1.7 ±0.15	0.5 ±0.15	6.4 ±0.3	HS403	HS412
-	16	16	0.65 ±0.1	17.8 ±0.2	4	2 ±0.15	0.6 ±0.15	7 ±0.3	HS404	-
-	20	20	0.65 ±0.1	22.4 ±0.2	5	2.3 ±0.25	0.6 ±0.15	9.6 ±0.3	HS405	-
-	24	24	0.8 ±0.15	26.8 ±0.2	6	2.5 ±0.25	0.6 ±0.15	11 ±0.3	HS406	-
-	32	32	0.9 ±0.15	35.2 ±0.2	8	2.8 ±0.3	0.7 ±0.15	13.6 ±0.3	HS407	-
-	52	52	1 ±0.15	54 ±0.2	13	3 ±0.3	0.7 ±0.15	19 ±0.6	HS408	-

Part Number Table

Description	Part Number
Heatshrink, Black, 4mm, 1.2m	HS400
Heatshrink, Sleeving, 6mm, 4:1	HS401
Heatshrink, Sleeving, 8mm, 4:1	HS402
Heatshrink, Sleeving, 12mm, 4:1	HS403
Heat Shrink, Black, 16mm, 1.2m	HS404
Heatshrink, 20mm, Black, 1.2m	HS405
Heat Shrink, Adhesive, Black, 24mm, 1.2m	HS406

Description	Part Number
Heat Shrink, Adhesive, Black, 32mm, 1.2m	HS407
Heatshrink, Sleeving, 52mm, 4:1	HS408
Heatshrink, Sleeving, 4mm, 4:1, 5m	HS409
Heatshrink, Sleeving, 6mm, 4:1, 5m	HS410
Heatshrink, Sleeving, 8mm, 4:1, 5m	HS411
Heatshrink, Sleeving, 12mm, 4:1, 5m	HS412

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

