PNP Silicon Planar Switching Transistor, TO-39







Pin Configuration

- 1. Emitter
- 2. Base
- 3. Collector

Absolute Maximum Ratings

| Parameter | Symbol | Value | Unit |
|---|----------|-------------|-------------|
| Collector Emitter Voltage | VCEO | 600 | |
| Collector Base Voltage | Vсвр | 40 | V |
| Emitter Base Voltage | VEBO | 60 | |
| Collector Current Continuous | Ic | 5 | mA |
| Power Dissipation @ Ta=25°C Derate Above 25°C | Do | 600 3.43 | mW mW/°C |
| Power Dissipation @ Tc=25°C Derate Above 25°C | PD | 3 17.2 | W mW/°C |
| Operating And Storage Junction Temperature Range | ТJ, TSTG | -65 to +200 | °C |

Electrical Characteristics: (TA = 25°C unless otherwise specified)

| Description | Symbol | Test Condition | Min. | Тур. | Max. | Unit |
|---------------------------|--------|-------------------------|------|------|------|------|
| Collector Emitter Voltage | *VCEO | Ic=10mA, Iв=0 | 40 | - | - | |
| Collector Base Voltage | Vсво | Ic=10μA, IE=0 | 60 | - | - | V |
| Emitter Base Voltage | VEBO | IE=10mA, Ic=0 | 5 | - | - | |
| Collector Cut Off Current | ICEX | VCE=30V, VBE=0.5V | - | - | 50 | A |
| Callantar Cut Off Current | lana | VcB=50V, IE=0 | - | - | 20 | nA |
| Collector Cut Off Current | Ісво | Vcb=50V, IE=0, Ta=150°C | - | - | 20 | μΑ |
| Base Current | Ів | VCE=30V, VBE=0.5V | - | - | 50 | nA |

| Description | Symbol | Test Condition | Values | |
|-----------------|--------|--------------------|-----------|--|
| | | Ic=0.1mA, VcE=10V | >35 | |
| DC Current Gain | | Ic=1mA, VcE=10V | >50 | |
| | hFE | Ic=10mA, VcE=10V | >75 | |
| | | *Ic=150mA, VcE=10V | 100 - 300 | |
| | | *Ic=500mA, VcE=10V | >30 | |

^{*}Pulse Test: Pulse Width ≤300µs, Duty Cycle ≤2%

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



PNP Silicon Planar Switching Transistor, TO-39



Small Signal Characteristics


| Description | Symbol | Test Condition | Min. | Тур. | Max. | Unit |
|--------------------------------------|-----------|--|------|------|------------|--------|
| Collector Emitter Saturation Voltage | *VCE(sat) | Ic=150mA, Iв=15mA Ic=500mA, Iв=50mA | - | - | 0.4 1.6 | V V |
| Base Emitter Saturation Voltage | *VBE(sat) | Ic=150mA, Iв=15mA Ic=500mA, Iв=50mA | - | - | 1.3 2.6 | V V |
| Transition Frequency | **fT | Ic=50mA, VcE=20V, f=100MHz | 200 | - | - | MHz |
| Output Capacitance | Cobo | Vсв=10V, IE=0, f=100kHz | - | - | 8 | pF |
| Input Capacitance | Cibo | Vве=2V, Iс=0, f=100kHz | - | - | 30 | pF |

Switching Time

| Description | Symbol | Test Condition | Min. | Тур. | Max. | Unit |
|---------------|--------|--|------|------|------|------|
| Delay Time | td | | - | - | 10 | ns |
| Rise Time | tr | Ic=150mA, I _{B1} =15mA, V _{CC} =30V | - | - | 40 | ns |
| Turn On Time | ton | | - | - | 45 | ns |
| Storage Time | ts | | - | - | 80 | ns |
| Fall Time | tf | Ic=150mA, I _{B1} = I _{B2} =15mA, Vcc=6V | - | - | 30 | ns |
| Turn Off Time | toff | | - | - | 100 | ns |

^{*}Pulse Test: Pulse Width ≤ 300ms, Duty Cycle ≤ 2%

TO-39 Metal Can Package



| Dimensions | Min. | Max. |
|------------|------|------|
| А | 8.5 | 9.39 |
| В | 7.74 | 8.5 |
| С | 6.09 | 6.6 |
| D | 0.4 | 0.53 |
| Е | - | 0.88 |
| F | 2.41 | 2.66 |
| G | 4.82 | 5.33 |
| Н | 0.71 | 0.86 |
| J | 0.73 | 1.02 |
| K | 12.7 | - |
| L | 42° | 48° |

Dimensions: Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



 $^{^{**}}$ fT is defined as the frequency at which $Ih_{fe}I$ extrapolates to unity.

PNP Silicon Planar Switching Transistor, TO-39



Part Number Table

| Description | Part Number | | |
|--|-------------|--|--|
| PNP Silicon Planar Switching Transistor, TO-39 | 2N2905 | | |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

