

www.amphenol-sine.com







Environmentally-Sealed, Multi-Pin, Heavy-Duty, Plastic or Metal Circular Connectors

Amphenol Sine Systems' **DuraMate™ Family** of environmentally-sealed, multi-pin, heavy duty, plastic (AHDP) or metal (AHDM/AHDBM) circular connectors provide an economical, quick-connect, bayonet-locking system manufactured to withstand the challenges and complexities of harsh-environment, off-road applications. Our ISOBUS products specifically meet ISO 11783 standards (for control and communications between tractors, implements and software) for agricultural applications.

Currently available in the following Series:



DM Dura Mate AHDP ISOBUS 91 Series (DM) Dura Mate AHDM/AHDBM ISOBUS 91 Series

DuraMate™ AHDP (Pgs 3-7): Size 18 with 8 insert arrangements 2, 6, 8, 14(x3), 20 and 21

Size 24 with 13 insert arrangements 7(x2), 9, 16, 18, 19, 21, 23, 27, 29, 31, 35 and 47

DuraMate[™] AHDM (Pgs 8-11): Size 18 with 6 insert arrangements 2, 6, 8, 14, 20 and 21

Size 24 with 13 insert arrangements 7(x2), 9, 16, 18, 19, 21, 23, 27, 29, 31, 35 and 47

DuraMate™ AHDP ISOBUS 91 (Pgs 12-16): Size 24, 9 Position

DuraMate™ AHDM/AHDBM ISOBUS 91 (Pgs 17-22): Size 24, 9 Position

Key Features

- 3 key-way bayonet design ensures proper mating of connectors
- High density signal and mixed power insert configurations
- Operating temperature range: -55°C to +125°C
- High current configurations incorporating revolutionary RADSOK® contacts
- High strength impact resistant & lightweight thermoplastic or zinc-alloy metal housings
- Low insertion force stamped terminals offer improved manufacturing efficiencies
- Environmentally-sealed and engineered rapid and secure mating system achieves IP68/IP69K protection (in mated condition) from ingress of dust, water, mud and other contaminants and is vibration resistent
- Sealing features consisting of durable high temperature silicone provide barrier from lubricating oils, hydraulic fluids and fossil fuels
- Backshells maintain a compression-fit design to resist maximum pull-out forces and facilitate strain-relief for jacketed cable ranges
- Wire entry sealing available in three separate ranges for discrete wire applications
- Wide Thread Adapters (WTA) provide an enhanced threading for use with our wide variety of screw-on or clamshell backshells (AHDP Only)
- Smooth Ring Adapters (SRA) are designed for use without backshells for a smaller footprint (AHDP Only)
- Backshell Ring Adapters (BRA) allow for use with other compatible industry-standard snap-on backshells (AHDP Only)
- Utilizes A Series[™] standard contact system (Stamped & Formed or Machined)




Standard products. Custom solutions Customer Service +1 800 394 7732







DuraMate™ AHDM/AHDP Series - Part Numbering Sequence





www.amphenol-sine.com



DM Dura **Mate**™AHDP

Environmentally-Sealed, Multi-Pin, Heavy-Duty, Plastic, Circular Connectors

Available in Size 18 with 8 insert arrangements 2, 6, 8, 14(x3), 20 and 21 **Available in Size 24 with 13 insert arrangements** 7(x2), 9, 16, 18, 19, 21, 23, 27, 29, 31, 35 and 47

The **DuraMate™ AHDP** environmentally-sealed, multi-pin, heavy duty, plastic, circular connector series provides an economical quick-connect bayonet locking system manufactured to withstand the challenges and complexities of harsh environment off-road applications.

- 3 keyway bayonet design ensures proper mating of connectors
- High density signal and mixed power insert configurations
- High current configurations incorporating revolutionary RADSOK® contacts
- Low insertion force stamped terminals offer improved manufacturing efficiencies
- Sealing features consisting of durable high temperature silicone provide barrier from lubricating oils, hydraulic fluids and fossil fuels
- Backshells maintain a compression-fit design to resist maximum pull-out forces and facilitate strain-relief for jacketed cable ranges.
- Wire entry sealing available in four separate ranges for discrete wire applications
- Wide Thread Adapters (WTA) provide an enhanced threading for use with our wide variety of screw-on or clamshell backshells
- Smooth Ring Adapters (SRA) are designed for use without backshells for a smaller footprint
- Backshell Ring Adapters (BRA) allow for use with other compatible industry-standard snap-on backshells
- Utilizes A Series[™] standard contact system (Stamped & Formed or Machined)

DuraMate[™] AHDP - Material & Performance Specifications

Current Rating per Contact	Size 4 - 100A Size 8 - 86A Size 12 - 25A Size 16 - 13A Size 20 - 7.5A	Housing Material	Thermoplastic
Operating Temperature	-55°C to +125°C	Insulation Insert	Thermoplastic
Dielectric Withstanding Voltage	Current Leakage -2mA at 1500 VAC	Seal	Silicone Rubber
Degree of Protection	IP68/69K (in mated condition)	Contact	A Series™ Common System
Mating Cycle Durability	100 Cycles	Compliance	RoHS





Standard products. Custom solutions Customer Service +1 800 394 7732





www.amphenol-sine.com

DuraMateTM AHDP - Insert Arrangements (1) C030 - 6 Position/2 Used (Size 4); (2) C041 - Receptacle w Diagnostic Keying; (3) CL20 - Plug w Diagnostic Keying; (4) CL22 - 7 Position Alt Construction)

Size 18	Size 18	Size	9 18	Size	e 18	Size 18	Size 18	Size	e 18	Size 18
18-06 ⁽¹⁾ 2 Size 4	18-06 2 Size 4, 4 Size 16	18- 8 Siz	-08 e 12		-14 ze 16	18-14 ⁽²⁾ 14 Size 16	18-14 ⁽³⁾ 14 Size 16		-20 18 Size 20	18-21 21 Size 20
$\bigcirc \bigcirc$			•							
Normal	Normal	Normal	Reduced	Normal	Reduced	Normal	Normal	Normal	Reduced	Normal

Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24
24-07 1 Size 8 (RADSOK®) 6 Size 12	24-07 ⁽⁴⁾ 3 Size 4, 4 Size 16	24-09 1 Size 4, 2 Size 8 6 Size 12	24-16 16 Size 12	24-18 1 Size 8, 3 Size 12 14 Size 16	24-19 6 Size 12, 13 Size 16	24-21 4 Size 12, 17 Size 16	24-23 23 Size 16	24-27 4 Size 12, 23 Size 16	24-29 4 Size 12, 19 Size 16 6 Size 20
Normal	Normal	Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Reduced	Reduced

Size	24	Size 24	Size 24
24-31 31 Size 16		24-35 3 Size 16, 32 Size 20	24-47 5 Size 16, 42 Size 20
			00000 00000 00000 00000 00000 00000 0000
Reduced	Thin	Reduced	Reduced

	Contac	t Legend (S	ize/Max. C	urrent)	
0	۲	0	•	•	o
4+/100A 4/100A	8/60A	8/86A RADSOK®	12/25A	16/13A	20/7.5A

DuraMate™ AHDP - Recommended Wire Insulation Overall Diameter (OD) 4+ contact is only available for 24-07CL22

Contact Size	Typical Wire Range	Normal Seal	Thin Seal	Reduced Sea	l (See datasheets)
4+	4AWG (25.0-21.0mm²)	7.9-10.67mm (0.311-0.420")	-	-	-
4	6AWG (16.0-13.0mm²)	6.63-7.41mm (0.261-0.292")	-	6.63-7.41mm (0.261-0.292")	-
8	8-10AWG (10.0-5.0mm²)	4.83-6.10mm (0.190-0.240")	-	3.43-5.59mm (0.135-0.220")	-
12	10-14AWG (6.0 2.0mm²)	3.43-4.32mm (0.1350170")	-	2.46-4.01mm (0.135-0.158")	2.46-4.01mm (0.135-0.158")
16	14-20AWG (2.0-0.5mm²)	2.54-3.40mm (0.100-0.134")	2.23-2.69mm (0.088106")	1.35-3.05mm(0.053-0.120")	1.35-2.62mm (0.053-0.103")
20	16-22AWG (1.5-0.35mm²)	1.02-2.41mm (0.040095")	-	1.02-02.41mm (0.040-0.095")	1.02-2.10mm (0.040-0.083")

DuraMate[™] AHDP - Backshell Options and Accessory Overview



Contact Removal Tools

Blank Seal Plugs



DuraMate™ AHDP - Plug & Receptacle Options (Dimensions in mm)

Size 18 Plug	Size 18 Receptacle	Size 24 Plug	Size 24 Receptacle
Wide Thread Adapter (WTA)			
Smooth Ring Adapter (SRA)			
Backshell Ring Adapter (BRA)			

DuraMate[™] AHDP w PanelMate[™] - Receptacle Options (Dimensions in mm)

Size 18 Plug	Size 18 Receptacle	Size 24 Plug	Size 24 Receptacle
-	PanelMate™ with Wide Thread Adapter (WTA)	-	PanelMate™ with Wide Thread Adapter (WTA)
-		-	
-	PanelMate™ with Smooth Ring Adapter (SRA)	-	PanelMate™ with Smooth Ring Adapter (SRA)
-		-	
-	PanelMate™ with Backshell Ring Adapter (BRA)	-	PanelMate™ with Backshell Ring Adapter (BRA)
-	4 lm r/2 50	-	960, tem



DuraMate[™] AHDP - Backshell Options and Accessories

Image	Part Number	Description
	AHDPBS-015-1805	Size 18, Backshell, Conduit, Snap Over, Right Angle 90°, Duramate™ AHDP Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-18NUT Adapter
	AHDPBS-15L017-1805	Size 18, Backshell, Conduit, Snap-Over, Right Angle 180°, DuraMate™ AHDP Note: For use with Backshell Ring Adapter (BRA)
O Brach	AHDPBS-011-2405	Size 24, Backshell, Conduit, Snap Over, Right Angle 90°, DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-24NUT Adapter
	AHDPBS-11L017-2405	Size 24, Backshell, Conduit, Snap-Over, Right Angle 180°, DuraMate™ AHDP Note: For use with Backshell Ring Adapter (BRA)
	AHDPBS-016-1805	Size 18, Backshell, Conduit, Snap Over, Straight 180°, Duramate™ AHDP Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-18NUT Adapter
· .	AHDPBS-16L017-1805	Size 18, Backshell, Conduit, Snap-Over, Straight, DuraMate™ AHDP Note: For use with Backshell Ring Adapter (BRA)
1ª lin	AHDPBS-010-2405	Size 24, Backshell, Conduit, Snap Over, Straight 180°, DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-24NUT Adapter
	AHDPBS-10L017-2405	Size 24, Backshell, Conduit, Snap-Over, Straight, DuraMate™ AHDP Note: For use with Backshell Ring Adapter (BRA)
(in the second s	AHDPBS-0406-001	Size 24, Backshell, Tie Wrap, Wide Thread Adapter (WTA), DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDPBS-18-001	Size 18, Backshell, Tie Wrap, Wide Thread Adapter (WTA), Cable Diameter Range 14.5mm - 18.0mm, Duramate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDPBS-0406-002	Size 24, Backshell, Wide Thread Adapter (WTA), 2 PC, Compression Nut Cable Diameter Range 14.5mm - 18.0mm, DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDPBS-0406-003	Size 24, Backshell, Wide Thread Adapter (WTA), 2 PC, Compression Nut Cable Diameter Range 19.5mm - 24.1mm, DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDPBS-18-002	Size 18, Backshell, Wide Thread Adapter (WTA), 2PC, Compression Nut Cable Diameter Range 14.5mm-18.0mm, Duramate™ AHDP Note: For use with Wide Thread Adapter (WTA)
Circ	AHDPBS-0406-SM01	Size 24, Backshell, Sealed, Cable Grommet, DuraMate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDPBS-18-SM01	Size 18, Backshell, Sealed, Cable Grommet, Duramate™ AHDP Note: For use with Wide Thread Adapter (WTA)
	AHDC06-24	Size 24, Receptacle Cap, Sealed, DuraMate™ AHDP
	AHDC06-18	Size 18, Receptacle Cap, Sealed, DuraMate™ AHDP
	AHDC04-24	Size 24, Plug Cap, Sealed, DuraMate™ AHDP
	AHDC04-18	Size 18, Plug Cap, Sealed, DuraMate™ AHDP



DuraMate[™] AHDP - Backshell Options and Accessories, cont.

Image	Part Number	Description
	AHDC04-24-PM	Size 24, Plug Cap, Sealed, Threaded, DuraMate™ AHDP
	AHDC04-24-PMT	Size 24, Plug Cap, w Tether, Threaded, Lock Washer, Sealed, DuraMate™ AHDP
	AHDC04-24-T	Size 24, Plug Cap, w Tether, Sealed, DuraMate™ AHDP
	AHDP24-PN01	Size 24, Panel Nut, Duramate™ AHDP
0	AHDP18-PN01	Size 18, Panel Nut, DuraMate™ AHDP
	AT14-001-2486	Size 24, Lock Washer, Wave, Duramate™ AHDP
\bigcirc	AT14-002-1886	Size 18, Lock Washer, Wave, DuraMate™ AHDP
	AHDP-16-04477	Size 24, Rubber Flange Seal, Duramate™ AHDP
\mathbf{O}	AHDP-16-04978	Size 18, Rubber Flange Seal, DuraMate™ AHDP
	A114019	Size 4, Blank Seal Plug
	A114018	Size 8, Blank Seal Plug
(C)	A114017	Size 12/16, Blank Seal Plug
<	AT13-217-1605	Size 16, Locking Seal Plug
~	AT13-204-2005	Size 20, Blank Seal Plug
	AT11-027-0405	Size 4+, Contact Removal Tool, 4AWG
	AT114009	Size 4, Contact Removal Tool, 6AWG
	AT11-001-3.6M	Size 8, Contact Removal Tool, 7-10AWG
	AT114008	Size 8, Contact Removal Tool, 8-10AWG
	AT11-337-1205	Size 12 , Contact Removal Tool, 12-14AWG
	AT11-310-1605	Size 16, Contact Removal Tool, 16-20AWG
	AT11-240-2005	Size 20, Contact Removal Tool, 20-22AWG



www.amphenol-sine.com



(DM) Dura Mate[™] AHDP ISOBUS 91 Series

Environmentally-Sealed, Multi-Pin, Heavy-Duty, Plastic Circular ISOBUS Connectors

Available in Size 24, 9 Position

Amphenol Sine Systems' **DuraMate™ AHDP ISOBUS 91 Series** of environmentally-sealed, multi-pin, heavy duty, circular plastic (AHDP) plugs & receptacles provide an economical, quick-connect, circular bayonet locking system **designed to meet ISO 11783 standards (for control and communications between tractors, implements and software)** and withstand the challenges and complexities of harsh environment, off-road, agrcultural applications.

Key ISOBUS 91 Series Features

- + One-to-one alternative for all HDP20 parts
- + Compatible to other industry standard circular bayonet versions
- + AHDP 91 Series Plugs have a jumper (bridged contacts) between Pin 4 & 5
- + AHDP 91 Series Receptacles do not have a jumper (bridged contact)
- + Options for up to 6AWG/16mm² power wires
- + Full range of backshell options

DuraMate™ Features

- 3 key-way bayonet design ensures proper mating of connectors
- High density signal and mixed power insert configurations
- Operating temperature range: -55°C to +125°C
- High-strength, impact resistant & lightweight thermoplastic housings
- Low-insertion force stamped terminals offer improved manufacturing efficiencies
- Environmentally-sealed and engineered rapid and secure mating system achieves IP67/IP69K protection (in mated condition) from ingress of dust, water, mud and other contaminants and is vibration resistent
- Sealing features consisting of durable high-temperature silicone provide barrier from lubricating oils, hydraulic fluids and fossil fuels
- Backshells maintain a compression-fit design to resist maximum pull-out forces and facilitate strain-relief for jacketed cable ranges
- Wire entry sealing available in four separate ranges for discrete wire applications
- Wide Thread Adapters (WTA) provides an enhanced threading for use with our wide variety of screw-on or clamshell backshells
- Smooth Ring Adapters (SRA) are designed for use without backshells for a smaller footprint
- Utilizes A Series™ standard contact system (Stamped & Formed or Machined)

DuraMate[™] AHDP ISOBUS 91 Series - Material & Performance Specifications

Current Rating per Contact	Size 8, 60A Size 12, 25A Size 16, 13A	Housing Material	Thermoplastic				
Operating Temperature	-55°C to +125°C	Insulation Insert	Thermoplastic				
Dielectric Withstanding Voltage	Current Leakage -2mA at 1500 VAC	Seal	Silicone Rubber				
Degree of Protection	IP67/69K (in mated condition)	Contact	A Series™ Common System				
Mating Cycle Durability	100 Cycles	Compliance	RoHS				



Standard products. Custom solutions Customer Service +1 800 394 7732



Updated 06/2022





DuraMate[™] AHDP ISOBUS 91 Series - Insert Arrangements

Size	24
24- 2 Size 8, 1 5 Siz	2 Size 12,
Normal	Reduced

,	Contact Legend (Size/Max. Current)							
	۲	۲	₽	•				
	8/60A 6AWG	8/60A 8-10AWG	12/25A	16/13A				

DuraMate™ AHDP ISOBUS 91 Series - Recommended Wire Insulation Overall Diameter (OD)

Contact Size	Typical Wire Range	Normal Seal	Reduced Seal	Reduced Seal for 6AWG/16mm ² (Size 8 Contacts Only)	
8	6-10AWG (5.0-16.0mm²)	4.83-6.10mm (0.190-0.240'')	3.43-5.59mm (0.135-0.220'')	6.50-7.42mm (0.256-0.292'')	
12	10-14AWG (6.0 2.0mm²)	3.40-4.32mm (0.134-0.170'')	2.46-4.01mm (0.135-0.158'')	2.46-4.01mm (0.135-0.158")	
16	14-20AWG (2.0-0.5mm²)	2.54-3.40mm (0.100-0.134'')	1.35-3.05mm (0.053-0.120")	1.35-3.05mm (0.053-0.120")z	

DuraMate™ AHDP ISOBUS 91 Series - Backshell Options and Accessory Overview



DuraMate[™] AHDP ISOBUS 91 Series - Plug & Receptacle Options (Dimensions in mm)

Size 24 Plug	Size 24 Receptacle	Size 24 Plug	Size 24 Receptacle
Wide Thread Adapter (WTA)	Wide Thread Adapter (WTA)	Smooth Ring Adapter (SRA)	Smooth Ring Adapter (SRA)



DuraMate™ AHDP ISOBUS 91 Series - Standard Plugs

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDP06-24-91SN-SRA	9 Position, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Normal Diameter Seal (Green), Smooth Ring Adapter (SRA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP06-24-91SN-WTA	9 Position, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Normal Diameter Seal (Green), Wide Thread Adapter (WTA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP06-24-91SR-SRA	9 Position, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Smooth Ring Adapter (SRA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP06-24-91SR-WTA	9 Position, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Wide Thread Adapter (WTA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP06-24-91SR16-SRA	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Smooth Ring Adapter (SRA), Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP06-24-91SR16-WTA	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Wide Thread Adapter (WTA), Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨

DuraMate™ AHDP ISOBUS 91 Series - Standard Receptacles

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDP04-24-91PN-SRA	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Normal Diameter Seal (Green), Smooth Ring Adapter (SRA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP04-24-91PN-WTA	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Normal Diameter Seal (Green), Wide Thread Adapter (WTA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP04-24-91PR-SRA	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Smooth Ring Adapter (SRA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨



DuraMate[™] AHDP ISOBUS 91 Series - Standard Receptacles, cont.

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDP04-24-91PR-WTA	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Wide Thread Adapter (WTA)	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP04-24-91PR16-SRA	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Smooth Ring Adapter (SRA), Size 8 Contact, 6AWG/16mm² Wire Seal Note: Use AT60-204-08141-16 contacts for 6AWG/16mm² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDP04-24-91PR16-WTA	9 Pos, Receptacle, Pin, Size 24, DuraMate [™] AHDP ISOBUS 91 Series, Plastic, Reduced Diameter Seal (Blue), Wide Thread Adapter (WTA), Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT60-204-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨

DuraMate™ AHDP ISOBUS 91 Series - Backshell Options and Accessories

Image	Part Number	Description
STAL)	AHDPBS-011-2405	Size 24, Backshell, Conduit, Snap Over, Right Angle 90°, DuraMate™ AHDP ISOBUS 91 Series Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-24NUT Adapter
	AHDPBS-010-2405	Size 24, Backshell, Conduit, Snap Over, Straight 180°, DuraMate™ AHDP ISOBUS 91 Series Note: For use with Wide Thread Adapter (WTA). May also be used on DuraMate™ AHDM with P/N AHDM-BS-24NUT Adapter
	AHDPBS-0406-001	Size 24, Backshell, Tie Wrap, Wide Thread Adapter (WTA), DuraMate™ AHDP ISOBUS 91 Series Note: For use with Wide Thread Adapter (WTA).
i p	AHDPBS-0406-002	Size 24, Backshell, Wide Thread Adapter (WTA), 2 PC, Compression Nut, Cable Diameter Range 14.5mm - 18.0mm, DuraMate™ AHDP ISOBUS 91 Series
	AHDPBS-0406-003	Size 24, Backshell, Wide Thread Adapter (WTA), 2 PC, Compression Nut, Cable Diameter Range 19.5mm - 24.1mm, DuraMate™ AHDP ISOBUS 91 Series
Citte	AHDPBS-0406-SM01	Size 24, Backshell, Sealed, Cable Grommet, DuraMate™ AHDP ISOBUS 91 Series
	AHDC06-24	Size 24, Receptacle Cap, Sealed, DuraMate™ AHDP ISOBUS 91 Series



DuraMate™ AHDP ISOBUS 91 Series - Backshell Options and Accessories, cont.

Image	Part Number	Description
	AHDC04-24-PM	Size 24, Plug Cap, Sealed, Threaded, DuraMate™ AHDP ISOBUS 91 Series
	AHDC04-24-PMT	Size 24, Plug Cap, w Tether, Threaded, Lock Washer, Sealed, DuraMate™ AHDP ISOBUS 91 Series
0	AHDP24-PN01	Size 24, Panel Nut, DuraMate™ AHDP ISOBUS 91 Series
\bigcirc	AT14-001-2486	Size 24, Lock Washer, Wave, DuraMate™ AHDP ISOBUS 91 Series
0	AHDP-16-04477	Size 24, Rubber Flange Seal, DuraMate™ AHDP ISOBUS 91 Series
	A114018	Size 8, Blank Seal Plug
	A114017	Size 12/16, Blank Seal Plug
_	AT13-217-1605	Size 16, Locking Seal Plug
	AT11-310-1605	Size 16, Contact Removal Tool, Light Blue, 16-20AWG
K	AT11-337-1205	Size 12 , Contact Removal Tool, Orange, 12-14AWG
	AT11-001-3.6M	Size 8, Contact Removal Tool, Black, 7-10AWG
~	AT114008	Size 8, Contact Removal Tool, Green, 8-10AWG
	AT60-204-08141-16	Size 8, 6AWG/16mm ² Wire Range, Contact, Pin, Nickel-plated Note: Refer to Plug/Receptacle datasheets for a complete list of available contacts
	AT62-203-08141-16	Size 8, 6AWG/16mm ² Wire Range, Contact, Socket, Nickel-plated Note: Refer to Plug/Receptacle datasheets for a complete list of available contacts



www.amphenol-sine.com



DM Dura Mate AHDM

Environmentally-Sealed, Multi-Pin, Heavy-Duty, Metal, Circular Connectors

Available in Size 18 with 6 insert arrangements 2, 6, 8, 14, 20 and 21 **Available in Size 24 with 13 insert arrangements** 7(x2), 9, 16, 18, 19, 21, 23, 27, 29, 31, 35 and 47

The **DuraMate™ AHDM** environmentally-sealed, multi-pin, heavy duty, metal, circular connector series provides an economical quick-connect bayonet locking system manufactured to withstand the challenges and complexities of harsh environment off-road applications.

- 3 key-way bayonet design ensures proper mating of connectors
- High density signal and mixed power insert configurations
- Operating temperature range: -55°C to +125°C
- High current configurations incorporating revolutionary RADSOK® contacts
- High strength impact resistant & lightweight zinc-alloy metal housings
- Low insertion force stamped terminals offer improved manufacturing efficiencies
- Environmentally-sealed and engineered rapid and secure mating system achieves IP68/IP69K protection (in mated condition) from ingress of dust, water, mud and other contaminants and is vibration resistant.
- Sealing features consisting of durable high temperature silicone provide barrier from lubricating oils, hydraulic fluids and fossil fuels
- Backshells maintain a compression-fit design to resist maximum pull-out forces and facilitate strain-relief for jacketed cable ranges.
- Utilizes A Series[™] standard contact system (Stamped & Formed or Machined)
- Wire entry sealing available in three separate ranges for discrete wire applications
- Integrated Wide Threading provides an enhanced threading for use with our wide variety of screw-on or clamshell backshells

DuraMate[™] AHDM - Material & Performance Specifications

Current Rating per Contact	Size 4 - 100A Size 8 - 86A Size 12 - 25A Size 16 - 13A Size 20 - 7.5A	Housing Material	Zinc-Alloy	
Operating Temperature	-55°C to +125°C	Insulation Insert	Thermoplastic	
Dielectric Withstanding Voltage	Current Leakage -2mA at 1500 VAC	Seal	Silicone Rubber	
Degree of Protection	IP68/69K (in mated condition)	Contact	A Series™ Common System	
Mating Cycle Durability	100 Cycles	Compliance	RoHS	





Standard products. Custom solutions Customer Service +1 800 394 7732





www.amphenol-sine.com

DuraMateTM AHDM - Insert Arrangements (1) C030 - 6 Position/2 Used (Size 4); (4) CL22 - 7 Position Alt Construction)

Size 18	Size 18	Size	e 18	Size	e 18	Size	e 18	Size 18
18-06 ⁽¹⁾ 2 Size 4	18-06 2 Size 4, 4 Size 16		-08 ie 12		-14 ze 16		-20 18 Size 20	18-21 21 Size 20
		(•				(°•		
Normal	Normal	Normal	Reduced	Normal	Reduced	Normal	Reduced	Normal

Contact Legend (Size/Max. Current)								
\bigcirc	۲	0	•	•	o			
4+/100A 4/100A	8/60A	8/86A RADSOK®	12/25A	16/13A	20/7.5A			

Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24	Size 24
24-07 1 Size 8 (RADSOK®) 6 Size 12	24-07 ⁽⁴⁾ 3 Size 4+, 4 Size 16	24-09 1 Size 4, 2 Size 8 6 Size 12	24-16 16 Size 12	24-18 1 Size 8, 3 Size 12 14 Size 16	24-19 6 Size 12, 13 Size 16	24-21 4 Size 12, 17 Size 16	24-23 23 Size 16	24-27 4 Size 12, 23 Size 16	24-29 4 Size 12, 19 Size 16 6 Size 20
Normal	Normal	Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Normal Reduced	Reduced	Reduced

Size 24		Size 24	Size 24
24-31 31 Size 16		24-35 3 Size 16, 32 Size 20	24-47 5 Size 16, 42 Size 20
Reduced	Thin	Reduced	Reduced

DuraMateTM AHDM - Recommended Wire Insulation Overall Diameter (OD) 4+ contact is only available for 24-07CL22


Contact Size	Typical Wire Range	Normal Seal	Thin Seal	Reduced Seal	(See datasheets)
4+	4AWG (25.0-21.0mm²)	7.9-10.67mm (0.311-0.420'')	-	-	-
4	6AWG (16.0-13.0mm²)	6.63-7.41mm (0.261-0.292'')	-	6.63-7.41mm (0.261-0.292'')	-
8	8-10AWG (10.0-5.0mm²)	4.83-6.10mm (0.190-0.240'')	-	3.43-5.59mm (0.135-0.220")	-
12	10-14AWG (6.0 2.0mm²)	3.43-4.32mm (0.1350170")	-	2.46-4.01mm (0.135-0.158")	2.46-4.01mm (0.135-0.158'')
16	14-20AWG (2.0-0.5mm ²)	2.54-3.40mm (0.100-0.134")	2.23-2.69mm (0.088106")	1.35-3.05mm(0.053-0.120")	1.35-2.62mm (0.053-0.103'')
20	16-22AWG (1.5-0.35mm²)	1.02-2.41mm (0.040095")	-	1.02-02.41mm (0.040-0.095")	1.02-2.10mm (0.040-0.083")

DuraMate™ AHDM - Backshell Options and Accessory Overview





DuraMate™ AHDM - Plug & Receptacle Options (Dimensions in mm)



DuraMate[™] AHDM - Backshell Options and Accessories

Image	Part Number	Description
and the second	AHDMBS-24-002	Size 24, Backshell, 2 PC, DuraMate™ AHDM
	AHDMBS-18-002	Size 18, Backshell, 2 PC, DuraMate™ AHDM
	AHDMBS-24-001	Size 24, Backshell, Tie Wrap, End Bell, DuraMate™ AHDM
(·	AHDMBS-18-001	Size 18, Backshell, Tie Wrap, End Bell, DuraMate™ AHDM
	AHDMBS-24-059	Size 24, Backshell, w Cable Clamp, DuraMate™ AHDM
	AHDMBS-18-059	Size 18, Backshell, w Cable Clamp, DuraMate™ AHDM
	AHDMBS-24-SM01	Size 24, Backshell, Metal, DuraMate™ AHDM
	AHDMBS-18-SM01	Size 18, Backshell, Metal, DuraMate™ AHDM
	AHDM-BS-24NUT	Size 24, Adapter for use with: AHDPBS-010-2405 AHDP Backshell, Conduit, Snap-Over, Straight 180 AHDPBS-011-2405 AHDP Backshell, Conduit, Snap-Over, Right Angle 90
	AHDM-BS-18NUT	Size 18, Adapter for use with: AHDPBS-015-1805 AHDP Backshell, Conduit, Snap-Over, Straight 180 AHDPBS-016-1805 AHDP Backshell, Conduit, Snap-Over, Right Angle 90
	AHDC34-24	Size 24, Protective Cap for Plug, DuraMate™ AHDM
	AHDC34-18	Size 18, Protective Cap for Plug, DuraMate™ AHDM
	AHDC36-24	Size 24, Protective Cap for Receptacle, DuraMate™ AHDM
	AHDC36-18	Size 18, Protective Cap for Receptacle, DuraMate™ AHDM
\sim	A112264	Size 24, Lockwasher, DuraMate™ AHDM
	A114021	Size 18, Lockwasher, DuraMate™ AHDM



DuraMate[™] AHDM - Backshell Options and Accessories, cont.

Image	Part Number	Description
	A112263-90	Size 24, Nut, DuraMate™ AHDM
	A114020-90	Size 18, Nut, DuraMate™ AHDM
	A114019	Size 4, Blank Seal Plug
	A114018	Size 8, Blank Seal Plug
	A114017	Size 12/16, Blank Seal Plug
	AT13-217-1605	Size 16, Locking Seal Plug
~	AT13-204-2005	Size 20, Blank Seal Plug
	AT11-027-0405	Size 4+, Contact Removal Tool, 4AWG
	AT114009	Size 4, Contact Removal Tool, 6AWG
	AT11-001-3.6M	Size 8, Contact Removal Tool, 7-10AWG
	AT114008	Size 8, Contact Removal Tool, 8-10AWG
	AT11-337-1205	Size 12 , Contact Removal Tool, 12-14AWG
	AT11-310-1605	Size 16, Contact Removal Tool, 16-20AWG
	AT11-240-2005	Size 20, Contact Removal Tool, 20-22AWG



www.amphenol-sine.com



DM) Dura Mate[™]AHDM/AHDBM ISOBUS 91 Series

Environmentally-Sealed, Multi-Pin, Heavy-Duty, Metal Circular ISOBUS Connectors

Available in Size 24, 9 Position

Amphenol Sine Systems' DuraMate™ AHDM/AHDBM ISOBUS 91 Series of environmentally-sealed, multi-pin, heavy-duty, circular metal plugs (AHDM) and breakaway metal (AHDBM) plugs & receptacles provide an economical, quick-connect, bayonet locking system designed to meet ISO 11783 standards (for control and communications between tractors, implements and software) and withstand the challenges and complexities of harsh environment, off-road, agricultural applications.

Key ISOBUS 91 Series Features

- One-to-one alternative for all HD30/HDB36 parts
- Compatible to other industry standard (Circular Bayonet) versions while retaining full breakaway functionality
- AHDM 91 Series Plugs have a jumper (bridged contacts) between Pin 4 & 5
- AHDM/AHDBM 91 Series Receptacles don't have a jumper (bridged contact)
- Options for up to 16mm² power wires
- Full range of backshell options

Important

- AHDBM 91 Series Plugs are intermateable to other industry standard versions and allow full breakaway functionality if used with suitable breakaway-ready Receptacles (like AHDBM 91 Receptacles)
- AHDM 91 Series Plugs are intermateable to other industry standard versions but do not retain breakaway functionality
- AHDBM 91 Series Receptacles (Circular Bayonet) are intermateable to other industry standard plugs and allow breakaway functionality when used with a breakaway Plugs (like AHDBM 91 Plugs)
- Available upon request and not shown on this flyer: AHDM 91 Series Receptacles (Drop Shaped Bayonet) are not intermateable to all industry standard versions and do not retain breakaway functionality

DuraMate[™] Features

- 3 key-way bayonet design ensures proper mating of connectors
- High density signal and mixed power insert configurations
- Operating temperature range: -55°C to +125°C
- High-strength, impact resistant & lightweight zinc-alloy metal housings
- Low-insertion force stamped terminals offer improved manufacturing efficiencies
- Environmentally-sealed and engineered rapid and secure mating system achieves IP67/IP69K protection (in mated condition) from ingress of dust, water, mud and other contaminants and is vibration resistent
- Sealing features consisting of durable high-temperature silicone provide barrier from lubricating oils, hydraulic fluids and fossil fuels
- Backshells maintain a compression-fit design to resist maximum pull-out forces and facilitate strain-relief for jacketed cable ranges
- Wire entry sealing available in four separate ranges for discrete wire applications
- Integrated Wide Threading provides an enhanced threading for use with our wide variety of screw-on or clamshell backshells
- Utilizes A Series[™] standard contact system (Stamped & Formed or Machined)



Standard products. Custom solutions Customer Service +1 800 394 7732





AHDBM Circular Bayonet Breakaway-Ready Receptacle

Standard Plua

AHDBM Circular Bayonet Breakaway Plug





www.amphenol-sine.com

DuraMate™ AHDM/AHDBM ISOBUS 91 Series - Material & Performance Specifications

Current Rating per Contact	Size 8, 60A; Size 12, 25A; Size 16, 13A	Housing Material	Zinc-alloy/Aluminum-alloy
Operating Temperature	-55°C to +125°C	Insulation Insert	Thermoplastic
Dielectric Withstanding Voltage	Current Leakage-2mA at 1500 VAC	Seal	Silicone Rubber
Degree of Protection	IP67/69K (in mated condition)	Contact	A Series™ Common System
Mating Cycle Durability	100 Cycles	Compliance	RoHS

DuraMate[™] AHDM/AHDBM ISOBUS 91 Series - Insert Arrangements

Size 24

24-09 2 Size 8, 2 Size 12,	Conto	act Legend (S	ize/Max. Cu	urrent)
5 Size 16	۲	۲	•	•
	8/60A 6AWG	8/60A 8-10AWG	12/25A	16/13A

DuraMate™ AHDM/AHDBM ISOBUS 91 Series - Recommended Wire Insulation Overall Diameter (OD)

Contact Size	Typical Wire Range	Normal Seal	Reduced Seal	Reduced Seal for 6AWG/16mm ² (Size 8 Contacts Only)
8	6-10AWG (5.0-16.0mm²)	4.83-6.10mm (0.190-0.240'')	3.43-5.59mm (0.135-0.220'')	6.50-7.42mm (0.256-0.292'')
12	10-14AWG (6.0 2.0mm²)	3.40-4.32mm (0.134-0.170'')	2.46-4.01mm (0.135-0.158'')	2.46-4.01mm (0.135-0.158'')
16	14-20AWG (2.0-0.5mm ²)	2.54-3.40mm (0.100-0.134'')	1.35-3.05mm (0.053-0.120")	1.35-3.05mm (0.053-0.120'')

DuraMate™ AHDM/AHDBM ISOBUS 91 Series - Backshell Options and Accessory Overview



Contact Removal Tools

DuraMate™ AHDM ISOBUS 91 Series - Plug & Receptacle Options (Dimensions in mm)





DuraMate™ AHDM ISOBUS 91 Series - Standard Plugs

lmage	Part Number	Description	Contact Size/ Amps	Voltage
	AHDM06-24-91SN	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDM06-24-91SN-059	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading, Cable Clamp Backshell	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDM06-24-91SR	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDM06-24-91SR-059	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDM06-24-91SR16	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDM06-24-91SR16-059	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨

DuraMate™ AHDBM ISOBUS 91 Series - Breakaway Plugs

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDBM06-24-91SN	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM06-24-91SN-059	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading, Cable Clamp Backshell, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM06-24-91SR	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨



DuraMate™ AHDBM ISOBUS 91 Series - Breakaway Plugs, cont.

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDBM06-24-91SR-059	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM06-24-91SR16	9 Pos, Kit, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell, Breakaway, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM06-24-91SR16-059	9 Pos, Plug, Socket, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Breakaway, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT62-203-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨

DuraMate™ AHDBM ISOBUS 91 Series - Breakway-Ready Receptacles

Image	Part Number	Description	Contact Size/ Amps	Voltage
	AHDBM04-24-91PN	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM04-24-91PN-059	9 Pos, Kit, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Normal Diameter Seal (Green), Integrated Wide Threading, Cable Clamp Backshell, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM04-24-91PR	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM04-24-91PR-059	9 Pos, Kit, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell, Breakway-Ready	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM04-24-91PR16	9 Pos, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Breakway-Ready, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT60-204-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250∨
	AHDBM04-24-91PR16-059	9 Pos, Kit, Receptacle, Pin, Size 24, DuraMate™ AHDBM ISOBUS 91 Series, Metal, Reduced Diameter Seal (Blue), Integrated Wide Threading, Cable Clamp Backshell, Breakway-Ready, Size 8 Contact, 6AWG/16mm ² Wire Seal Note: Use AT60-204-08141-16 contacts for 6AWG/16mm ² applications	Size 8, 60A Size 12, 25A Size 16, 13A	250V



DuraMate™ AHDM/AHDBM ISOBUS 91 Series - Backshell Options and Accessories

Image	Part Number	Description
(terest	AHDMBS-24-002	Size 24, Backshell, 2 PC, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
	AHDMBS-24-001	Size 24, Backshell, Tie Wrap, End Bell, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
	AHDMBS-24-059	Size 24, Backshell, w Cable Clamp, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
Com	AHDMBS-24-SM01	Size 24, Backshell, Metal, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
	AHDM-BS-24NUT	Size 24, Adapter for use with: AHDPBS-010-2405 AHDP Backshell, Conduit, Snap-Over, Straight 180 AHDPBS-011-2405 AHDP Backshell, Conduit, Snap-Over, Right Angle 90
50	AHDC34-24	Size 24, Protective Cap for Plug, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
	AHDC36-24	Size 24, Protective Cap for Receptacle, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
0	A112264	Size 24, Lockwasher, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
\bigcirc	A112263-90	Size 24, Nut, DuraMate™ AHDM/AHDBM ISOBUS 91 Series
	A114018	Size 8, Blank Seal Plug
-	A114017	Size 12/16, Blank Seal Plug
_	AT13-217-1605	Size 16, Locking Seal Plug
	AT11-310-1605	Size 16, Contact Removal Tool, Light Blue, 16-20AWG



DuraMate[™] AHDM/AHDBM ISOBUS 91 Series - Backshell Options and Accessories, cont.

Image	Part Number	Description
-	AT11-337-1205	Size 12 , Contact Removal Tool, Orange, 12-14AWG
	AT11-001-3.6M	Size 8, Contact Removal Tool, Black, 7-10AWG
~	AT114008	Size 8, Contact Removal Tool, Green, 8-10AWG
	AT60-204-08141-16	Size 8, 6AWG/16mm ² Wire Range, Contact, Pin, Nickel-plated Note: Refer to Plug/Receptacle datasheets for a complete list of available contacts
	AT62-203-08141-16	Size 8, 6AWG/16mm ² Wire Range, Contact, Socket, Nickel-plated Note: Refer to Plug/Receptacle datasheets for a complete list of available contacts

For more information, contact: Customer Service, +1 800 394 7732, csr@amphenol-sine.com

© 2018 Amphenol Sine Systems Corporation, 44274 Morley Drive, Clinton Township MI 48036 USA. www.amphenol-sine.com. Customer Service +1 800 394 7732 Every effort has been made to ensure that the information contained in this document is accurate at the time of publication. Specifications or information stated in this document are subject to change without notice.