

RAYCHEM | RAYCHEM DWHF

TE Internal #: ER34322001

Heat Shrink Tubing, Black, Dual Wall, .472 in [12 mm] Expanded Inside, .157 in [4 mm] Recovered Inside, 3:1 Shrink Ratio, RAYCHEM

DWHF

View on TE.com >



Heat Shrink Tubing



Primary Product Color: Black

Wall Type: **Dual**

Expanded Inside Diameter (Min): 12 mm [.472 in]

Recovered Inside Diameter (Max): 4 mm [.157 in]

Shrink Ratio: 3:1

Features

Product Type Features	
Wall Type	Dual
Body Features	
Primary Product Color	Black
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Flexible
Dimensions	
Expanded Inside Diameter (Min)	12 mm[.472 in]
Recovered Inside Diameter (Max)	4 mm[.157 in]
Heat Shrink Tubing Size Range	12. – 4. mm[.472 – .157 in]
Usage Conditions	
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-55 – 110 °C
Heat Shrink Tubing Resistance	Fluids, Mechanical Damage, Strain Relief

135 °C

Global

Recovery Temperature

Product Availability

Applicable Region



Packaging Features

Packaging Method	Bag & Box
Other	
Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: DBMC (5%) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





TE Part # EG1118-000 CV1981-ST-120V1600W-US



TE Part # CJ2087-000 HL2010E-KIT-120V



TE Part # EG1120-000 CV1981-ST-120V1600W-UK



TE Part # EG1115-000 CV1981-ST-230V1600W-CH




TE Part # EG1116-000 CV1981-ST-230V1600W-UK



TE Part # EG1114-000 CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM DWHF



Documents

Product Drawings DWHF-12/4-0-STK

English

Datasheets & Catalog Pages

DWHF Tubing

English

Product Specifications

Quality Specification

English