



SIEMENS



SENTRON • SIVACON • ALPHA

Low-Voltage Power Distribution and Electrical Installation Technology

Miniature Circuit Breakers

Catalog
Extract
LV 10

Edition
10/2018

[siemens.com/lowvoltage](https://www.siemens.com/lowvoltage)

Related catalogs

Low-Voltage Power Distribution and Electrical Installation Technology LV 10
 SENTRON • SIVACON • ALPHA
 Protection, Switching, Measuring and Monitoring
 Devices, Switchboards and Distribution Systems

PDF (E86060-K8280-A101-A8-7600)
 Print (E86060-K8280-A101-A6-7600)



Air Circuit Breakers and Molded Case Circuit Breakers with UL Certification LV 18
 SENTRON

PDF (E86060-K8280-E347-A1-7600)



Industrial Controls IC 10
 SIRIUS

PDF (E86060-K1010-A101-A9-7600)



Industrial Communication IK PI
 SIMATIC NET

E86060-K6710-A101-B8-7600



DELTA ET D1
 Switches and Socket Outlets

PDF



SITRAIN
 Training for Industry

www.siemens.com/sitrain



Catalog PDF / Contact

Catalog PDF

Digital versions of the catalogs are available in the Siemens Industry Online Support.

www.siemens.com/lowvoltage/catalogs



Contact

Your personal contact can be found in our Contacts Database at:

www.siemens.com/automation-contact



Industry Mall / TIA ST / CA 01

Industry Mall

Information and Ordering Platform on the Internet:

www.siemens.com/industrymall



Siemens TIA Selection Tool

for the selection, configuration and ordering of TIA products and devices

www.siemens.com/tst



Products for Automation and Drives CA 01
 Interactive Catalog
 Download

www.siemens.com/ca01download




Trademarks

All product designations may be registered trademarks or product names of Siemens AG or other supplying companies. Third parties using these trademarks or product names for their own purposes may infringe upon the rights of the trademark owners. Further information about low-voltage power distribution and electrical installation technology is available on the Internet at:

www.siemens.com/lowvoltage

Technical Support



Expert advice on technical questions with a wide range of demand-optimized services for all our products and systems.

www.siemens.com/lowvoltage/support-request

Low-Voltage Power Distribution and Electrical Installation Technology

Protection, Switching, Measuring and Monitoring Devices, Switchboards and Distribution Systems

SENTRON · SIVACON · ALPHA



Catalog LV 10 · 10/2018

Supersedes:
Catalog LV 10 · 04/2018

Refer to the Industry Mall for current updates of
this catalog:

www.siemens.com/industrymall

The products in this catalog can also be found in the
Interactive Catalog CA 01.

Article No.: E86060-D4001-A510-D8-7500

Please contact your local Siemens branch.

© Siemens AG 2019

The products and systems listed in this
catalog are developed and manufactured
using a certified quality management system
in accordance with EN ISO 9001:2008.

Protection, Switching, Measuring and Monitoring Devices	Air Circuit Breakers	1
	Molded Case Circuit Breakers	2
	Miniature Circuit Breakers	3
	Residual Current Protective Devices / Arc Fault Detection Devices (AFDDs)	4
	Fuse Systems	5
	Overvoltage Protection Devices	6
	Switch Disconnectors	7
	Transfer Switching Equipment and Load Transfer Switches	8
	Switching Devices	9
	Transformers, Power Supply Units and Socket Outlets	10
	Busbar Systems	11
	Measuring Devices and Power Monitoring	12
	Monitoring Devices	13
	Terminal Blocks	14
	Software	15
Switchboards and Distribution Systems	Switchboards	16
	Busbar Trunking Systems	17
	System Cubicles, System Lighting and System Air-Conditioning	18
	Power Distribution Boards / Distribution Boards	19
	Appendix	20

Opening information

Ordering notes

Overview

Ordering special versions

When ordering products that differ from the standard versions listed in the catalog, "-Z" must be added to the Article No. indicated and the required features must be specified using alphanumeric order codes or plain text.

Ordering very small quantities

When very small orders are placed, the costs associated with order processing are greater than the order value. We therefore recommend that you combine several small orders. Where this is not possible, we regret that we are obliged to make a small processing charge: for orders with a net goods value of less than € 250 we charge a € 20 supplement to cover our order processing and invoicing costs.

Explanations of Selection and ordering data

Standard delivery time (SD)

- Preferred type Preferred types are device types that can be delivered immediately ex works, i.e. they are dispatched within 24 hours.

Price units (PU)

The price unit defines the number of units, sets or meters to which the specified price applies.

Packaging size (PS)

The packaging size defines the number of units, sets or meters, for example, for outer packaging.
Only the quantity defined by the packaging size or a multiple thereof can be ordered.

Price group (PG)

Each product is allocated to a price group.

Example

5TT3400
SD: Preferred type
PG: 13C
Ordering quantity 1 unit or a multiple thereof

8US1923-5CA02
PG: 14O
Ordering quantity 10 units or a multiple thereof

8WH9000-1GA00
PG: 12X
Ordering quantity 50 units or a multiple thereof

SD	Article No.	Price per PU	PU (UNIT, SET, M)	PS*	PG
d					
►	5TT3400		1	1 unit	1BK
	8US1923-5CA02		1	10 units	1CU
	8WH9000-1GA00		100	50 units	1BT

Note:

The article numbers shown here and the specifications regarding selection and ordering data are examples only. When ordering, always use the selection and ordering data in the product chapters.

Metal surcharges/export markings

To compensate fluctuating prices of raw materials (for example silver, copper, aluminum, lead, gold, dysprosium and neodymium), surcharges are calculated on a daily basis for products containing these raw materials using the metal factor. A surcharge for the particular raw material is added to the price of a product if the basic quotations for this raw material are exceeded.

Each product's metal factor dictates for which raw materials the metal surcharges are calculated, from which quotation and with which calculation method (weight or percentage method).

An exact explanation of the metal factor can be found at: www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf

A product's export markings/metal surcharges are updated daily at www.siemens.com/industrymall.

Miniature Circuit Breakers




3/2	Introduction
3/4	5SL miniature circuit breakers
3/5	Introduction
3/7	5SL3, 4500 A
3/9	5SL6, 6000 A
3/9	5SL4, 10000 A
3/13	5SY and 5SP miniature circuit breakers
3/15	Introduction
3/17	5SY6, 6000 A
3/21	5SY4, 10000 A
3/22	5SP4, high-current, 10000 A
3/22	5SY5, universal current, 10000 A
3/24	5SY7, 15000 A
3/27	5SY8, 25000 A
3/29	5SJ6...-KS miniature circuit breakers, with plug-in terminals
3/32	5SY miniature circuit breakers, 1+N in 1 MW
3/33	Introduction
3/34	5SY30, 4500 A
3/34	5SY60, 6000 A
3/35	5ST busbar system
3/36	Additional components
3/46	Electrical components NEW
3/46	Mechanical components
3/49	Busbars
3/59	5ST standard busbars
3/59	5ST3 busbars acc. to UL 508
3/63	5ST2 distribution blocks
3/67	SIKclip wiring system
3/69	5SJ4...-HG miniature circuit breakers acc. to UL 489 and IEC, and accessories
3/80	SHU 5SP3 main miniature circuit breakers
	For further technical product information:
	Configuration Manual
	Miniature Circuit Breakers
	Article No.: 3ZW1012-5SL61-0CB1
	Siemens Industry Online Support:
	www.siemens.com/lowvoltage/product-support
	→ Entry type:
	Application example
	Certificate
	Characteristic
	Download
	FAQ
	Manual
	Product note
	Software archive
	Technical data

Miniature Circuit Breakers

Introduction

Overview

Devices	Page	Application	Standards
 5SL miniature circuit breakers	3/3	For all applications from 0.3 A to 63 A with tripping characteristics B, C and D with a rated breaking capacity of 4500 A, 6000 A and 10000 A acc. to EN 60898-1.	EN 60898-1
 5SY and 5SP miniature circuit breakers	3/13	For all applications from 0.3 A to 125 A with a rated breaking capacity of 10000 A and 15000 A acc. to EN 60898-1. Applications for universal current from 0.3 A to 63 A, version 25 kA, acc. to EN 60947-2.	EN 60898-1/-2 EN 60947-2 UL 1077 CSA 22.2 GB 10963.1/-2
 5SJ6 ...- KS miniature circuit breakers, with plug-in terminals	3/29	For socket outlet and lighting circuits in all building installations. The plug-in terminals offer easy front connection for manual insertion of conductors, which considerably reduces mounting times.	EN 60898-1
 5SY miniature circuit breakers, 1+N in 1 MW	3/32	For socket outlet and lighting circuits in all building installations where a switchable neutral conductor is required. The miniature circuit breaker 1+N saves space in the distribution board.	EN 60898-1
 Additional components	3/36	Auxiliary switches, fault signal contacts, shunt trips, undervoltage releases for higher system availability, RC units for personal safety and remote controlled mechanisms for remote switching.	
 Busbars	3/49	Busbars in 10 mm ² and 16 mm ² save space in the distribution board and time during mounting. Busbars in 18 mm ² and 25 mm ² acc. to UL 508 and CSA.	UL 508
 5SJ4 ...- .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories	3/69	Miniature circuit breakers can be used as "branch circuit protection" and are approved for the connection type "same polarity" and "opposite polarity" in the characteristics B, C and D acc. to UL 489, from 0.3 A to 63 A.	UL 489
 SHU 5SP3 main miniature circuit breakers	3/80	Voltage-independent selective main miniature circuit breakers (SHU) in the precounter area support downstream miniature circuit breakers by providing better current limitation.	DIN VDE 0641-21

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

Introduction

3

Overview

The 5SL miniature circuit breakers are intended for use up to 6 kA/10 kA. These devices have system features that are characteristic of all Siemens miniature circuit breakers.

They are also suitable for the quick and easy mounting of additional components, such as auxiliary switches and fault signal contacts.


The 5SL4 miniature circuit breakers can also be combined with shunt trips, undervoltage releases and arc fault detection devices.

To facilitate cable entry, the devices are equipped with rectangular terminals for the accommodation of pin busbars with cables up to 35 mm². The rated current range is between 0.3 A and 63 A. The 5SL miniature circuit breakers are available in characteristics B, C and D.


Benefits



- Effective touch protection when grasping and manually operating the latching slide with latch-down option.



- Easy-to-mount busbar assembly.
- Consistent bus mounting concept throughout the Siemens miniature circuit breaker range.



- Individual devices can be removed from the bus-mounted assembly without the use of tools.



- The 5SL4 miniature circuit breakers are suitable for the quick and easy mounting of arc fault detection devices, auxiliary switches, fault signal contacts, shunt trips and undervoltage releases.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

Introduction

Technical specifications

		5SL3	5SL6	5SL4
Standards		EN 60898-1		
Approvals		see chapter "Appendix"		
Tripping characteristic		B, C		
Rated voltage U_n	V AC	230/400		
Operational voltage				
• Min.	V AC/DC per pole	24		
• Max.	V AC V DC/pole	250/440 60 ¹⁾		
				60 ^{1) 2)}
Rated breaking capacity				
• I_{cn} acc. to IEC/EN 60898-1	kA AC	4.5	6	10
• I_{cu} acc. to IEC/EN 60947-2	kA AC	4.5	6	10
Insulation coordination				
• Rated insulation voltage	V AC	250/440		
• Pollution degree for overvoltage category		2/III		
• Rated impulse withstand voltage U_{imp}	kV AC	4		
Rated frequency	Hz	50/60		
Touch protection	Acc. to EN 50274	Yes		
Handle end position , sealable		Yes		
Degree of protection		IP20 with connected conductors, IP40 in the area of the handle with distribution cover		
CFC and silicone-free		Yes		
Conductor cross-sections				
• 1-wire				
- Solid ($\leq 10 \text{ mm}^2$) / stranded ($\geq 16 \text{ mm}^2$)	mm^2	0.75 ... 35		
- Finely stranded with non-insulated end sleeve	mm^2	0.75 ... 25		
- Finely stranded with insulated end sleeve	mm^2	0.75 ... 25		
- Finely stranded without end sleeve	mm^2	1 ... 35		
• 2-wire, same cross-section				
- Solid ($\leq 10 \text{ mm}^2$) / stranded ($\geq 16 \text{ mm}^2$)	mm^2	0.75 ... 10		
- Finely stranded with non-insulated end sleeve	mm^2	0.75 ... 4		
- Finely stranded with insulated end sleeve	mm^2	0.75 ... 4		
- Finely stranded without end sleeve	mm^2	1 ... 4		
• 1-wire + busbar (pin thickness 1.5 mm)				
- Solid ($\leq 10 \text{ mm}^2$) / stranded ($\geq 16 \text{ mm}^2$)	mm^2	10 ... 25		
- Finely stranded with non-insulated end sleeve	mm^2	6 ... 25		
- Finely stranded with insulated end sleeve	mm^2	6 ... 16		
Terminals	± screw (Pozidriv)	2		
• Terminal tightening torque	Nm	2.5 ... 3		
Mounting position		Any		
Service life , on average, with rated load		20000 actuations		
Storage temperature	°C	-40 ... +75, 95% humidity up to 55 °C		
Ambient temperature	°C	-25 ... +45, occasionally +55, max. 95% humidity		
		-25 ... +55, max. 95% humidity		
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles		

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.

²⁾ Exempt: Characteristic C: 0.3 ... 1 A, characteristic D: 0.3 ... 2 A.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL3, 4500 A

Overview

The 5SL miniature circuit breakers are particularly suitable for the demands of 4.5 kA and 6 kA applications in infrastructure, such as residential buildings and small commercial buildings.

Selection and ordering data

4500 3		I_n	Mounting width	SD	Characteristic B				PS	PG	SD	Characteristic C			
					Article No.	Price per PU	PU (UNIT, SET, M)					Article No.	Price per PU	PU (UNIT, SET, M)	
		A	MW ¹⁾	d	www.siemens.com/product?Article No.						d	www.siemens.com/product?Article No.			
Miniature circuit breakers 4500 A															
		1P, 230/400 V AC													
		0.3	1	--								5SL3114-7		1	1 unit 1AE
		0.5		--								5SL3105-7		1	1 unit 1AE
		1		--								5SL3101-7		1	1 unit 1AE
		1.6		--								5SL3115-7		1	1 unit 1AE
		2		--								5SL3102-7		1	1 unit 1AE
		3		--								5SL3103-7		1	1 unit 1AE
		4		--								5SL3104-7		1	1 unit 1AE
		6		5SL3106-6			1	1 unit 1AE				5SL3106-7		1	1 unit 1AE
		8		--								5SL3108-7		1	1 unit 1AE
		10		5SL3110-6			1	1 unit 1AE				5SL3110-7		1	1 unit 1AE
		13		5SL3113-6				1 unit 1AE				5SL3113-7		1	1 unit 1AE
		16		5SL3116-6			1	1 unit 1AE				5SL3116-7		1	1 unit 1AE
		20		5SL3120-6			1	1 unit 1AE				5SL3120-7		1	1 unit 1AE
		25		5SL3125-6			1	1 unit 1AE				5SL3125-7		1	1 unit 1AE
		32		5SL3132-6			1	1 unit 1AE				5SL3132-7		1	1 unit 1AE
		1P+N, 230 V AC													
		0.3	2	--								5SL3514-7		1	1 unit 1AE
		0.5		--								5SL3505-7		1	1 unit 1AE
		1		--								5SL3501-7		1	1 unit 1AE
		1.6		--								5SL3515-7		1	1 unit 1AE
		2		--								5SL3502-7		1	1 unit 1AE
		3		--								5SL3503-7		1	1 unit 1AE
		4		--								5SL3504-7		1	1 unit 1AE
		6		5SL3506-6			1	1 unit 1AE				5SL3506-7		1	1 unit 1AE
		8		--								5SL3508-7		1	1 unit 1AE
		10		5SL3510-6			1	1 unit 1AE				5SL3510-7		1	1 unit 1AE
		13		5SL3513-6				1 unit 1AE				5SL3513-7		1	1 unit 1AE
		16		5SL3516-6			1	1 unit 1AE				5SL3516-7		1	1 unit 1AE
		20		5SL3520-6			1	1 unit 1AE				5SL3520-7		1	1 unit 1AE
		25		5SL3525-6			1	1 unit 1AE				5SL3525-7		1	1 unit 1AE
		32		5SL3532-6			1	1 unit 1AE				5SL3532-7		1	1 unit 1AE
		2P, 400 V AC													
		0.3	2	--								5SL3214-7		1	1 unit 1AE
		0.5		--								5SL3205-7		1	1 unit 1AE
		1		--								5SL3201-7		1	1 unit 1AE
		1.6		--								5SL3215-7		1	1 unit 1AE
		2		--								5SL3202-7		1	1 unit 1AE
		3		--								5SL3203-7		1	1 unit 1AE
		4		--								5SL3204-7		1	1 unit 1AE
		6		5SL3206-6			1	1 unit 1AE				5SL3206-7		1	1 unit 1AE
		8		--								5SL3208-7		1	1 unit 1AE
		10		5SL3210-6			1	1 unit 1AE				5SL3210-7		1	1 unit 1AE
		13		5SL3213-6				1 unit 1AE				5SL3213-7		1	1 unit 1AE
		16		5SL3216-6			1	1 unit 1AE				5SL3216-7		1	1 unit 1AE
		20		5SL3220-6			1	1 unit 1AE				5SL3220-7		1	1 unit 1AE
		25		5SL3225-6			1	1 unit 1AE				5SL3225-7		1	1 unit 1AE
		32		5SL3232-6			1	1 unit 1AE				5SL3232-7		1	1 unit 1AE
		40		5SL3240-6			1	1 unit 1AE				5SL3240-7		1	1 unit 1AE
		50		5SL3250-6			1	1 unit 1AE				5SL3250-7		1	1 unit 1AE
		63		5SL3263-6			1	1 unit 1AE				5SL3263-7		1	1 unit 1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL3, 4500 A

4500 3		I_n	Mounting width	SD	Characteristic B				PS	PG	SD	Characteristic C				
		A	MW ¹⁾	d	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)				d	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
Miniature circuit breakers 4500 A																
	3P, 400 V AC															
	1	3	--									5SL3301-7		1	1 unit	1AE
	2		--									5SL3302-7		1	1 unit	1AE
	3		--									5SL3303-7		1	1 unit	1AE
	4		--									5SL3304-7		1	1 unit	1AE
	6		5SL3306-6			1	1 unit	1AE				5SL3306-7		1	1 unit	1AE
	10		5SL3310-6			1	1 unit	1AE				5SL3310-7		1	1 unit	1AE
	16		5SL3316-6			1	1 unit	1AE				5SL3316-7		1	1 unit	1AE
	20		5SL3320-6			1	1 unit	1AE				5SL3320-7		1	1 unit	1AE
	25		5SL3325-6			1	1 unit	1AE				5SL3325-7		1	1 unit	1AE
	32		5SL3332-6			1	1 unit	1AE				5SL3332-7		1	1 unit	1AE
	40		5SL3340-6			1	1 unit	1AE				5SL3340-7		1	1 unit	1AE
	50		5SL3350-6			1	1 unit	1AE				5SL3350-7		1	1 unit	1AE
	63		5SL3363-6			1	1 unit	1AE				5SL3363-7		1	1 unit	1AE
	3P+N, 400 V AC															
	1	4	--									5SL3601-7		1	1 unit	1AE
	2		--									5SL3602-7		1	1 unit	1AE
	3		--									5SL3603-7		1	1 unit	1AE
	4		--									5SL3604-7		1	1 unit	1AE
	6		5SL3606-6			1	1 unit	1AE				5SL3606-7		1	1 unit	1AE
	8		--									5SL3608-7		1	1 unit	1AE
	10		5SL3610-6			1	1 unit	1AE				5SL3610-7		1	1 unit	1AE
	13		5SL3613-6			1	1 unit	1AE				5SL3613-7		1	1 unit	1AE
	16		5SL3616-6			1	1 unit	1AE				5SL3616-7		1	1 unit	1AE
	20		5SL3620-6			1	1 unit	1AE				5SL3620-7		1	1 unit	1AE
	25		5SL3625-6			1	1 unit	1AE				5SL3625-7		1	1 unit	1AE
	32		5SL3632-6			1	1 unit	1AE				5SL3632-7		1	1 unit	1AE
	40		5SL3640-6			1	1 unit	1AE				5SL3640-7		1	1 unit	1AE
	50		5SL3650-6			1	1 unit	1AE				5SL3650-7		1	1 unit	1AE
	63		5SL3663-6			1	1 unit	1AE				5SL3663-7		1	1 unit	1AE
	4P, 400 V AC															
	1	4	--									5SL3401-7		1	1 unit	1AE
	2		--									5SL3402-7		1	1 unit	1AE
	3		--									5SL3403-7		1	1 unit	1AE
	4		--									5SL3404-7		1	1 unit	1AE
	6		--									5SL3406-7		1	1 unit	1AE
	10		--									5SL3410-7		1	1 unit	1AE
	13		--									5SL3413-7		1	1 unit	1AE
	16		--									5SL3416-7		1	1 unit	1AE
	20		--									5SL3420-7		1	1 unit	1AE
	25		--									5SL3425-7		1	1 unit	1AE
	32		--									5SL3432-7		1	1 unit	1AE
	40		--									5SL3440-7		1	1 unit	1AE
	50		--									5SL3450-7		1	1 unit	1AE
	63		--									5SL3463-7		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL6, 6000 A

Selection and ordering data

6000 3			I_n	Mounting width	SD	Characteristic B				Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic C		Price per PU	PU (UNIT, SET, M)	PS	PG
			A	MW ¹⁾	d									d						
Miniature circuit breakers 6000 A																				
	1P, 230/400 V AC																			
	0.3	1	--													5SL6114-7		1	1 unit	1AC
	0.5		--													5SL6105-7		1	1 unit	1AC
	1		--													5SL6101-7		1	1 unit	1AC
	1.6		--													5SL6115-7		1	1 unit	1AC
	2	NEW		5SL6102-6		1	1 unit	1AB								5SL6102-7		1	1 unit	1AC
	3		--													5SL6103-7		1	1 unit	1AC
	4	NEW		5SL6104-6		1	1 unit	1AB								5SL6104-7		1	1 unit	1AC
	6		--	5SL6106-6		1	1 unit	1AB								5SL6106-7		1	1 unit	1AC
	8		--													5SL6108-7		1	1 unit	1AC
	10		--	5SL6110-6		1	1 unit	1AB								5SL6110-7		1	1 unit	1AC
	13		--	5SL6113-6		1	1 unit	1AB								5SL6113-7		1	1 unit	1AC
	16		--	5SL6116-6		1	1 unit	1AB								5SL6116-7		1	1 unit	1AC
	20		--	5SL6120-6		1	1 unit	1AB								5SL6120-7		1	1 unit	1AC
25		--	5SL6125-6		1	1 unit	1AB								5SL6125-7		1	1 unit	1AC	
32		--	5SL6132-6		1	1 unit	1AB								5SL6132-7		1	1 unit	1AC	
40		--	5SL6140-6		1	1 unit	1AB								5SL6140-7		1	1 unit	1AC	
50		--	5SL6150-6		1	1 unit	1AB								5SL6150-7		1	1 unit	1AC	
63		--	5SL6163-6		1	1 unit	1AB								5SL6163-7		1	1 unit	1AC	
	1P+N, 230 V AC																			
	0.3	2	--													5SL6514-7		1	1 unit	1AC
	0.5		--													5SL6505-7		1	1 unit	1AC
	1		--													5SL6501-7		1	1 unit	1AC
	1.6		--													5SL6515-7		1	1 unit	1AC
	2		--													5SL6502-7		1	1 unit	1AC
	3		--													5SL6503-7		1	1 unit	1AC
	4		--													5SL6504-7		1	1 unit	1AC
	6		--	5SL6506-6		1	1 unit	1AB								5SL6506-7		1	1 unit	1AC
	8		--													5SL6508-7		1	1 unit	1AC
	10		--	5SL6510-6		1	1 unit	1AB								5SL6510-7		1	1 unit	1AC
	13		--	5SL6513-6		1	1 unit	1AB								5SL6513-7		1	1 unit	1AC
	16		--	5SL6516-6		1	1 unit	1AB								5SL6516-7		1	1 unit	1AC
	20		--	5SL6520-6		1	1 unit	1AB								5SL6520-7		1	1 unit	1AC
25		--	5SL6525-6		1	1 unit	1AB								5SL6525-7		1	1 unit	1AC	
32		--	5SL6532-6		1	1 unit	1AB								5SL6532-7		1	1 unit	1AC	
40		--	5SL6540-6		1	1 unit	1AB								5SL6540-7		1	1 unit	1AC	
50		--	5SL6550-6		1	1 unit	1AB								5SL6550-7		1	1 unit	1AC	
63		--	5SL6563-6		1	1 unit	1AB								5SL6563-7		1	1 unit	1AC	
	2P, 400 V AC																			
	0.3	2	--													5SL6214-7		1	1 unit	1AC
	0.5		--													5SL6205-7		1	1 unit	1AC
	1		--													5SL6201-7		1	1 unit	1AC
	1.6		--													5SL6215-7		1	1 unit	1AC
	2		--													5SL6202-7		1	1 unit	1AC
	3		--													5SL6203-7		1	1 unit	1AC
	4		--													5SL6204-7		1	1 unit	1AC
	6		--	5SL6206-6		1	1 unit	1AB								5SL6206-7		1	1 unit	1AC
	8		--													5SL6208-7		1	1 unit	1AC
	10		--	5SL6210-6		1	1 unit	1AB								5SL6210-7		1	1 unit	1AC
	13		--	5SL6213-6		1	1 unit	1AB								5SL6213-7		1	1 unit	1AC
	16		--	5SL6216-6		1	1 unit	1AB								5SL6216-7		1	1 unit	1AC
	20		--	5SL6220-6		1	1 unit	1AB								5SL6220-7		1	1 unit	1AC
	25		--	5SL6225-6		1	1 unit	1AB								5SL6225-7		1	1 unit	1AC
	32		--	5SL6232-6		1	1 unit	1AB								5SL6232-7		1	1 unit	1AC
	40		--	5SL6240-6		1	1 unit	1AB								5SL6240-7		1	1 unit	1AC
	50		--	5SL6250-6		1	1 unit	1AB								5SL6250-7		1	1 unit	1AC
	63		--	5SL6263-6		1	1 unit	1AB								5SL6263-7		1	1 unit	1AC

1) 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL6, 6000 A

6000 3		I_n	Mounting width	SD	Characteristic B Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic C Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d						d					
Miniature circuit breakers 6000 A															
	3P, 400 V AC														
	0.3	3	--								5SL6314-7		1	1 unit	1AC
	0.5		--								5SL6305-7		1	1 unit	1AC
	1		--								5SL6301-7		1	1 unit	1AC
	1.6		--								5SL6315-7		1	1 unit	1AC
	2		--								5SL6302-7		1	1 unit	1AC
	3		--								5SL6303-7		1	1 unit	1AC
	4		--								5SL6304-7		1	1 unit	1AC
	6		5SL6306-6		1	1 unit	1AB				5SL6306-7		1	1 unit	1AC
	8		--								5SL6308-7		1	1 unit	1AC
	10		5SL6310-6		1	1 unit	1AB				5SL6310-7		1	1 unit	1AC
	13		5SL6313-6		1	1 unit	1AB				5SL6313-7		1	1 unit	1AC
	16		5SL6316-6		1	1 unit	1AB				5SL6316-7		1	1 unit	1AC
	20		5SL6320-6		1	1 unit	1AB				5SL6320-7		1	1 unit	1AC
	25		5SL6325-6		1	1 unit	1AB				5SL6325-7		1	1 unit	1AC
	32		5SL6332-6		1	1 unit	1AB				5SL6332-7		1	1 unit	1AC
	40		5SL6340-6		1	1 unit	1AB				5SL6340-7		1	1 unit	1AC
	50		5SL6350-6		1	1 unit	1AB				5SL6350-7		1	1 unit	1AC
	63		5SL6363-6		1	1 unit	1AB				5SL6363-7		1	1 unit	1AC
	3P+N, 400 V AC														
	0.3	4	--								5SL6614-7		1	1 unit	1AC
	0.5		--								5SL6605-7		1	1 unit	1AC
	1		--								5SL6601-7		1	1 unit	1AC
	1.6		--								5SL6615-7		1	1 unit	1AC
	2		--								5SL6602-7		1	1 unit	1AC
	3		--								5SL6603-7		1	1 unit	1AC
	4		--								5SL6604-7		1	1 unit	1AC
	6		5SL6606-6		1	1 unit	1AB				5SL6606-7		1	1 unit	1AC
	8		--								5SL6608-7		1	1 unit	1AC
	10		5SL6610-6		1	1 unit	1AB				5SL6610-7		1	1 unit	1AC
	13		5SL6613-6		1	1 unit	1AB				5SL6613-7		1	1 unit	1AC
	16		5SL6616-6		1	1 unit	1AB				5SL6616-7		1	1 unit	1AC
	20		5SL6620-6		1	1 unit	1AB				5SL6620-7		1	1 unit	1AC
	25		5SL6625-6		1	1 unit	1AB				5SL6625-7		1	1 unit	1AC
	32		5SL6632-6		1	1 unit	1AB				5SL6632-7		1	1 unit	1AC
	40		5SL6640-6		1	1 unit	1AB				5SL6640-7		1	1 unit	1AC
	50		5SL6650-6		1	1 unit	1AB				5SL6650-7		1	1 unit	1AC
	63		5SL6663-6		1	1 unit	1AB				5SL6663-7		1	1 unit	1AC
	4P, 400 V AC														
	0.3	4	--								5SL6414-7		1	1 unit	1AC
	0.5		--								5SL6405-7		1	1 unit	1AC
	1		--								5SL6401-7		1	1 unit	1AC
	1.6		--								5SL6415-7		1	1 unit	1AC
	2		--								5SL6402-7		1	1 unit	1AC
	3		--								5SL6403-7		1	1 unit	1AC
	4		--								5SL6404-7		1	1 unit	1AC
	6		5SL6406-6		1	1 unit	1AB				5SL6406-7		1	1 unit	1AC
	8		--								5SL6408-7		1	1 unit	1AC
	10		5SL6410-6		1	1 unit	1AB				5SL6410-7		1	1 unit	1AC
	13		5SL6413-6		1	1 unit	1AB				5SL6413-7		1	1 unit	1AC
	16		5SL6416-6		1	1 unit	1AB				5SL6416-7		1	1 unit	1AC
	20		5SL6420-6		1	1 unit	1AB				5SL6420-7		1	1 unit	1AC
	25		5SL6425-6		1	1 unit	1AB				5SL6425-7		1	1 unit	1AC
	32		5SL6432-6		1	1 unit	1AB				5SL6432-7		1	1 unit	1AC
	40		5SL6440-6		1	1 unit	1AB				5SL6440-7		1	1 unit	1AC
	50		5SL6450-6		1	1 unit	1AB				5SL6450-7		1	1 unit	1AC
	63		5SL6463-6		1	1 unit	1AB				5SL6463-7		1	1 unit	1AC

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL4, 10000 A

Selection and ordering data

10000 3			I_n	Mounting width	SD	Characteristic B	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG
			A	MW ¹⁾	d	Article No. www.siemens.com/ product?Article No.					d	Article No. www.siemens.com/ product?Article No.				
Miniature circuit breakers 10000 A																
	1P, 230/400 V AC															
	0.3	1				---						5SL4114-7		1	1 unit	1AC
	0.5					---						5SL4105-7		1	1 unit	1AC
	1					5SL4101-6		1	1 unit	1AB		5SL4101-7		1	1 unit	1AC
	1.6					---						5SL4115-7		1	1 unit	1AC
	2					5SL4102-6		1	1 unit	1AB		5SL4102-7		1	1 unit	1AC
	3					5SL4103-6		1	1 unit	1AB		5SL4103-7		1	1 unit	1AC
	4					5SL4104-6		1	1 unit	1AB		5SL4104-7		1	1 unit	1AC
	6					5SL4106-6		1	1 unit	1AB		5SL4106-7		1	1 unit	1AC
	8					5SL4108-6		1	1 unit	1AB		5SL4108-7		1	1 unit	1AC
	10				►	5SL4110-6		1	1 unit	1AB		5SL4110-7		1	1 unit	1AC
	13					5SL4113-6		1	1 unit	1AB		5SL4113-7		1	1 unit	1AC
	16				►	5SL4116-6		1	1 unit	1AB	►	5SL4116-7		1	1 unit	1AC
	20					5SL4120-6		1	1 unit	1AB		5SL4120-7		1	1 unit	1AC
	25					5SL4125-6		1	1 unit	1AB		5SL4125-7		1	1 unit	1AC
	32					5SL4132-6		1	1 unit	1AB		5SL4132-7		1	1 unit	1AC
40					5SL4140-6		1	1 unit	1AB		5SL4140-7		1	1 unit	1AC	
50					5SL4150-6		1	1 unit	1AB		5SL4150-7		1	1 unit	1AC	
63					5SL4163-6		1	1 unit	1AB		5SL4163-7		1	1 unit	1AC	
	1P+N, 230 V AC															
	0.3	2				---						5SL4514-7		1	1 unit	1AC
	0.5					---						5SL4505-7		1	1 unit	1AC
	1					5SL4501-6		1	1 unit	1AB		5SL4501-7		1	1 unit	1AC
	1.6					---						5SL4515-7		1	1 unit	1AC
	2					5SL4502-6		1	1 unit	1AB		5SL4502-7		1	1 unit	1AC
	3					5SL4503-6		1	1 unit	1AB		5SL4503-7		1	1 unit	1AC
	4					5SL4504-6		1	1 unit	1AB		5SL4504-7		1	1 unit	1AC
	6					5SL4506-6		1	1 unit	1AB		5SL4506-7		1	1 unit	1AC
	8					5SL4508-6		1	1 unit	1AB		5SL4508-7		1	1 unit	1AC
	10					5SL4510-6		1	1 unit	1AB	►	5SL4510-7		1	1 unit	1AC
	13					5SL4513-6		1	1 unit	1AB		5SL4513-7		1	1 unit	1AC
	16					5SL4516-6		1	1 unit	1AB		5SL4516-7		1	1 unit	1AC
	20					5SL4520-6		1	1 unit	1AB		5SL4520-7		1	1 unit	1AC
	25					5SL4525-6		1	1 unit	1AB		5SL4525-7		1	1 unit	1AC
	32					5SL4532-6		1	1 unit	1AB		5SL4532-7		1	1 unit	1AC
40					5SL4540-6		1	1 unit	1AB		5SL4540-7		1	1 unit	1AC	
50					5SL4550-6		1	1 unit	1AB		5SL4550-7		1	1 unit	1AC	
63					5SL4563-6		1	1 unit	1AB		5SL4563-7		1	1 unit	1AC	
	2P, 400 V AC															
	0.3	2				---						5SL4214-7		1	1 unit	1AC
	0.5					---						5SL4205-7		1	1 unit	1AC
	1					5SL4201-6		1	1 unit	1AB		5SL4201-7		1	1 unit	1AC
	1.6					---						5SL4215-7		1	1 unit	1AC
	2					5SL4202-6		1	1 unit	1AB		5SL4202-7		1	1 unit	1AC
	3					5SL4203-6		1	1 unit	1AB		5SL4203-7		1	1 unit	1AC
	4					5SL4204-6		1	1 unit	1AB		5SL4204-7		1	1 unit	1AC
	6					5SL4206-6		1	1 unit	1AB		5SL4206-7		1	1 unit	1AC
	8					5SL4208-6		1	1 unit	1AB		5SL4208-7		1	1 unit	1AC
	10					5SL4210-6		1	1 unit	1AB		5SL4210-7		1	1 unit	1AC
	13					5SL4213-6		1	1 unit	1AB		5SL4213-7		1	1 unit	1AC
	16					5SL4216-6		1	1 unit	1AB		5SL4216-7		1	1 unit	1AC
	20					5SL4220-6		1	1 unit	1AB		5SL4220-7		1	1 unit	1AC
	25					5SL4225-6		1	1 unit	1AB		5SL4225-7		1	1 unit	1AC
	32					5SL4232-6		1	1 unit	1AB		5SL4232-7		1	1 unit	1AC
	40					5SL4240-6		1	1 unit	1AB		5SL4240-7		1	1 unit	1AC
	50					5SL4250-6		1	1 unit	1AB		5SL4250-7		1	1 unit	1AC
	63					5SL4263-6		1	1 unit	1AB		5SL4263-7		1	1 unit	1AC

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL4, 10000 A

10000 3		DVE	I_n	Mounting width	SD	Characteristic B	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG
A		MW ¹⁾	d			Article No. www.siemens.com/product?Article No.					d	Article No. www.siemens.com/product?Article No.				
Miniature circuit breakers 10000 A																
	3P, 400 V AC															
	0.3	3	--									5SL4314-7		1	1 unit	1AC
	0.5	--										5SL4305-7		1	1 unit	1AC
	1		5SL4301-6		1	1 unit	1AB					5SL4301-7		1	1 unit	1AC
	1.6		--									5SL4315-7		1	1 unit	1AC
	2		5SL4302-6		1	1 unit	1AB					5SL4302-7		1	1 unit	1AC
	3		5SL4303-6		1	1 unit	1AB					5SL4303-7		1	1 unit	1AC
	4		5SL4304-6		1	1 unit	1AB					5SL4304-7		1	1 unit	1AC
	6		5SL4306-6		1	1 unit	1AB					5SL4306-7		1	1 unit	1AC
	8		5SL4308-6		1	1 unit	1AB					5SL4308-7		1	1 unit	1AC
	10		5SL4310-6		1	1 unit	1AB					5SL4310-7		1	1 unit	1AC
	13		5SL4313-6		1	1 unit	1AB					5SL4313-7		1	1 unit	1AC
	16		5SL4316-6		1	1 unit	1AB					5SL4316-7		1	1 unit	1AC
	20		5SL4320-6		1	1 unit	1AB					5SL4320-7		1	1 unit	1AC
	25		5SL4325-6		1	1 unit	1AB					5SL4325-7		1	1 unit	1AC
	32		5SL4332-6		1	1 unit	1AB					5SL4332-7		1	1 unit	1AC
	40		5SL4340-6		1	1 unit	1AB					5SL4340-7		1	1 unit	1AC
50		5SL4350-6		1	1 unit	1AB					5SL4350-7		1	1 unit	1AC	
63		5SL4363-6		1	1 unit	1AB					5SL4363-7		1	1 unit	1AC	
	3P+N, 400 V AC															
	0.3	4	--									5SL4614-7		1	1 unit	1AC
	0.5	--										5SL4605-7		1	1 unit	1AC
	1		5SL4601-6		1	1 unit	1AB					5SL4601-7		1	1 unit	1AC
	1.6		--									5SL4615-7		1	1 unit	1AC
	2		5SL4602-6		1	1 unit	1AB					5SL4602-7		1	1 unit	1AC
	3		5SL4603-6		1	1 unit	1AB					5SL4603-7		1	1 unit	1AC
	4		5SL4604-6		1	1 unit	1AB					5SL4604-7		1	1 unit	1AC
	6		5SL4606-6		1	1 unit	1AB					5SL4606-7		1	1 unit	1AC
	8		5SL4608-6		1	1 unit	1AB					5SL4608-7		1	1 unit	1AC
	10		5SL4610-6		1	1 unit	1AB					5SL4610-7		1	1 unit	1AC
	13		5SL4613-6		1	1 unit	1AB					5SL4613-7		1	1 unit	1AC
	16		5SL4616-6		1	1 unit	1AB					5SL4616-7		1	1 unit	1AC
	20		5SL4620-6		1	1 unit	1AB					5SL4620-7		1	1 unit	1AC
	25		5SL4625-6		1	1 unit	1AB					5SL4625-7		1	1 unit	1AC
	32		5SL4632-6		1	1 unit	1AB					5SL4632-7		1	1 unit	1AC
	40		5SL4640-6		1	1 unit	1AB					5SL4640-7		1	1 unit	1AC
50		5SL4650-6		1	1 unit	1AB					5SL4650-7		1	1 unit	1AC	
63		5SL4663-6		1	1 unit	1AB					5SL4663-7		1	1 unit	1AC	
	4P, 400 V AC															
	0.3	4	--									5SL4414-7		1	1 unit	1AC
	0.5	--										5SL4405-7		1	1 unit	1AC
	1		5SL4401-6		1	1 unit	1AB					5SL4401-7		1	1 unit	1AC
	1.6		--									5SL4415-7		1	1 unit	1AC
	2		5SL4402-6		1	1 unit	1AB					5SL4402-7		1	1 unit	1AC
	3		5SL4403-6		1	1 unit	1AB					5SL4403-7		1	1 unit	1AC
	4		5SL4404-6		1	1 unit	1AB					5SL4404-7		1	1 unit	1AC
	6		5SL4406-6		1	1 unit	1AB					5SL4406-7		1	1 unit	1AC
	8		5SL4408-6		1	1 unit	1AB					5SL4408-7		1	1 unit	1AC
	10		5SL4410-6		1	1 unit	1AB					5SL4410-7		1	1 unit	1AC
	13		5SL4413-6		1	1 unit	1AB					5SL4413-7		1	1 unit	1AC
	16		5SL4416-6		1	1 unit	1AB					5SL4416-7		1	1 unit	1AC
	20		5SL4420-6		1	1 unit	1AB					5SL4420-7		1	1 unit	1AC
	25		5SL4425-6		1	1 unit	1AB					5SL4425-7		1	1 unit	1AC
	32		5SL4432-6		1	1 unit	1AB					5SL4432-7		1	1 unit	1AC
	40		5SL4440-6		1	1 unit	1AB					5SL4440-7		1	1 unit	1AC
50		5SL4450-6		1	1 unit	1AB					5SL4450-7		1	1 unit	1AC	
63		5SL4463-6		1	1 unit	1AB					5SL4463-7		1	1 unit	1AC	

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL4, 10000 A

 	I_n	Mounting width	SD	Characteristic D Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d					
Miniature circuit breakers 10000 A								
	1P, 230/400 V AC	1						
	0.3			5SL4114-8		1	1 unit	1AA
	0.5			5SL4105-8		1	1 unit	1AA
	1			5SL4101-8		1	1 unit	1AA
	1.6			5SL4115-8		1	1 unit	1AA
	2			5SL4102-8		1	1 unit	1AA
	3			5SL4103-8		1	1 unit	1AA
	4			5SL4104-8		1	1 unit	1AA
	6			5SL4106-8		1	1 unit	1AA
	8			5SL4108-8		1	1 unit	1AA
	10			5SL4110-8		1	1 unit	1AA
	13			5SL4113-8		1	1 unit	1AA
	16			5SL4116-8		1	1 unit	1AA
	20			5SL4120-8		1	1 unit	1AA
	25			5SL4125-8		1	1 unit	1AA
	32			5SL4132-8		1	1 unit	1AA
	40			5SL4140-8		1	1 unit	1AA
	50			5SL4150-8		1	1 unit	1AA
	63			5SL4163-8		1	1 unit	1AA
	1P+N, 230 V AC	2						
	0.3			5SL4514-8		1	1 unit	1AA
	0.5			5SL4505-8		1	1 unit	1AA
	1			5SL4501-8		1	1 unit	1AA
	1.6			5SL4515-8		1	1 unit	1AA
	2			5SL4502-8		1	1 unit	1AA
	3			5SL4503-8		1	1 unit	1AA
	4			5SL4504-8		1	1 unit	1AA
	6			5SL4506-8		1	1 unit	1AA
	8			5SL4508-8		1	1 unit	1AA
	10			5SL4510-8		1	1 unit	1AA
	13			5SL4513-8		1	1 unit	1AA
	16			5SL4516-8		1	1 unit	1AA
	20			5SL4520-8		1	1 unit	1AA
	25			5SL4525-8		1	1 unit	1AA
	32			5SL4532-8		1	1 unit	1AA
	40			5SL4540-8		1	1 unit	1AA
	50			5SL4550-8		1	1 unit	1AA
	63			5SL4563-8		1	1 unit	1AA
	2P, 400 V AC	2						
	0.3			5SL4214-8		1	1 unit	1AA
	0.5			5SL4205-8		1	1 unit	1AA
	1			5SL4201-8		1	1 unit	1AA
	1.6			5SL4215-8		1	1 unit	1AA
	2			5SL4202-8		1	1 unit	1AA
	3			5SL4203-8		1	1 unit	1AA
	4			5SL4204-8		1	1 unit	1AA
	6			5SL4206-8		1	1 unit	1AA
	8			5SL4208-8		1	1 unit	1AA
	10			5SL4210-8		1	1 unit	1AA
	13			5SL4213-8		1	1 unit	1AA
	16			5SL4216-8		1	1 unit	1AA
	20			5SL4220-8		1	1 unit	1AA
	25			5SL4225-8		1	1 unit	1AA
	32			5SL4232-8		1	1 unit	1AA
	40			5SL4240-8		1	1 unit	1AA
	50			5SL4250-8		1	1 unit	1AA
	63			5SL4263-8		1	1 unit	1AA

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SL Miniature Circuit Breakers

5SL4, 10000 A

10000 3 DVE	I_n	Mounting width	SD	Characteristic D Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d					
Miniature circuit breakers 10000 A								
	3P, 400 V AC	3						
	0.3			5SL4314-8	1	1 unit	1AA	
	0.5			5SL4305-8	1	1 unit	1AA	
	1			5SL4301-8	1	1 unit	1AA	
	1.6			5SL4315-8	1	1 unit	1AA	
	2			5SL4302-8	1	1 unit	1AA	
	3			5SL4303-8	1	1 unit	1AA	
	4			5SL4304-8	1	1 unit	1AA	
	6			5SL4306-8	1	1 unit	1AA	
	8			5SL4308-8	1	1 unit	1AA	
	10			5SL4310-8	1	1 unit	1AA	
	13			5SL4313-8	1	1 unit	1AA	
	16			5SL4316-8	1	1 unit	1AA	
	20			5SL4320-8	1	1 unit	1AA	
	25			5SL4325-8	1	1 unit	1AA	
32	5SL4332-8	1	1 unit	1AA				
40	5SL4340-8	1	1 unit	1AA				
50	5SL4350-8	1	1 unit	1AA				
63	5SL4363-8	1	1 unit	1AA				
	3P+N, 400 V AC	4						
	0.3			5SL4614-8	1	1 unit	1AA	
	0.5			5SL4605-8	1	1 unit	1AA	
	1			5SL4601-8	1	1 unit	1AA	
	1.6			5SL4615-8	1	1 unit	1AA	
	2			5SL4602-8	1	1 unit	1AA	
	3			5SL4603-8	1	1 unit	1AA	
	4			5SL4604-8	1	1 unit	1AA	
	6			5SL4606-8	1	1 unit	1AA	
	8			5SL4608-8	1	1 unit	1AA	
	10			5SL4610-8	1	1 unit	1AA	
	13			5SL4613-8	1	1 unit	1AA	
	16			5SL4616-8	1	1 unit	1AA	
	20			5SL4620-8	1	1 unit	1AA	
	25			5SL4625-8	1	1 unit	1AA	
32	5SL4632-8	1	1 unit	1AA				
40	5SL4640-8	1	1 unit	1AA				
50	5SL4650-8	1	1 unit	1AA				
63	5SL4663-8	1	1 unit	1AA				
	4P, 400 V AC	4						
	0.3			5SL4414-8	1	1 unit	1AA	
	0.5			5SL4405-8	1	1 unit	1AA	
	1			5SL4401-8	1	1 unit	1AA	
	1.6			5SL4415-8	1	1 unit	1AA	
	2			5SL4402-8	1	1 unit	1AA	
	3			5SL4403-8	1	1 unit	1AA	
	4			5SL4404-8	1	1 unit	1AA	
	6			5SL4406-8	1	1 unit	1AA	
	8			5SL4408-8	1	1 unit	1AA	
	10			5SL4410-8	1	1 unit	1AA	
	13			5SL4413-8	1	1 unit	1AA	
	16			5SL4416-8	1	1 unit	1AA	
	20			5SL4420-8	1	1 unit	1AA	
	25			5SL4425-8	1	1 unit	1AA	
32	5SL4432-8	1	1 unit	1AA				
40	5SL4440-8	1	1 unit	1AA				
50	5SL4450-8	1	1 unit	1AA				
63	5SL4463-8	1	1 unit	1AA				

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

Introduction

Overview

Miniature circuit breakers are used to protect systems and installations in buildings and for industrial applications.

Used in industrial applications and plant engineering, miniature-circuit breakers can be supplemented with additional components, such as auxiliary switches, fault signal contacts, shunt trips, undervoltage releases, remote controlled mechanisms, RC units, and arc fault detection devices.

The devices are approved for worldwide use according to IEC standards for power supply systems up to 250/440 V AC. 72 V DC per pole is permitted in DC systems.


For North America, there is an additional approval according to UL 1077 for use as "supplementary protectors" in systems up to 480/277 V AC. For use in ship building, the devices also have numerous certifications according to shipping classifications BV, DNV, GL and LRS. For information on this, [see chapter "Appendix" in "Standards and Approvals"](#).

3


Benefits



- Optional top or bottom infeed as the terminals are identical
- Clear and visible conductor connection in front of the rear busbar facilitates controls
- The conductor is easily inserted into the terminal thanks to the large and easily accessible wiring space



- Quick and easy manual removal of miniature circuit breakers from the busbar assembly, for example if connections need to be changed
- Time-saving replacement of parts as busbars no longer need to be freed from adjacent devices



- Double terminal chambers permit accommodation of 2 wires of different cross-sections.



- The 5SY miniature circuit breakers are ideal for the quick and easy mounting of auxiliary switches and fault signal contacts. Captive metal brackets on the additional components ensure the quick and easy mounting of devices on the miniature circuit breakers without the need for tools.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

Introduction

Technical specifications

		5SY6	5SY4	5SY7	5SY8	5SY5	5SP4
Standards		EN 60898-1 EN 60947-2	EN 60898-1 EN 60947-2	EN 60898-1 EN 60947-2	EN 60947-2	EN 60898-2	EN 60898-1
Approvals		see chapter "Appendix"					
Rated voltage U_n	V AC V DC	230/400 --	230/400 --	230/400 --	230/400 --	230/400 220/440/ 880 ⁵⁾	230/400 --
Operational voltage							
	Min. V AC/DC/pole	24	24	24	24	24	24
Acc. to EN 60898-1/-2 and EN 60947-2	Max. V DC/pole	72 ⁴⁾	72 ⁴⁾	72 ⁴⁾	72 ⁴⁾	250	72
	Max. V AC	250/440	250/440	250/440	250/440	250/440	250/440
Breaking capacity¹⁾							
• I_{cn} acc. to IEC/EN 60898-1	kA AC	6	10	15	--	10	10
• I_{cn} acc. to IEC/EN 60898-2	kA DC	10	10	15	--	10	10
• I_{cu} acc. to IEC/EN 60947-2	kA AC kA DC	30 ... 10 ¹⁾ 15	35 ... 10 ¹⁾ 15	50 ... 15 ¹⁾ 15	70 ... 20 ¹⁾ 15	35 ... 10 ¹⁾ 15	10 15
Acc. to UL 1077 and CSA C22.2 No. 235	SC	supplementary protector, OC, FW 0, OL 0, TC 3 at 50 °C U2: see Certificate of Compliance					
Insulation coordination							
• Rated insulation voltage	V AC V DC/pole	250/440 --	--	--	--	250	--
• Rated impulse withstand voltage U_{imp}	kV AC	4	--	--	--	--	--
Pollution degree for overvoltage category		3/III ³⁾					
Rated frequency	Hz	50/60					
Touch protection	Acc. to EN 50274	Yes					
Handle end position, sealable		Yes					
Degree of protection	Acc. to EN 60529	IP20 with connected conductors, IP40 in the area of the handle with distribution cover					
CFC and silicone-free		Yes					
Mounting							
• Snap-on fixing system		Yes					--
• Standard mounting rail and screw fixing		--					Yes
Terminals	± screw (Pozidriv)	2					
• Tunnel terminals at both ends		--					Yes
• Combined terminals at both ends		Yes					--
• Terminal tightening torque	Nm lb-in	2.5 ... 3.5 max. 22 ... 26					2.5 ... 3.5 22 ... 31
Conductor cross-sections							
• Solid and stranded	mm ²	0.75 ... 35					4 ... 50
• Finely stranded, with end sleeve	mm ²	0.75 ... 25					1.5 ... 35
• AWG conductors (Cu 60/75 °C $I_n \leq 40$ A; 60 °C $I_n > 40$ A)	AWG	14 ... 4					14 ... 2
Mains connection							
• AC		Any					
• DC		Any					Any
Mounting position		Any					
Service life		20000					
On average, with rated load	Actuations Actuations	10000, for 5SY5 at 40 A, 50 A and 63 A					
Ambient temperature	°C	-25 ... +55, max. 95% humidity -40 ... +70 for 5SY4, 5SY5 and 5SY7, 95% humidity up to 55 °C					
Storage temperature	°C	-40 ... +75, 95% humidity up to 55 °C					
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles					
Shock	Acc. to IEC 60068-2-27	m/s ² 150 at 11 ms half-sine					
Resistance to vibrations	Acc. to IEC 60068-2-6	m/s ² 50 at 25 ... 150 Hz and 60 at 35 Hz (4 s)					

¹⁾ For detailed information, see Configuration Manual "Miniature Circuit Breakers" (www.siemens.com/lowvoltage/manuals).

²⁾ Ensure compliance with the specified polarity when connecting DC.

³⁾ 5SY54.. 4-pole, degree of pollution 2 for overvoltage category II.

⁴⁾ Exempt: C/D 0.3 A ... 0.5 A

⁵⁾ 5SY54.. 4-pole 880 V is not a standardized voltage acc. to EN 60898-1, suitable for max. 1000 V DC if the four poles are connected in series.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY6, 6000 A

Selection and ordering data

6000 3		I_n	Mounting width	SD	Characteristic B				PU (UNIT, SET, M)	PS	PG	SD	Characteristic C				PU (UNIT, SET, M)	PS	PG
					Article No. www.siemens.com/product?Article No.	Price per PU							Article No. www.siemens.com/product?Article No.	Price per PU					
		A	MW ¹⁾	d								d							
Miniature circuit breakers 6000 A																			
	1P, 230/400 V AC																		
		0.3	1	--									5SY6114-7				1	1 unit	1AC
		0.5		--									5SY6105-7				1	1 unit	1AC
		1		--									5SY6101-7				1	1 unit	1AC
		1.6		--									5SY6115-7				1	1 unit	1AC
		2		5SY6102-6				1	1 unit	1AB			5SY6102-7				1	1 unit	1AC
		3		--									5SY6103-7				1	1 unit	1AC
		4		5SY6104-6				1	1 unit	1AB			5SY6104-7				1	1 unit	1AC
		5		--									5SY6111-7				1	1 unit	1AC
		6		5SY6106-6				1	1 unit	1AB			5SY6106-7				1	1 unit	1AC
		8		--									5SY6108-7				1	1 unit	1AC
		10		5SY6110-6				1	1 unit	1AB			5SY6110-7				1	1 unit	1AC
		13		5SY6113-6				1	1 unit	1AB			5SY6113-7				1	1 unit	1AC
		15		--									5SY6118-7				1	1 unit	1AC
		16		5SY6116-6				1	1 unit	1AB			5SY6116-7				1	1 unit	1AC
		20		5SY6120-6				1	1 unit	1AB			5SY6120-7				1	1 unit	1AC
		25		5SY6125-6				1	1 unit	1AB			5SY6125-7				1	1 unit	1AC
		30		--									5SY6130-7				1	1 unit	1AC
		32		5SY6132-6				1	1 unit	1AB			5SY6132-7				1	1 unit	1AC
		40		5SY6140-6				1	1 unit	1AB			5SY6140-7				1	1 unit	1AC
		50		5SY6150-6				1	1 unit	1AB			5SY6150-7				1	1 unit	1AC
		63		5SY6163-6				1	1 unit	1AB			5SY6163-7				1	1 unit	1AC
	1P+N, 230 V AC																		
		0.3	2	--									5SY6514-7				1	1 unit	1AC
		0.5		--									5SY6505-7				1	1 unit	1AC
		1		--									5SY6501-7				1	1 unit	1AC
		1.6		--									5SY6515-7				1	1 unit	1AC
		2		--									5SY6502-7				1	1 unit	1AC
		3		--									5SY6503-7				1	1 unit	1AC
		4		--									5SY6504-7				1	1 unit	1AC
		6		5SY6506-6				1	1 unit	1AB			5SY6506-7				1	1 unit	1AC
		8		--									5SY6508-7				1	1 unit	1AC
		10		5SY6510-6				1	1 unit	1AB			5SY6510-7				1	1 unit	1AC
		13		5SY6513-6				1	1 unit	1AB			5SY6513-7				1	1 unit	1AC
		16		5SY6516-6				1	1 unit	1AB			5SY6516-7				1	1 unit	1AC
		20		5SY6520-6				1	1 unit	1AB			5SY6520-7				1	1 unit	1AC
		25		5SY6525-6				1	1 unit	1AB			5SY6525-7				1	1 unit	1AC
		32		5SY6532-6				1	1 unit	1AB			5SY6532-7				1	1 unit	1AC
		40		5SY6540-6				1	1 unit	1AB			5SY6540-7				1	1 unit	1AC
		50		5SY6550-6				1	1 unit	1AB			5SY6550-7				1	1 unit	1AC
		63		5SY6563-6				1	1 unit	1AB			5SY6563-7				1	1 unit	1AC
	2P, 400 V AC																		
		0.3	2	--									5SY6214-7				1	1 unit	1AC
		0.5		--									5SY6205-7				1	1 unit	1AC
		1		--									5SY6201-7				1	1 unit	1AC
		1.6		--									5SY6215-7				1	1 unit	1AC
		2		--									5SY6202-7				1	1 unit	1AC
		3		--									5SY6203-7				1	1 unit	1AC
		4		--									5SY6204-7				1	1 unit	1AC
		5		--									5SY6211-7				1	1 unit	1AC
		6		5SY6206-6				1	1 unit	1AB			5SY6206-7				1	1 unit	1AC
		8		--									5SY6208-7				1	1 unit	1AC
		10		5SY6210-6				1	1 unit	1AB			5SY6210-7				1	1 unit	1AC
		13		5SY6213-6				1	1 unit	1AB			5SY6213-7				1	1 unit	1AC
		15		--									5SY6218-7				1	1 unit	1AC
		16		5SY6216-6				1	1 unit	1AB			5SY6216-7				1	1 unit	1AC
		20		5SY6220-6				1	1 unit	1AB			5SY6220-7				1	1 unit	1AC
		25		5SY6225-6				1	1 unit	1AB			5SY6225-7				1	1 unit	1AC
		30		--									5SY6230-7				1	1 unit	1AC
		32		5SY6232-6				1	1 unit	1AB			5SY6232-7				1	1 unit	1AC
		40		5SY6240-6				1	1 unit	1AB			5SY6240-7				1	1 unit	1AC
		50		5SY6250-6				1	1 unit	1AB			5SY6250-7				1	1 unit	1AC
		63		5SY6263-6				1	1 unit	1AB			5SY6263-7				1	1 unit	1AC

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY6, 6000 A

6000			I_n	Mounting width	SD	Characteristic B				PU (UNIT, SET, M)	PS	PG	SD	Characteristic C			
3		Article No. www.siemens.com/product?Article No.				Price per PU			Article No. www.siemens.com/product?Article No.					Price per PU	PU (UNIT, SET, M)	PS	PG
Miniature circuit breakers 6000 A																	
	3P, 400 V AC																
	0.3	3	--												1	1 unit	1AC
	0.5		--												1	1 unit	1AC
	1		--												1	1 unit	1AC
	1.6		--												1	1 unit	1AC
	2		--												1	1 unit	1AC
	3		--												1	1 unit	1AC
	4		--												1	1 unit	1AC
	5		--												1	1 unit	1AC
	6		5SY6306-6				1	1 unit	1AB						1	1 unit	1AC
	8		--												1	1 unit	1AC
	10		5SY6310-6				1	1 unit	1AB						1	1 unit	1AC
	13		5SY6313-6				1	1 unit	1AB						1	1 unit	1AC
	15		--												1	1 unit	1AC
	16		5SY6316-6				1	1 unit	1AB						1	1 unit	1AC
	20		5SY6320-6				1	1 unit	1AB						1	1 unit	1AC
	25		5SY6325-6				1	1 unit	1AB						1	1 unit	1AC
30		--												1	1 unit	1AC	
32		5SY6332-6				1	1 unit	1AB						1	1 unit	1AC	
40		5SY6340-6				1	1 unit	1AB						1	1 unit	1AC	
50		5SY6350-6				1	1 unit	1AB						1	1 unit	1AC	
63		5SY6363-6				1	1 unit	1AB						1	1 unit	1AC	
	3P+N, 400 V AC																
	0.3	4	--												1	1 unit	1AC
	0.5		--												1	1 unit	1AC
	1		--												1	1 unit	1AC
	1.6		--												1	1 unit	1AC
	2		--												1	1 unit	1AC
	3		--												1	1 unit	1AC
	4		--												1	1 unit	1AC
	6		5SY6606-6				1	1 unit	1AB						1	1 unit	1AC
	8		--												1	1 unit	1AC
	10		5SY6610-6				1	1 unit	1AB						1	1 unit	1AC
	13		5SY6613-6				1	1 unit	1AB						1	1 unit	1AC
	16		5SY6616-6				1	1 unit	1AB						1	1 unit	1AC
	20		5SY6620-6				1	1 unit	1AB						1	1 unit	1AC
	25		5SY6625-6				1	1 unit	1AB						1	1 unit	1AC
	32		5SY6632-6				1	1 unit	1AB						1	1 unit	1AC
	40		5SY6640-6				1	1 unit	1AB						1	1 unit	1AC
50		5SY6650-6				1	1 unit	1AB						1	1 unit	1AC	
63		5SY6663-6				1	1 unit	1AB						1	1 unit	1AC	
	4P, 400 V AC																
	0.3	4	--												1	1 unit	1AC
	0.5		--												1	1 unit	1AC
	1		--												1	1 unit	1AC
	1.6		--												1	1 unit	1AC
	2		--												1	1 unit	1AC
	3		--												1	1 unit	1AC
	4		--												1	1 unit	1AC
	6		5SY6406-6				1	1 unit	1AB						1	1 unit	1AC
	8		--												1	1 unit	1AC
	10		5SY6410-6				1	1 unit	1AB						1	1 unit	1AC
	13		5SY6413-6				1	1 unit	1AB						1	1 unit	1AC
	16		5SY6416-6				1	1 unit	1AB						1	1 unit	1AC
	20		5SY6420-6				1	1 unit	1AB						1	1 unit	1AC
	25		5SY6425-6				1	1 unit	1AB						1	1 unit	1AC
	32		5SY6432-6				1	1 unit	1AB						1	1 unit	1AC
	40		5SY6440-6				1	1 unit	1AB						1	1 unit	1AC
50		5SY6450-6				1	1 unit	1AB						1	1 unit	1AC	
63		5SY6463-6				1	1 unit	1AB						1	1 unit	1AC	

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY4, 10000 A

Selection and ordering data

10000 3		I _n	Mounting width	SD	Characteristic A					PS	PG	SD	Characteristic B					PS	PG
					Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)						Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)				
		A	MW ¹⁾	d								d							
Miniature circuit breakers 10000 A																			
	1P, 230/400 V AC																		
	0.5	1			5SY4105-5		1	1 unit	1AA				--						
	1				5SY4101-5		1	1 unit	1AA				--						
	1.6				5SY4115-5		1	1 unit	1AA				--						
	2				5SY4102-5		1	1 unit	1AA				5SY4102-6		1	1 unit	1AB		
	3				5SY4103-5		1	1 unit	1AA				--						
	4				5SY4104-5		1	1 unit	1AA				5SY4104-6		1	1 unit	1AB		
	6				5SY4106-5		1	1 unit	1AA				5SY4106-6		1	1 unit	1AB		
	8				5SY4108-5		1	1 unit	1AA				--						
	10				5SY4110-5		1	1 unit	1AA				5SY4110-6		1	1 unit	1AB		
	13				5SY4113-5		1	1 unit	1AA				5SY4113-6		1	1 unit	1AB		
	16				5SY4116-5		1	1 unit	1AA				5SY4116-6		1	1 unit	1AB		
	20				5SY4120-5		1	1 unit	1AA				5SY4120-6		1	1 unit	1AB		
	25				5SY4125-5		1	1 unit	1AA				5SY4125-6		1	1 unit	1AB		
	32				5SY4132-5		1	1 unit	1AA				5SY4132-6		1	1 unit	1AB		
	40				5SY4140-5		1	1 unit	1AA				5SY4140-6		1	1 unit	1AB		
	50				5SY4150-5		1	1 unit	1AA				5SY4150-6		1	1 unit	1AB		
	63				5SY4163-5		1	1 unit	1AA				5SY4163-6		1	1 unit	1AB		
	80				--								5SY4180-6		1	1 unit	1AB		
	1P+N, 230 V AC																		
	1	2			5SY4501-5		1	1 unit	1AA				--						
	1.6				5SY4515-5		1	1 unit	1AA				--						
	2				5SY4502-5		1	1 unit	1AA				--						
	3				5SY4503-5		1	1 unit	1AA				--						
	4				5SY4504-5		1	1 unit	1AA				--						
	6				5SY4506-5		1	1 unit	1AA				5SY4506-6		1	1 unit	1AB		
	8				5SY4508-5		1	1 unit	1AA				--						
	10				5SY4510-5		1	1 unit	1AA				5SY4510-6		1	1 unit	1AB		
	13				5SY4513-5		1	1 unit	1AA				5SY4513-6		1	1 unit	1AB		
	16				5SY4516-5		1	1 unit	1AA				5SY4516-6		1	1 unit	1AB		
	20				5SY4520-5		1	1 unit	1AA				5SY4520-6		1	1 unit	1AB		
	25				5SY4525-5		1	1 unit	1AA				5SY4525-6		1	1 unit	1AB		
	32				5SY4532-5		1	1 unit	1AA				5SY4532-6		1	1 unit	1AB		
	40				5SY4540-5		1	1 unit	1AA				5SY4540-6		1	1 unit	1AB		
	50				5SY4550-5		1	1 unit	1AA				5SY4550-6		1	1 unit	1AB		
	63				5SY4563-5		1	1 unit	1AA				5SY4563-6		1	1 unit	1AB		
	2P, 400 V AC																		
	0.5	2			5SY4205-5		1	1 unit	1AA				--						
	1				5SY4201-5		1	1 unit	1AA				--						
	1.6				5SY4215-5		1	1 unit	1AA				--						
	2				5SY4202-5		1	1 unit	1AA				--						
	3				5SY4203-5		1	1 unit	1AA				--						
	4				5SY4204-5		1	1 unit	1AA				--						
	6				5SY4206-5		1	1 unit	1AA				5SY4206-6		1	1 unit	1AB		
	8				5SY4208-5		1	1 unit	1AA				--						
	10				5SY4210-5		1	1 unit	1AA				5SY4210-6		1	1 unit	1AB		
	13				5SY4213-5		1	1 unit	1AA				5SY4213-6		1	1 unit	1AB		
	16				5SY4216-5		1	1 unit	1AA				5SY4216-6		1	1 unit	1AB		
	20				5SY4220-5		1	1 unit	1AA				5SY4220-6		1	1 unit	1AB		
	25				5SY4225-5		1	1 unit	1AA				5SY4225-6		1	1 unit	1AB		
	32				5SY4232-5		1	1 unit	1AA				5SY4232-6		1	1 unit	1AB		
	40				5SY4240-5		1	1 unit	1AA				5SY4240-6		1	1 unit	1AB		
	50				5SY4250-5		1	1 unit	1AA				5SY4250-6		1	1 unit	1AB		
	63				5SY4263-5		1	1 unit	1AA				5SY4263-6		1	1 unit	1AB		
	80				--								5SY4280-6		1	1 unit	1AB		

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY4, 10000 A

10000 3		I_n	Mounting width	SD	Characteristic A				PU (UNIT, SET, M)	PS	PG	SD	Characteristic B				
					Article No. www.siemens.com/ product?Article No.	Price per PU							Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
A	MW ¹⁾	d										d					
Miniature circuit breakers 10000 A																	
	3P, 400 V AC																
	0.5	3	5SY4305-5					1	1 unit	1AA	--						
	1		5SY4301-5					1	1 unit	1AA	--						
	1.6		5SY4315-5					1	1 unit	1AA	--						
	2		5SY4302-5					1	1 unit	1AA	--						
	3		5SY4303-5					1	1 unit	1AA	--						
	4		5SY4304-5					1	1 unit	1AA	--						
	6		5SY4306-5					1	1 unit	1AA	5SY4306-6			1	1 unit	1AB	
	8		5SY4308-5					1	1 unit	1AA	--						
	10		5SY4310-5					1	1 unit	1AA	5SY4310-6			1	1 unit	1AB	
	13		5SY4313-5					1	1 unit	1AA	5SY4313-6			1	1 unit	1AB	
	16		5SY4316-5					1	1 unit	1AA	5SY4316-6			1	1 unit	1AB	
	20		5SY4320-5					1	1 unit	1AA	5SY4320-6			1	1 unit	1AB	
	25		5SY4325-5					1	1 unit	1AA	5SY4325-6			1	1 unit	1AB	
	32		5SY4332-5					1	1 unit	1AA	5SY4332-6			1	1 unit	1AB	
	40		5SY4340-5					1	1 unit	1AA	5SY4340-6			1	1 unit	1AB	
50		5SY4350-5					1	1 unit	1AA	5SY4350-6			1	1 unit	1AB		
63		5SY4363-5					1	1 unit	1AA	5SY4363-6			1	1 unit	1AB		
80		--								5SY4380-6			1	1 unit	1AB		
	3P+N, 400 V AC																
	1	4	5SY4601-5					1	1 unit	1AA	--						
	1.6		5SY4615-5					1	1 unit	1AA	--						
	2		5SY4602-5					1	1 unit	1AA	--						
	3		5SY4603-5					1	1 unit	1AA	--						
	4		5SY4604-5					1	1 unit	1AA	--						
	6		5SY4606-5					1	1 unit	1AA	5SY4606-6			1	1 unit	1AB	
	8		5SY4608-5					1	1 unit	1AA	--						
	10		5SY4610-5					1	1 unit	1AA	5SY4610-6			1	1 unit	1AB	
	13		5SY4613-5					1	1 unit	1AA	5SY4613-6			1	1 unit	1AB	
	16		5SY4616-5					1	1 unit	1AA	5SY4616-6			1	1 unit	1AB	
	20		5SY4620-5					1	1 unit	1AA	5SY4620-6			1	1 unit	1AB	
	25		5SY4625-5					1	1 unit	1AA	5SY4625-6			1	1 unit	1AB	
	32		5SY4632-5					1	1 unit	1AA	5SY4632-6			1	1 unit	1AB	
	40		5SY4640-5					1	1 unit	1AA	5SY4640-6			1	1 unit	1AB	
	50		5SY4650-5					1	1 unit	1AA	5SY4650-6			1	1 unit	1AB	
63		5SY4663-5					1	1 unit	1AA	5SY4663-6			1	1 unit	1AB		
	4P, 400 V AC																
	1	4	5SY4401-5					1	1 unit	1AA	--						
	1.6		5SY4415-5					1	1 unit	1AA	--						
	2		5SY4402-5					1	1 unit	1AA	--						
	3		5SY4403-5					1	1 unit	1AA	--						
	4		5SY4404-5					1	1 unit	1AA	--						
	6		5SY4406-5					1	1 unit	1AA	5SY4406-6			1	1 unit	1AB	
	8		5SY4408-5					1	1 unit	1AA	--						
	10		5SY4410-5					1	1 unit	1AA	5SY4410-6			1	1 unit	1AB	
	13		5SY4413-5					1	1 unit	1AA	5SY4413-6			1	1 unit	1AB	
	16		5SY4416-5					1	1 unit	1AA	5SY4416-6			1	1 unit	1AB	
	20		5SY4420-5					1	1 unit	1AA	5SY4420-6			1	1 unit	1AB	
	25		5SY4425-5					1	1 unit	1AA	5SY4425-6			1	1 unit	1AB	
	32		5SY4432-5					1	1 unit	1AA	5SY4432-6			1	1 unit	1AB	
	40		5SY4440-5					1	1 unit	1AA	5SY4440-6			1	1 unit	1AB	
	50		5SY4450-5					1	1 unit	1AA	5SY4450-6			1	1 unit	1AB	
63		5SY4463-5					1	1 unit	1AA	5SY4463-6			1	1 unit	1AB		
80		--								5SY4480-6			1	1 unit	1AB		

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY4, 10000 A

10000 3		I_n	Mounting width	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic D	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d	Article No. www.siemens.com/ product?Article No.					d	Article No. www.siemens.com/ product?Article No.				
Miniature circuit breakers 10000 A															
	1P, 230/400 V AC														
	0.3	1			5SY4114-7		1	1 unit	1AC		5SY4114-8		1	1 unit	1AA
	0.5				5SY4105-7		1	1 unit	1AC		5SY4105-8		1	1 unit	1AA
	1				5SY4101-7		1	1 unit	1AC		5SY4101-8		1	1 unit	1AA
	1.6				5SY4115-7		1	1 unit	1AC		5SY4115-8		1	1 unit	1AA
	2		▶		5SY4102-7		1	1 unit	1AC		5SY4102-8		1	1 unit	1AA
	3				5SY4103-7		1	1 unit	1AC		5SY4103-8		1	1 unit	1AA
	4		▶		5SY4104-7		1	1 unit	1AC		5SY4104-8		1	1 unit	1AA
	5				5SY4111-7		1	1 unit	1AC		--				
	6		▶		5SY4106-7		1	1 unit	1AC		5SY4106-8		1	1 unit	1AA
	8				5SY4108-7		1	1 unit	1AC		5SY4108-8		1	1 unit	1AA
	10		▶		5SY4110-7		1	1 unit	1AC		5SY4110-8		1	1 unit	1AA
	13				5SY4113-7		1	1 unit	1AC		5SY4113-8		1	1 unit	1AA
	15				5SY4118-7		1	1 unit	1AC		--				
	16		▶		5SY4116-7		1	1 unit	1AC		5SY4116-8		1	1 unit	1AA
	20				5SY4120-7		1	1 unit	1AC		5SY4120-8		1	1 unit	1AA
	25				5SY4125-7		1	1 unit	1AC		5SY4125-8		1	1 unit	1AA
	30				5SY4130-7		1	1 unit	1AC		--				
	32				5SY4132-7		1	1 unit	1AC		5SY4132-8		1	1 unit	1AA
	35				5SY4135-7		1	1 unit	1AC		--				
	40				5SY4140-7		1	1 unit	1AC		5SY4140-8		1	1 unit	1AA
	45				5SY4145-7		1	1 unit	1AC		--				
	50				5SY4150-7		1	1 unit	1AC		5SY4150-8		1	1 unit	1AA
	60				5SY4160-7		1	1 unit	1AC		--				
	63				5SY4163-7		1	1 unit	1AC		5SY4163-8		1	1 unit	1AA
	80				5SY4180-7		1	1 unit	1AC		--				
	1P+N, 230 V AC														
	0.3	2			5SY4514-7		1	1 unit	1AC		5SY4514-8		1	1 unit	1AA
	0.5				5SY4505-7		1	1 unit	1AC		5SY4505-8		1	1 unit	1AA
	1				5SY4501-7		1	1 unit	1AC		5SY4501-8		1	1 unit	1AA
	1.6				5SY4515-7		1	1 unit	1AC		5SY4515-8		1	1 unit	1AA
	2				5SY4502-7		1	1 unit	1AC		5SY4502-8		1	1 unit	1AA
	3				5SY4503-7		1	1 unit	1AC		5SY4503-8		1	1 unit	1AA
	4				5SY4504-7		1	1 unit	1AC		5SY4504-8		1	1 unit	1AA
	6				5SY4506-7		1	1 unit	1AC		5SY4506-8		1	1 unit	1AA
	8				5SY4508-7		1	1 unit	1AC		5SY4508-8		1	1 unit	1AA
	10				5SY4510-7		1	1 unit	1AC		5SY4510-8		1	1 unit	1AA
	13				5SY4513-7		1	1 unit	1AC		5SY4513-8		1	1 unit	1AA
	16				5SY4516-7		1	1 unit	1AC		5SY4516-8		1	1 unit	1AA
	20				5SY4520-7		1	1 unit	1AC		5SY4520-8		1	1 unit	1AA
	25				5SY4525-7		1	1 unit	1AC		5SY4525-8		1	1 unit	1AA
	32				5SY4532-7		1	1 unit	1AC		5SY4532-8		1	1 unit	1AA
	40				5SY4540-7		1	1 unit	1AC		5SY4540-8		1	1 unit	1AA
	50				5SY4550-7		1	1 unit	1AC		5SY4550-8		1	1 unit	1AA
	63				5SY4563-7		1	1 unit	1AC		5SY4563-8		1	1 unit	1AA
	80				5SY4580-7		1	1 unit	1AC		--				
	2P, 400 V AC														
	0.3	2			5SY4214-7		1	1 unit	1AC		5SY4214-8		1	1 unit	1AA
	0.5				5SY4205-7		1	1 unit	1AC		5SY4205-8		1	1 unit	1AA
	1				5SY4201-7		1	1 unit	1AC		5SY4201-8		1	1 unit	1AA
	1.6				5SY4215-7		1	1 unit	1AC		5SY4215-8		1	1 unit	1AA
	2		▶		5SY4202-7		1	1 unit	1AC		5SY4202-8		1	1 unit	1AA
	3				5SY4203-7		1	1 unit	1AC		5SY4203-8		1	1 unit	1AA
	4				5SY4204-7		1	1 unit	1AC		5SY4204-8		1	1 unit	1AA
	5				5SY4211-7		1	1 unit	1AC		--				
	6		▶		5SY4206-7		1	1 unit	1AC		5SY4206-8		1	1 unit	1AA
	8				5SY4208-7		1	1 unit	1AC		5SY4208-8		1	1 unit	1AA
	10		▶		5SY4210-7		1	1 unit	1AC		5SY4210-8		1	1 unit	1AA
	13				5SY4213-7		1	1 unit	1AC		5SY4213-8		1	1 unit	1AA
	15				5SY4218-7		1	1 unit	1AC		--				
	16		▶		5SY4216-7		1	1 unit	1AC		5SY4216-8		1	1 unit	1AA
	20				5SY4220-7		1	1 unit	1AC		5SY4220-8		1	1 unit	1AA
	25				5SY4225-7		1	1 unit	1AC		5SY4225-8		1	1 unit	1AA
	30				5SY4230-7		1	1 unit	1AC		--				
	32				5SY4232-7		1	1 unit	1AC		5SY4232-8		1	1 unit	1AA
	35				5SY4235-7		1	1 unit	1AC		--				
	40				5SY4240-7		1	1 unit	1AC		5SY4240-8		1	1 unit	1AA
	45				5SY4245-7		1	1 unit	1AC		--				
	50				5SY4250-7		1	1 unit	1AC		5SY4250-8		1	1 unit	1AA
	60				5SY4260-7		1	1 unit	1AC		--				
	63				5SY4263-7		1	1 unit	1AC		5SY4263-8		1	1 unit	1AA
	80				5SY4280-7		1	1 unit	1AC		--				

Minimum order quantity (PS) or a multiple thereof can be ordered.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY4, 10000 A

10000 3		I_n	Mounting width	SD	Characteristic C Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic D Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d						d					
Miniature circuit breakers 10000 A															
	3P, 400 V AC														
	0.3	3		5SY4314-7		1	1 unit	1AC		5SY4314-8		1	1 unit	1AA	
	0.5			5SY4305-7		1	1 unit	1AC		5SY4305-8		1	1 unit	1AA	
	1			5SY4301-7		1	1 unit	1AC		5SY4301-8		1	1 unit	1AA	
	1.6			5SY4315-7		1	1 unit	1AC		5SY4315-8		1	1 unit	1AA	
	2			5SY4302-7		1	1 unit	1AC		5SY4302-8		1	1 unit	1AA	
	3			5SY4303-7		1	1 unit	1AC		5SY4303-8		1	1 unit	1AA	
	4			5SY4304-7		1	1 unit	1AC		5SY4304-8		1	1 unit	1AA	
	5			5SY4311-7		1	1 unit	1AC		--					
	6			5SY4306-7		1	1 unit	1AC		5SY4306-8		1	1 unit	1AA	
	8			5SY4308-7		1	1 unit	1AC		5SY4308-8		1	1 unit	1AA	
	10		▶	5SY4310-7		1	1 unit	1AC		5SY4310-8		1	1 unit	1AA	
	13			5SY4313-7		1	1 unit	1AC		5SY4313-8		1	1 unit	1AA	
	15			5SY4318-7		1	1 unit	1AC		--					
	16		▶	5SY4316-7		1	1 unit	1AC		5SY4316-8		1	1 unit	1AA	
	20			5SY4320-7		1	1 unit	1AC		5SY4320-8		1	1 unit	1AA	
	25			5SY4325-7		1	1 unit	1AC		5SY4325-8		1	1 unit	1AA	
	30			5SY4330-7		1	1 unit	1AC		--					
	32		▶	5SY4332-7		1	1 unit	1AC		5SY4332-8		1	1 unit	1AA	
	35			5SY4335-7		1	1 unit	1AC		--					
	40			5SY4340-7		1	1 unit	1AC		5SY4340-8		1	1 unit	1AA	
	45			5SY4345-7		1	1 unit	1AC		--					
	50			5SY4350-7		1	1 unit	1AC		5SY4350-8		1	1 unit	1AA	
	60			5SY4360-7		1	1 unit	1AC		--					
	63			5SY4363-7		1	1 unit	1AC		5SY4363-8		1	1 unit	1AA	
	80			5SY4380-7		1	1 unit	1AC		--					
	3P+N, 400 V AC														
	0.3	4		5SY4614-7		1	1 unit	1AC		5SY4614-8		1	1 unit	1AA	
	0.5			5SY4605-7		1	1 unit	1AC		5SY4605-8		1	1 unit	1AA	
	1			5SY4601-7		1	1 unit	1AC		5SY4601-8		1	1 unit	1AA	
	1.6			5SY4615-7		1	1 unit	1AC		5SY4615-8		1	1 unit	1AA	
	2			5SY4602-7		1	1 unit	1AC		5SY4602-8		1	1 unit	1AA	
	3			5SY4603-7		1	1 unit	1AC		5SY4603-8		1	1 unit	1AA	
	4			5SY4604-7		1	1 unit	1AC		5SY4604-8		1	1 unit	1AA	
	6			5SY4606-7		1	1 unit	1AC		5SY4606-8		1	1 unit	1AA	
	8			5SY4608-7		1	1 unit	1AC		5SY4608-8		1	1 unit	1AA	
	10			5SY4610-7		1	1 unit	1AC		5SY4610-8		1	1 unit	1AA	
	13			5SY4613-7		1	1 unit	1AC		5SY4613-8		1	1 unit	1AA	
	16			5SY4616-7		1	1 unit	1AC		5SY4616-8		1	1 unit	1AA	
	20			5SY4620-7		1	1 unit	1AC		5SY4620-8		1	1 unit	1AA	
	25			5SY4625-7		1	1 unit	1AC		5SY4625-8		1	1 unit	1AA	
	32			5SY4632-7		1	1 unit	1AC		5SY4632-8		1	1 unit	1AA	
	40			5SY4640-7		1	1 unit	1AC		5SY4640-8		1	1 unit	1AA	
	50			5SY4650-7		1	1 unit	1AC		5SY4650-8		1	1 unit	1AA	
	63			5SY4663-7		1	1 unit	1AC		5SY4663-8		1	1 unit	1AA	
	80			5SY4680-7		1	1 unit	1AC		--					
	4P, 400 V AC														
	0.3	4		5SY4414-7		1	1 unit	1AC		5SY4414-8		1	1 unit	1AA	
	0.5			5SY4405-7		1	1 unit	1AC		5SY4405-8		1	1 unit	1AA	
	1			5SY4401-7		1	1 unit	1AC		5SY4401-8		1	1 unit	1AA	
	1.6			5SY4415-7		1	1 unit	1AC		5SY4415-8		1	1 unit	1AA	
	2			5SY4402-7		1	1 unit	1AC		5SY4402-8		1	1 unit	1AA	
	3			5SY4403-7		1	1 unit	1AC		5SY4403-8		1	1 unit	1AA	
	4			5SY4404-7		1	1 unit	1AC		5SY4404-8		1	1 unit	1AA	
	6			5SY4406-7		1	1 unit	1AC		5SY4406-8		1	1 unit	1AA	
	8			5SY4408-7		1	1 unit	1AC		5SY4408-8		1	1 unit	1AA	
	10			5SY4410-7		1	1 unit	1AC		5SY4410-8		1	1 unit	1AA	
	13			5SY4413-7		1	1 unit	1AC		5SY4413-8		1	1 unit	1AA	
	16			5SY4416-7		1	1 unit	1AC		5SY4416-8		1	1 unit	1AA	
	20			5SY4420-7		1	1 unit	1AC		5SY4420-8		1	1 unit	1AA	
	25			5SY4425-7		1	1 unit	1AC		5SY4425-8		1	1 unit	1AA	
	32			5SY4432-7		1	1 unit	1AC		5SY4432-8		1	1 unit	1AA	
	40			5SY4440-7		1	1 unit	1AC		5SY4440-8		1	1 unit	1AA	
	50			5SY4450-7		1	1 unit	1AC		5SY4450-8		1	1 unit	1AA	
	63			5SY4463-7		1	1 unit	1AC		5SY4463-8		1	1 unit	1AA	
	80			5SY4480-7		1	1 unit	1AC		--					

¹⁾ 1 MW (modular width) = 18 mm.


Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SP4, high-current, 10000 A

Selection and ordering data

10000		I_n	Mounting width	SD	Characteristic B	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d	Article No. www.siemens.com/product?Article No.				
Miniature circuit breakers 10000 A, high-current									
	1P, 230/400 V AC								
	80	1.5			5SP4180-6		1	1 unit	1AB
	100				5SP4191-6		1	1 unit	1AB
	125				5SP4192-6		1	1 unit	1AB
	2P, 400 V AC								
	80	3			5SP4280-6		1	1 unit	1AB
	100				5SP4291-6		1	1 unit	1AB
	125				5SP4292-6		1	1 unit	1AB
	3P, 400 V AC								
	80	4.5			5SP4380-6		1	1 unit	1AB
	100				5SP4391-6		1	1 unit	1AB
	125				5SP4392-6		1	1 unit	1AB
	4P, 400 V AC								
	80	6			5SP4480-6		1	1 unit	1AB
	100				5SP4491-6		1	1 unit	1AB
	125				5SP4492-6		1	1 unit	1AB

10000		I_n	Mounting width	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic D	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d	Article No. www.siemens.com/product?Article No.					d	Article No. www.siemens.com/product?Article No.				
Miniature circuit breakers 10000 A, high-current															
	1P, 230/400 V AC														
	80	1.5			5SP4180-7		1	1 unit	1AC		5SP4180-8		1	1 unit	1AA
	100				5SP4191-7		1	1 unit	1AC		5SP4191-8		1	1 unit	1AA
	125				5SP4192-7		1	1 unit	1AC		--				
	2P, 400 V AC														
	80	3			5SP4280-7		1	1 unit	1AC		5SP4280-8		1	1 unit	1AA
	100				5SP4291-7		1	1 unit	1AC		5SP4291-8		1	1 unit	1AA
	125				5SP4292-7		1	1 unit	1AC		--				
	3P, 400 V AC														
	80	4.5			5SP4380-7		1	1 unit	1AC		5SP4380-8		1	1 unit	1AA
	100				5SP4391-7		1	1 unit	1AC		5SP4391-8		1	1 unit	1AA
	125				5SP4392-7		1	1 unit	1AC		--				
	4P, 400 V AC														
	80	6			5SP4480-7		1	1 unit	1AC		5SP4480-8		1	1 unit	1AA
	100				5SP4491-7		1	1 unit	1AC		5SP4491-8		1	1 unit	1AA
	125				5SP4492-7		1	1 unit	1AC		--				

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY5, universal current, 10000 A

Selection and ordering data

10000 3 	I_n	Mounting width	SD	Characteristic B					SD	Characteristic C				
				Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG		Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d						d					
Miniature circuit breakers 10000 A, universal current														
	1P, 230/400 V AC, 220 V DC													
	0.3	1		--						5SY5114-7		1	1 unit	1AC
	0.5			--						5SY5105-7		1	1 unit	1AC
	1			--						5SY5101-7		1	1 unit	1AC
	1.6			--						5SY5115-7		1	1 unit	1AC
	2			5SY5102-6		1	1 unit	1AB		5SY5102-7		1	1 unit	1AC
	3			--						5SY5103-7		1	1 unit	1AC
	4			5SY5104-6		1	1 unit	1AB		5SY5104-7		1	1 unit	1AC
	6			5SY5106-6		1	1 unit	1AB		5SY5106-7		1	1 unit	1AC
	8			--						5SY5108-7		1	1 unit	1AC
	10			5SY5110-6		1	1 unit	1AB		5SY5110-7		1	1 unit	1AC
	13			5SY5113-6		1	1 unit	1AB		5SY5113-7		1	1 unit	1AC
	16			5SY5116-6		1	1 unit	1AB		5SY5116-7		1	1 unit	1AC
	20			5SY5120-6		1	1 unit	1AB		5SY5120-7		1	1 unit	1AC
	25			5SY5125-6		1	1 unit	1AB		5SY5125-7		1	1 unit	1AC
	32			5SY5132-6		1	1 unit	1AB		5SY5132-7		1	1 unit	1AC
	40			5SY5140-6		1	1 unit	1AB		5SY5140-7		1	1 unit	1AC
	50			5SY5150-6		1	1 unit	1AB		5SY5150-7		1	1 unit	1AC
	63			5SY5163-6		1	1 unit	1AB		5SY5163-7		1	1 unit	1AC
	2P, 400 V AC, 440 V DC													
	0.3	2		--						5SY5214-7		1	1 unit	1AC
	0.5			--						5SY5205-7		1	1 unit	1AC
	1			--						5SY5201-7		1	1 unit	1AC
	1.6			--						5SY5215-7		1	1 unit	1AC
	2			--						5SY5202-7		1	1 unit	1AC
	3			--						5SY5203-7		1	1 unit	1AC
	4			--						5SY5204-7		1	1 unit	1AC
	6			5SY5206-6		1	1 unit	1AB ▶		5SY5206-7		1	1 unit	1AC
	8			--						5SY5208-7		1	1 unit	1AC
	10			5SY5210-6		1	1 unit	1AB		5SY5210-7		1	1 unit	1AC
	13			5SY5213-6		1	1 unit	1AB		5SY5213-7		1	1 unit	1AC
	16			5SY5216-6		1	1 unit	1AB		5SY5216-7		1	1 unit	1AC
	20			5SY5220-6		1	1 unit	1AB		5SY5220-7		1	1 unit	1AC
	25			5SY5225-6		1	1 unit	1AB		5SY5225-7		1	1 unit	1AC
	32			5SY5232-6		1	1 unit	1AB		5SY5232-7		1	1 unit	1AC
	40			5SY5240-6		1	1 unit	1AB		5SY5240-7		1	1 unit	1AC
	50			5SY5250-6		1	1 unit	1AB		5SY5250-7		1	1 unit	1AC
	63			5SY5263-6		1	1 unit	1AB		5SY5263-7		1	1 unit	1AC

¹⁾ 1 MW (modular width) = 18 mm.

For application examples, see Configuration Manual "Miniature Circuit Breakers" (www.siemens.com/lowvoltage/manuals).

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY5, universal current, 10000 A

10000 3		D E	I_n	Mounting width	SD	Characteristic B	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG
			A	MW ¹⁾	d	Article No. www.siemens.com/ product?Article No.					d	Article No. www.siemens.com/ product?Article No.				
Miniature circuit breakers 10000 A, universal current																
	4P, 400 V AC, 880 V DC (max. 1000 V DC)															
	0.3	1	--									5SY5414-7		1	1 unit	1AC
	0.5		--									5SY5405-7		1	1 unit	1AC
	1		--									5SY5401-7		1	1 unit	1AC
	1.6		--									5SY5415-7		1	1 unit	1AC
	2		--									5SY5402-7		1	1 unit	1AC
	3		--									5SY5403-7		1	1 unit	1AC
	4		--									5SY5404-7		1	1 unit	1AC
	6		5SY5406-6				1	1 unit	1AB			5SY5406-7		1	1 unit	1AC
	8		--									5SY5408-7		1	1 unit	1AC
	10		5SY5410-6				1	1 unit	1AB			5SY5410-7		1	1 unit	1AC
	13		5SY5413-6				1	1 unit	1AB			5SY5413-7		1	1 unit	1AC
	16		5SY5416-6				1	1 unit	1AB			5SY5416-7		1	1 unit	1AC
	20		5SY5420-6				1	1 unit	1AB			5SY5420-7		1	1 unit	1AC
	25		5SY5425-6				1	1 unit	1AB			5SY5425-7		1	1 unit	1AC
32		5SY5432-6				1	1 unit	1AB			5SY5432-7		1	1 unit	1AC	
40		5SY5440-6				1	1 unit	1AB			5SY5440-7		1	1 unit	1AC	
50		5SY5450-6				1	1 unit	1AB			5SY5450-7		1	1 unit	1AC	
63		5SY5463-6				1	1 unit	1AB			5SY5463-7		1	1 unit	1AC	

¹⁾ 1 MW (modular width) = 18 mm.

Note:

The 5ST3600 or 5ST3630 busbars enable simple wiring of 4-pole miniature circuit breakers, [see page 3/59](#).

For application examples, [see Configuration Manual "Miniature Circuit Breakers"](#) (www.siemens.com/lowvoltage/manuals).

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY7, 15000 A

Selection and ordering data

15000		I_n	Mounting width	SD	Characteristic B Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
		A	MW ¹⁾	d					
Miniature circuit breakers 15000 A									
	1P, 230/400 V AC								
	6	1			5SY7106-6		1	1 unit	1AB
	10				5SY7110-6		1	1 unit	1AB
	13				5SY7113-6		1	1 unit	1AB
	16				5SY7116-6		1	1 unit	1AB
	20				5SY7120-6		1	1 unit	1AB
	25				5SY7125-6		1	1 unit	1AB
	32				5SY7132-6		1	1 unit	1AB
	40				5SY7140-6		1	1 unit	1AB
	50				5SY7150-6		1	1 unit	1AB
	63				5SY7163-6		1	1 unit	1AB
	1P+N, 230 V AC								
	6	2			5SY7506-6		1	1 unit	1AB
	10				5SY7510-6		1	1 unit	1AB
	13				5SY7513-6		1	1 unit	1AB
	16				5SY7516-6		1	1 unit	1AB
	20				5SY7520-6		1	1 unit	1AB
	25				5SY7525-6		1	1 unit	1AB
	32				5SY7532-6		1	1 unit	1AB
	40				5SY7540-6		1	1 unit	1AB
	50				5SY7550-6		1	1 unit	1AB
	63				5SY7563-6		1	1 unit	1AB
	2P, 400 V AC								
	6	2			5SY7206-6		1	1 unit	1AB
	10				5SY7210-6		1	1 unit	1AB
	13				5SY7213-6		1	1 unit	1AB
	16				5SY7216-6		1	1 unit	1AB
	20				5SY7220-6		1	1 unit	1AB
	25				5SY7225-6		1	1 unit	1AB
	32				5SY7232-6		1	1 unit	1AB
	40				5SY7240-6		1	1 unit	1AB
	50				5SY7250-6		1	1 unit	1AB
	63				5SY7263-6		1	1 unit	1AB
	3P, 400 V AC								
	6	3			5SY7306-6		1	1 unit	1AB
	10				5SY7310-6		1	1 unit	1AB
	13				5SY7313-6		1	1 unit	1AB
	16				5SY7316-6		1	1 unit	1AB
	20				5SY7320-6		1	1 unit	1AB
	25				5SY7325-6		1	1 unit	1AB
	32				5SY7332-6		1	1 unit	1AB
	40				5SY7340-6		1	1 unit	1AB
	50				5SY7350-6		1	1 unit	1AB
	63				5SY7363-6		1	1 unit	1AB
	3P+N, 400 V AC								
	6	4			5SY7606-6		1	1 unit	1AB
	10				5SY7610-6		1	1 unit	1AB
	13				5SY7613-6		1	1 unit	1AB
	16				5SY7616-6		1	1 unit	1AB
	20				5SY7620-6		1	1 unit	1AB
	25				5SY7625-6		1	1 unit	1AB
	32				5SY7632-6		1	1 unit	1AB
	40				5SY7640-6		1	1 unit	1AB
	50				5SY7650-6		1	1 unit	1AB
	63				5SY7663-6		1	1 unit	1AB
	4P, 400 V AC								
	6	4			5SY7406-6		1	1 unit	1AB
	10				5SY7410-6		1	1 unit	1AB
	13				5SY7413-6		1	1 unit	1AB
	16				5SY7416-6		1	1 unit	1AB
	20				5SY7420-6		1	1 unit	1AB
	25				5SY7425-6		1	1 unit	1AB
	32				5SY7432-6		1	1 unit	1AB
	40				5SY7440-6		1	1 unit	1AB
	50				5SY7450-6		1	1 unit	1AB
	63				5SY7463-6		1	1 unit	1AB

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY7, 15000 A

15000		I_n	Mounting width	SD	Characteristic C				PU (UNIT, SET, M)	PS	PG	SD	Characteristic D				PU (UNIT, SET, M)	PS	PG
					Article No.	Price per PU							Article No.	Price per PU					
		A	MW ¹⁾	d	www.siemens.com/product?Article No.							d	www.siemens.com/product?Article No.						
Miniature circuit breakers 15000 A																			
	1P, 230/400 V AC																		
	0.3	1			5SY7114-7				1	1 unit	1AC		5SY7114-8				1	1 unit	1AA
	0.5				5SY7105-7				1	1 unit	1AC		5SY7105-8				1	1 unit	1AA
	1				5SY7101-7				1	1 unit	1AC		5SY7101-8				1	1 unit	1AA
	1.6				5SY7115-7				1	1 unit	1AC		5SY7115-8				1	1 unit	1AA
	2				5SY7102-7				1	1 unit	1AC		5SY7102-8				1	1 unit	1AA
	3				5SY7103-7				1	1 unit	1AC		5SY7103-8				1	1 unit	1AA
	4				5SY7104-7				1	1 unit	1AC		5SY7104-8				1	1 unit	1AA
	6				5SY7106-7				1	1 unit	1AC		5SY7106-8				1	1 unit	1AA
	8				5SY7108-7				1	1 unit	1AC		5SY7108-8				1	1 unit	1AA
	10				5SY7110-7				1	1 unit	1AC		5SY7110-8				1	1 unit	1AA
	13				5SY7113-7				1	1 unit	1AC		5SY7113-8				1	1 unit	1AA
	16				5SY7116-7				1	1 unit	1AC		5SY7116-8				1	1 unit	1AA
	20				5SY7120-7				1	1 unit	1AC		5SY7120-8				1	1 unit	1AA
	25				5SY7125-7				1	1 unit	1AC		5SY7125-8				1	1 unit	1AA
	32				5SY7132-7				1	1 unit	1AC		5SY7132-8				1	1 unit	1AA
	40				5SY7140-7				1	1 unit	1AC		5SY7140-8				1	1 unit	1AA
	50				5SY7150-7				1	1 unit	1AC		5SY7150-8				1	1 unit	1AA
	63				5SY7163-7				1	1 unit	1AC		5SY7163-8				1	1 unit	1AA
	1P+N, 230 V AC																		
	0.3	2			5SY7514-7				1	1 unit	1AC		5SY7514-8				1	1 unit	1AA
	0.5				5SY7505-7				1	1 unit	1AC		5SY7505-8				1	1 unit	1AA
	1				5SY7501-7				1	1 unit	1AC		5SY7501-8				1	1 unit	1AA
	1.6				5SY7515-7				1	1 unit	1AC		5SY7515-8				1	1 unit	1AA
	2				5SY7502-7				1	1 unit	1AC		5SY7502-8				1	1 unit	1AA
	3				5SY7503-7				1	1 unit	1AC		5SY7503-8				1	1 unit	1AA
	4				5SY7504-7				1	1 unit	1AC		5SY7504-8				1	1 unit	1AA
	6				5SY7506-7				1	1 unit	1AC		5SY7506-8				1	1 unit	1AA
	8				5SY7508-7				1	1 unit	1AC		5SY7508-8				1	1 unit	1AA
	10				5SY7510-7				1	1 unit	1AC		5SY7510-8				1	1 unit	1AA
	13				5SY7513-7				1	1 unit	1AC		5SY7513-8				1	1 unit	1AA
	16				5SY7516-7				1	1 unit	1AC		5SY7516-8				1	1 unit	1AA
	20				5SY7520-7				1	1 unit	1AC		5SY7520-8				1	1 unit	1AA
	25				5SY7525-7				1	1 unit	1AC		5SY7525-8				1	1 unit	1AA
	32				5SY7532-7				1	1 unit	1AC		5SY7532-8				1	1 unit	1AA
	40				5SY7540-7				1	1 unit	1AC		5SY7540-8				1	1 unit	1AA
	50				5SY7550-7				1	1 unit	1AC		5SY7550-8				1	1 unit	1AA
	63				5SY7563-7				1	1 unit	1AC		5SY7563-8				1	1 unit	1AA
	2P, 400 V AC																		
	0.3	2			5SY7214-7				1	1 unit	1AC		5SY7214-8				1	1 unit	1AA
	0.5				5SY7205-7				1	1 unit	1AC		5SY7205-8				1	1 unit	1AA
	1				5SY7201-7				1	1 unit	1AC		5SY7201-8				1	1 unit	1AA
	1.6				5SY7215-7				1	1 unit	1AC		5SY7215-8				1	1 unit	1AA
	2				5SY7202-7				1	1 unit	1AC		5SY7202-8				1	1 unit	1AA
	3				5SY7203-7				1	1 unit	1AC		5SY7203-8				1	1 unit	1AA
	4				5SY7204-7				1	1 unit	1AC		5SY7204-8				1	1 unit	1AA
	6				5SY7206-7				1	1 unit	1AC		5SY7206-8				1	1 unit	1AA
	8				5SY7208-7				1	1 unit	1AC		5SY7208-8				1	1 unit	1AA
	10				5SY7210-7				1	1 unit	1AC		5SY7210-8				1	1 unit	1AA
	13				5SY7213-7				1	1 unit	1AC		5SY7213-8				1	1 unit	1AA
	16				5SY7216-7				1	1 unit	1AC		5SY7216-8				1	1 unit	1AA
	20				5SY7220-7				1	1 unit	1AC		5SY7220-8				1	1 unit	1AA
	25				5SY7225-7				1	1 unit	1AC		5SY7225-8				1	1 unit	1AA
	32				5SY7232-7				1	1 unit	1AC		5SY7232-8				1	1 unit	1AA
	40				5SY7240-7				1	1 unit	1AC		5SY7240-8				1	1 unit	1AA
	50				5SY7250-7				1	1 unit	1AC		5SY7250-8				1	1 unit	1AA
	63				5SY7263-7				1	1 unit	1AC		5SY7263-8				1	1 unit	1AA

1) 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY7, 15000 A

15000		I_n	Mounting width	SD	Characteristic C	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic D	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG		
		A	MW ¹⁾	d							d								
Miniature circuit breakers 15000 A																			
	3P, 400 V AC																		
	0.3	3		5SY7314-7		1	1 unit	1AC				5SY7314-8		1	1 unit	1AA			
	0.5			5SY7305-7		1	1 unit	1AC				5SY7305-8		1	1 unit	1AA			
	1			5SY7301-7		1	1 unit	1AC				5SY7301-8		1	1 unit	1AA			
	1.6			5SY7315-7		1	1 unit	1AC				5SY7315-8		1	1 unit	1AA			
	2			5SY7302-7		1	1 unit	1AC				5SY7302-8		1	1 unit	1AA			
	3			5SY7303-7		1	1 unit	1AC				5SY7303-8		1	1 unit	1AA			
	4			5SY7304-7		1	1 unit	1AC				5SY7304-8		1	1 unit	1AA			
	6			5SY7306-7		1	1 unit	1AC				5SY7306-8		1	1 unit	1AA			
	8			5SY7308-7		1	1 unit	1AC				5SY7308-8		1	1 unit	1AA			
	10			5SY7310-7		1	1 unit	1AC				5SY7310-8		1	1 unit	1AA			
	13			5SY7313-7		1	1 unit	1AC				5SY7313-8		1	1 unit	1AA			
	16			5SY7316-7		1	1 unit	1AC				5SY7316-8		1	1 unit	1AA			
	20			5SY7320-7		1	1 unit	1AC				5SY7320-8		1	1 unit	1AA			
	25			5SY7325-7		1	1 unit	1AC				5SY7325-8		1	1 unit	1AA			
	32			5SY7332-7		1	1 unit	1AC				5SY7332-8		1	1 unit	1AA			
	40			5SY7340-7		1	1 unit	1AC				5SY7340-8		1	1 unit	1AA			
	50			5SY7350-7		1	1 unit	1AC				5SY7350-8		1	1 unit	1AA			
63			5SY7363-7		1	1 unit	1AC				5SY7363-8		1	1 unit	1AA				
	3P+N, 400 V AC																		
	0.3	4		5SY7614-7		1	1 unit	1AC				5SY7614-8		1	1 unit	1AA			
	0.5			5SY7605-7		1	1 unit	1AC				5SY7605-8		1	1 unit	1AA			
	1			5SY7601-7		1	1 unit	1AC				5SY7601-8		1	1 unit	1AA			
	1.6			5SY7615-7		1	1 unit	1AC				5SY7615-8		1	1 unit	1AA			
	2			5SY7602-7		1	1 unit	1AC				5SY7602-8		1	1 unit	1AA			
	3			5SY7603-7		1	1 unit	1AC				5SY7603-8		1	1 unit	1AA			
	4			5SY7604-7		1	1 unit	1AC				5SY7604-8		1	1 unit	1AA			
	6			5SY7606-7		1	1 unit	1AC				5SY7606-8		1	1 unit	1AA			
	8			5SY7608-7		1	1 unit	1AC				5SY7608-8		1	1 unit	1AA			
	10			5SY7610-7		1	1 unit	1AC				5SY7610-8		1	1 unit	1AA			
	13			5SY7613-7		1	1 unit	1AC				5SY7613-8		1	1 unit	1AA			
	16			5SY7616-7		1	1 unit	1AC				5SY7616-8		1	1 unit	1AA			
	20			5SY7620-7		1	1 unit	1AC				5SY7620-8		1	1 unit	1AA			
	25			5SY7625-7		1	1 unit	1AC				5SY7625-8		1	1 unit	1AA			
	32			5SY7632-7		1	1 unit	1AC				5SY7632-8		1	1 unit	1AA			
	40			5SY7640-7		1	1 unit	1AC				5SY7640-8		1	1 unit	1AA			
	50			5SY7650-7		1	1 unit	1AC				5SY7650-8		1	1 unit	1AA			
63			5SY7663-7		1	1 unit	1AC				5SY7663-8		1	1 unit	1AA				
	4P, 400 V AC																		
	0.3	4		5SY7414-7		1	1 unit	1AC				5SY7414-8		1	1 unit	1AA			
	0.5			5SY7405-7		1	1 unit	1AC				5SY7405-8		1	1 unit	1AA			
	1			5SY7401-7		1	1 unit	1AC				5SY7401-8		1	1 unit	1AA			
	1.6			5SY7415-7		1	1 unit	1AC				5SY7415-8		1	1 unit	1AA			
	2			5SY7402-7		1	1 unit	1AC				5SY7402-8		1	1 unit	1AA			
	3			5SY7403-7		1	1 unit	1AC				5SY7403-8		1	1 unit	1AA			
	4			5SY7404-7		1	1 unit	1AC				5SY7404-8		1	1 unit	1AA			
	6			5SY7406-7		1	1 unit	1AC				5SY7406-8		1	1 unit	1AA			
	8			5SY7408-7		1	1 unit	1AC				5SY7408-8		1	1 unit	1AA			
	10			5SY7410-7		1	1 unit	1AC				5SY7410-8		1	1 unit	1AA			
	13			5SY7413-7		1	1 unit	1AC				5SY7413-8		1	1 unit	1AA			
	16			5SY7416-7		1	1 unit	1AC				5SY7416-8		1	1 unit	1AA			
	20			5SY7420-7		1	1 unit	1AC				5SY7420-8		1	1 unit	1AA			
	25			5SY7425-7		1	1 unit	1AC				5SY7425-8		1	1 unit	1AA			
	32			5SY7432-7		1	1 unit	1AC				5SY7432-8		1	1 unit	1AA			
	40			5SY7440-7		1	1 unit	1AC				5SY7440-8		1	1 unit	1AA			
	50			5SY7450-7		1	1 unit	1AC				5SY7450-8		1	1 unit	1AA			
63			5SY7463-7		1	1 unit	1AC				5SY7463-8		1	1 unit	1AA				

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY8, 25000 A

Selection and ordering data

			Characteristic C				Characteristic D						
I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
A	MW ¹⁾	d						d					
Miniature circuit breakers 25000 A													
	1P, 230/400 V AC												
	0.3	1	5SY8114-7		1	1 unit	1AC		5SY8114-8		1	1 unit	1AA
	0.5		5SY8105-7		1	1 unit	1AC		5SY8105-8		1	1 unit	1AA
	1		5SY8101-7		1	1 unit	1AC		5SY8101-8		1	1 unit	1AA
	1.6		5SY8115-7		1	1 unit	1AC		5SY8115-8		1	1 unit	1AA
	2		5SY8102-7		1	1 unit	1AC		5SY8102-8		1	1 unit	1AA
	3		5SY8103-7		1	1 unit	1AC		5SY8103-8		1	1 unit	1AA
	4		5SY8104-7		1	1 unit	1AC		5SY8104-8		1	1 unit	1AA
	6		5SY8106-7		1	1 unit	1AC		5SY8106-8		1	1 unit	1AA
	8		5SY8108-7		1	1 unit	1AC		5SY8108-8		1	1 unit	1AA
	10		5SY8110-7		1	1 unit	1AC		5SY8110-8		1	1 unit	1AA
	13		5SY8113-7		1	1 unit	1AC		5SY8113-8		1	1 unit	1AA
	16		5SY8116-7		1	1 unit	1AC		5SY8116-8		1	1 unit	1AA
	20		5SY8120-7		1	1 unit	1AC		5SY8120-8		1	1 unit	1AA
	25		5SY8125-7		1	1 unit	1AC		5SY8125-8		1	1 unit	1AA
	32		5SY8132-7		1	1 unit	1AC		5SY8132-8		1	1 unit	1AA
	40		5SY8140-7		1	1 unit	1AC		5SY8140-8		1	1 unit	1AA
	50		5SY8150-7		1	1 unit	1AC		5SY8150-8		1	1 unit	1AA
	63		5SY8163-7		1	1 unit	1AC		5SY8163-8		1	1 unit	1AA
	1P+N, 230 V AC												
	0.3	2	5SY8514-7		1	1 unit	1AC		5SY8514-8		1	1 unit	1AA
	0.5		5SY8505-7		1	1 unit	1AC		5SY8505-8		1	1 unit	1AA
	1		5SY8501-7		1	1 unit	1AC		5SY8501-8		1	1 unit	1AA
	1.6		5SY8515-7		1	1 unit	1AC		5SY8515-8		1	1 unit	1AA
	2		5SY8502-7		1	1 unit	1AC		5SY8502-8		1	1 unit	1AA
	3		5SY8503-7		1	1 unit	1AC		5SY8503-8		1	1 unit	1AA
	4		5SY8504-7		1	1 unit	1AC		5SY8504-8		1	1 unit	1AA
	6		5SY8506-7		1	1 unit	1AC		5SY8506-8		1	1 unit	1AA
	8		5SY8508-7		1	1 unit	1AC		5SY8508-8		1	1 unit	1AA
	10		5SY8510-7		1	1 unit	1AC		5SY8510-8		1	1 unit	1AA
	13		5SY8513-7		1	1 unit	1AC		5SY8513-8		1	1 unit	1AA
	16		5SY8516-7		1	1 unit	1AC		5SY8516-8		1	1 unit	1AA
	20		5SY8520-7		1	1 unit	1AC		5SY8520-8		1	1 unit	1AA
	25		5SY8525-7		1	1 unit	1AC		5SY8525-8		1	1 unit	1AA
	32		5SY8532-7		1	1 unit	1AC		5SY8532-8		1	1 unit	1AA
	40		5SY8540-7		1	1 unit	1AC		5SY8540-8		1	1 unit	1AA
	50		5SY8550-7		1	1 unit	1AC		5SY8550-8		1	1 unit	1AA
	63		5SY8563-7		1	1 unit	1AC		5SY8563-8		1	1 unit	1AA
	2P, 400 V AC												
	0.3	2	5SY8214-7		1	1 unit	1AC		5SY8214-8		1	1 unit	1AA
	0.5		5SY8205-7		1	1 unit	1AC		5SY8205-8		1	1 unit	1AA
	1		5SY8201-7		1	1 unit	1AC		5SY8201-8		1	1 unit	1AA
	1.6		5SY8215-7		1	1 unit	1AC		5SY8215-8		1	1 unit	1AA
	2		5SY8202-7		1	1 unit	1AC		5SY8202-8		1	1 unit	1AA
	3		5SY8203-7		1	1 unit	1AC		5SY8203-8		1	1 unit	1AA
	4		5SY8204-7		1	1 unit	1AC		5SY8204-8		1	1 unit	1AA
	6		5SY8206-7		1	1 unit	1AC		5SY8206-8		1	1 unit	1AA
	8		5SY8208-7		1	1 unit	1AC		5SY8208-8		1	1 unit	1AA
	10		5SY8210-7		1	1 unit	1AC		5SY8210-8		1	1 unit	1AA
	13		5SY8213-7		1	1 unit	1AC		5SY8213-8		1	1 unit	1AA
	16		5SY8216-7		1	1 unit	1AC		5SY8216-8		1	1 unit	1AA
	20		5SY8220-7		1	1 unit	1AC		5SY8220-8		1	1 unit	1AA
	25		5SY8225-7		1	1 unit	1AC		5SY8225-8		1	1 unit	1AA
	32		5SY8232-7		1	1 unit	1AC		5SY8232-8		1	1 unit	1AA
	40		5SY8240-7		1	1 unit	1AC		5SY8240-8		1	1 unit	1AA
	50		5SY8250-7		1	1 unit	1AC		5SY8250-8		1	1 unit	1AA
	63		5SY8263-7		1	1 unit	1AC		5SY8263-8		1	1 unit	1AA

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY and 5SP Miniature Circuit Breakers

5SY8, 25000 A


I _n	Mounting width	SD	Characteristic C				PU (UNIT, SET, M)	PS	PG	SD	Characteristic D				PU (UNIT, SET, M)	PS	PG
			Article No. www.siemens.com/product?ArticleNo.	Price per PU							Article No. www.siemens.com/product?ArticleNo.	Price per PU					
A	MW ¹⁾	d								d							
Miniature circuit breakers 25000 A																	
3P, 400 V AC																	
	0.3	3	5SY8314-7		1	1 unit	1AC				5SY8314-8		1	1 unit	1AA		
	0.5		5SY8305-7		1	1 unit	1AC				5SY8305-8		1	1 unit	1AA		
	1		5SY8301-7		1	1 unit	1AC				5SY8301-8		1	1 unit	1AA		
	1.6		5SY8315-7		1	1 unit	1AC				5SY8315-8		1	1 unit	1AA		
	2		5SY8302-7		1	1 unit	1AC				5SY8302-8		1	1 unit	1AA		
	3		5SY8303-7		1	1 unit	1AC				5SY8303-8		1	1 unit	1AA		
	4		5SY8304-7		1	1 unit	1AC				5SY8304-8		1	1 unit	1AA		
	6		5SY8306-7		1	1 unit	1AC				5SY8306-8		1	1 unit	1AA		
	8		5SY8308-7		1	1 unit	1AC				5SY8308-8		1	1 unit	1AA		
	10		5SY8310-7		1	1 unit	1AC				5SY8310-8		1	1 unit	1AA		
	13		5SY8313-7		1	1 unit	1AC				5SY8313-8		1	1 unit	1AA		
	16		5SY8316-7		1	1 unit	1AC				5SY8316-8		1	1 unit	1AA		
	20		5SY8320-7		1	1 unit	1AC				5SY8320-8		1	1 unit	1AA		
	25		5SY8325-7		1	1 unit	1AC				5SY8325-8		1	1 unit	1AA		
	32		5SY8332-7		1	1 unit	1AC				5SY8332-8		1	1 unit	1AA		
	40		5SY8340-7		1	1 unit	1AC				5SY8340-8		1	1 unit	1AA		
	50		5SY8350-7		1	1 unit	1AC				5SY8350-8		1	1 unit	1AA		
	63		5SY8363-7		1	1 unit	1AC				5SY8363-8		1	1 unit	1AA		
3P+N, 400 V AC																	
	0.3	4	5SY8614-7		1	1 unit	1AC				5SY8614-8		1	1 unit	1AA		
	0.5		5SY8605-7		1	1 unit	1AC				5SY8605-8		1	1 unit	1AA		
	1		5SY8601-7		1	1 unit	1AC				5SY8601-8		1	1 unit	1AA		
	1.6		5SY8615-7		1	1 unit	1AC				5SY8615-8		1	1 unit	1AA		
	2		5SY8602-7		1	1 unit	1AC				5SY8602-8		1	1 unit	1AA		
	3		5SY8603-7		1	1 unit	1AC				5SY8603-8		1	1 unit	1AA		
	4		5SY8604-7		1	1 unit	1AC				5SY8604-8		1	1 unit	1AA		
	6		5SY8606-7		1	1 unit	1AC				5SY8606-8		1	1 unit	1AA		
	8		5SY8608-7		1	1 unit	1AC				5SY8608-8		1	1 unit	1AA		
	10		5SY8610-7		1	1 unit	1AC				5SY8610-8		1	1 unit	1AA		
	13		5SY8613-7		1	1 unit	1AC				5SY8613-8		1	1 unit	1AA		
	16		5SY8616-7		1	1 unit	1AC				5SY8616-8		1	1 unit	1AA		
	20		5SY8620-7		1	1 unit	1AC				5SY8620-8		1	1 unit	1AA		
	25		5SY8625-7		1	1 unit	1AC				5SY8625-8		1	1 unit	1AA		
	32		5SY8632-7		1	1 unit	1AC				5SY8632-8		1	1 unit	1AA		
	40		5SY8640-7		1	1 unit	1AC				5SY8640-8		1	1 unit	1AA		
	50		5SY8650-7		1	1 unit	1AC				5SY8650-8		1	1 unit	1AA		
	63		5SY8663-7		1	1 unit	1AC				5SY8663-8		1	1 unit	1AA		
4P, 400 V AC																	
	0.3	4	5SY8414-7		1	1 unit	1AC				5SY8414-8		1	1 unit	1AA		
	0.5		5SY8405-7		1	1 unit	1AC				5SY8405-8		1	1 unit	1AA		
	1		5SY8401-7		1	1 unit	1AC				5SY8401-8		1	1 unit	1AA		
	1.6		5SY8415-7		1	1 unit	1AC				5SY8415-8		1	1 unit	1AA		
	2		5SY8402-7		1	1 unit	1AC				5SY8402-8		1	1 unit	1AA		
	3		5SY8403-7		1	1 unit	1AC				5SY8403-8		1	1 unit	1AA		
	4		5SY8404-7		1	1 unit	1AC				5SY8404-8		1	1 unit	1AA		
	6		5SY8406-7		1	1 unit	1AC				5SY8406-8		1	1 unit	1AA		
	8		5SY8408-7		1	1 unit	1AC				5SY8408-8		1	1 unit	1AA		
	10		5SY8410-7		1	1 unit	1AC				5SY8410-8		1	1 unit	1AA		
	13		5SY8413-7		1	1 unit	1AC				5SY8413-8		1	1 unit	1AA		
	16		5SY8416-7		1	1 unit	1AC				5SY8416-8		1	1 unit	1AA		
	20		5SY8420-7		1	1 unit	1AC				5SY8420-8		1	1 unit	1AA		
	25		5SY8425-7		1	1 unit	1AC				5SY8425-8		1	1 unit	1AA		
	32		5SY8432-7		1	1 unit	1AC				5SY8432-8		1	1 unit	1AA		
	40		5SY8440-7		1	1 unit	1AC				5SY8440-8		1	1 unit	1AA		
	50		5SY8450-7		1	1 unit	1AC				5SY8450-8		1	1 unit	1AA		
	63		5SY8463-7		1	1 unit	1AC				5SY8463-8		1	1 unit	1AA		

¹⁾ 1 MW (modular width) = 18 mm.


Overview

Miniature circuit breakers with plug-in terminals are used for the protection of socket outlets and lighting circuits with the most common rated currents of 10 to 20 A.


Benefits



- Double, self-contained, screwless outgoing terminals for fast connection of conductors.



- Removal of individual conductors requires no tools and ensures high operating reliability.
- No end sleeves required for finely stranded conductors. This saves mounting time.



- Conventional pin busbars are used for the incoming terminal. This ensures clear, manageable and convenient access to all terminals as part of the uniform Siemens connection concept.

Miniature Circuit Breakers

5SJ6...-KS miniature circuit breakers, with plug-in terminals

Technical specifications

		5SJ6...-KS
Standards		EN 60898-1
Approvals		see chapter "Appendix"
Rated voltage U_n	V AC	230/400
Operational voltage		
• Min.		V AC/DC/pole 24
• Max.		V AC 250/440 V DC/pole 60 ¹⁾
Rated breaking capacity	Acc. to EN 60898-1	kA AC 6
Insulation coordination		
• Rated insulation voltage		V AC 250/440
• Pollution degree for overvoltage category		2/III
Rated frequency	Hz	50/60
Touch protection	Acc. to EN 50274	Yes
Handle end position , sealable		Yes
Degree of protection	Acc. to EN 60529	IP20 with connected conductors, IP40 in the area of the handle with distribution cover
CFC and silicone-free		Yes
Terminals		Screwless terminals on the outgoing terminals for 1.5 ... 4 mm ²
Conductor cross-sections		
• Top, plug-in terminals		
- Solid, stranded and finely stranded, without end sleeve		mm ² 1.5 ... 4
- Finely stranded, with end sleeve		mm ² 1.5 ... 2.5
• Bottom, tunnel terminal ± screw (Pozidriv)		2
- Solid, stranded or finely stranded, with end sleeve		mm ² 0.75 ... 25
Mounting position		Any
Service life , on average, with rated load		20000 actuations
Ambient temperature	°C	-25 ... +45, occasionally +55, max. 95% humidity
Storage temperature	°C	-40 ... +75, 95% humidity up to 55 °C
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.

Miniature Circuit Breakers

5SJ6...-KS miniature circuit breakers, with plug-in terminals

Selection and ordering data

6000 3		I_n	Mounting width	SD	Characteristic B				PU (UNIT, SET, M)	PS	PG	SD	Characteristic C				PU (UNIT, SET, M)	PS	PG
					Article No. www.siemens.com/ product?Article No.	Price per PU							Article No. www.siemens.com/ product?Article No.	Price per PU					
		A	MW ¹⁾	d								d							
Miniature circuit breakers with plug-in terminal																			
	1P																		
	10	1			5SJ6110-6KS				1	1 unit	1AB		5SJ6110-7KS				1	1 unit	1AC
	13				5SJ6113-6KS				1	1 unit	1AB		5SJ6113-7KS				1	1 unit	1AC
	16				5SJ6116-6KS				1	1 unit	1AB		5SJ6116-7KS				1	1 unit	1AC
	20				5SJ6120-6KS				1	1 unit	1AB		5SJ6120-7KS				1	1 unit	1AC
	1P+N																		
	10	2			5SJ6510-6KS				1	1 unit	1AB		5SJ6510-7KS				1	1 unit	1AC
	13				5SJ6513-6KS				1	1 unit	1AB		5SJ6513-7KS				1	1 unit	1AC
	16				5SJ6516-6KS				1	1 unit	1AB		5SJ6516-7KS				1	1 unit	1AC
	20				5SJ6520-6KS				1	1 unit	1AB		5SJ6520-7KS				1	1 unit	1AC
	2P																		
	10	2			5SJ6210-6KS				1	1 unit	1AB		5SJ6210-7KS				1	1 unit	1AC
	13				5SJ6213-6KS				1	1 unit	1AB		5SJ6213-7KS				1	1 unit	1AC
	16				5SJ6216-6KS				1	1 unit	1AB		5SJ6216-7KS				1	1 unit	1AC
	20				5SJ6220-6KS				1	1 unit	1AB		5SJ6220-7KS				1	1 unit	1AC
	3P																		
	10	3			5SJ6310-6KS				1	1 unit	1AB		5SJ6310-7KS				1	1 unit	1AC
	13				5SJ6313-6KS				1	1 unit	1AB		5SJ6313-7KS				1	1 unit	1AC
	16				5SJ6316-6KS				1	1 unit	1AB		5SJ6316-7KS				1	1 unit	1AC
	20				5SJ6320-6KS				1	1 unit	1AB		5SJ6320-7KS				1	1 unit	1AC

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY Miniature Circuit Breakers, 1+N in 1 MW

Introduction

Overview


These miniature circuit breakers are used for the protection of systems and installations with switched neutral conductors in distribution boards with little space. They are just a single modular width.

Compact busbars facilitate installation in space-saving distribution boards.

Benefits



- Auxiliary switches and fault signal contacts from the high-capacity range can be freely mounted on these miniature circuit breakers. This increases availability and cuts down on logistics.



- The infeed can be implemented either from the top or the bottom. Additional terminals with lateral cable entry facilitate mounting when using large conductor cross-sections.

Technical specifications

		5SY30..	5SY60.. ¹⁾
Standards		EN 60898-1	
Approvals		see chapter "Appendix"	
Rated voltage U_n	V AC	230	
Operational voltage			
• Min.	V AC/DC	24	
• Max.	V AC	250	
	V DC/pole	72	
Rated breaking capacity I_{cn}	kA AC	4.5	6
Insulation coordination			
• Rated insulation voltage	V AC	250	
• Pollution degree for overvoltage category		2/III	
Rated frequency	Hz	50/60	
Touch protection	Acc. to EN 50274	Yes	
Handle end position , sealable		Yes	
Degree of protection	Acc. to EN 60259	IP20 with connected conductors, IP40 in the area of the handle with distribution cover	
CFC and silicone-free		Yes	
Terminals	± screw (Pozidriv)	2	
• Solid and stranded, top and bottom terminal	mm ²	0.75 ... 16	
• Finely stranded, with end sleeve, top and bottom terminal	mm ²	0.75 ... 10	
• Terminal tightening torque	Nm	2.0 ... 2.5	
Mounting position		Any	
Service life			
On average, with rated load		20000 actuations At 2 A/4 A and 40 A: 8000 actuations	
Ambient temperature	°C	-25 ... +45, occasionally +55, max. 95% humidity	
Storage temperature	°C	-40 ... +75	
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles	
Resistance to vibrations	Acc. to IEC 60068-2-6	m/s ²	50 at 25 ... 150 Hz and 60 at 35 Hz (4 s)

¹⁾ Not for Belgium

Miniature Circuit Breakers

5SY Miniature Circuit Breakers, 1+N in 1 MW

5SY30, 4500 A

Selection and ordering data

4 500 3	I_n	Mounting width	SD	Characteristic C Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d					
Miniature circuit breakers 4500 A								
	1P+N, 230 V AC							
	N connection, right							
	2	2		5SY3002-7		1	1 unit	1AE
	4			5SY3004-7		1	1 unit	1AE
	6			5SY3006-7		1	1 unit	1AE
	8			5SY3008-7		1	1 unit	1AE
	10			5SY3010-7		1	1 unit	1AE
	13			5SY3013-7		1	1 unit	1AE
	16			5SY3016-7		1	1 unit	1AE
	20			5SY3020-7		1	1 unit	1AE
	25			5SY3025-7		1	1 unit	1AE
	32			5SY3032-7		1	1 unit	1AE
	40			5SY3040-7		1	1 unit	1AE
	N connection, left							
	2	2		5SY3002-7KL		1	1 unit	1AE
	4			5SY3004-7KL		1	1 unit	1AE
	6			5SY3006-7KL		1	1 unit	1AE
	8			5SY3008-7KL		1	1 unit	1AE
	10			5SY3010-7KL		1	1 unit	1AE
	13			5SY3013-7KL		1	1 unit	1AE
	16			5SY3016-7KL		1	1 unit	1AE
	20			5SY3020-7KL		1	1 unit	1AE
	25			5SY3025-7KL		1	1 unit	1AE
	32			5SY3032-7KL		1	1 unit	1AE
	40			5SY3040-7KL		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SY Miniature Circuit Breakers, 1+N in 1 MW

5SY60, 6000 A

Selection and ordering data

6000 3			Characteristic B				Characteristic C						
I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
A	MW ¹⁾	d						d					
Miniature circuit breakers, compact, 1+N (1P+N), 230 V AC ²⁾													
	N pole, right												
	2	1	--					5SY6002-7		1	1 unit	1AC	
	4		--					5SY6004-7		1	1 unit	1AC	
	6		5SY6006-6		1	1 unit	1AB	5SY6006-7		1	1 unit	1AC	
	8		--					5SY6008-7		1	1 unit	1AC	
	10		5SY6010-6		1	1 unit	1AB	5SY6010-7		1	1 unit	1AC	
	13		5SY6013-6		1	1 unit	1AB	5SY6013-7		1	1 unit	1AC	
	16		5SY6016-6		1	1 unit	1AB	5SY6016-7		1	1 unit	1AC	
	20		5SY6020-6		1	1 unit	1AB	5SY6020-7		1	1 unit	1AC	
	25		5SY6025-6		1	1 unit	1AB	5SY6025-7		1	1 unit	1AC	
32		5SY6032-6		1	1 unit	1AB	5SY6032-7		1	1 unit	1AC		
40		5SY6040-6		1	1 unit	1AB	5SY6040-7		1	1 unit	1AC		
	N pole, left												
	2	1	--					5SY6002-7KL		1	1 unit	1AC	
	4		--					5SY6004-7KL		1	1 unit	1AC	
	6		--					5SY6006-7KL		1	1 unit	1AC	
	8		--					5SY6008-7KL		1	1 unit	1AC	
	10		--					5SY6010-7KL		1	1 unit	1AC	
	13		--					5SY6013-7KL		1	1 unit	1AC	
	16		--					5SY6016-7KL		1	1 unit	1AC	
	20		--					5SY6020-7KL		1	1 unit	1AC	
	25		--					5SY6025-7KL		1	1 unit	1AC	
32		--					5SY6032-7KL		1	1 unit	1AC		
40		--					5SY6040-7KL		1	1 unit	1AC		




¹⁾ 1 MW (modular width) = 18 mm.

²⁾ Not for Belgium

Miniature Circuit Breakers

5SY Miniature Circuit Breakers, 1+N in 1 MW

5ST busbar system

	Pin spacing MW ¹⁾	Length mm	SD d	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
5ST37 busbar system, 10 mm², for 1+N miniature circuit breakers in 1 MW of the compact range, can be cut, with end caps								
	Single-phase, 12 MW For 12 MCBs 1+N, gray	1	216	5ST3762		1	10 units	1AD
	For 12 MCBs 1+N, blue		216	5ST3763		1	10 units	1AD
	Single-phase For MCBs 1+N, gray	1	1016	5ST3764		1	10 units	1AD
	For MCBs 1+N, blue		1016	5ST3765		1	10 units	1AD
Terminals								
	Terminals, short • For conductors up to 25 mm² • Infeed on side • Specially for single-phase busbars and for 5ST3615-1 three-phase busbars			5ST3768		1	25 units	1AD
	Terminals, short, IP20 • For conductors up to 25 mm² • Infeed on side • Specially for single-phase busbars and for 5ST3615-1 three-phase busbars			5ST3771-2		1	10 units	1AD
End caps for 5ST376 busbars								
	1 set comprises a right and a left cap Gray			5ST3766		1	10 sets	1AD
	Blue			5ST3767		1	10 sets	1AD
5ST36 busbar systems, 10 mm², for miniature circuit breakers, fixed lengths, cannot be cut, fully insulated								
	Three-phase For 6 MCBs 1+N	1	102	5ST3613		1	10 units	1AD
	For 9 MCBs 1+N		257.5	5ST3614		1	10 units	1AD
	For 12 MCBs 1+N		210	5ST3615		1	10 units	1AD


¹⁾ 1 MW (modular width) = 18 mm.

Dimensional drawings


5ST36

Pin spacing in MW

Dimensions of side view in mm (approx.).




5ST3613
5ST3614
5ST3615



5ST37

Pin spacing in MW

Dimensions of side view in mm (approx.).



5ST3762
5ST3764

5ST3763
5ST3765

Miniature Circuit Breakers

Additional Components

Electrical components

Overview

The Siemens mounting concept supports the combination of all 5ST3 additional components with 5SY and 5SP miniature circuit breakers and with 5SU1 RCBOs.

5SL and 5SY60... miniature circuit breakers are suitable for mounting auxiliary switches and fault signal contacts. Auxiliary switches can also be mounted on 5TE8 flush-mounting circuit breakers and 5SG71 MINIZED switch disconnectors.

Auxiliary switches (AS)

The auxiliary switch (AS) always signals the contact position of the miniature circuit breaker, regardless of whether the miniature circuit breaker was tripped manually or as the result of a fault. An additional version is also available for the switching of small currents and voltages for the control of programmable control systems (PLCs) according to EN 61131-2. The auxiliary switch with test button enables the testing of control circuits without the need to switch the miniature circuit breaker.

Fault signal contacts (FC)

The fault signal contact (FC) signals the automatic tripping of the miniature circuit breaker in the event of a fault, such as an overload or a short circuit. If the fault signal contact is activated, the contact position does not change if the miniature circuit breaker is tripped manually. Fault signal contacts with TEST and RESET buttons enable the testing of control circuits without the need to trip the miniature circuit breaker. The red RESET button integrated in the handle also indicates the automatic tripping of the MCB. The signal can be acknowledged manually using the RESET button.

Shunt trips (ST)

Shunt trips are used for remote tripping of miniature circuit breakers.

Undervoltage releases (UR)

Undervoltage releases are integrated (e.g. in EMERGENCY-STOP loops), thus ensuring that the miniature circuit breaker trips in the event of an emergency, which, in turn, ensures disconnection of the control circuit according to EN 60204. In the event that the voltage is interrupted or too low, it also trips, i.e. prevents activation of the miniature circuit breaker.

RC units

RC units can be combined with miniature circuit breakers of characteristics A, B, C and D. They then form a combination of RCCB and miniature circuit breakers for personnel, fire and line protection. The combinations can be tailored to meet individual requirements.

For information on RC units, see [chapter "Residual Current Protective Devices / Arc Fault Detection Devices \(AFDDs\)"](#).

Remote controlled mechanisms (RC)

Remote controlled mechanisms are used for the remote ON/OFF switching of miniature circuit breakers with or without RC unit, residual current operated circuit breakers, RCBOs or isolators and also enable local manual switching of these devices. A tripped combination must be acknowledged prior to switching back on.

The device combination with the auto reclose device (ARD) types tries up to three times to switch on again in the event of a fault. If a fault continues to exist, the combination remains switched off. The remote controlled mechanism has a mode selector switch with the functions: "OFF", "RC OFF" and "RC ON".

Explanation of selector switch positions:

- OFF (for the 177 - 270 V devices): The remote controlled mechanism is switched off, blocked mechanically and can be sealed and/or locked.
- RC OFF: Only manual operation is possible.
- RC ON: Both manual and remote operation are possible (except for in the case of the basic 12 - 48 V devices).

In the event that a device is tripped by a fault, the handle of the basic device and remote controlled mechanism switches to the OFF position. If, depending on the device version, the combination has switched off, an attempt can be made either via ARD or remotely to switch on again. If a fault continues to exist, the combination is switched off and can only be switched on again locally manually.

Matching adapters have to be ordered additionally to enable the remote controlled mechanisms to be combined with the residual current operated circuit breakers, miniature circuit breakers, RCBOs and ON/OFF switches.

Benefits

Can be universally retrofitted with all additional components



- The 5SL, 5SY and 5SP miniature circuit breakers are ideal for the quick and easy mounting of auxiliary switches and fault signal contacts. Captive metal brackets on the additional components ensure the quick and easy mounting of devices on the miniature circuit breakers without the need for tools.



- Fault signal contacts with TEST and RESET button enable the simple testing of auxiliary circuits and, in the event of a fault, acknowledgement of the fault over the RESET button, without the need to switch the miniature circuit breakers.



- The auxiliary switches with TEST button enable the simple manual testing of control circuits during operation of the entire installation, without the need to switch the miniature circuit breakers.

Remote controlled mechanisms




- Remote controlled mechanisms with ARD and Power have integrated auxiliary switches and fault signal contacts.
- More 5ST3... additional components, such as AS, FC, ST and UR, can be added to the right-hand side of the remote controlled mechanism in line with the Siemens mounting concept.
- The remote controlled mechanisms with ARD and Power have an LED display on the front of the device to show the switching state and for diagnostics.
- The 5ST3070 remote controlled mechanism has an extended temperature range from -40 °C to +70 °C.

Miniature Circuit Breakers

Additional Components

Electrical components

Portfolio overview



Miniature Circuit Breakers

Additional Components

Electrical components

Combination options remote controlled mechanism – adapter – mount-on device

		5SL4/6 1-2 MW	5SL4/6 3-4 MW	5TL1 1-2 MW	5TL1 3-4 MW	5SY4/5/6/7/8 5SY60 1-2 MW	5SY4/5/6/7/8 3-4 MW
	RC mech. Basic (1.5 MW) – 5ST3053 12 V - 30 V AC 12 V - 48 V DC						
	RC mech. Basic (2 MW) – 5ST3054 230 V AC						
	RC mech. Power (2 MW) – 5ST3055 12 V - 30 V AC 12 V - 48 V DC						
	RC mech. Power (2 MW) – 5ST3056 230 V AC						
	RC mech. ARD* (2 MW) – 5ST3057 12 V - 30 V AC 12 V - 48 V DC						
	RC mech. ARD* (2 MW) – 5ST3058 230 V AC						
	RC mech. Power (2 MW) – 5ST3070 12 V - 30 V AC 12 V - 48 V DC						

* ARD = Auto Reclose Device

I201_19642

Miniature Circuit Breakers

Additional Components

Electrical components

Combination options remote controlled mechanism – adapter – mount-on device

	5SV3	5SU1	5SM2 + 5SL 2-pole	5SM2 + 5SL 3-4-pole	5SM2 + 5SY 2-pole	5SM2 + 5SY 3-4-pole
						
RC mech. Basic (1.5 MW) – 5ST3053 12 V - 30 V AC 12 V - 48 V DC	not compatible	 up to 3 MW Adapter 5ST3820-5	not compatible	not compatible	not compatible	not compatible
RC mech. Basic (2 MW) – 5ST3054 230 V AC	not compatible	 up to 3 MW Adapter 5ST3820-5	not compatible	not compatible	not compatible	not compatible
RC mech. Power (2 MW) – 5ST3055 12 V - 30 V AC 12 V - 48 V DC	 Adapter 5ST3820-6	 Adapter 5ST3820-5	 Adapter 5ST3820-3 add. 5ST3820-6	 Adapter 5ST3820-3 add. 5ST3820-7	 Adapter 5ST3820-3 add. 5ST3820-1	 Adapter 5ST3820-3 add. 5ST3820-2
RC mech. Power (2 MW) – 5ST3056 230 V AC	 Adapter 5ST3820-6	 Adapter 5ST3820-5	 Adapter 5ST3820-3 add. 5ST3820-6	 Adapter 5ST3820-3 add. 5ST3820-7	 Adapter 5ST3820-3 add. 5ST3820-1	 Adapter 5ST3820-3 add. 5ST3820-2
RC mech. ARD* (2 MW) – 5ST3057 12 V - 30 V AC 12 V - 48 V DC	 Adapter 5ST3820-6	 Adapter 5ST3820-5	 Adapter 5ST3820-3 add. 5ST3820-6	 Adapter 5ST3820-3 add. 5ST3820-7	 Adapter 5ST3820-3 add. 5ST3820-1	 Adapter 5ST3820-3 add. 5ST3820-2
RC mech. ARD* (2 MW) – 5ST3058 230 V AC	 Adapter 5ST3820-6	 Adapter 5ST3820-5	 Adapter 5ST3820-3 add. 5ST3820-6	 Adapter 5ST3820-3 add. 5ST3820-7	 Adapter 5ST3820-3 add. 5ST3820-1	 Adapter 5ST3820-3 add. 5ST3820-2
RC mech. Power (2 MW) – 5ST3070 12 V - 30 V AC 12 V - 48 V DC	 Adapter 5ST3820-6	 Adapter 5ST3820-5	 Adapter 5ST3820-3 add. 5ST3820-6	 Adapter 5ST3820-3 add. 5ST3820-7	 Adapter 5ST3820-3 add. 5ST3820-1	 Adapter 5ST3820-3 add. 5ST3820-2

* ARD = Auto Reclose Device

I201_19642

Technical specifications

		Remote controlled mechanisms						
		Basic		Power		ARD (with automatic restart)		Power
								
		5ST3053	5ST3054	5ST3055	5ST3056	5ST3057	5ST3058	5ST3070
Standards		EN 50557 (VDE 0640-20)						
Rated voltages U_n	V AC	12 ... 30	177 ... 270	12 ... 30	177 ... 270	12 ... 30	177 ... 270	12 ... 30
	V DC	12 ... 48		12 ... 48		12 ... 48		12 ... 48
• Rated frequency f_n	Hz	50 ... 60						
Rated power dissipation	VA	≤ 1 in standby						
Module width	mm	27 (1.5 MW)	36 (2 MW)					
Ambient temperature	°C	-25 ... +45						-40 ... +70
Storage temperature	°C	-40 ... +55						-40 ... +70
Degree of protection		IP20						
Pollution degree for overvoltage category		3/II	3/III	3/II	3/III	3/II	3/III	3/II
Service life, on average, with rated load		10 000 actuations						
Conductor cross-sections	mm ²	0.5 ... 1.5						
	AWG	14 ... 30						
Terminal tightening torque	Nm lb-in	0.2 ... 0.25 2.0						
Cable length in the control circuit	m	≤ 1500						
Number of remote switching operations/min.		2						
Number of automatic reclose attempts		--					3	--
Sliding selector with locking device		--	✓	✓	✓	✓	✓	✓
Integrated auxiliary switches		--			1 CO; 2 A; 250 V			
Integrated fault signal contact		--			1 CO; 2 A; 250 V			
Possible device combinations		MCBs up to 4 MW, RCBOs up to 3 MW			MCBs, RCCBs up to 4P, RCBOs up to 3 MW, RC unit + MCB, ON/OFF switches: 5TL1, 5TE2			

Miniature Circuit Breakers

Additional Components

Electrical components

Selection and ordering data

	Rated voltage	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	U_n V	MW ¹⁾	d					
	Remote controlled mechanisms (RC mech.)							
	• Basic	12 ... 30 V AC 12 ... 48 V DC	1.5	5ST3053		1	1 unit	1AD
		177 ... 270 V AC	2	5ST3054		1	1 unit	1AD
	• Power	12 ... 30 V AC 12 ... 48 V DC	2	5ST3055		1	1 unit	1AD
		177 ... 270 V AC		5ST3056		1	1 unit	1AD
	• Power with automatic reclose function	12 ... 30 V AC 12 ... 48 V DC	2	5ST3057		1	1 unit	1AD
		177 ... 270 V AC		5ST3058		1	1 unit	1AD
	• With extended function NEW	12 ... 30 V AC 12 ... 48 V DC	2	5ST3070		1	1 unit	1AD
	Note Matching adapters must be ordered separately.							
	Accessories for remote controlled mechanisms							
	• Adapters for: - 5SY MCBs 1-2 MW - 5SM2 RC unit with 5SY, 2-pole			5ST3820-1		1	1 unit	1AD
	• Adapters for: - 5SY MCBs 3-4 MW - 5SM2 RC unit with 5SY, 3-4-pole			5ST3820-2		1	1 unit	1AD
	• Adapters for: - 5SM2 RC unit			5ST3820-3		1	1 unit	1AD
	• Adapters for: - 5SU1 RCBOs			5ST3820-5		1	1 unit	1AD
	• Adapters for: - 5SL MCBs 1-2-pole - 5TL1 1-2-pole - 5SV3 RCCBs 2/4-pole - 5SM2 RC unit with 5SL, 2-pole			5ST3820-6		1	1 unit	1AD
	• Adapters for: - 5SL MCBs 3-4-pole - 5TL1 3-4-pole - 5SM2 RC unit with 5SL, 3-4-pole			5ST3820-7		1	1 unit	1AD

¹⁾ 1 MW (modular width) = 18 mm.

Technical specifications

		Auxiliary switches (AS)		Fault signal contacts (FC)
		5ST3010, 5ST3010-2 5ST3011, 5ST3011-2 5ST3012, 5ST3012-2	5ST3013 ¹⁾ , 5ST3013-2 ²⁾ 5ST3014 ¹⁾ , 5ST3014-2 ²⁾ 5ST3015 ¹⁾ , 5ST3015-2 ²⁾	5ST3020, 5ST3020-2 5ST3021, 5ST3021-2 5ST3022, 5ST3022-2
Standards		IEC/EN 62019; IEC/EN 60947-5-1; UL 1077; CSA C22.2 No. 235		
Approvals		see chapter "Appendix"		
Short-circuit protection		< 500 A: 5SL B6/C6 miniature circuit breakers - Up to 1 kA: 5SY B6/C6 miniature circuit breakers or gG 6 A fuse		
Contact load				
• Min.		50 mA, 24 V	1) = 1 mA/5 V DC 2) = 5 mA/5 V DC	50 mA, 24 V
• Max.		--	1) = 100 mA/30 V DC 2) = 30 mA/30 V DC	--
• Acc. to IEC/EN 62019 and 60947-5-1:				
- 400 V AC, AC-14, NO	A	2	--	2
- 230 V AC, AC-14, NO	A	6	--	6
- 400 V AC, AC-13, NC	A	2	--	2
- 230 V AC, AC-13, NC	A	6	--	6
• Acc. to IEC/EN 62019 (acc. to IEC/EN 60947-5-1):				
- 220 V DC, DC-13, NO + NC	A	1 (0.5)	--	1 (0.5)
- 110 V DC, DC-13, NO + NC	A	1 (0.75)	--	1 (0.75)
- 60 V DC, DC-13, NO + NC	A	3 (1.5)	--	3 (1.5)
- 24 V DC, DC-13, NO + NC	A	6 (3)	--	6 (3)
Service life, on average, with rated load		20000 actuations		
Conductor cross-sections		mm ² AWG	0.5 ... 2.5 22 ... 14	
Terminals				
• Terminal tightening torque		Nm lb-in	0.5 4.5	
Rated frequency		Hz	50/60	
Mounting position			Any	
Ambient temperature		°C	-25 ... +55	
Storage temperature		°C	-40 ... +75	
Resistance to climate		Acc. to IEC 60068-2-30 Cycles	28	
Shock		Acc. to IEC 60068-2-27 m/s	50 at 11 ms half-sine	
Resistance to vibrations		Acc. to IEC 60068-2-6 m/s ²	50 at 10 ... 150 Hz	

		Undervoltage releases (UR)		Shunt trips (ST)	
		5ST304.	5ST3030	5ST3031	
Standards		EN 60947-1			
Rated voltages U_n		V AC	230	110 ... 415	24 ... 48
		V DC	24, 110	110 ... 220	24 ... 48
• Operating range U_n			0.85 ... 1.1 x U_n	0.7 ... 1.1 x U_n	
• Rated frequency f_n		Hz	--	50 ... 60	
Response limits: Tripping			< 0.35 ... 0.7 x U_n	--	
Short-circuit protection		Miniature circuit breakers B/C 6 A or fuse gG 6 A			
Minimum contact load		50 mA, 24 V			
Tripping operations		max. 2000			
Service life, on average, with rated load		20000 actuations			
Conductor cross-sections		mm ² AWG	0.5 ... 2.5 22 ... 14		
Terminals					
• Terminal tightening torque		Nm lb-in	0.8 6.8		
Mounting position			Any		
Ambient temperature		°C	-25 ... +55		
Storage temperature		°C	-40 ... +75		
Resistance to climate		Acc. to IEC 60068-2-30 Cycles	28		
Shock		Acc. to IEC 60068-2-27 m/s	50 at 11 ms half-sine		
Resistance to vibrations		Acc. to IEC 60068-2-6 m/s ²	50 at 10 ... 150 Hz		
Switching frequency			--		
Switching duration		s	--		
Minimum command duration		s	--		
Rated power dissipation		VA	--		
Rated frequency		Hz	50/60		
Behavior in the event of control voltage failure			--		

For technical specifications of RC units, see chapter "Residual Current Protective Devices / Arc Fault Detection Devices (AFDDs)".

Miniature Circuit Breakers

Additional Components

Electrical components

Selection and ordering data

	Rated voltage U_n V	Mounting width MW ¹⁾	SD d	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	Auxiliary switches (AS) For 5SL, 5SY, 5SP and 5TL1 miniature circuit breakers, 5SU1 RCBOs, for 5SV residual current protective devices and 5TE8 switches							
	1 NO + 1 NC For low power	0.5	►	5ST3010		1	1 unit	1AD
			►	5ST3013		1	1 unit	1AD
	2 NO For low power			5ST3011 5ST3014		1 1	1 unit 1 unit	1AD 1AD
	2 NC For low power			5ST3012 5ST3015		1 1	1 unit 1 unit	1AD 1AD
	Auxiliary switches (AS) with TEST button For 5SL, 5SY, 5SP and 5TL1 miniature circuit breakers, 5SU1, 5TL1 RCBOs, for 5SV residual current protective devices and 5TE8 switches							
	1 NO + 1 NC For low power	0.5		5ST3010-2 5ST3013-2		1 1	1 unit 1 unit	1AD 1AD
	2 NO For low power			5ST3011-2 5ST3014-2		1 1	1 unit 1 unit	1AD 1AD
	2 NC For low power			5ST3012-2 5ST3015-2		1 1	1 unit 1 unit	1AD 1AD
	Fault signal contacts (FC) For 5SL, 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs, for 5SV residual current protective devices							
	1 NO + 1 NC	0.5	►	5ST3020		1	1 unit	1AD
	2 NO			5ST3021		1	1 unit	1AD
	2 NC			5ST3022		1	1 unit	1AD
	Fault signal contacts (FC) with TEST and ACKNOWLEDGE button For 5SL, 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs, for 5SV residual current protective devices							
	1 NO + 1 NC	0.5	►	5ST3020-2		1	1 unit	1AD
	2 NO			5ST3021-2		1	1 unit	1AD
	2 NC			5ST3022-2		1	1 unit	1AD
	Undervoltage releases (UR) For 5SL4, 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs, for 5SV residual current protective devices, but not for 5SY60.. and 5SL6 miniature circuit breakers With integrated auxiliary switch							
	230 AC	1	►	5ST3040		1	1 unit	1AD
	110 DC			5ST3041		1	1 unit	1AD
	24 DC			5ST3042		1	1 unit	1AD
	Without integrated auxiliary switch							
	230 AC	1	►	5ST3043		1	1 unit	1AD
	Shunt trips (ST) For 5SL4, 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs, for 5SV residual current protective devices, but not for 5SY60.. and 5SL6 miniature circuit breakers							
	110 ... 415 V AC	1	►	5ST3030		1	1 unit	1AD
	24 ... 48 V AC/DC	1	►	5ST3031		1	1 unit	1AD

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers
Additional Components

Electrical components

Rated residual current	Rated current	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
$I_{\Delta n}$ mA	I_n A	MW ¹⁾	d					

RC units



For further information on RC units,
see chapter "Residual Current Protective Devices / Arc
Fault Detection Devices (AFDDs)"


¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Additional Components

Mechanical components

Selection and ordering data

Version	Mounting width MW ¹⁾	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
 Mechanical rotary operating mechanism complete with handle - For 5SY, but not for 5SYx0 1+N in 1 MW - For 5SP4, 5SL, 5TL1, 5TE2, 5TE8, 5SU1 Versions - Handle black - Handle red/yellow		d	5ST3060 5ST3061		1	1 unit	1AD
					1	1 unit	1AD
 Terminal covers For miniature circuit breakers, but not for 5SY60. . . For additional covering of the screw openings per pole, sealable. In the case of 5SY, also prevents removal of device from the standard mounting rail.		►	5ST3800		1	10 units	1AD
 Handle locking devices Sealable to prevent undesired mechanical ON/OFF switching For 5SP and 5SY miniature circuit breakers For padlock with max. 3 mm shackle			5ST3801		1	1 unit	1AD
 For 5SL, 5SV, 5TL1 miniature circuit breakers For padlock with 3 ... 6 mm shackle			5ST3806		1	5 units	1AD
 Padlocks Padlocks for 5ST3801 and 5ST3806 locking devices, 5ST30 remote controlled mechanisms (except for 5ST3053)			5ST3802		1	1 unit	1AD
Locking devices For 5SP and 5SY miniature circuit breakers comprising 5ST3801 handle locking device and 5ST3802 padlock			5ST3803		1	1 set	1AD
Locking devices For 5SL, 5SV, 5TL1 miniature circuit breakers, comprising 5ST3806 handle locking device and 5ST3802 padlock			5ST3807		1	1 set	1AD
 Spacers Can be placed on either side of the standard mounting rail. Two spacers allow for convenient cable routing	0.5		5TG8240		1	2 units	1BK
 Device labels Adhesive, for modular installation devices, e.g. 5SY, 5SL, 5TL1, etc. Versions 15 mm x 6 mm, white (WIN 098) 15 mm x 6 mm, yellow (WIN 099)			8WH8210-0AA35 8WH8210-0AA36		100	3740 units	1BT
					100	3740 units	1BT

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Additional Components

Mechanical components

Version		SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
		d					
Labeling system							
Available from:		Murrplastik Systemtechnik GmbH Postfach 1143 71570 Oppenweiler, Germany Telephone: +49 7191-482-0 Email: info@murrplastik.de					
	Terminal covers, gray For surface mounting, degree of protection IP40, sealable, with 35 mm standard mounting rail • Up to 2.5 MW • Up to 4.5 MW		5SW3004 5SW3005		1 1	1 unit 1 unit	1BE 1BE
	Wall enclosures, gray For flush mounting, degree of protection IP40, with 35 mm standard mounting rail • Up to 2.5 MW • Up to 4.5 MW		5SW3006 5SW3007		1 1	1 unit 1 unit	1BE 1BE
	Molded-plastic enclosures, gray For surface mounting, degree of protection IP54, with 35 mm standard mounting rail, sealable, with transparent hinged lid For 4.5 MW		5SW1200		1	1 unit	1BE
	Covers Can be assembled as mini distribution board, suitable for all devices, cover parts prepared for rail mounting of conventional label caps, comprising: • End plates (for snapping onto standard mounting rail) • Angled profile (approx. 1 m long) • Alternative flat profiles (as a cover between the rows of devices, length approx. 1 m)	▶	5ST2134 5ST2135 5ST2136		1 1 1	10 units 5 units 5 units	1AD 1AD 1AD
	Holders for front panel installation Universal use for devices from 1 to 6 MW Cutout dimensions: Height 45 ^{+0.5} mm Width 23, 41, 59, 77, 95 or 113 mm		7LF9006		1	1 unit	1BK
	Intermediate frames for 70 mm devices in 55 mm ALPHA SIMBOX small distribution boards Versions • 1-tier • 2-tier • 3-tier • 4-tier		8GB4561 8GB4562 8GB4563 8GB4564		1 1 1 1	1 unit 1 unit 1 unit 1 unit	1BO 1BO 1BO 1BO
For further information on ALPHA distribution boards, ALPHA SIMBOX small distribution boards and intermediate frames, see chapter "Power Distribution Boards / Distribution Boards" .							

For further information on ALPHA distribution boards, ALPHA SIMBOX small distribution boards and intermediate frames, see chapter "Power Distribution Boards / Distribution Boards".

Miniature Circuit Breakers


Additional Components

Mechanical components

More information

The Siemens mounting concept supports the combination of all 5ST3 additional components with miniature circuit breakers of the 5SY and 5SP series and RCBOs of the 5SU1 series.

5SL and 5SY60.. miniature circuit breakers are suitable for mounting auxiliary switches and fault signal contacts. Auxiliary switches can also be mounted on 5TE8 flush-mounting circuit breakers and 5SG71 MINIZED switch disconnectors. In the case of the 5SY6 miniature circuit breaker and in the case of the RCBO, the arc fault detection device can be mounted on the left-hand side.



For further information on the mounting concept for RCBOs, see chapter "Residual Current Protective Devices / Arc Fault Detection Devices (AFDDs)".

Overview

The busbar system with pin-type connections can be used for all 5SL6, 5SJ6...-KS and 5SY miniature circuit breakers with or without mounted auxiliary switch (AS) or fault signal contact (FC).

Busbars in 10 mm² and 16 mm² versions are available.

With bars that can be cut to length, the 5ST37 busbar system can be tailored to any requirements.


The extremely flexible 5ST36 busbar system with fixed lengths also enables installation in any length as the busbars can be overlapped.

There is no further need for time-consuming tasks, such as cutting, cutting to length, deburring, cleaning of cut surfaces and mounting of end caps.


Any free pins on the busbars can be made safe by covering with touch protection.

For further information on the bus-mounting of miniature circuit breakers with residual current operated circuit breakers, see chapter "Residual Current Protective Devices / Arc Fault Detection Devices (AFDDs)".


Benefits




- Between the rows of devices, the busbar, which is located at the bottom and behind the conductor, provides an optimum wiring space with easy view of the inserted conductor. This enables easy control of connections.



- The ability to overlap when mounting the busbars enables a cross-section enlargement of up to 32 mm² using the respective components, 10 mm² and 16 mm².



- By overlapping the busbars with fixed lengths, it is possible to achieve device combinations with any number of devices.



- The fact that the connection of the conductor is always clearly visible facilitates cable entry of all pole types and considerably reduces mounting times.

Miniature Circuit Breakers


Busbars

5ST standard busbars


Technical specifications

			5ST3
Standards			EN 60439-1 (VDE 0660-500): 2005-01
Busbar material			SF-Cu F 24
Partition material			Plastic, Cycoloy 3600 Heat-resistant over 90 °C Flame-retardant and self-extinguishing, dioxin and halogen-free
Rated operating voltage U_c	V AC		400
Rated current I_n			
• Cross-section 10 mm ²			A 63
• Cross-section 16 mm ²			A 80
Rated impulse withstand voltage U_{imp}	kV		4
Test pulse voltage (1.2/50)	kV		6.2
Rated conditional short-circuit current I_{cc}	kA		25
Resistance to climate			
• Constant atmosphere			Acc. to DIN 50015
• Humid heat			Acc. to IEC 60068-2-30
			23/83; 40/92; 55/20 28 cycles
Insulation coordination			
• Overvoltage category			III
• Pollution degree			2
Maximum busbar current I_S per phase			
• Infeed at the start of the busbar			
- Cross-section 10 mm ²			A 63
- Cross-section 16 mm ²			A 80
• Infeed at the center of the busbar			
- Cross-section 10 mm ²			A 100
- Cross-section 16 mm ²			A 130

Infeed at the start or end of the busbar





Infeed along the busbar or midpoint infeed



The sum of the outgoing current per branch (1, 2, 3 ... n) must not be greater than the max. busbar current I_S /phase.

Selection and ordering data


	Pin spacing	Length	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
5ST36 busbar systems, 10 mm², for miniature circuit breakers, fixed lengths, cannot be cut, fully insulated								
	Single-phase							
	For 2 MCBs 1P	1	33	5ST3600		1	10 units	1AD
	For 6 MCBs 1P		105	5ST3601		1	10 units	1AD
	For 12 MCBs 1P		210	5ST3602		1	10 units	1AD
	Single-phase, for MCBs with AS or FC							
	For 2 MCBs 1P	1.5	40	5ST3603		1	10 units	1AD
	For 6 MCBs 1P		156.5	5ST3604		1	10 units	1AD
	For 9 MCBs 1P		237	5ST3605		1	10 units	1AD
	Two-phase							
	For 2 MCBs 2P	1	75.5	5ST3606		1	10 units	1AD
	For 3 MCBs 2P		105	5ST3607		1	10 units	1AD
	For 6 MCBs 2P		210	5ST3608		1	10 units	1AD
	Three-phase							
	For 2 MCBs 3P	1	102	5ST3613		1	10 units	1AD
	For 3 MCBs 3P		157.5	5ST3614		1	10 units	1AD
	For 4 MCBs 3P		210	5ST3615		1	10 units	1AD
	Three-phase, for MCBs with AS or FC							
	For 2 MCBs 3P	1+1+1.5	115	5ST3616		1	10 units	1AD
	For 4 MCBs 3P		237	5ST3617		1	10 units	1AD
	For 6 MCBs 1P	1.5	125	5ST3618		1	10 units	1AD
	For 9 MCBs 1P		229	5ST3620		1	10 units	1AD
	Three-phase							
	For 1 RCCB 4P N right and 8 MCBs 1P	1	210	5ST3624		1	10 units	1AD
	For 1 RCCB 4P N left and 8 MCBs 1P	1	192	5ST3667		1	10 units	1AD
	Four-phase							
	For 2 MCBs 4P or 3P+N	1	145	5ST3621		1	10 units	1AD
	For 3 MCBs 4P or 3P+N		215	5ST3622		1	10 units	1AD
	For 6 MCBs 2P or 1P+N		215	5ST3623		1	10 units	1AD
5ST36 busbars, 16 mm², for miniature circuit breakers, fixed lengths, cannot be cut, fully insulated								
	Single-phase							
	For 2 MCBs 1P	1	33	5ST3630		1	10 units	1AD
	For 6 MCBs 1P		105	5ST3631		1	10 units	1AD
	For 12 MCBs 1P		210	5ST3632		1	10 units	1AD
	Single-phase, for MCBs with AS or FC							
	For 2 MCBs 1P	1.5	40	5ST3633		1	10 units	1AD
	For 6 MCBs 1P		156.5	5ST3634		1	10 units	1AD
	For 9 MCBs 1P		237	5ST3635		1	10 units	1AD
	Two-phase							
	For 2 MCBs 2P	1	75.5	5ST3636		1	10 units	1AD
	For 3 MCBs 2P		105	5ST3637		1	10 units	1AD
	For 6 MCBs 2P		210	5ST3638		1	10 units	1AD
	Two-phase, for MCBs with AS or FC							
	For 2 MCBs 2P	1 + 1.5	75.5	5ST3640		1	10 units	1AD
	For 3 MCBs 2P		120.5	5ST3641		1	10 units	1AD
	For 5 MCBs 2P		210	5ST3642		1	10 units	1AD

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Busbars

5ST standard busbars



	Pin spacing	Length	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
5ST36 busbars, 16 mm ² , for miniature circuit breakers, fixed lengths, cannot be cut, fully insulated								
Three-phase								
For 2 MCBs 3P	1	102.5		5ST3643		1	10 units	1AD
For 3 MCBs 3P		157.5		5ST3644		1	10 units	1AD
For 4 MCBs 3P		210	▶	5ST3645		1	10 units	1AD
Three-phase, for MCBs with AS or FC								
For 2 MCBs 3P	1+1+1.5	115		5ST3646		1	10 units	1AD
For 4 MCBs 3P		237		5ST3647		1	10 units	1AD
For 6 MCBs 1P	1.5	156		5ST3648		1	10 units	1AD
For 9 MCBs 1P		245		5ST3650		1	10 units	1AD
Three-phase								
For 1 RCCB 4P N right and 8 MCBs 1P	1	210		5ST3654		1	10 units	1AD
For 1 RCCB 4P N left and 8 MCBs 1P	1	210		5ST3668		1	10 units	1AD
Four-phase								
For 2 MCBs 4P or 3P+N	1			5ST3651		1	10 units	1AD
For 3 MCBs 4P or 3P+N				5ST3652		1	10 units	1AD
For 6 MCBs 2P or 1P+N				5ST3653		1	10 units	1AD
Touch protection								
	For free connections, yellow (RAL 1004) 5 x 1 pin 10 mm ²			▶	5ST3655	1	10 units	1AD
	20 x 5ST3613 + 10 x 5ST3614 + 50 x 5ST3615 + 50 x 5ST3655				5ST3656	1	1 set	1AD
	16 mm ²				5ST3657	1	1 set	1AD
5ST37 busbar system, 10 mm ² , 12 MW for miniature circuit breakers, can be cut, with end caps								
	Single-phase, angled							
	For 12 MCBs 1P	1	214		5ST3730	1	1 unit	1AD
	For 9 MCBs 1P with AS or FC	1.5			5ST3732	1	1 unit	1AD
Two-phase								
For 6 MCBs 2P	1			5ST3734	1	1 unit	1AD	
For 4 MCBs 2P with AS or FC	1+1.5			5ST3736	1	1 unit	1AD	
Three-phase								
For 4 MCBs 3P	1		▶	5ST3738	1	1 unit	1AD	
For 3 MCBs 3P with AS or FC	1+1+1.5			5ST3741	1	1 unit	1AD	
For 3 MCBs 1P with AS or FC	1.5			5ST3743	1	1 unit	1AD	
Four-phase								
For 3 MCBs 4P or 3P+N	1			5ST3745		1	1 unit	1AD
5ST37 busbar system, 10 mm ² , 56 MW for miniature circuit breakers, can be cut, without end caps								
	Single-phase, angled							
	For MCBs 1P	1	1016		5ST3731	1	1 unit	1AD
	For MCBs 1P with AS or FC	1.5			5ST3733	1	1 unit	1AD
Two-phase								
For MCBs 1P and UR or AR	2			5ST3735-2	1	1 unit	1AD	
For MCBs 2P	1			5ST3735	1	1 unit	1AD	
For MCBs 2P with AS or FC	1+1.5			5ST3737	1	1 unit	1AD	
Three-phase								
For MCBs 3P	1		▶	5ST3740	1	1 unit	1AD	
For MCBs 3P with AS or FC	1+1+1.5			5ST3742	1	1 unit	1AD	
For MCBs 1P with AS or FC	1.5			5ST3744	1	1 unit	1AD	
Four-phase								
For MCBs 4P or 3P+N	1			5ST3746	1	1 unit	1AD	
For MCBs 2P with AS or FC and RCBOs 1P+N with AS or FC	1+1.5			5ST3746-2	1	1 unit	1AD	

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Busbars

5ST standard busbars

	Pin spacing MW ¹⁾	Length mm	SD d	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
5ST37 busbar system, 16 mm², 12 MW for miniature circuit breakers, can be cut, with end caps								
	Single-phase, angled							
	For MCBs 1P	1	214	▶ 5ST3700		1	1 unit	1AD
	For MCBs 1P with AS or FC	1.5		▶ 5ST3702		1	1 unit	1AD
	Two-phase							
	For MCBs 2P	1		▶ 5ST3704		1	1 unit	1AD
	For MCBs 2P with AS or FC	1+1.5		▶ 5ST3706		1	1 unit	1AD
	Three-phase							
	For MCBs 3P	1		▶ 5ST3708		1	1 unit	1AD
	For MCBs 3P with AS or FC	1+1+1.5		▶ 5ST3711		1	1 unit	1AD
	For MCBs 1P with AS or FC	1.5		▶ 5ST3713		1	1 unit	1AD
	Four-phase							
	For MCBs 4P or 3P+N	1		▶ 5ST3715		1	1 unit	1AD
5ST37 busbar system, 16 mm², 56 MW for miniature circuit breakers, can be cut, without end caps								
	Single-phase, angled							
	For MCBs 1P	1	1016	▶ 5ST3701		1	1 unit	1AD
	For MCBs 1P with AS or FC	1.5		▶ 5ST3703		1	1 unit	1AD
	Two-phase							
	For MCBs 2P	1		▶ 5ST3705		1	1 unit	1AD
	For MCBs 2P with AS or FC	1+1.5		▶ 5ST3707		1	1 unit	1AD
	Three-phase							
	For MCBs 3P	1		▶ 5ST3710		1	1 unit	1AD
	For MCBs 3P with AS or FC	1+1+1.5		▶ 5ST3712		1	1 unit	1AD
	For MCBs 1P with AS or FC	1.5		▶ 5ST3714		1	1 unit	1AD
	Four-phase							
	For MCBs 4P or 3P+N	1		▶ 5ST3716		1	1 unit	1AD
5ST37 busbar system, 10 mm², 56 MW can be cut, without end caps, with touch protection								
Four-phase								
For MCBs 2P and RCBOs 1P+N	1	1000		▶ 5ST3770-2		1	10 units	1AD
5ST37 busbar system, 16 mm², 56 MW can be cut, without end caps, with touch protection								
Four-phase								
For MCBs 2P and RCBOs 1P+N	1	1000		▶ 5ST3770-3		1	10 units	1AD
5ST37 busbar system, 10 mm², 16 MW can be cut, with end caps, with touch protection								
Four-phase								
For RCCBs 4P, N right and 6 MCBs 1P+N	1	292		▶ 5ST3770-4		1	10 units	1AD
5ST37 busbar system, 16 mm², 16 MW can be cut, with end caps, with touch protection								
Four-phase								
For RCCBs 4P, N right and 6 MCBs 1P+N	1	292		▶ 5ST3770-5		1	10 units	1AD
End caps for 5ST37, can be cut								
	For single-phase busbars		▶	5ST3748		1	10 units	1AD
	For two-phase and three-phase busbars		▶	5ST3750		1	10 units	1AD
	For four-phase busbars		▶	5ST3718		1	10 units	1AD
Terminals for 5ST36 and 5ST37 busbars								
	Terminals for conductors up to 25 mm²							
	• With cable entry in the center			▶ 5ST3768-3		1	10 units	1AD
	• With cable entry on the left			▶ 5ST3768-4		1	10 units	1AD
	• With cable entry on the right			▶ 5ST3768-5		1	10 units	1AD
	Terminals for conductors up to 50 mm²							
	• With cable entry in the center			▶ 5ST3760-3		1	10 units	1AD
	• With cable entry on the left			▶ 5ST3760-4		1	10 units	1AD
	• With cable entry on the right			▶ 5ST3760-5		1	10 units	1AD
	Note							
	The terminals are not suitable for 5ST376.							

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Busbars



5ST standard busbars

		Length of cable	Number of phases	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
		mm		d					
Series connectors, 10 mm²									
	• N conductor blue	125	1		5ST3781-0		1	10 units	1AD
	• Cable black				5ST3791-0		1	10 units	1AD
	• Cable black		3		5ST3793-0		1	3 units	1AD
	• N conductor blue	150	1		5ST3781-1		1	10 units	1AD
	• Cable black				5ST3791-1		1	10 units	1AD
	• Cable black		3		5ST3793-1		1	3 units	1AD
Series connectors, 16 mm²									
	• N conductor blue	125	1		5ST3782-0		1	10 units	1AD
	• Cable black				5ST3792-0		1	10 units	1AD
	• Cable black		3		5ST3794-0		1	3 units	1AD
	• N conductor blue	150	1		5ST3782-1		1	10 units	1AD
	• Cable black				5ST3792-1		1	10 units	1AD
	• Cable black		3		5ST3794-1		1	3 units	1AD
	• N conductor blue	200	1		5ST3781-2		1	10 units	1AD
	• Cable black				5ST3791-2		1	10 units	1AD
	• Cable black		3		5ST3793-2		1	3 units	1AD
	• Cables: - 3 x black - 1 x blue		3+N		5ST3793-3		1	3 units	1AD

Miniature Circuit Breakers

Busbars

5ST standard busbars

	Pin spacing	Length	SD	Article No. www.siemens.com/product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
5ST37 busbar system, 10 mm², 12 MW for 1+N miniature circuit breakers in 1 MW of the compact range, can be cut, with end caps								
	Single-phase							
	For 12 MCBs 1+N, gray	1	216	5ST3762		1	10 units	1AD
	For 12 MCBs 1+N, blue	1		5ST3763		1	10 units	1AD
5ST37 busbar system, 10 mm², 56 MW for 1+N miniature circuit breakers in 1 MW of the compact range, can be cut, without end caps								
	Single-phase							
	For MCBs 1+N, gray	1	1016	5ST3764		1	10 units	1AD
	For MCBs 1+N, blue	1		5ST3765		1	10 units	1AD
End caps for 5ST376								
	1 set comprises a right and a left cap							
	Gray			5ST3766		1	10 sets	1AD
	Blue			5ST3767		1	10 sets	1AD
Terminals								
	Terminals, short							
	- For conductors up to 25 mm² - Infeed on side - Specially for single-phase busbars and for 5ST3615-1 three-phase busbars			5ST3768		1	25 units	1AD
	Terminals, short, IP20							
	- For conductors up to 25 mm² - Infeed on side - Specially for single-phase busbars and for 5ST3615-1 three-phase busbars			5ST3771-2		1	10 units	1AD

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Busbars


5ST standard busbars

Dimensional drawings


5ST36

Pin spacing in MW (modular width; 1 MW = 18 mm)


Dimensions of side view in mm (approx.)




5ST3600
5ST3630
5ST3601
5ST3602
5ST3631
5ST3632
5ST3603
5ST3633
5ST3604
5ST3605
5ST3634
5ST3635




5ST3606
5ST3607
5ST3608




5ST3636
5ST3637
5ST3638
5ST3640
5ST3641
5ST3642




5ST3613
5ST3614
5ST3615
5ST3667
5ST3616
5ST3617
5ST3618
5ST3620



5ST3643
5ST3644
5ST3645
5ST3668
5ST3646
5ST3647
5ST3648
5ST3650




5ST3621
5ST3622
5ST3623




5ST3651
5ST3652
5ST3653

5ST36**Pin spacing in MW (modular width; 1 MW = 18 mm)**

Dimensions of side view in mm (approx.)




5ST3624




5ST3654

5ST37**Pin spacing in MW (modular width; 1 MW = 18 mm)**


Dimensions of side view in mm (approx.)




5ST3700 5ST3702
 5ST3701 5ST3703
 5ST3730 5ST3732
 5ST3731 5ST3733
 Single-phase Single-phase




5ST3704 5ST3706
 5ST3705 5ST3707
 5ST3734 5ST3736
 5ST3735 5ST3737
 Two-phase Two-phase




5ST3708 5ST3711 5ST3713
 5ST3710 5ST3712 5ST3714
 5ST3738 5ST3741 5ST3743
 5ST3740 5ST3742 5ST3744



5ST3715
 5ST3716
 5ST3745
 5ST3746



5ST3746-2



5ST3735-2

Miniature Circuit Breakers


Busbars

5ST standard busbars


5ST37

Pin spacing in MW (modular width; 1 MW = 18 mm)


Dimensions of side view in mm (approx.)




5ST3770-2




5ST3770-3




5ST3770-4



5ST3770-5



5ST3762
5ST3764



5ST3763
5ST3765

Overview


Products according to UL standards are used in North America, but also in several other countries. This is important in particular for exporting machines or electrical switchboard assemblies and equipment to the USA. Acceptance and delivery are possible only if the relevant UL standards are satisfied.

The 5ST37 busbar system according to UL 508 and CSA is suitable for both universal use worldwide with all 5SY and 5SP miniature circuit breakers for "Supplementary Protection" certified according to UL 1077 and for 3NW and 3NC fuse holders certified according to UL 512. Not approved for use in feeder circuits.


The busbars are available in single, two and three-phase versions with different pin spacings and with two cross-sections, 18 mm² and 25 mm². Infeed can be directly into the terminals of the miniature circuit breaker or through connection terminals.

The connection terminals are available in two versions – for direct infeed at the busbar or for infeed directly at the miniature circuit breaker/fuse holder. Pins that are not required can be covered with touch protection covers.


Benefits



- Busbar with infeed through a connection terminal directly on the miniature circuit breaker up to a conductor cross-section of 35 mm².



- Infeed directly on the miniature circuit breaker up to a conductor cross-section of 35 mm² and connection terminal for connection directly on the busbar up to a conductor cross-section of 50 mm²
- Suitable for universal use according to both IEC and UL standards
- Can be used for 5SY, 5SP miniature circuit breakers and for Class CC, SITOP cylindrical and semiconductor fuse holders
- UL-tested combination – device and busbar
- Different cross-sections 18 mm² and 25 mm²



- Bus mounting with infeed at the fuse holder for conductor cross-sections up to 35 mm².

Miniature Circuit Breakers


Busbars

5ST3 busbars acc. to UL 508


Technical specifications

			5ST37...-0HG	5ST37...-2HG	5ST3770-0HG	5ST3770-1HG
Standards			UL 508, CSA C22.2 No. 14-M 95 / IEC 60999			
Approvals			UL 508 File No. E328403 CSA			
Operational voltage						
• Acc. to IEC			V AC	690		
• Acc. to UL 508			V AC	600		
Rated conditional short-circuit current			kA	10		
• Dielectric strength			kV/mm	25		
• Surge strength			kV	> 9.5		
Max. current	UL	A	--	--	115	
	IEC	A	--	--	160	
Maximum busbar current I_S per phase						
• Infeed at the start of the busbar			A	80	100	--
• Infeed at the center of the busbar			A	160	200	--
Insulation coordination						
• Overvoltage category			III			
• Pollution degree			2			
Short-circuit current load capability						
18 mm ²			10000 A RMS sym. 600 V for three circuits			
25 mm ²			100000 A RMS sym. for protection with Class J 175 A			
			100000 A RMS sym. for protection with Class J 200 A			
Busbar cross-section			mm ² Cu	18	25	--
Infeed			Any			
Conductor cross-sections	Solid	AWG	--	--	10 ... 1/0	10 ... 1
		mm ²	--	--	6 ... 35 (Cu 60 °C)	6 ... 50 (Cu 75 °C)
	Stranded	AWG	--	--	10 ... 2	
		mm ²	--	--	6 ... 35	
Terminals						
± screw (Pozidriv)			--	--	2	2
• Terminal tightening torque			Nm	--	5	3.5
			lb-in	--	50	35

Infeed at the start or end of the busbar



Infeed along the busbar or midpoint infeed





The sum of the outgoing current per branch (1, 2, 3 ... n) must not be greater than the max. busbar current I_S /phase.

Miniature Circuit Breakers

Busbars

5ST3 busbars acc. to UL 508

Selection and ordering data

	Pin spacing	Length	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
5ST37...-HG busbars acc. to UL 508, 18 mm², can be cut, without end caps								
	Single-phase							
	• For MCBs 1P (5SY) or fuse holders 10 x 38 mm/class CC (3NC1091, 3NW7513-0HG)	1	1000	5ST3701-0HG		1	1 unit	1AE
	• For MCBs 1P (5SY, 5SP) with AS or FC or fuse holders 14 x 51 mm (3NC1491, 3NW7111)	1.5	1000	5ST3703-0HG		1	1 unit	1AE
	Two-phase							
	• For MCBs 2P (5SY) or fuse holders 10 x 38 mm/class CC (3NC1092, 3NW7523-0HG)	1	1000	5ST3705-0HG		1	1 unit	1AE
	• For MCBs 2P (5SY) with AS or FC	1+1.5	1000	5ST3707-0HG		1	1 unit	1AE
	Three-phase							
	• For MCBs 3P (5SY) or fuse holders 10 x 38 mm/class CC (3NC1093, 3NW7533-0HG)	1	1000	5ST3710-0HG		1	1 unit	1AE
	• For MCBs 3P (5SY) with AS or FC	1+1+1.5	1000	5ST3712-0HG		1	1 unit	1AE
	• For MCBs 1P (5SY, 5SP) with AS or FC or fuse holders 14 x 51 mm (3NC1493, 3NW7131)	1.5	1000	5ST3714-0HG		1	1 unit	1AE
5ST37...-HG busbars acc. to UL 508, 25 mm², can be cut, without end caps								
	Single-phase							
	For MCBs 1P (5SP) or fuse holders 14 x 51 mm (3NC1491, 3NW7111)	1.5	1000	5ST3701-2HG		1	1 unit	1AE
	Two-phase							
	For MCBs 2P (5SP) or fuse holders 14 x 51 mm (3NC1492, 3NW7121)	1.5	1000	5ST3705-2HG		1	1 unit	1AE
	Three-phase							
	For MCBs 3P (5SP) or fuse holders 14 x 51 mm (3NC1493, 3NW7131)	1.5	1000	5ST3710-2HG		1	1 unit	1AE
End caps for 5ST37...-HG								
	• For single-phase busbars			5ST3748-0HG		1	10 units	1AE
	• For two- and three-phase busbars			5ST3750-0HG		1	10 units	1AE
Terminals according to UL 508								
	Infeed to device							
	35 mm ²			5ST3770-0HG		1	10 units	1AE
	Infeed to busbar							
	50 mm ²			5ST3770-1HG		1	10 units	1AE
Touch protection cover for busbars according to UL 508								
	5 x 1 pin			5ST3655-0HG		1	10 units	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Busbars


5ST3 busbars acc. to UL 508

Dimensional drawings


5ST37 busbars

Pin spacing in MW (modular width; 1 MW = 18 mm)


Dimensions of side view in mm (approx.)




5ST3701-0HG 5ST3703-0HG




5ST3705-0HG 5ST3707-0HG




5ST3710-0HG 5ST3712-0HG 5ST3714-0HG




5ST3701-2HG




5ST3705-2HG



5ST3710-2HG




5ST3750-0HG



5ST3748-0HG

5ST3770-0HG




5ST3770-1HG

5ST36 touch protection covers

Pin spacing in MW (modular width; 1 MW = 18 mm)

Dimensions of side view in mm (approx.)



5ST3655-0HG

Overview

Distribution blocks for standard rail mounting

Using distribution blocks it is possible to implement single, two, three and four-phase systems with a rated current of up to 400 A. This allows supply terminals to be divided into several load circuits with different cable cross-sections.

The distribution blocks are made of thermoplastic with electrical and mechanical components, which enables their use under high thermal and mechanical load acc. to IEC 60947-7-1.

Technical specifications

			5ST2501	5ST2502	5ST2503
Standards, certifications			IEC 60947-7-1		
Degree of protection			IP20		
Poles			4		
Approved cable			Copper		
Conductor cross-section					
• Inputs per pole - Solid/stranded conductor acc. to IEC		mm²	1 x 2.5 ... 16	1 x 6 ... 35	1 x 10 ... 50
	Neutral conductor	mm²	1 x 1.5 ... 16	1 x 6 ... 35	--
	- Finely stranded with end sleeve	mm²	1 x 1.5 ... 10	1 x 6 ... 25	1 x 10 ... 35
	Neutral conductor	mm²	--	1 x 6 ... 25	--
• Outputs per pole - Solid/stranded conductor acc. to IEC	Large	mm²	8 x 1.5 ... 10	2 x 4 ... 16	3 x 10 ... 35
	Small	mm²	--	5 x 1.5 ... 6	8 x 2.5 ... 16
	Neutral conductor	Large	mm²	6 x 4 ... 16	--
		Small	mm²	--	--
	- Finely stranded with end sleeve	Large	mm²	4 x 1.5 ... 10	3 x 10 ... 25
		Small	mm²	2 x 4 ... 10	--
	Neutral conductor	Small	mm²	8 x 1.5 ... 10	8 x 1.5 ... 16
		Large	mm²	5 x 1.5 ... 6	--
	Small	mm²	6 x 4 ... 10	--	
			4 x 1.5 ... 6	--	
Tightening torque					
• Inputs		lb-in	13.5	13.5	3.5 ... 5
	Plug-in connection	Nm	1.5 PZ2	1.5 PZ2	2 PZ2
• Outputs	Large	lb-in	13.5	13.5	13.5
		Nm	1.5	1.5	1.5
	Plug-in connection		PZ1	PZ2	PZ2
	Small	lb-in	--	7.2	13.5
	Nm	--	0.8	1.5	
Plug-in connection		--	PZ1	PZ2	
Operational voltage					
• IEC, max.		V	690	690	690
Overcurrent protection					
• Max. rated current		A	80	125	160
• Rated peak withstand current (<i>I</i> _{pk})		kA	21.6	24	20
• Rated short-time withstand current (<i>I</i> _{cw} 1 s)		kA	3	4.2	6.2
Block dimensions (D x H x W)		mm	88 x 49 x 85	75 x 45 x 98	102 x 47 x 87

Miniature Circuit Breakers

Busbars

5ST2 distribution blocks

UL types

		5ST2504	5ST2505	5ST2507	5ST2508	5ST2511
Standards, certifications		UL 1059 / UL 486E / IEC 60947-7-1 UL File No. E80027 / XCFR2 C22.2 No. 158 -1987 / XCFR8				
Degree of protection		IP20				
Poles		1				
Approved cable		Copper				
Wiring type • Front/back		Factory and field wiring Pressure wire connector				
Conductor cross-section						
• Inputs						
- Solid and stranded conductor acc. to UL	Large AWG	3 x 14 ... 4	1 x 8 ... 2	1 x 8 ... 2 / 0	1 x 2 ... 4 / 0	1 x 3 / 0 ... 350 MCM
- Solid and stranded acc. to IEC	mm ²	3 x 2.5 ... 25	10 ... 35	10 ... 70	35 ... 120	95 ... 185
- Solid and stranded conductor acc. to UL	Small AWG	--	1 x 14 ... 6	--		
- Solid and stranded acc. to IEC	mm ²	--	2.5 ... 25	--		
- Finely stranded with end sleeve acc. to UL	Large AWG	3 x 14 ... 6	1 x 8 ... 2	1 x 8 ... 1	1 x 2 ... 3 / 0	3 / 0 ... 300 MCM
- Finely stranded with end sleeve acc. to IEC	mm ²	3 x 2.5 ... 16	10 ... 35	10 ... 50	35 ... 95	95 ... 150
- Finely stranded with end sleeve acc. to UL	Small AWG	--	1 x 14 ... 6	--		
- Finely stranded with end sleeve acc. to IEC	mm ²	--	2.5 ... 25	--		
• Outputs						
- Solid and stranded conductor acc. to UL	Top AWG	4 x 14 ... 10	6 x 14 ... 4	6 x 14 ... 4	4 x 16 ... 8	2 x 14 ... 2
- Solid and stranded acc. to IEC	mm ²	2.5 ... 6	2.5 ... 16	2.5 ... 16	2.5 ... 10	2 x 2.5 ... 35
- Solid and stranded conductor acc. to UL	Center AWG	--			5 x 14 ... 6	
- Solid and stranded acc. to IEC	mm ²	--			2.5 ... 16	5 x 2.5 ... 16
- Solid and stranded conductor acc. to UL	Bottom AWG	4 x 14 ... 10	--		2 x 14 ... 2	4 x 14 ... 8
- Solid and stranded acc. to IEC	mm ²	2.5 ... 6	--		2 x 2.5 ... 35	4 x 2.5 ... 10
- Finely stranded with end sleeve acc. to UL	Top AWG	4 x 14 ... 10	6 x 14 ... 6	6 x 14 ... 6	2 x 14 ... 4	
- Finely stranded with end sleeve acc. to IEC	mm ²	2.5 ... 6	2.5 ... 16	2.5 ... 16	2 x 2.5 ... 25	
- Finely stranded with end sleeve acc. to UL	Bottom AWG	4 x 14 ... 10	--		2 x 14 ... 4	5 x 14 ... 4
- Finely stranded with end sleeve acc. to IEC	mm ²	2.5 ... 6	--		2 x 2.5 ... 25	4 x 2.5 ... 25
Tightening torque						
• Inputs	lb-in	13.2 ... 26.5	31 ... 44	44 ... 53	170 ... 186	222
	Nm	1.5 ... 3	3.5 ... 5	5 ... 6	19 ... 21	25
	Plug-in connection		Allen key (4 mm)	Allen key (5 mm)	Allen key (6 mm)	Allen key (8 mm)
• Outputs	Large lb-in	13.2 ... 26.5	17.7 ... 26.5	13.2 ... 26.5	31 ... 62	
	Nm	1.5 ... 3	2 ... 3	1.5 ... 3	3.5 ... 7	
	Plug-in connection	PZ2			Standard screwdriver	
	Small lb-in	7 ... 13.2	--		18 ... 27	
	Nm	0.8 ... 1.5	--		2 ... 3	
	Plug-in connection	PZ1	--		Standard screwdriver	
Amperes per pole, max. (UL/IEC)	A	80/80	115/125	160/160	230/250	310/400
Operational voltage						
• UL, max. (AC)	V	600				
• IEC, max. (AC/DC)	V	1000/1500				
Overcurrent protection						
• Required class		J				
• Max. rated current (UL/IEC)	A	80/80	115/125	160/160	230/250	310/400
• SCCR RMS Sym A	kA	100				
• Rated peak withstand current (I_{pk})	kA	2.7	30		51	
• Rated short-time withstand current (I_{cw} 1 s)	kA	1.9	4.2	11	21	
Clearance						
• Air	inches (mm)	3 / 8 (9.5)				
• Creepage distance	inches (mm)	1 / 2 (12.7)				
Ambient temperature	°C	-25 ... +75				
Fire class		UL 94V-0				
Block dimensions (D x H x W)	mm	66 x 47 x 27	74 x 47 x 27	92 x 49 x 35	96 x 49 x 45	96 x 49 x 45
Connections		With cable up to 16 mm ²	With connector or cable up to 16 mm ² ¹⁾	Lateral incoming feeder for parallel connection with copper bar (max. 16 x 5 mm)	--	--


¹⁾ Copper jumper is tested for a rated current of 100 A

Miniature Circuit Breakers

Busbars

5ST2 distribution blocks

Selection and ordering data


	Version	Standard	I	U	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
			A	V	MW	d					
Distribution blocks											
	1-pole	UL 1059 / UL 486E / IEC 60947-7-1	80	600	1.5		5ST2504		1	1 unit	1AD
			125	600	1.5		5ST2505		1	1 unit	1AD
		UL File No. E80027 / XCFR2	160	600	2	▶	5ST2507		1	1 unit	1AD
		C22.2 No. 158 -1987 / XCFR8									
		UL 486E / IEC 60947-7-1	250	600	2.5	▶	5ST2508		1	1 unit	1AD
		UL File No. E80027 / XCFR2	350	600	2.5	▶	5ST2511		1	1 unit	1AD
5ST2504											
	4-pole	IEC 60947-7-1	80	500	5		5ST2501		1	1 unit	1AD
5ST2501											
		IEC 60947-7-1	125	690	5.5		5ST2502		1	1 unit	1AD
5ST2502											
		IEC 60947-7-1	160	500	9		5ST2503		1	1 unit	1AD
5ST2503											
Accessories											
	Connector for 5ST2505 distribution board		--	--	--		5ST2506		1	10 units	1AD
	• With touch protection • 20 mm ² • Single-phase • 32 mm										
5ST2506											
	Terminal lug ring terminal end for distribution block										
	Versions						5ST2510 5ST2512		1 1	10 units 10 units	1AD 1AD
		• For 5ST2508 distribution block • For 5ST2511 distribution block									

Miniature Circuit Breakers


Busbars

5ST2 distribution blocks


Dimensional drawings




5ST2504




5ST2505




5ST2507




5ST2508




5ST2511



5ST2501



5ST2502



5ST2503

Overview

SIKclip is a fast wiring system that simplifies the connection of control switches:

- For mounting directly on the rear vertical CU busbar system
- Mounting using brackets on the rear of the standard mounting rail.

The 4-pole busbar can handle loads of up to 250 A, each individual contact up to 63 A.

High degree of protection because each contact is locked individually.

SIKclip is made of thermoplastic acc. to IEC 60439-3 and is suitable for high thermal loads.

Technical specifications

			5ST25..
Test specifications			EN 60947-1, EN 61439-1
Degree of protection			IP20
Max. rated current I_n	A		250 at 40 °C ambient temperature
Max. rated output current I_n	A		63 at 40 °C ambient temperature
Rated operational voltage U_n	V AC		400
Rated insulation voltage	V AC		660
Test voltage	kV		2.5, 50 Hz
Connecting cables			40 A (6 mm ²), 63 A (10 mm ²)
Connecting cable type			H07VK
Ambient temperature	°C		-5 ... +60

Selection and ordering data

	Length	Conductor cross-section	Color of insulation	SD	Article No. www.siemens.com/product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	mm	mm ²		d					
	SIKclip busbar								
	12 MW				5ST2520		1	1 unit	1AD
	24 MW				5ST2521		1	1 unit	1AD
	36 MW				5ST2522		1	1 unit	1AD
	Connecting cables with plug								
	120	6	Black		5ST2523		1	10 units	1AD
			Blue		5ST2524		1	10 units	1AD
		10	Black		5ST2525		1	10 units	1AD
			Blue		5ST2526		1	10 units	1AD
	220	6	Black		5ST2527		1	10 units	1AD
			Blue		5ST2528		1	10 units	1AD
		10	Black		5ST2530		1	10 units	1AD
			Blue		5ST2531		1	10 units	1AD
	Crimp connectors				5ST2532		1	20 units	1AD
	For connection to cables 4/6 mm ²								
	Fixing brackets				5ST2533		1	2 units	1AD
	For mounting on the rear of the standard mounting rail (pair)								

Note:

To install the SIKclip wiring system in the ALPHA AS, the busbars must be installed in a vertical rear position, but not recessed. If the busbars are in a recessed position the cables will not reach the circuit breakers.


Miniature Circuit Breakers

Busbars

SIKclip wiring system

Dimensional drawings

3



Overview

UL standards are used in North America as well as in several other countries. This is of particular importance to European exporters of electrical switchboard assemblies and equipment for machines who export to the USA, as their products will only be accepted if they meet the relevant UL standards.

A wide range of low-voltage circuit protection devices from Siemens comply with UL standards and are therefore suitable for implementation worldwide in both IEC/EN and UL applications within the framework of their specified use.

Miniature circuit breakers certified to UL 489 permit use as an all-round solution for protection tasks in distribution boards, control cabinets and control systems to UL 508A as "branch protectors". In particular, they are also approved for the protection of electrical circuits in heating, ventilating and cooling systems (HVAC), as well as for DC applications up to 60 V/125 V.

This covers a wide range of protection tasks, both in residential and non-residential buildings, as well as in industry. The tripping characteristics B, C and D to IEC/EN 60898-1 have been adapted so that they fall in the permissible tripping range according to UL 489, as well as for applications at 25 °C and 40 °C.

This means that the devices are approved for use according to both standards. The enclosure dimensions of the devices correspond to DIN format. This means that the device series are suitable for universal use worldwide according to IEC or UL standards.

The key difference between the three device series is their application in different power supply systems.

- 5SJ4...-HG40: 240/120 V AC, 1-pole, "same polarity only",
- 5SJ4...-HG41: 240 V AC, 1-, 2- and 3-pole,
- 5SJ4...-HG42: 480Y/277 V AC, 1-, 2- and 3-pole.


The terminals are suitable for "field wiring". This means that the devices can be installed not only in factory-built distribution boards and control cabinets, but also on-site in a customer system.

Using this mounting concept, all 5ST3...-HG additional components can be combined with miniature circuit breakers of the 5SJ4...-HG range. The auxiliary switch (AS) signals the contact position. In the event of a fault, the fault signal contact (FC) signals the automatic tripping of the miniature circuit breaker as well as the contact position. Shunt trips (ST) are used for remote tripping of miniature circuit breakers. Captive metal brackets on the additional components ensure fast mounting on the devices.


Single, two and three-phase busbars in 3 lengths with 6, 12 or 18 pins are available as accessories for all device series for "field wiring". The infeed is via connection terminals, which are available in two versions, for direct infeed at either the busbar or the miniature circuit breakers. Pins that are not required can be covered with touch protection covers.

Benefits


- Can be used globally for all applications in residential, non-residential and industrial buildings. This facilitates the planning of installations and enhances export opportunities
- The devices can be used according to IEC/EN 60898-1 and UL 489, which means they can be installed anywhere in the world
- Miniature circuit breakers with 480Y/277 V up to 40 A, with 240/120 V and 240 V up to 63 A
- Can be used for both AC voltage and DC voltage up to 125 V
- Rated breaking capacity up to 14 kA in acc. with UL 489 and up to 15 kA in acc. with IEC 60947-2
- Fast mounting with busbars up to 115 A and feeder terminals up to 50 mm²



- Infeed directly at miniature circuit breaker for conductor cross-sections up to 35 mm²



- Bus mounting with central infeed directly on the busbar up to conductor cross-section of 50 mm²



- Accessories: Auxiliary switches, fault signal contacts and shunt trips up to 480 V can be easily mounted onto the miniature circuit breaker

Miniature Circuit Breakers

5SJ4...-HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

Technical specifications

		5SJ4...-HG40	5SJ4...-HG41	5SJ4...-HG42
Standards		EN 60947-2; UL 489 (UL File E243414); UL 489A (UL File E332105); CSA 22.2 No. 5-02		
Approvals		see chapter "Appendix"		
Tripping characteristic		B, C, D	C, D	
Rated voltage				
• Acc. to EN 60947-2	V AC	230/400	230/400	230/400
• Acc. to UL 489 and CSA C22.2 No 5-02	V AC V DC/1P V DC/2P	240/120 60 --	240 60 125	480/277 60 125
Operational voltage	Min.	V AC/DC per pole	24	
• Acc. to IEC 60947-2	Max.	V DC/pole	72	
• Acc. to UL 489	Max.	V AC V DC/pole	250/440 60	
Rated breaking capacity				
• I_{cu} acc. to IEC 60947-2	kA AC	10		
• Acc. to UL 489/UL 489A and CSA C22.2 No. 5-02	kA AC	14/10 ¹⁾	14/10 ¹⁾	10 ¹⁾
Insulation coordination				
• Rated insulation voltage	V AC	250	250/440	
• Pollution degree for overvoltage category		3/III		
Rated frequency	Hz	50/60		
Touch protection acc. to EN 50274		Yes		
Handle end position, sealable		Yes		
Degree of protection acc. to EN 60529		IP40 in the area of the handle		
CFC and silicone-free		Yes		
Mounting		On standard mounting rail		
Terminals	± screw (Pozidriv)	2		
• Combined terminals at both ends		Yes		
• Terminal tightening torque, only for Cu, 60/75 °C	Nm lb-in	3.5 31		
Conductor cross-sections				
• Solid and stranded, acc. to UL 489 and CSA 22.2 No 5-02	AWG	18 ... 4		
• Solid and stranded, acc. to IEC 60898-1	mm ²	0.75 ... 25		
• Finely stranded, with end sleeve	mm ²	0.75 ... 25		
Mains connection		Any		
Mounting position		Any		
Service life, on average, with rated load		20000 actuations		
EMC environment				
• Acc. to EN 60947-2		Suitable for environment "B" (immunity to interference not applicable)		
Ambient temperature	°C	-25 ... +55, max. 95% humidity		
Storage temperature	°C	-40 ... +75, 95% humidity up to 55 °C		
Resistance to climate acc. to IEC 60068-2-30		6 cycles		
Resistance to vibrations acc. to IEC 60068-2-6	m/s ²	50 at 25 ... 150 Hz and 60 at 35 Hz (4 s)		

¹⁾ For detailed information about rated switching capacity, see Configuration Manual "Miniature Circuit Breakers" (www.siemens.com/lowvoltage/manuals).

5SJ4...HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

3

Additional components		Auxiliary switches (AS)		Fault signal contacts (FC)		Shunt trips (ST)	
		5ST3010-0HG 5ST3011-0HG 5ST3012-0HG		5ST3020-0HG 5ST3021-0HG 5ST3022-0HG		5ST3030-0HG	5ST3031-0HG
Standards		UL 489, UL File E321559; CSA 22.2 No. 5-02 IEC/EN 62019, IEC/EN 60947-5-1					
Operational voltage/operational current (load)							
• Acc. to IEC/EN 62019 (acc. to IEC/EN 60947-5-1)	V AC	400	230			110 ... 415	24 ... 60
	NC: AC-13 A, NO: AC-14 A	2	6			--	--
	V DC	220	110	60	24	--	24 ... 60
	DC-13 A	1 (0.5)	1 (0.75)	3 (1.5)	6 (3)	--	--
• Acc. to UL	V AC	480	277	240	120	110 ... 480	24 ... 60
	A AC	1.5	3	4	6	--	--
	V DC	125	60			--	24 ... 60
	A DC	1	3			--	--
Rated frequency	Hz	50/60					
Short-circuit protection		Miniature circuit breaker or 6 A fuse					
Minimum contact load		50 mA, 24 V					
Tripping operations		--		--		Max. 2000	
Service life, on average, with rated load		12000 actuations					
Primary operating range	x U_n	--				0.7 ... 1.1	
Conductor cross-sections	AWG mm ²	22 ... 14 0.5 ... 2.5				22 ... 14 0.5 ... 2.5	
Terminals	± screw (Pozidriv)	1		1		1	
• Terminal tightening torque	Nm	0.5				0.8	
	lb-in	4.5				6.8	

Version	Busbars		Busbars, can be cut	Terminals		
Type	5ST3663-.HG ¹⁾ 5ST3664-.HG ¹⁾ 5ST3665-.HG ¹⁾		5ST3701-3HG 5ST3703-3HG 5ST3705-3HG 5ST3707-3HG 5ST3710-3HG 5ST3712-3HG 5ST3714-3HG	5ST3666-0HG ¹⁾	5ST3666-2HG ¹⁾	5ST3770-3HG
Standards	UL 489; UL File No. E321559		UL 489; UL File No. E315616	UL 489; UL File No. E321559		UL 489; UL File No. E315616
Operational voltage • Acc. to IEC • Acc. to UL 489	V AC V AC	1000/1-pole 1000/1-pole		600/2- to 3-pole 600/2- to 3-pole (60 Hz)		
Rated conditional short-circuit current • Dielectric strength • Surge strength	kA kV/mm kV	10 kA at 600 V 35 > 9.5	10 kA at 600 V with J 175 A fuse > 10	10 kA at 600 V > 9.5		10 kA at 600 V with J 175 A fuse > 10
Rated current	A	115 at 40 °C ambient temperature	80 (infeed end) 160 (infeed center) at 35 °C ambient temperature	115 (Cu 75 °C) 95 (Cu 60 °C) at 40 °C ambient temperature	115 (Cu 75 °C) 110 (Cu 60 °C) at 40 °C ambient temperature	115 (Cu 75 °C) 95 (Cu 60 °C) at 35 °C ambient temperature
Insulation coordination • Pollution degree • Overvoltage category	2 III					
Busbar cross-section (Cu)	mm ²	16	18	16		
Infeed	Any					
Conductor cross-sections • AWG cables • Solid and stranded	AWG mm ²	-- --		14 ... 2 2.5 ... 35	14 ... 1 2.5 ... 50	14 ... 2 2.5 ... 35
Terminals • Terminal tightening torque	Nm lb-in	-- -- --		6 mm Allen key 5.5 50	± screw (Pozidriv) 2 4 35	6 mm Allen key 5.5 50
Temperature resistance	°C	125 – UL 94-V0/0.4 mm				
Interrupting rating	10 kA at 600 V AC/DC					

1) Note:

The busbars and terminals are suitable for applications up to 80 A if installed in distribution boards with min. dimensions of 18 x 18 x 6.25 inches, or up to 115 A if installed in distribution boards with min. dimensions of 30 x 30 x 10 inches.

Miniature Circuit Breakers

5SJ4. . . - .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

Selection and ordering data

I_n	Mounting width	SD	Characteristic B	Price per PU	PU (UNIT, SET, M)	PS	PG
			Article No. www.siemens.com/product?Article No.				
A	MW ¹⁾	d					
Miniature circuit breakers "same polarity only" 1P, 240 V AC							
6	1		5SJ4106-6HG40		1	1 unit	1AE
10			5SJ4110-6HG40		1	1 unit	1AE
13			5SJ4113-6HG40		1	1 unit	1AE
15			5SJ4118-6HG40		1	1 unit	1AE
16			5SJ4116-6HG40		1	1 unit	1AE
20			5SJ4120-6HG40		1	1 unit	1AE
25			5SJ4125-6HG40		1	1 unit	1AE
30			5SJ4130-6HG40		1	1 unit	1AE
32			5SJ4132-6HG40		1	1 unit	1AE
35			5SJ4135-6HG40		1	1 unit	1AE
40			5SJ4140-6HG40		1	1 unit	1AE
45			5SJ4145-6HG40		1	1 unit	1AE
50			5SJ4150-6HG40		1	1 unit	1AE
60			5SJ4160-6HG40		1	1 unit	1AE
63			5SJ4163-6HG40		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.



Miniature Circuit Breakers

5SJ4. . . - .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

			Characteristic C				Characteristic D						
I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
A	MW ¹⁾	d						d					
	Miniature circuit breakers "same polarity only" 1P, 240 V AC												
	0.3	1	5SJ4114-7HG40		1	1 unit	1AE		5SJ4114-8HG40		1	1 unit	1AE
	0.5		5SJ4105-7HG40		1	1 unit	1AE		5SJ4105-8HG40		1	1 unit	1AE
	1		5SJ4101-7HG40		1	1 unit	1AE		5SJ4101-8HG40		1	1 unit	1AE
	1.6		5SJ4115-7HG40		1	1 unit	1AE		5SJ4115-8HG40		1	1 unit	1AE
	2		5SJ4102-7HG40		1	1 unit	1AE		5SJ4102-8HG40		1	1 unit	1AE
	3		5SJ4103-7HG40		1	1 unit	1AE		5SJ4103-8HG40		1	1 unit	1AE
	4		5SJ4104-7HG40		1	1 unit	1AE		5SJ4104-8HG40		1	1 unit	1AE
	5		5SJ4111-7HG40		1	1 unit	1AE		5SJ4111-8HG40		1	1 unit	1AE
	6		5SJ4106-7HG40		1	1 unit	1AE		5SJ4106-8HG40		1	1 unit	1AE
	8		5SJ4108-7HG40		1	1 unit	1AE		5SJ4108-8HG40		1	1 unit	1AE
	10		5SJ4110-7HG40		1	1 unit	1AE		5SJ4110-8HG40		1	1 unit	1AE
	13		5SJ4113-7HG40		1	1 unit	1AE		5SJ4113-8HG40		1	1 unit	1AE
	15		5SJ4118-7HG40		1	1 unit	1AE		5SJ4118-8HG40		1	1 unit	1AE
	16		5SJ4116-7HG40		1	1 unit	1AE		5SJ4116-8HG40		1	1 unit	1AE
	20		5SJ4120-7HG40		1	1 unit	1AE		5SJ4120-8HG40		1	1 unit	1AE
	25		5SJ4125-7HG40		1	1 unit	1AE		5SJ4125-8HG40		1	1 unit	1AE
	30		5SJ4130-7HG40		1	1 unit	1AE		5SJ4130-8HG40		1	1 unit	1AE
	32		5SJ4132-7HG40		1	1 unit	1AE		5SJ4132-8HG40		1	1 unit	1AE
	35		5SJ4135-7HG40		1	1 unit	1AE		5SJ4135-8HG40		1	1 unit	1AE
	40		5SJ4140-7HG40		1	1 unit	1AE		5SJ4140-8HG40		1	1 unit	1AE
	45		5SJ4145-7HG40		1	1 unit	1AE		5SJ4145-8HG40		1	1 unit	1AE
	50		5SJ4150-7HG40		1	1 unit	1AE		5SJ4150-8HG40		1	1 unit	1AE
	60		5SJ4160-7HG40		1	1 unit	1AE		5SJ4160-8HG40		1	1 unit	1AE
63		5SJ4163-7HG40		1	1 unit	1AE		5SJ4163-8HG40		1	1 unit	1AE	
	Miniature circuit breakers 1P, 240 V AC												
	0.3	1	5SJ4114-7HG41		1	1 unit	1AE		5SJ4114-8HG41		1	1 unit	1AE
	0.5		5SJ4105-7HG41		1	1 unit	1AE		5SJ4105-8HG41		1	1 unit	1AE
	1		5SJ4101-7HG41		1	1 unit	1AE		5SJ4101-8HG41		1	1 unit	1AE
	1.6		5SJ4115-7HG41		1	1 unit	1AE		5SJ4115-8HG41		1	1 unit	1AE
	2		5SJ4102-7HG41		1	1 unit	1AE		5SJ4102-8HG41		1	1 unit	1AE
	3		5SJ4103-7HG41		1	1 unit	1AE		5SJ4103-8HG41		1	1 unit	1AE
	4		5SJ4104-7HG41		1	1 unit	1AE		5SJ4104-8HG41		1	1 unit	1AE
	5		5SJ4111-7HG41		1	1 unit	1AE		5SJ4111-8HG41		1	1 unit	1AE
	6		5SJ4106-7HG41		1	1 unit	1AE		5SJ4106-8HG41		1	1 unit	1AE
	8		5SJ4108-7HG41		1	1 unit	1AE		5SJ4108-8HG41		1	1 unit	1AE
	10		5SJ4110-7HG41		1	1 unit	1AE		5SJ4110-8HG41		1	1 unit	1AE
	13		5SJ4113-7HG41		1	1 unit	1AE		5SJ4113-8HG41		1	1 unit	1AE
	15		5SJ4118-7HG41		1	1 unit	1AE		5SJ4118-8HG41		1	1 unit	1AE
	16		5SJ4116-7HG41		1	1 unit	1AE		5SJ4116-8HG41		1	1 unit	1AE
	20		5SJ4120-7HG41		1	1 unit	1AE		5SJ4120-8HG41		1	1 unit	1AE
	25		5SJ4125-7HG41		1	1 unit	1AE		5SJ4125-8HG41		1	1 unit	1AE
	30		5SJ4130-7HG41		1	1 unit	1AE		5SJ4130-8HG41		1	1 unit	1AE
	32		5SJ4132-7HG41		1	1 unit	1AE		5SJ4132-8HG41		1	1 unit	1AE
	35		5SJ4135-7HG41		1	1 unit	1AE		5SJ4135-8HG41		1	1 unit	1AE
	40		5SJ4140-7HG41		1	1 unit	1AE		5SJ4140-8HG41		1	1 unit	1AE
	45		5SJ4145-7HG41		1	1 unit	1AE		5SJ4145-8HG41		1	1 unit	1AE
	50		5SJ4150-7HG41		1	1 unit	1AE		5SJ4150-8HG41		1	1 unit	1AE
	60		5SJ4160-7HG41		1	1 unit	1AE		5SJ4160-8HG41		1	1 unit	1AE
63		5SJ4163-7HG41		1	1 unit	1AE		5SJ4163-8HG41		1	1 unit	1AE	

1) 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SJ4... - .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

	I_n	Mounting width	SD	Characteristic C				Characteristic D							
				Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG	
	A	MW ¹⁾	d						d						
	Miniature circuit breakers 2P, 240 V AC														
	0.3	2		5SJ4214-7HG41		1	1 unit	1AE		5SJ4214-8HG41			1	1 unit	1AE
	0.5			5SJ4205-7HG41		1	1 unit	1AE		5SJ4205-8HG41			1	1 unit	1AE
	1			5SJ4201-7HG41		1	1 unit	1AE		5SJ4201-8HG41			1	1 unit	1AE
	1.6			5SJ4215-7HG41		1	1 unit	1AE		5SJ4215-8HG41			1	1 unit	1AE
	2			5SJ4202-7HG41		1	1 unit	1AE		5SJ4202-8HG41			1	1 unit	1AE
	3			5SJ4203-7HG41		1	1 unit	1AE		5SJ4203-8HG41			1	1 unit	1AE
	4			5SJ4204-7HG41		1	1 unit	1AE		5SJ4204-8HG41			1	1 unit	1AE
	5			5SJ4211-7HG41		1	1 unit	1AE		5SJ4211-8HG41			1	1 unit	1AE
	6			5SJ4206-7HG41		1	1 unit	1AE		5SJ4206-8HG41			1	1 unit	1AE
	8			5SJ4208-7HG41		1	1 unit	1AE		5SJ4208-8HG41			1	1 unit	1AE
	10			5SJ4210-7HG41		1	1 unit	1AE		5SJ4210-8HG41			1	1 unit	1AE
	13			5SJ4213-7HG41		1	1 unit	1AE		5SJ4213-8HG41			1	1 unit	1AE
	15			5SJ4218-7HG41		1	1 unit	1AE		5SJ4218-8HG41			1	1 unit	1AE
	16			5SJ4216-7HG41		1	1 unit	1AE		5SJ4216-8HG41			1	1 unit	1AE
	20			5SJ4220-7HG41		1	1 unit	1AE		5SJ4220-8HG41			1	1 unit	1AE
	25			5SJ4225-7HG41		1	1 unit	1AE		5SJ4225-8HG41			1	1 unit	1AE
	30			5SJ4230-7HG41		1	1 unit	1AE		5SJ4230-8HG41			1	1 unit	1AE
	32			5SJ4232-7HG41		1	1 unit	1AE		5SJ4232-8HG41			1	1 unit	1AE
	35			5SJ4235-7HG41		1	1 unit	1AE		5SJ4235-8HG41			1	1 unit	1AE
40			5SJ4240-7HG41		1	1 unit	1AE		5SJ4240-8HG41			1	1 unit	1AE	
45			5SJ4245-7HG41		1	1 unit	1AE		5SJ4245-8HG41			1	1 unit	1AE	
50			5SJ4250-7HG41		1	1 unit	1AE		5SJ4250-8HG41			1	1 unit	1AE	
60			5SJ4260-7HG41		1	1 unit	1AE		5SJ4260-8HG41			1	1 unit	1AE	
63			5SJ4263-7HG41		1	1 unit	1AE		5SJ4263-8HG41			1	1 unit	1AE	
	Miniature circuit breakers 3P, 240 V AC														
	0.3	3		5SJ4314-7HG41		1	1 unit	1AE		5SJ4314-8HG41			1	1 unit	1AE
	0.5			5SJ4305-7HG41		1	1 unit	1AE		5SJ4305-8HG41			1	1 unit	1AE
	1			5SJ4301-7HG41		1	1 unit	1AE		5SJ4301-8HG41			1	1 unit	1AE
	1.6			5SJ4315-7HG41		1	1 unit	1AE		5SJ4315-8HG41			1	1 unit	1AE
	2			5SJ4302-7HG41		1	1 unit	1AE		5SJ4302-8HG41			1	1 unit	1AE
	3			5SJ4303-7HG41		1	1 unit	1AE		5SJ4303-8HG41			1	1 unit	1AE
	4			5SJ4304-7HG41		1	1 unit	1AE		5SJ4304-8HG41			1	1 unit	1AE
	5			5SJ4311-7HG41		1	1 unit	1AE		5SJ4311-8HG41			1	1 unit	1AE
	6			5SJ4306-7HG41		1	1 unit	1AE		5SJ4306-8HG41			1	1 unit	1AE
	8			5SJ4308-7HG41		1	1 unit	1AE		5SJ4308-8HG41			1	1 unit	1AE
	10			5SJ4310-7HG41		1	1 unit	1AE		5SJ4310-8HG41			1	1 unit	1AE
	13			5SJ4313-7HG41		1	1 unit	1AE		5SJ4313-8HG41			1	1 unit	1AE
	15			5SJ4318-7HG41		1	1 unit	1AE		5SJ4318-8HG41			1	1 unit	1AE
	16			5SJ4316-7HG41		1	1 unit	1AE		5SJ4316-8HG41			1	1 unit	1AE
	20			5SJ4320-7HG41		1	1 unit	1AE		5SJ4320-8HG41			1	1 unit	1AE
	25			5SJ4325-7HG41		1	1 unit	1AE		5SJ4325-8HG41			1	1 unit	1AE
	30			5SJ4330-7HG41		1	1 unit	1AE		5SJ4330-8HG41			1	1 unit	1AE
	32			5SJ4332-7HG41		1	1 unit	1AE		5SJ4332-8HG41			1	1 unit	1AE
	35			5SJ4335-7HG41		1	1 unit	1AE		5SJ4335-8HG41			1	1 unit	1AE
40			5SJ4340-7HG41		1	1 unit	1AE		5SJ4340-8HG41			1	1 unit	1AE	
45			5SJ4345-7HG41		1	1 unit	1AE		5SJ4345-8HG41			1	1 unit	1AE	
50			5SJ4350-7HG41		1	1 unit	1AE		5SJ4350-8HG41			1	1 unit	1AE	
60			5SJ4360-7HG41		1	1 unit	1AE		5SJ4360-8HG41			1	1 unit	1AE	
63			5SJ4363-7HG41		1	1 unit	1AE		5SJ4363-8HG41			1	1 unit	1AE	

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SJ4. . . - .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

I_n	Mounting width	SD	Characteristic C				PU (UNIT, SET, M)	PS	PG	SD	Characteristic D				PU (UNIT, SET, M)	PS	PG
			Article No.	Price per PU							Article No.	Price per PU					
A	MW ¹⁾	d	www.siemens.com/product?Article No.							d	www.siemens.com/product?Article No.						
Miniature circuit breakers 1P, 480Y/277 V AC																	
	0.3	1	5SJ4114-7HG42				1	1 unit	1AE		5SJ4114-8HG42				1	1 unit	1AE
	0.5		5SJ4105-7HG42				1	1 unit	1AE		5SJ4105-8HG42				1	1 unit	1AE
	1		5SJ4101-7HG42				1	1 unit	1AE		5SJ4101-8HG42				1	1 unit	1AE
	1.6		5SJ4115-7HG42				1	1 unit	1AE		5SJ4115-8HG42				1	1 unit	1AE
	2		5SJ4102-7HG42				1	1 unit	1AE		5SJ4102-8HG42				1	1 unit	1AE
	3		5SJ4103-7HG42				1	1 unit	1AE		5SJ4103-8HG42				1	1 unit	1AE
	4		5SJ4104-7HG42				1	1 unit	1AE		5SJ4104-8HG42				1	1 unit	1AE
	5		5SJ4111-7HG42				1	1 unit	1AE		5SJ4111-8HG42				1	1 unit	1AE
	6		5SJ4106-7HG42				1	1 unit	1AE		5SJ4106-8HG42				1	1 unit	1AE
	8		5SJ4108-7HG42				1	1 unit	1AE		5SJ4108-8HG42				1	1 unit	1AE
	10		5SJ4110-7HG42				1	1 unit	1AE		5SJ4110-8HG42				1	1 unit	1AE
	13		5SJ4113-7HG42				1	1 unit	1AE		5SJ4113-8HG42				1	1 unit	1AE
	15		5SJ4118-7HG42				1	1 unit	1AE		5SJ4118-8HG42				1	1 unit	1AE
	16		5SJ4116-7HG42				1	1 unit	1AE		5SJ4116-8HG42				1	1 unit	1AE
	20		5SJ4120-7HG42				1	1 unit	1AE		5SJ4120-8HG42				1	1 unit	1AE
	25		5SJ4125-7HG42				1	1 unit	1AE		5SJ4125-8HG42				1	1 unit	1AE
	30		5SJ4130-7HG42				1	1 unit	1AE		5SJ4130-8HG42				1	1 unit	1AE
	32		5SJ4132-7HG42				1	1 unit	1AE		5SJ4132-8HG42				1	1 unit	1AE
	35		5SJ4135-7HG42				1	1 unit	1AE		--						
	40		5SJ4140-7HG42				1	1 unit	1AE		--						
Miniature circuit breakers 2P, 480Y/277 V AC																	
	0.3	2	5SJ4214-7HG42				1	1 unit	1AE		5SJ4214-8HG42				1	1 unit	1AE
	0.5		5SJ4205-7HG42				1	1 unit	1AE		5SJ4205-8HG42				1	1 unit	1AE
	1		5SJ4201-7HG42				1	1 unit	1AE		5SJ4201-8HG42				1	1 unit	1AE
	1.6		5SJ4215-7HG42				1	1 unit	1AE		5SJ4215-8HG42				1	1 unit	1AE
	2		5SJ4202-7HG42				1	1 unit	1AE		5SJ4202-8HG42				1	1 unit	1AE
	3		5SJ4203-7HG42				1	1 unit	1AE		5SJ4203-8HG42				1	1 unit	1AE
	4		5SJ4204-7HG42				1	1 unit	1AE		5SJ4204-8HG42				1	1 unit	1AE
	5		5SJ4211-7HG42				1	1 unit	1AE		5SJ4211-8HG42				1	1 unit	1AE
	6		5SJ4206-7HG42				1	1 unit	1AE		5SJ4206-8HG42				1	1 unit	1AE
	8		5SJ4208-7HG42				1	1 unit	1AE		5SJ4208-8HG42				1	1 unit	1AE
	10		5SJ4210-7HG42				1	1 unit	1AE		5SJ4210-8HG42				1	1 unit	1AE
	13		5SJ4213-7HG42				1	1 unit	1AE		5SJ4213-8HG42				1	1 unit	1AE
	15		5SJ4218-7HG42				1	1 unit	1AE		5SJ4218-8HG42				1	1 unit	1AE
	16		5SJ4216-7HG42				1	1 unit	1AE		5SJ4216-8HG42				1	1 unit	1AE
	20		5SJ4220-7HG42				1	1 unit	1AE		5SJ4220-8HG42				1	1 unit	1AE
	25		5SJ4225-7HG42				1	1 unit	1AE		5SJ4225-8HG42				1	1 unit	1AE
	30		5SJ4230-7HG42				1	1 unit	1AE		5SJ4230-8HG42				1	1 unit	1AE
	32		5SJ4232-7HG42				1	1 unit	1AE		5SJ4232-8HG42				1	1 unit	1AE
	35		5SJ4235-7HG42				1	1 unit	1AE		--						
	40		5SJ4240-7HG42				1	1 unit	1AE		--						

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

5SJ4...-HG miniature circuit breakers acc. to UL 489 and IEC, and accessories



	I_n	Mounting width	SD	Characteristic C	Price per PU	PU (UNIT, SET, M)	PS	PG	SD	Characteristic D	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d	Article No. www.siemens.com/product?Article No.					d	Article No. www.siemens.com/product?Article No.				
Miniature circuit breakers 3P, 480Y/277 V AC														
0.3	3			5SJ4314-7HG42		1	1 unit	1AE		5SJ4314-8HG42		1	1 unit	1AE
0.5				5SJ4305-7HG42		1	1 unit	1AE		5SJ4305-8HG42		1	1 unit	1AE
1				5SJ4301-7HG42		1	1 unit	1AE		5SJ4301-8HG42		1	1 unit	1AE
1.6				5SJ4315-7HG42		1	1 unit	1AE		5SJ4315-8HG42		1	1 unit	1AE
2				5SJ4302-7HG42		1	1 unit	1AE		5SJ4302-8HG42		1	1 unit	1AE
3				5SJ4303-7HG42		1	1 unit	1AE		5SJ4303-8HG42		1	1 unit	1AE
4				5SJ4304-7HG42		1	1 unit	1AE		5SJ4304-8HG42		1	1 unit	1AE
5				5SJ4311-7HG42		1	1 unit	1AE		5SJ4311-8HG42		1	1 unit	1AE
6				5SJ4306-7HG42		1	1 unit	1AE		5SJ4306-8HG42		1	1 unit	1AE
8				5SJ4308-7HG42		1	1 unit	1AE		5SJ4308-8HG42		1	1 unit	1AE
10				5SJ4310-7HG42		1	1 unit	1AE		5SJ4310-8HG42		1	1 unit	1AE
13				5SJ4313-7HG42		1	1 unit	1AE		5SJ4313-8HG42		1	1 unit	1AE
15				5SJ4318-7HG42		1	1 unit	1AE		5SJ4318-8HG42		1	1 unit	1AE
16				5SJ4316-7HG42		1	1 unit	1AE		5SJ4316-8HG42		1	1 unit	1AE
20				5SJ4320-7HG42		1	1 unit	1AE		5SJ4320-8HG42		1	1 unit	1AE
25				5SJ4325-7HG42		1	1 unit	1AE		5SJ4325-8HG42		1	1 unit	1AE
30				5SJ4330-7HG42		1	1 unit	1AE		5SJ4330-8HG42		1	1 unit	1AE
32				5SJ4332-7HG42		1	1 unit	1AE		5SJ4332-8HG42		1	1 unit	1AE
35				5SJ4335-7HG42		1	1 unit	1AE		--				
40				5SJ4340-7HG42		1	1 unit	1AE		--				

	Mounting width	SD	Article No. www.siemens.com/product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	d					
 Auxiliary switches (AS) acc. to UL 489							
1 NO + 1 NC	0.5		5ST3010-0HG		1	1 unit	1AE
2 NO			5ST3011-0HG		1	1 unit	1AE
2 NC			5ST3012-0HG		1	1 unit	1AE
 Fault signal contacts (FC) acc. to UL 489							
1 NO + 1 NC	0.5		5ST3020-0HG		1	1 unit	1AE
2 NO			5ST3021-0HG		1	1 unit	1AE
2 NC			5ST3022-0HG		1	1 unit	1AE
 Shunt trips (ST) acc. to UL 489							
110 ... 480 V AC	1		5ST3030-0HG		1	1 unit	1AE
24 ... 60 V AC/DC		▶	5ST3031-0HG		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.

5SJ4... -HG miniature circuit breakers acc. to UL 489 and IEC, and accessories

Accessories

	Pin spacing	Length	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
Busbars acc. to UL 489 specially for 5SJ4... -HG.. miniature circuit breakers, fixed lengths, cannot be cut ²⁾ , UL File E321559								
	Single-phase							
	For 6 MCBs 1P	1	100	5ST3663-0HG		1	10 units	1AE
	For 12 MCBs 1P		205	5ST3663-1HG		1	10 units	1AE
	For 18 MCBs 1P		310	5ST3663-2HG		1	10 units	1AE
	Two-phase							
	For 3 MCBs 2P	1	100	5ST3664-0HG		1	10 units	1AE
	For 6 MCBs 2P		205	5ST3664-1HG		1	10 units	1AE
	For 9 MCBs 2P		310	5ST3664-2HG		1	10 units	1AE
	Three-phase							
For 2 MCBs 3P	1	100	5ST3665-0HG		1	10 units	1AE	
For 4 MCBs 3P		205	5ST3665-1HG		1	10 units	1AE	
For 6 MCBs 3P		310	5ST3665-2HG		1	10 units	1AE	
Busbars acc. to UL 489 specially for 5SJ4... -HG.. miniature circuit breakers, can be cut, UL File E315616								
	Single-phase							
	For MCBs 1P	1	1016	5ST3701-3HG		1	1 unit	1AE
	For MCBs 1P with AS or FC		1016	5ST3703-3HG		1	1 unit	1AE
	Two-phase							
	For MCBs 2P	1	1016	5ST3705-3HG		1	1 unit	1AE
	For MCBs 2P with AS or FC		1016	5ST3707-3HG		1	1 unit	1AE
	Three-phase							
	For MCBs 3P	1	1016	5ST3710-3HG		1	1 unit	1AE
	For MCBs 3P with AS or FC	1+1+1.5	1016	5ST3712-3HG		1	1 unit	1AE
For MCBs 3x (1P with AS or FC)		1016	5ST3714-3HG		1	1 unit	1AE	
Note								
For the UL 489 busbars that can be cut, use only the associated separate infeed, end cap and touch protection cover.								
Terminals according to UL 489								
	Infeed at the miniature circuit breaker							
	• Specially for 5SJ4... -HG.. miniature circuit breakers			5ST3666-0HG		1	10 units	1AE
	• Max. 35 mm ²							
	Infeed at the miniature circuit breaker							
	• Specially for 5SJ4... -HG.. miniature circuit breakers			5ST3770-3HG		1	10 units	1AE
	• Only for 5ST37...-3HG busbars that can be cut							
	Infeed at the busbar							
	Max. 50 mm ²			5ST3666-2HG		1	10 units	1AE
End cap for 5ST37...-3HG, can be cut acc. to UL 489								
	End cap							
	For single, two, three-phase busbars			5ST3750-3HG		1	10 units	1AE

1) 1 MW (modular width) = 18 mm.

2) All unassigned pins of the busbar must be covered with 5ST3666-1HG touch protection covers.

Miniature Circuit Breakers

5SJ4. . . - .HG miniature circuit breakers acc. to UL 489 and IEC, and accessories


	Pin spacing	Length	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	MW ¹⁾	mm	d					
Touch protection covers for busbars acc. to UL 489								
	Touch protection covers 3 × 1 pin			5ST3666-1HG		1	10 units	1AE
	Touch protection covers • For 5ST37...-3HG busbars that can be cut only • 3 × 1 pin			5ST3655-3HG		1	10 units	1AE
Handle locking devices acc. to UL, UL File E321559								
	Can be sealed against undesired manual ON/OFF switching, sealable, for padlock With max. 3 mm shackle			5ST3801		1	1 unit	1AD
Padlocks								
	For 5ST3801 handle locking device			5ST3802		1	1 unit	1AD

¹⁾ 1 MW (modular width) = 18 mm.

More information

Mounting concept for mounting 5ST30...-0HG accessories on 5SJ4...-HG miniature circuitbreakers

The diagram shows which additional components can be mounted on the right.



Miniature Circuit Breakers

SHU 5SP3 main miniature circuit breakers

Overview

The selective main miniature circuit breaker is used as a circuit breaker on meter panels.

Characteristic E is adapted to the special application requirements for cascade circuits between melting fuses and miniature circuit breakers in distributor circuits.

Used in conjunction with downstream miniature circuit breakers, SHU 5SP3 main miniature circuit breakers ensure effective protection and optimum availability of the plant.

Benefits

- Quick and easy installation on busbar and standard mounting rail
- Reliable and high selectivity
- Optimum availability of the consumer load
- The SHU 5SP3 main miniature circuit breaker operates on a voltage-independent basis
- High and safe selectivity between sub-distribution and meter panel ensures the continued supply of the unaffected circuits in the event of a fault, thus improving system availability
- In the event of a fault, the SHU 5SP3 main miniature circuit breaker prevents an existing short-circuit from being reconnected until the cause of the fault has been eliminated
- The SHU 5SP3 selective main miniature circuit breaker ensures fast and safe disconnection and reconnection of loads
- It complies with all the requirements of TAB 2007 and can therefore be used in metering systems

Technical specifications

			5SP37...-1	5SP37...-2, 5SP37...-2KK0.	5SP38...-2
Standards			DIN VDE 0645	DIN VDE 0641-21	
Rated voltage U_n					
• 1-pole • 3 x 1-pole			V AC V AC	230/400 400	-- 400
Operational voltage			Min. Max.	V AC V AC	110 440
Rated frequency			Hz	50 ... 60	
Rated current I_n			A	16 ... 100	16 ... 63
Rated insulation voltage U_i			V AC	690	
Rated breaking capacity I_{cn}			A	25000	
Insulation coordination					
• Overvoltage category • Pollution degree				IV 3	
Impulse withstand voltage U_{imp}			kV	6	
Impact resistance				30 g, at least 3 impacts, impact duration 11 ms	
Resistance to vibrations				2 g, 20 frequency cycles 5 ... 150 ... 15 Hz	
Switching position indication				OFF = green, ON = red	
Main switch characteristics			Acc. to EN 60204-1	Yes	
Handle end position, sealable				Yes	
Cutoff			ON/OFF	--	Locking slide with lock, additional wire seal, cable ties and Antilux
Device depth			mm	92	
Degree of protection				IP20 with connected conductors	
Mains connection				Any	
Mounting position				Any	
Mounting				On standard mounting rail or interface adapter	Direct tool-free mounting on the busbar system
Service life, on average, with rated load			Actuations	20000	
Wire connections				Saddle terminals at both ends	
• Top					Screwless spring terminal for flexible cables, in particular for meter connecting cables acc. to DIN 43870-3
• Bottom					Box terminal, also for infeed to the busbar system, up to 100 A infeed current
Conductor cross-sections					
• Top and bottom, solid and stranded			mm ²	2.5 ... 70	--
• Top and bottom, finely stranded			mm ²	2.5 ... 50	--
• Top, finely stranded			mm ²	--	2.5 ... 16
• Bottom, solid, stranded and finely stranded, with end sleeve			mm ²	--	2.5 ... 50
Storage temperature			°C	-40 ... +70	
Ambient temperature			°C	-25 ... +55	

Miniature Circuit Breakers

SHU 5SP3 main miniature circuit breakers

Selection and ordering data

I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
A	MW ¹⁾	d					
 Main miniature circuit breakers, 1P, L1 For direct busbar mounting (spacing: 40 mm), no further accessories required							
16	1.5		5SP3716-2KK01		1	1 unit	1AE
20			5SP3720-2KK01		1	1 unit	1AE
25			5SP3725-2KK01		1	1 unit	1AE
35			5SP3735-2KK01		1	1 unit	1AE
40			5SP3740-2KK01		1	1 unit	1AE
50			5SP3750-2KK01		1	1 unit	1AE
63			5SP3763-2KK01		1	1 unit	1AE
 Main miniature circuit breakers, 1P, L2 For direct busbar mounting (spacing: 40 mm), no further accessories required							
16	1.5		5SP3716-2KK02		1	1 unit	1AE
20			5SP3720-2KK02		1	1 unit	1AE
25			5SP3725-2KK02		1	1 unit	1AE
35			5SP3735-2KK02		1	1 unit	1AE
40			5SP3740-2KK02		1	1 unit	1AE
50			5SP3750-2KK02		1	1 unit	1AE
63			5SP3763-2KK02		1	1 unit	1AE
 Main miniature circuit breakers, 1P, L3 For direct busbar mounting (spacing: 40 mm), no further accessories required							
16	1.5		5SP3716-2KK03		1	1 unit	1AE
20			5SP3720-2KK03		1	1 unit	1AE
25			5SP3725-2KK03		1	1 unit	1AE
35			5SP3735-2KK03		1	1 unit	1AE
40			5SP3740-2KK03		1	1 unit	1AE
50			5SP3750-2KK03		1	1 unit	1AE
63			5SP3763-2KK03		1	1 unit	1AE
 Main miniature circuit breakers, 1P each 1 x L1, L2, L3, packaged as a set For direct busbar mounting (spacing: 40 mm), no further accessories required							
16	3 x 1.5		5SP3716-2		1	1 set	1AE
20			5SP3720-2		1	1 set	1AE
25			5SP3725-2		1	1 set	1AE
35			5SP3735-2		1	1 set	1AE
40			5SP3740-2		1	1 set	1AE
50			5SP3750-2		1	1 set	1AE
63			5SP3763-2		1	1 set	1AE
 Main miniature circuit breakers, 3 x 1P single-pole switching For direct busbar mounting (spacing: 40 mm), no further accessories required							
16	4.5		5SP3816-2		1	1 unit	1AE
20			5SP3820-2		1	1 unit	1AE
25			5SP3825-2		1	1 unit	1AE
35			5SP3835-2		1	1 unit	1AE
40			5SP3840-2		1	1 unit	1AE
50			5SP3850-2		1	1 unit	1AE
63			5SP3863-2		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers


SHU 5SP3 main miniature circuit breakers

	I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d					
Acc. to DIN 0641-21 for mounting on 35 mm standard mounting rail								
	Main miniature circuit breakers, 1P							
	16	1.5		5SP3716-3		1	1 unit	1AE
	20			5SP3720-3		1	1 unit	1AE
	25			5SP3725-3		1	1 unit	1AE
	35			5SP3735-3		1	1 unit	1AE
	40			5SP3740-3		1	1 unit	1AE
	50			5SP3750-3		1	1 unit	1AE
	63			5SP3763-3		1	1 unit	1AE
	Main miniature circuit breakers, 3 x 1P							
	16	4.5		5SP3816-3		1	1 unit	1AE
	20			5SP3820-3		1	1 unit	1AE
	25			5SP3825-3		1	1 unit	1AE
	35			5SP3835-3		1	1 unit	1AE
	40			5SP3840-3		1	1 unit	1AE
	50			5SP3850-3		1	1 unit	1AE
	63			5SP3863-3		1	1 unit	1AE
	Main miniature circuit breakers, 2P							
	16	3		5SP3216-3		1	1 unit	1AE
	20			5SP3220-3		1	1 unit	1AE
	25			5SP3225-3		1	1 unit	1AE
	35			5SP3235-3		1	1 unit	1AE
	40			5SP3240-3		1	1 unit	1AE
	50			5SP3250-3		1	1 unit	1AE
	63			5SP3263-3		1	1 unit	1AE
	Main miniature circuit breakers, 3P							
	16	4.5		5SP3316-3		1	1 unit	1AE
	20			5SP3320-3		1	1 unit	1AE
	25			5SP3325-3		1	1 unit	1AE
	35			5SP3335-3		1	1 unit	1AE
	40			5SP3340-3		1	1 unit	1AE
	50			5SP3350-3		1	1 unit	1AE
	63			5SP3363-3		1	1 unit	1AE
	Main miniature circuit breakers, 4P							
	16	6		5SP3416-3		1	1 unit	1AE
	20			5SP3420-3		1	1 unit	1AE
	25			5SP3425-3		1	1 unit	1AE
	35			5SP3435-3		1	1 unit	1AE
	40			5SP3440-3		1	1 unit	1AE
	50			5SP3450-3		1	1 unit	1AE
	63			5SP3463-3		1	1 unit	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

SHU 5SP3 main miniature circuit breakers

	I_n	Mounting width	SD	Article No. www.siemens.com/ product?Article No.	Price per PU	PU (UNIT, SET, M)	PS	PG
	A	MW ¹⁾	d					
	Main miniature circuit breakers, 1P For mounting on standard mounting rail, busbar (spacing: 40 mm, with 5ST1 busbar adapter), or for screw fixing 80 100			5SP3780 5SP3791		1 1	1 unit 1 unit	1AE 1AE
	Main miniature circuit breakers, 3 x 1P Premounted on 5ST1324 busbar adapter; can be clipped onto busbars (spacing: 40 mm); including three 5ST1323 transparent operating protective covers 80 100	6		5SP3780-1 5SP3791-1		1 1	1 set 1 set	1AE 1AE
	Mounting plates For mounting on standard mounting rails according to EN 50022 For 1 or 2 standard mounting rails, universal application, tier spacing 125 mm		▶	5ST1322		1	10 units	1AE
	Busbar adapters for 5SP37.. and 5SP37...-1 Suitable for busbar spacing 40 mm can be equipped with 3 selective main miniature circuit breakers			5ST1328		1	1 unit	1AE
	Breaker blocking covers for 5SP37.. and 5SP37...-1 To prevent manual switching OFF			5ST1318		1	10 units	1AE
	Operating protective covers, transparent, for 5SP37.. and 5SP37...-1 Multiple locking options against accidental and intentional operation • Padlocks • Phillips screwdrivers • Special wrenches (Antilux) • These can be installed by the operator or the power utility			5ST1323		1	3 units	1AE
	Terminal covers for 5SP37.. and 5SP37...-1 2 units required per device Terminal covers in compliance with cladding dimensions acc. to DIN 43880			5ST1316		1	6 units	1AE

¹⁾ 1 MW (modular width) = 18 mm.

Miniature Circuit Breakers

Notes

3

1. General standards

By using this catalog you can acquire hardware and software products described therein from Siemens AG subject to these conditions of sale and delivery (hereinafter: CSD). Please note: the scope, the quality and the conditions for supplies and services, including software products, by any Siemens group or Regional Company having a registered office outside of Germany, shall be subject exclusively to the General Terms and Conditions of the respective Siemens entity. These CSD apply exclusively for orders placed with Siemens AG, Germany.

1.1 For customers with a seat or registered office in Germany

For customers with a seat or registered office in Germany, the following shall be subordinate to these CSD

- for installation, the "Standard Terms and Conditions for Installation –Germany" and
- for Plant Analytics Services the "Standard Terms and Conditions for Plant Analytics Services – for Customers in Germany"¹⁾ and
- for standalone software products and software products that are part of another product or project, the "General License Conditions for Software Products for Automation and Drives for Customers with a Seat or Registered Office in Germany"¹⁾ and
- for other supplies and services, the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"¹⁾.
In the event that such other supplies and services include open-source software, the conditions of which override the "General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry"¹⁾, the product will be supplied with a notice detailing the special conditions that apply for the relevant open-source software. This applies accordingly in the case of a reference to other third-party software components.

1.2 For customers with a seat or registered office outside of Germany

For customers with a seat or registered office outside of Germany, the following shall be subordinate to these CSD

- for Plant Analytics Services the "Standard Terms and Conditions for Plant Analytics Services"¹⁾ (only available in English) and
- for services, the "International Terms & Conditions for Services"¹⁾ supplemented by the "Software Licensing Conditions"¹⁾ and
- for the supply of other hardware and software the "International Terms & Conditions for Products"¹⁾ supplemented by the "Software Licensing Conditions"¹⁾.

1.3 For customers with framework agreements

To the extent that our products and services are covered by an existing framework agreement, the conditions there apply instead of this CSD.

2. Prices

The prices are in € (euros) ex works, excluding packaging.

The sales tax (value added tax) is not included in the prices. It shall be debited separately at the respective rate according to the applicable legal regulations.

Prices are subject to change without prior notice. We will debit the prices valid at the time of delivery.

To compensate fluctuating prices of raw materials (for example silver, copper, aluminum, lead, gold, dysprosium and neodymium), surcharges are calculated on a daily basis for products containing these raw materials using the metal factor. A surcharge for the particular raw material is added to the price of a product if the basic quotations for this raw material are exceeded.

Each product's metal factor dictates for which raw materials the metal surcharges are calculated, from which quotation and with which calculation method (weight or percentage method).

An exact explanation of the metal factor can be found at:
www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf

The surcharge will be calculated (except in the case of dysprosium and neodymium) on the basis of the official price on the day prior to receipt of the order or prior to the release order for calculation of the surcharge.

In the event of placement of an order, the relevant three-month average price from the quarter prior to order receipt or the release order shall be used with a one-month buffer to calculate the dysprosium and neodymium surcharge ("rare earths") (you will find details in the aforementioned explanation of the metal factor).

3. Additional terms and conditions

All dimensions are in mm. In Germany, according to the German law on units in metrology, data in inches only apply to devices for export.

Illustrations are not binding.

Insofar as there are no remarks on the corresponding pages of this catalog - especially with regard to data, dimensions and weights given - these are subject to change without prior notice.

¹⁾ You can download the text of the Siemens AG terms and conditions of trade at
www.siemens.com/automation/salesmaterial-as/catalog/en/terms_of_trade_en.pdf

Appendix

Conditions of sale and delivery

4. Export regulations

We shall not be obligated to fulfill this agreement if such fulfillment is prevented by any impediments arising out of national or international foreign trade or customs requirements or any embargoes or other sanctions.

Exporting may be subject to authorization. In delivery information, we label authorization obligations according to German, European and US export lists.

Our products are controlled by the U.S. authorities (goods labeled with "ECCN" not equal to "N") and may only be supplied to the stated country of the end user for sole use by the end user. Without U.S. government approval or other approval under U.S. law, the products may not be sold, transferred or otherwise forwarded to other countries or to other persons other than the specified end user, either in their original form or after further processing into other goods. Goods labeled with an "AL" not equal to "N" are subject European/national export authorization requirements.

Please note that you can also preview the export designations in the respective product description via our "Industry Mall" online catalog system. The deciding factors, however, are the AL or ECCN export designations indicated on order confirmations, delivery notes and invoices.

Unmarked items or items marked "AL:N" / "ECCN:N" or "AL:9X9999" / "ECCN: 9X9999" may require authorization based on their intended use or ultimate destination.

If you transfer goods (hardware and/or software and/or technology as well as corresponding documentation, regardless of the mode of provision) delivered by us or works and services (including all kinds of technical support) performed by us to a third party worldwide, you shall comply with all applicable national and international (re-) export control regulations.

If required to conduct export control checks, you, at our request, shall promptly provide us with all information pertaining to particular end customers, destination and intended use of goods, works and services provided by us, as well as any relevant export control restrictions.

The products listed in this catalog may be subject to European/German and/or US export regulations. Therefore, any export requiring a license is subject to approval by the competent authorities.

Errors excepted and subject to change without prior notice.

Further information can be obtained from our branch offices listed at www.siemens.com/lowvoltage/contact

Interactive Catalog		<i>Catalog</i>
Products for Automation and Drives	CA 01	
Building Control		
GAMMA Building Control	ET G1	
Drive Systems		
SINAMICS G130 Drive Converter Chassis Units	D 11	
SINAMICS G150 Drive Converter Cabinet Units		
<i>Digital: SINAMICS PERFECT HARMONY GH180 Medium-Voltage Air-Cooled Drives (Germany Edition)</i>	D 15.1	
SINAMICS G180 Converters – Compact Units, Cabinet Systems, Cabinet Units Air-Cooled and Liquid-Cooled	D 18.1	
SINAMICS S120 Chassis Format Converter Units	D 21.3	
SINAMICS S120 Cabinet Modules		
SINAMICS S150 Converter Cabinet Units		
SINAMICS S120 and SIMOTICS	D 21.4	
SINAMICS DCM DC Converter, Control Module	D 23.1	
SINAMICS Inverters for Single-Axis Drives · Built-In Units	D 31.1	
SINAMICS Inverters for Single-Axis Drives · Distributed Inverters	D 31.2	
<i>Digital: SINAMICS Converters for Single-Axis Drives · SINAMICS G120X</i>	D 31.5	
<i>Digital: SINAMICS S210 Servo Drive System</i>	D 32	
<i>Digital: SINAMICS V90 Basic Servo Drive System</i>	D 33	
<i>Digital: SINAMICS G120P and SINAMICS G120P Cabinet pump, fan, compressor converters</i>	D 35	
LOHER VARIO High Voltage Motors	D 83.2	
Flameproof, Type Series 1PS4, 1PS5, 1MV4 and 1MV5 Frame Size 355 to 1000, Power Range 80 to 7100 kW		
<i>Digital: Three-Phase Induction Motors SIMOTICS HV, SIMOTICS TN</i>	D 84.1	
<i>Digital: Three-Phase Induction Motors SIMOTICS HV</i>	D 84.3	
High Voltage Three-phase Induction Motors	D 84.9	
SIMOTICS HV Series A-compact PLUS		
<i>Digital: Modular Industrial Generators SIGENTICS M</i>	D 85.1	
Synchronous Motors with Permanent-Magnet Technology, HT-direct	D 86.2	
DC Motors	DA 12	
SIMOVERT PM Modular Converter Systems	DA 45	
MICROMASTER 420/430/440 Inverters	DA 51.2	
MICROMASTER 411/COMBIMASTER 411	DA 51.3	
<u>Low-Voltage Three-Phase-Motors</u>		
SIMOTOCS S-1FG1 Servo geared motors	D 41	
SIMOTICS Low-Voltage Motors	D 81.1	
SIMOTICS FD Low-Voltage Motors	D 81.8	
LOHER Low-Voltage Motors	D 83.1	
<i>Digital: MOTOX Geared Motors</i>	D 87.1	
SIMOGEAR Geared Motors	MD 50.1	
SIMOGEAR Electric-monorail geared motors	MD 50.8	
Light-load and heavy-load applications		
SIMOGEAR Gearboxes with adapter	MD 50.11	
<u>Mechanical Driving Machines</u>		
FLENDER Standard Couplings	MD 10.1	
FLENDER High Performance Couplings	MD 10.2	
FLENDER Backlash-free Couplings	MD 10.3	
FLENDER SIP Standard industrial planetary gear units	MD 31.1	
Motion Control		
SINUMERIK 840 Equipment for Machine Tools	NC 62	
SINUMERIK 808 Equipment for Machine Tools	NC 81.1	
SINUMERIK 828 Equipment for Machine Tools	NC 82	
SIMOTION Equipment for Production Machines	PM 21	
<i>Digital: Drive and Control Components for Cranes</i>	CR 1	
Process Instrumentation and Analytics		<i>Catalog</i>
<i>Digital: Field Instruments for Process Automation</i>	FI 01	
<i>Digital: Display Recorders SIREC D</i>	MP 20	
<i>Digital: SIPART Controllers and Software</i>	MP 31	
Products for Weighing Technology	WT 10	
<i>Digital: Process Analytical Instruments</i>	AP 01	
<i>Digital: Process Analytics, Components for Continuous Emission Monitoring</i>	AP 11	
Low-Voltage Power Distribution and Electrical Installation Technology		
SENTRON · SIVACON · ALPHA	LV 10	
Protection, Switching, Measuring and Monitoring Devices, Switchboards and Distribution Systems		
Electrical Components for the Railway Industry	LV 12	
Power Monitoring Made Simple	LV 14	
Components for Industrial Control Panels according to UL Standards	LV 16	
<i>Digital: Air circuit breakers and molded case circuit breakers with UL certification</i>	LV 18	
3WT Air Circuit Breakers up to 4000 A	LV 35	
3VT Molded Case Circuit Breakers up to 1600 A	LV 36	
<i>Digital: SIVACON System Cubicles, System Lighting and System Air-Conditioning</i>	LV 50	
<i>Digital: ALPHA Distribution Systems</i>	LV 51	
ALPHA FIX Terminal Blocks	LV 52	
SIVACON S4 Power Distribution Boards	LV 56	
SIVACON 8PS Busbar Trunking Systems	LV 70	
<i>Digital: DELTA Switches and Socket Outlets</i>	ET D1	
Vacuum Switching Technology and Components for Medium Voltage	HG 11.01	
Power Supply		
SITOP Power supply	KT 10.1	
Safety Integrated		
Safety Technology for Factory Automation	SI 10	
SIMATIC HMI / PC-based Automation		
Human Machine Interface Systems/PC-based Automation	ST 80/ST PC	
SIMATIC Ident		
Industrial Identification Systems	ID 10	
SIMATIC Industrial Automation Systems		
Products for Totally Integrated Automation	ST 70	
SIMATIC PCS 7 Process Control System	ST PCS 7	
System components		
SIMATIC PCS 7 Process Control System	ST PCS 7 T	
Technology components		
Add-ons for the SIMATIC PCS 7 Process Control System	ST PCS 7 AO	
SIMATIC S7-400 advanced controller	ST 400	
SIMATIC NET		
Industrial Communication	IK PI	
SIRIUS Industrial Controls		
<i>Digital: SIRIUS Industrial Controls</i>	IC 10	

*Digital: These catalogs are only available as a PDF.***Siemens Industry Online Support**Digital versions of the catalogs are available on the Internet at:
www.siemens.com/lowvoltage/catalogs

Get more information

www.siemens.com/lowvoltage

Siemens AG
Energy Management
Low Voltage & Products
Postfach 10 09 53
93009 Regensburg
Germany

© Siemens AG 2019
Subject to change without prior notice
PDF (E86060-K8280-A101-A8-7600)
KG 0119 1756 En
Produced in Germany

The information provided in this catalog contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. Availability and technical specifications are subject to change without notice.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept.

Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place.

For additional information on industrial security measures that may be implemented, please visit

<http://www.siemens.com/industrialsecurity>.

Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats.

To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under
<http://www.siemens.com/industrialsecurity>.