

# 65W 3 Port USB C Charger (PD)



## PART: TGR-USB-65W-PD-UK-3P-C

- USB 5 Stage Power Delivery Function for fast charging
- 100Vac~240Vac input
- Short Circuit, Over Voltage, Over Current, Over Temperature Protect
- Certified to UL CE SAA 62368
- Can charge iPhone, Samsung & Wide range of Smartphones, tablets, iPads and laptops including Apple, Acer, Asus, Lenovo, Dell, HP
- GaN Technology for ultra compact size
- Suitable for charging 3 devices at a time – Supplied with 1 x 2 metre USB C cable



The Tiger Power range of next generation USB chargers feature power delivery. A 5 stage, intelligent multi voltage charging solution which facilitates the fastest possible charging of your device where supported. The Power Delivery series includes our 65W USB charger TGR-USB-65W-PD-UK-3P-C which is supplied complete with a 2 metre USB C to USB C cable featuring Power On LED. The unit meets latest safety and efficiency legislation and is suitable for a wide range of applications. It features 3 ports (2 x USB C + 1 x USB A)

|   |  |
|---|--|
| Part number (USB C socket in case with USB C cable) : | TGR-USB-65W-PD-UK-3P-C                       |
| Input voltage:  | 100Vac~240Vac                                |
| Input frequency:                                      | 60Hz/50Hz                                    |
| Output USB C sockets 1 and 2 (stage 1):               | 5vdc (min. 0A / max. 3A)                     |
| Output USB C sockets 1 and 2 (stage 2):               | 9vdc (min. 0A / max. 3A)                     |
| Output USB C sockets 1 and 2 (stage 3):               | 12vdc (min. 0A / max 3A)                     |
| Output USB C sockets 1 and 2 (stage 4):               | 15vdc (min. 0A / max 3A)                     |
| Output USB C sockets 1 and 2 (stage 5):               | 20vdc (min. 0A / max 3.25A)                  |
| Short Circuit Protection:                             | Auto Recovery                                |
| Over Power Protection:                                | Auto Recovery                                |
| Over Temperature Protection:                          | Auto Recovery                                |
| Efficiency:   | 80% min. Nominal Input                       |
| Total Output Power (Each port separate)               | C1 (65W) + C2 (65W) + A1 (18W) (Max 65W)     |
| Total Output Power (All ports in use)                 | C1 + C2 (45W max) + A1 (18W) (Max 63W)       |
| Dimensions:   | 53mm * 53mm * 30.5mm                         |
| Safety approval:                                      | UL CE UKCA 62368                             |
| M.T.B.F:  | 20,000 hours (MIL-HDBK-217F) at 25 degrees C |
| Operating temperature:                                | 0°C to + 40°C                                |

### TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.