



DYMO® RHINO™ 4200

IND

Compact, time-saving labelling tool for on-the-go pros

- Prints 6/9/12/19 mm widths
- Exclusive 'Hot Keys' automatically size, space and format labels for specific industrial applications
- $\bullet\,$ Quick and comfortable text entry on the computer- style keyboard with country-specific layout
- Custom key (prevents needless repetition): Customise & save settings for individual label formats
- Kit version include: Rhino 4200 printer, hard carry case, 12mm black on white vinyl tape, rechargeable battery, AC adapter, and user guide

1852992

DYMO RHINO™ 4200 KIT

1801611



DYMO RHINO™ 4200 BOX









DYMO® RHINO™ 5200



The portable, affordable label printer for DataComm, electrical, audio/visual, security, MRO, construction and broadcast professionals.

- Meets all ANSI and TIA/EIA-606-A industry labelling standards
- Patented one-touch "hot keys" automatically format label text for electrical and patch panels, wire and cable flags, face plate tags, terminal blocks, horizontal and vertical wraps, vertical and fixed-length applications
 Kit version include: Rhino 5200 printer, hard carry case, 19mm black on white vinyl tape,
- 12mm black on white vinyl tape, rechargeable battery, AC adapter, and user guide

S0841390

DYMO RHINO™ 5200 KIT

S0841480

DYMO RHINO™ 5200 BOX





Available label width:











Rhino Features







MODEL / FEATURE	RHINO™ 4200	RHINO™ 5200 Kit Case	RHINO™ 6000+ Kit Case
PC Connectivity	No	No	Yes
Fonts	1	1	2
Lines Displayed On Screen	1	4	4
Character Sizes	7	7	7
Flag & Cable Wraps	Yes	Yes	Yes
Patch Panels	No	Yes	Yes
Electrical Panels	Yes	Yes	Yes
Vertical Printing	Yes	Yes	Yes
Repeat Printing	Yes	Yes	Yes
Multiple Lines Printing	4 lines	5 lines	5 lines
Serialisation	Simple	Advanced	Advanced
Memory	25 labels	100 labels	200 labels
Barcodes	Yes	Yes	Yes
Adapter	Optional	Included	Included
Battery Power	6 AA or Rechargeable	Rechargeable	Rechargeable
Weight	460 g	250 g	1.81 kg
Size	17.6 x 11.6 x 6 cm	11.4 x 21.2 x 7 cm	7.5 x 13.7 x 24.6 cm
Tape System	DYMO® IND	DYMO® IND	DYMO® IND
Tape Width	6/9/12/19 mm	6/9/12/19 mm	6/9/12/19/24 mm
Tape Supplied with Machine	Black/White 12 mm Flex Vinyl	Black/White 12 & 19 mm Flex Vinyl	White Vinyl 9 mm+ Flexible Nylon 24 mm
Warranty Guarantee**	1+1 years	1+1 years	1+1 years

 $^{^{\}star\star}~$ 1 year warranty +1 additional year upon registration on dymo.com







DYMO® RHINO™ 6000+

PC-connected or portable labeling tool

Create labels, or transfer files including barcodes and complex label layouts from DYMO ID™ software on PC to the Rhino 6000+ for easy editing on the job.

- Prints 6/9/12/19/24 mm widths
- Meets key ANSI and TIA/EIA-606-B industry labeling standards.
- Exclusive, one-touch "Hot Keys" automatically size, space and format label text
- For electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications including 5-line print capability.
- Print 8 barcode types including Code 39, Code 128, Codabar, UPC A/E, EAN 8/13, PDF 417, code 39 mod 43 variant and QR code.
- Symbol library with 250+ pre-programmed industry symbols, terms, fractions and punctuation marks.
- \bullet Including DYM0 $\mathrm{ID}^{\scriptscriptstyle\mathsf{TM}}$ software

2122967

DYMO RHINO™ 6000+ kitcase

Available label width:



12 mm







RHINO6000

DYMO® RHINO™ Industrial Labels IND



For use with Rhino series

• IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO colour standards.

• IND Permanent Polyester

Professional polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

• IND Heat Shrink

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.UL recognised as a component to UL 224, RoHS compliant, meets MIL-STD-202G, MIL-81531 & SAE-DTL 23053/5 (Class 1&3).

IND Flexible Nylon

Tear-proof material for labelling wires, cables and rounded surfaces







UL recognised component to UL 969. RoHS compliant.



Using DYMO ID is easy thanks to a uniform experience that integrates the same great features found on your RHINOTM label maker and packs them into a powerful PC-based software package. Available as a free download from dymo.com, DYMO ID will provide you with the functionality you need to tackle even the most complex labelling.

Rhino Industrial Labels



COLOUR	6 mm	9 mm	12 mm	19 mm	24 mm
IND Vinyl	Flat Surface Surface	Cable/Wire UV Resident	stant Water Resistant	Oil Resistant Chemical Resistant	Temperature: -40° C to 80° C
ABC	-	18443	18444	18445	1805430
ABC	-	-	18432	18433	1805431
ABC	-	-	18435	18436	-
ABC	-	-	1805416	1805422	-
ABC	-	1805437	1805435	1805436	1805432
ABC	-	-	1805243	1805417	-
ABC	-	-	1805414	1805420	-
IND Permanent Polyester	Flat Surface	Textured Surface UV Resident	stant Water Resistant	Oil Resistant Chemical Resistant	Temperature: -40° C to 80° C
ABC	1805442	18482	18483	18484	1734523
ABC	1805440	18508DMO	622289	622290	-
ABC	1805441	18485	18486	18487	-
IND Heat Shrink		Cable/Wire UV Resident	stant Water Resistant	Oil Resistant Chemical Resistant	Temperature: -55° C to 135° C
ABC	18051	18053	18055	18057	1805443
ABC	18052	18054	18056	18058	1805444
IND Flexible Nylon			Curved Surface	Cable/Wire UV Resistant	Temperature: -40° C to 60° C
ABC	-	-	18488	18489	1734524
ABC	-	-	18490	18491	1734525