

Busbar adapter, 45 mm, 32 A, DIN rail: 1, MSC-D...-PI, 32 A, Push in terminals



Part no. BBA0-32-PI
Catalog No. 199469
Alternate Catalog No. BBA0-32-PI

Delivery program

Accessories			Busbar adapters
			Approved to UL 508 For fitting to flat Cu-busbars with 60 mm between busbar centres, suitable for 5 mm and 10 mm busbar thickness
Connection technique			Push in terminals
For use with			Busbar adapter PKZ0, PKE
Rated operational voltage	U_e	V	690
Rated operational current	I_e	A	32
Terminal capacity			AWG 10 (6 mm ²)
Adapter width		mm	45
Adapter length		mm	200
DIN rail		Quantity	1
Adapter width		mm	45
For use with			PKZM0...-PI, PKE...-PI + DILM8...-PI PKZM0...-PI, PKE...-PI + DILM11...-PI PKZM0...-PI, PKE...-PI + DILM14...-PI PKZM0...-PI, PKE...-PI + DILM17...-PI PKZM0...-PI, PKE...-PI + DILM25...-PI PKZM0...-PI, PKE...-PI + DILM32...-PI

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55

Additional product information (links)

Motor starters and "Special Purpose Ratings" for the North American market	http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf
Busbar Component Adapters for modern Industrial control panels	http://www.moeller.net/binary/ver_techpapers/ver960en.pdf