DOL starter, 380 V 400 V 415 V: 0.37, 0.55 kW, Ir= 1 - 1.6 A, 24 V DC, DC, Push in terminals



Part no. MSC-D-1,6-M7(24VDC)-PI

Catalog No. 199576

Alternate Catalog XTSCPI1P6B007BTDNL

No

Delivery program

Don'tory program			
Basic function			DOL starters (complete devices)
Basic device			MSC
			IE3 ✓
Notes			Also suitable for motors with efficiency class IE3.
Connection technique			Push in terminals
Connection to SmartWire-DT			no
Motor ratings			
Motor rating			
AC-3			
380 V 400 V 415 V	P	kW	0.37 0.55
Rated operational current			
AC-3			
380 V 400 V 415 V	l _e	Α	1.1 1.5
Rated short-circuit current 380 - 415 V	I_q	kA	150
Setting range			
Setting range of overload releases	I _r	A	1 - 1.6
Coordination			Type of coordination "1" Type of coordination "2"
Contact sequence			
Actuating voltage			24 V DC
			DC voltage
B			

$\textbf{Motor-protective circuit-breakers} \ \mathsf{PKZM0-1,6}$

Contactor DILM7-10(...)

DOL starter wiring set

Mechanical connection element and electrical electric contact module PKZM0-XDM12-PI

Notes

The DOL starter (complete device) consists of a PKZM0 motor protective circuit breaker and a DILM contactor.

With the adapter-less top-hat rail mounting of starters up to 15 A, only the motor protective circuit breaker on the top-hat rail requires an adapter. The contactors are provided with mechanical support via a mechanical connection element.

Control wire guide with max. 6 conductors up to 2.5°mm external diameter or 4 conductors up to 3.5°mm external diameter.

From 16 A, the motor protective circuit breaker and contactor are mounted on the top hat rail adapter plate.

The connection of the main circuit between PKZ and contactor is established with electrical contact modules.

When using the auxiliary contacts DILA-XHIT... (-> 101042) the plug-in electrical connector can be removed without the removal of the front mounting auxiliary contact.

Technical data

General

Standards		IEC/EN 60947-4-1, VDE 0660
Mounting position		
Altitude	m	Max. 2000
Ambient temperature		-25 - +55

Main conducting paths			
Rated impulse withstand voltage	U_{imp}	V AC	6000
Overvoltage category/pollution degree			III/3
Rated operational voltage	U _e	V	230 - 415
Rated operational current			
Open, 3-pole: 50 – 60 Hz			
380 V 400 V	I _e	Α	1.6
Additional technical data			
Motor protective circuit breaker PKZM0, PKE			PKZM0 motor-protective circuit-breakers, see motor-protective circuit-breakers/

Motor protective circuit breaker PKZM0, PKE	PKZM0 motor-protective circuit-breakers, see motor-protective circuit-breakers/
	PKZM0 product group
	DILM contactors, see contactor product group
	DILET timing relay, ETR, see contactors, electronic timing relays product group
Davier consumntion	

Power consumption

DC operated	Sealing	W	2.6	
-------------	---------	---	-----	--

Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	55

Dimensions

Additional product information (links)

Motor starters and "Special Purpose Ratings" for the North American market	http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf
Busbar Component Adapters for modern Industrial control panels	http://www.moeller.net/binary/ver_techpapers/ver960en.pdf
Moeller_Online Selections Aids	http://www.moeller.net/en/support/slider/index.jsp