
USB Cable Dual USB-A Plastic Panel Jack to Dual USB-A Plug **Multicomp** PRO

Specifications

Current Rating
AWG Gauge
Temperature Range
IP Rating

: 2.1A : 20 AWG to 28 AWG : -40°C to +105°C : IP65

Diagram





RoHS

Compliant

Item	Part Name	Material / Finish	Qty
1	Housing	Thermoplastic; Colour: Black	1
2	Hex Nut	Thermoplastic; Colour: Black	1
3	Gasket	Silicone; Colour: Black	1
4	USB-A Receptacle	Housing: Thermoplastic; Colour: Black	2
		Contacts: Copper Alloy; Finish: Au Plated	
		Shell: Copper Alloy, Finish: Ni Plated	
5	PCB	FR-4	1
6	Glue	Epoxy; Colour: Black	-
7	Cable	UL2725 24AWG×1P+24AWG×2C+AL/MY+D+B, OD=5mm; Colour: Black	2
8	USB-A Receptacle	Housing: Thermoplastic; Colour: Black	
		Contacts: Copper Alloy; Finish: Au Plated	2
		Shell: Copper Alloy, Finish: Ni Plated	
9	Over Mold	PVC; Colour: Black	2

Part Number Table

	Description	Part Number
Dimensions : Millimetres	USB Cable, Dual USB-A Plastic Panel Rear Mount Jack to Dual USB-A Plug, 500mm	MP009825

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

