
NI-9852 Getting Started

2022-07-06



Contents

Overview.....	3
Safety Guidelines.....	3
Safety Guidelines for Hazardous Locations.....	3
Wiring the NI 9852.....	5
CAN Bus Topology and Termination.....	6
Connecting a CAN Bus to the NI 9852.....	6
Cabling Requirements for the NI 9852.....	7
Cable Specifications.....	7
Determining the Necessary Termination Resistance for the Board.....	7
Number of CAN Nodes.....	7
NI 9852 Hardware Overview.....	7
NI 9852 Specifications.....	8
Low-Speed/Fault Tolerant CAN Characteristics.....	8
Power Requirements.....	9
Physical Characteristics.....	9
Safety Voltages.....	9
Safety Compliance and Hazardous Locations Standards.....	10
Electromagnetic Compatibility.....	10
CE Compliance.....	11
Product Certifications and Declarations.....	11
Shock and Vibration.....	11
Environmental.....	11
Environmental Management.....	12
EU and UK Customers.....	12
电子信息产品污染控制管理办法(中国 RoHS).....	12
NI Services.....	12

Overview

This document explains how to connect to the NI 9852.



Note Before you begin, read the **NI 9852 Safety, Environmental, and Regulatory Information** document on ni.com/manuals and complete the software and hardware installation procedures in your chassis documentation.



Note The guidelines in this document are specific to the NI 9852. The other components in the system might not meet the same safety ratings. Refer to the documentation for each component in the system to determine the safety and EMC ratings for the entire system.

Safety Guidelines



Caution Observe all instructions and cautions in the user documentation. Using the product in a manner not specified can damage the product and compromise the built-in safety protection.



Attention Suivez toutes les instructions et respectez toutes les mises en garde de la documentation d'utilisation. L'utilisation du produit de toute autre façon que celle spécifiée risque de l'endommager et de compromettre la protection de sécurité intégrée.

Safety Guidelines for Hazardous Locations

The NI 9852 is suitable for use in Class I, Division 2, Groups A, B, C, D, T4 hazardous locations; Class I, Zone 2, AEx nA IIC T4 Gc and Ex nA IIC T4 Gc hazardous locations; and nonhazardous locations only. Follow these guidelines if you are installing the NI 9852 in a potentially explosive environment. Not following these guidelines may result in serious injury or death.



Caution Do not disconnect I/O-side wires or connectors unless power has been switched off or the area is known to be nonhazardous.



Caution Do not remove modules unless power has been switched off or the area is known to be nonhazardous.




Caution Substitution of components may impair suitability for Class I, Division 2, or Zone 2.



Caution The system must be installed in an enclosure certified for the intended hazardous (classified) location, having a tool secured cover/door, where a minimum protection of at least IP54 is provided.

Special Conditions for Hazardous Locations Use in Europe and Internationally


The NI 9852 has been evaluated as Ex nA IIC T4 Gc equipment under DEMKO 03ATEX 0626664X and is IECEx UL 14.0089X certified. Each NI 9852 is marked  II 3G and is suitable for use in Zone 2 hazardous locations, in ambient temperatures of $-40^{\circ}\text{C} \leq T_a \leq 70^{\circ}\text{C}$. If you are using the NI 9852 in Gas Group IIC hazardous locations, you must use the device in an NI chassis that has been evaluated as Ex nC IIC T4, Ex IIC T4, Ex nA IIC T4, or Ex nL IIC T4 equipment.




Caution Transient protection shall be provided that is set at a level not exceeding 140% of the peak rated voltage value of 85 V at the supply terminals to the equipment.



Caution The system shall only be used in an area of not more than Pollution Degree 2, as defined in IEC/EN 60664-1.



Caution The system shall be mounted in an ATEX/IECEx-certified enclosure with a minimum ingress protection rating of at least IP54 as defined in IEC/EN 60079-15.



Caution The enclosure must have a door or cover accessible only by the use of a tool.

Wiring the NI 9852

The NI 9852 has two 9-pin male D-Sub connectors that provides connections to a CAN bus. Each port on the NI 9852 has pins for CAN_H and CAN_L, to which you connect the CAN bus signals. Connect these signals using twisted-pair cable. Each port has two isolated common pins (COM) that are internally connected to the module’s isolated reference and serve as the reference ground for CAN_H and CAN_L. You can connect the CAN bus reference ground (sometimes referred to as CAN_V-) to one or both COM pins. The port also has an optional shield pin, SHLD, that you can connect to a shielded CAN cable. Connecting SHLD may improve signal integrity and EMC performance in a noisy environment. Both of the ports on the NI 9852 require an external power supply of +8 to +25 V to operate. Supply power from the CAN bus to the V_{SUP0} pin on CAN0, and the V_{SUP1} pin on CAN1. Pinouts for CAN0 and CAN1 of the NI 9852 are listed in Tables 1 and 2.


Connector	Pin	Signal
	1	No Connection (NC)
	2	CAN_L
	3	COM0
	4	NC
	5	SHLD
	6	COM0
	7	CAN_H
	8	NC
	9	V _{SUP0}

Table 1. Pin Assignments for CAN0


Connector	Pin	Signal
	1	No Connection (NC)
	2	CAN_L
	3	COM0
	4	NC
	5	SHLD
	6	COM0
	7	CAN_H
	8	NC
	9	V _{SUP0}

Table 2. Pin Assignments for CAN1

CAN Bus Topology and Termination

A CAN bus consists of two or more CAN nodes cabled together. The CAN_H and CAN_L pins of each node are connected to the main CAN bus cable through a short connection known as a “stub.” The pair of signal wires, CAN_H and CAN_L, constitutes a transmission line. Every device on a low-speed/fault-tolerant CAN network requires a termination resistor for each CAN data line: R_{RTH} for CAN_H and R_{RTL} for CAN_L.

Figure 1 shows a simplified diagram of a low-speed/fault-tolerant CAN bus with termination resistor placements.

Figure 1. CAN Bus Topology and Termination Resistor Locations



Connecting a CAN Bus to the NI 9852

You can connect each port of the NI 9852 to any location on a CAN bus. Figure 2 shows one example of connecting CAN0 of the NI 9852 directly to one CAN node, and CAN1 directly to another CAN node. CAN0 and CAN1 require an external power supply on the CAN bus.

Figure 2. Connecting Both Ports of the NI 9852 to CAN Buses



Cable Specifications

Cables should meet the physical medium requirements specified in ISO 11898, shown in the following table. Belden cable (3084A) meets all these requirements and should be suitable for most applications.

Characteristic	Value
Length-related resistance	90 mΩ/m nominal
Length-related capacitance: CAN_L and ground, CAN_H and ground, CAN_L and CAN_H	30 pF/m nominal

Table 3. ISO 11898 Specifications for Characteristics of a CAN_H and CAN_L Pair of Wires

Determining the Necessary Termination Resistance for the Board

Unlike High-Speed CAN, Low-Speed/Fault-Tolerant CAN requires termination at the Low-Speed/Fault-Tolerant CAN transceiver instead of on the cable itself. Termination requires two resistors, RTH for CAN_H and RTL for CAN_L. This configuration allows the Philips Fault-Tolerant CAN transceiver to detect and recover from bus faults. It is important to determine the overall termination of the existing network, or the termination of the individual device, before connecting it to a Low-Speed/Fault-Tolerant port. Philips recommends an overall RTH and RTL termination of 100 to 500 Ω (each) for a properly terminated low-speed network.

Termination on the low-speed/fault-tolerant ports of the NI 9852 is set through the NI 985x software to either 1 kΩ or 5 kΩ.

Number of CAN Nodes

The maximum number of nodes depends on the electrical characteristics of the nodes on the network. If all of the nodes meet the requirements of Low-Speed/Fault-Tolerant CAN, up to 32 nodes may be connected to the bus.

NI 9852 Hardware Overview

The NI 9852 has two full-featured, independent CAN ports that are isolated from each other, and from the other modules in the system. Each port on the NI 9852 has a Philips SJA1000 controller that is CAN 2.0B-compatible and fully supports both 11-bit and 29-bit identifiers. The port also has a Philips TJA1054A Low-Speed/Fault-Tolerant CAN transceiver that is fully compatible with the ISO 11898 standard and supports baud rates up to 125 Kbps.

Figure 3. NI 9852 Hardware Overview



NI 9852 Specifications

The following specifications are typical for the range -40 °C to 70 °C unless otherwise noted.

Low-Speed/Fault Tolerant CAN Characteristics

Transceiver	Philips TJA1054A
Max baud rate	125 Kbps
CAN_H, CAN_L bus lines voltage	-27 to +40 VDC
Supply voltage range (V_{SUP0}/V_{SUP1})	
CAN0	+8 to +36 VDC
CAN1	+8 to +36 VDC
R _{PTH}	1.11 kΩ ± 0.5% or 4.99 kΩ ± 0.5%
R _{RTL}	1.11 kΩ ± 0.5% or 4.99 kΩ ± 0.5%
MTBF	1,052,836 hours at 25 °C; Bellcore Issue 6, Method 1, Case 3, Limited Part Stress Method



Note Contact NI for Bellcore MTBF specifications at other temperatures or for MIL-HDBK-217F specifications.

Power Requirements

Power consumption from chassis	
Active Mode	
Transmitting	400 mW max
Receiving	400 mW max
Sleep mode	25 μ W max
Thermal dissipation (at 70 °C)	
Active mode	1.5 W max
Sleep mode	1.2 W max

Physical Characteristics

Dimensions	Visit ni.com/dimensions and search by module number.
Weight	Approximately 144 g (5.0 oz)

Safety Voltages

Connect only voltages that are within the following limits:

Maximum Voltage^[1]	
Port-to-COM	-27 V DC to +40 V DC maximum, Measurement Category I
External power supply (Vsup)	
Isolation	

Port-to-port

Continuous	60 V DC, Measurement Category I up to 5,000 m altitude
Withstand	500 V RMS, verified by a 5 s dielectric withstand test

Port-to-earth ground

Continuous	60 V DC, Measurement Category I up to 5,000 m altitude
Withstand	500 V RMS, verified by a 5 s dielectric withstand test

¹ The maximum voltage that can be applied or output between any port or V_{SUP} terminal and a COM terminal without creating a safety hazard.

Safety Compliance and Hazardous Locations Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1
- EN 60079-0, EN 60079-7
- IEC 60079-0, IEC 60079-7
- UL 60079-0, UL 60079-7
- CSA C22.2 No. 60079-0, CSA C22.2 No. 60079-7



Note For safety certifications, refer to the product label or the [Product Certifications and Declarations](#) section.

Hazardous Locations

U.S. (UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, AEx nA IIC T4 Gc
Canada (C-UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, Ex nA IIC T4 Gc
Europe (DEMKO)	Ex nA IIC T4 Gc

Electromagnetic Compatibility

- EN 61326 (IEC 61326): Class A emissions; Industrial immunity

CE Compliance

- 2014/34/EU; Potentially Explosive Atmospheres (ATEX)

Product Certifications and Declarations

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit ni.com/product-certifications, search by model number, and click the appropriate link.

Shock and Vibration

To meet these specifications, you must panel mount the system.

Operating vibration	
Random	5 g RMS, 10 Hz to 500 Hz
Sinusoidal	5 g, 10 Hz to 500 Hz
Operating shock	30 g, 11 ms half sine; 50 g, 3 ms half sine; 18 shocks at 6 orientations

Environmental

Refer to the manual for the chassis you are using for more information about meeting these specifications.

Operating temperature (IEC 60068-2-1, IEC 60068-2-2)	-40 °C to 70 °C
Storage temperature (IEC 60068-2-1, IEC 60068-2-2)	-40 °C to 85 °C
Ingress protection	IP40
Operating humidity (IEC 60068-2-30)	10% RH to 90% RH, noncondensing

Storage humidity (IEC 60068-2-30)	5% RH to 95% RH, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m


Indoor use only.

Environmental Management


NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

EU and UK Customers

-  Waste Electrical and Electronic Equipment (WEEE)—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法 (中国 RoHS)

-  中国 RoHS—NI 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 NI 中国 RoHS 合规性信息，请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)

NI Services

Visit ni.com/support to find support resources including documentation, downloads, and troubleshooting and application development self-help such as tutorials and examples.

Visit ni.com/services to learn about NI service offerings such as calibration options, repair, and replacement.

Visit ni.com/register to register your NI product. Product registration facilitates technical support and ensures that you receive important information updates from NI.

NI corporate headquarters is located at 11500 N Mopac Expwy, Austin, TX, 78759-3504, USA.