

Contactor, 3 pole, 380 V 400 V 7.5 kW, 1 N/O, 1 NC, 110 V 50 Hz, 120 V 60 Hz, AC operation, Push in terminals




Part no. DILM17-11(110V50HZ,120V60HZ)-PI
Catalog No. 199280
Alternate Catalog No. XTCEPI018C11A
EL-Nummer (Norway) 4190384

Delivery program

| | | | | |
|---|----------------|----|--|---|
| Product range | | | | Contactors |
| Application | | | | Contactors for Motors |
| Subrange | | | | Contactors up to 95 A, 3 pole |
| Utilization category | | | | AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-3/AC-3e: Normal AC induction motors: Starting, switching off while running AC-4: Normal AC induction motors: starting, plugging, reversing, inching |
| | | | | |
| Notes | | | | Also suitable for motors with efficiency class IE3. |
| Connection technique | | | | Push in terminals |
| Number of poles | | | | 3 pole |
| Rated operational current | | | | |
| AC-3 | | | | |
| Notes | | | | At maximum permissible ambient temperature (open.) Also tested according to AC-3e. |
| 380 V 400 V | I_e | A | | 17 |
| AC-1 | | | | |
| Conventional free air thermal current, 3 pole, 50 - 60 Hz | | | | |
| Open | | | | |
| at 40 °C | $I_{th} = I_e$ | A | | 40 |
| enclosed | I_{th} | A | | 32 |
| Conventional free air thermal current, 1 pole | | | | |
| open | I_{th} | A | | 88 |
| enclosed | I_{th} | A | | 80 |
| Max. rating for three-phase motors, 50 - 60 Hz | | | | |
| AC-3 | | | | |
| 220 V 230 V | P | kW | | 4.7 |
| 380 V 400 V | P | kW | | 7.5 |
| 660 V 690 V | P | kW | | 10.5 |
| AC-4 | | | | |
| 220 V 230 V | P | kW | | 2.5 |
| 380 V 400 V | P | kW | | 4.5 |
| 660 V 690 V | P | kW | | 6.5 |
| Contacts | | | | |
| N/O = Normally open | | | | 1 N/O |
| N/C = Normally closed | | | | 1 NC |
| Contact sequence | | | | |
| Can be combined with auxiliary contact | | | | DILM32-XHI...-PI DILA-XHI(V)...-PI |
| Actuating voltage | | | | 110 V 50 Hz, 120 V 60 Hz |
| Voltage AC/DC | | | | AC operation |
| Connection to SmartWire-DT | | | | no |
| Instructions | | | | Contacts to EN 50 012. with mirror contact. |
| Frame size | | | | 2 |

Technical data

General

| | | | |
|---|--------------|-------------------|--|
| Standards | | | IEC/EN 60947, VDE 0660, UL, CSA |
| Lifespan, mechanical | | | |
| AC operated | Operations | x 10 ⁶ | 10 |
| Operating frequency, mechanical | | | |
| AC operated | Operations/h | | 5000 |
| Climatic proofing | | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| Ambient temperature | | | |
| Open | | °C | -25 - +60 |
| Enclosed | | °C | - 25 - 40 |
| Storage | | °C | - 40 - 80 |
| Mounting position | | |  |
| Mechanical shock resistance (IEC/EN 60068-2-27) | | | |
| Half-sinusoidal shock, 10 ms | | | |
| Main contacts | | | |
| N/O contact | | g | 10 |
| Auxiliary contacts | | | |
| N/O contact | | g | 7 |
| N/C contact | | g | 5 |
| Mechanical shock resistance (IEC/EN 60068-2-27) when tabletop-mounted | | | |
| Half-sinusoidal shock, 10 ms | | | |
| Main contacts | | | |
| N/O contact | | g | 6.9 |
| Auxiliary contacts | | | |
| N/O contact | | g | 5.3 |
| N/C contact | | g | 3.5 |
| Degree of Protection | | | IP20 |
| Protection against direct contact when actuated from front (EN 50274) | | | Finger and back-of-hand proof |
| Altitude | | m | Max. 2000 |
| Weight | | | |
| AC operated | | kg | 0.44 |
| Spring-loaded terminal connection | | | |
| Tool | | | |
| Standard screwdriver | | | 3.0 x 0.5 |
| Push-in terminals | | | |
| Terminal capacity main cable | | | |
| Solid | | mm ² | 1 x (1 - 6) 2 x (1 - 6) |
| flexible | | mm ² | 1 x (1 - 10) 2 x (1 - 6) |
| flexible with ferrules | | mm ² | 1 x (1 - 6) 2 x (1 - 4) |
| flexible with ultrasonic welded busbar end | | mm ² | 1 x (1 - 10) 2 x (1 - 6) |
| flexible with uninsulated wire end ferrule | | mm ² | 1 x (1 - 6) 2 x (1 - 6) |
| Solid or stranded | | AWG | 18 - 8 |
| Stripping length | | mm | 12 |
| Standard screwdriver | | | 3.0 x 0.5 |
| Terminal capacity control circuit cables | | | |
| Solid | | mm ² | 1 x (0,5 - 2,5) |

| | | | |
|--|-----------------|--|------------------------------------|
| | | | 2 x (0,5 - 2,5) |
| flexible | mm ² | | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| flexible with ferrules | mm ² | | 1 x (0,5 - 1,5) 2 x (0,5 - 1,5) |
| flexible with ultrasonic welded busbar end | mm ² | | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| flexible with uninsulated wire end ferrule | mm ² | | 1 x (0,5 - 2,5) 2 x (0,5 - 2,5) |
| Solid or stranded | AWG | | 20 - 14 |
| Stripping length | mm | | 10 |
| Tool | | | |
| Standard screwdriver | mm | | 3.0 x 0.5 |

Main conducting paths

| | | | |
|--|------------------|------|-------|
| Rated impulse withstand voltage | U _{imp} | V AC | 8000 |
| Overvoltage category/pollution degree | | | III/3 |
| Rated insulation voltage | U _i | V AC | 690 |
| Rated operational voltage | U _e | V AC | 690 |
| Safe isolation to EN 61140 | | | |
| between coil and contacts | | V AC | 400 |
| between the contacts | | V AC | 400 |
| Making capacity (p.f. to IEC/EN 60947) | | | |
| | Up to 690 V | A | 238 |
| Breaking capacity | | | |
| 220 V 230 V | | A | 170 |
| 380 V 400 V | | A | 170 |
| 500 V | | A | 170 |
| 660 V 690 V | | A | 120 |
| Short-circuit rating | | | |
| Short-circuit protection maximum fuse | | | |
| Type "2" coordination | | | |
| 400 V | gG/gL 500 V | A | 35 |
| 690 V | gG/gL 690 V | A | 35 |
| Type "1" coordination | | | |
| 400 V | gG/gL 500 V | A | 63 |
| 690 V | gG/gL 690 V | A | 50 |

AC

| | | | |
|---|----------------------------------|---|---|
| AC-1 | | | |
| Rated operational current | | | |
| Conventional free air thermal current, 3 pole, 50 - 60 Hz | | | |
| Open | | | |
| at 40 °C | I _{th} = I _e | A | 40 |
| at 50 °C | I _{th} = I _e | A | 38 |
| at 55 °C | I _{th} = I _e | A | 37 |
| at 60 °C | I _{th} = I _e | A | 35 |
| enclosed | I _{th} | A | 32 |
| Conventional free air thermal current, 1 pole | | | |
| open | I _{th} | A | 88 |
| enclosed | I _{th} | A | 80 |
| AC-3 | | | |
| Rated operational current | | | |
| Open, 3-pole: 50 – 60 Hz | | | |
| Notes | | | At maximum permissible ambient temperature (open.) Also tested according to AC-3e. |
| 220 V 230 V | I _e | A | 17 |
| 240 V | I _e | A | 17 |
| 380 V 400 V | I _e | A | 17 |

| | | | |
|--------------------------|----------------|-----|------|
| 415 V | I _e | A | 17 |
| 440V | I _e | A | 17 |
| 500 V | I _e | A | 17 |
| 660 V 690 V | I _e | A | 12 |
| Motor rating | P | kWh | |
| 220 V 230 V | P | kW | 4.7 |
| 240V | P | kW | 5 |
| 380 V 400 V | P | kW | 7.5 |
| 415 V | P | kW | 8.7 |
| 440 V | P | kW | 9.5 |
| 500 V | P | kW | 11 |
| 660 V 690 V | P | kW | 10.5 |
| AC-4 | | | |
| Open, 3-pole: 50 – 60 Hz | | | |
| 220 V 230 V | I _e | A | 10 |
| 240 V | I _e | A | 10 |
| 380 V 400 V | I _e | A | 10 |
| 415 V | I _e | A | 10 |
| 440 V | I _e | A | 10 |
| 500 V | I _e | A | 10 |
| 660 V 690 V | I _e | A | 8 |
| Motor rating | P | kWh | |
| 220 V 230 V | P | kW | 2.5 |
| 240 V | P | kW | 3 |
| 380 V 400 V | P | kW | 4.5 |
| 415 V | P | kW | 5 |
| 440 V | P | kW | 5.5 |
| 500 V | P | kW | 6 |
| 660 V 690 V | P | kW | 6.5 |

Current heat loss

| | | | |
|---|--|----|-----|
| 3 pole, at I _{th} (60°) | | W | 7.9 |
| Current heat loss at I _e to AC-3/400 V | | W | 2.1 |
| Impedance per pole | | mΩ | 2.7 |

Magnet systems

| | | | |
|--|----------|------------------|-----------|
| Voltage tolerance | | | |
| AC operated | Pick-up | x U _c | 0.8 - 1.1 |
| Drop-out voltage AC operated | Drop-out | x U _c | 0.3 - 0.6 |
| Power consumption of the coil in a cold state and 1.0 x U _S | | | |
| 50 Hz | Pick-up | VA | 52 |
| 50 Hz | Sealing | VA | 7.1 |
| 50 Hz | Sealing | W | 2.1 |
| 60 Hz | Pick-up | VA | 67 |
| 60 Hz | Sealing | VA | 8.7 |
| 60 Hz | Sealing | W | 2.1 |
| Duty factor | | % DF | 100 |
| Changeover time at 100 % U _S (recommended value) | | | |
| Main contacts | | | |
| AC operated | | | |
| Closing delay | | ms | 16 - 22 |
| Opening delay | | ms | 8 - 14 |
| Arcing time | | ms | 10 |

Electromagnetic compatibility (EMC)

| | | | |
|-----------------------|--|--|-------------------------|
| Emitted interference | | | According to EN 60947-1 |
| Interference immunity | | | According to EN 60947-1 |

Rating data for approved types

| | | | |
|------------------------------|--|------|-----|
| Switching capacity | | | |
| Maximum motor rating | | | |
| Three-phase | | | |
| 200 V 208 V | | HP | 5 |
| 230 V 240 V | | HP | 5 |
| 460 V 480 V | | HP | 10 |
| 575 V 600 V | | HP | 15 |
| Single-phase | | | |
| 115 V 120 V | | HP | 2 |
| 230 V 240 V | | HP | 3 |
| General use | | A | 40 |
| Auxiliary contacts | | | |
| General Use | | | |
| AC | | V | 600 |
| AC | | A | 10 |
| DC | | V | 250 |
| DC | | A | 1 |
| Short Circuit Current Rating | | SCCR | |
| Basic Rating | | | |
| SCCR | | kA | 5 |
| max. Fuse | | A | 125 |
| max. CB | | A | 125 |

Design verification as per IEC/EN 61439

| | | | |
|--|--|----|-----|
| Technical data for design verification | | | |
| Operating ambient temperature min. | | °C | -25 |
| Operating ambient temperature max. | | °C | 60 |

Technical data ETIM 8.0

| | | | |
|---|--|----|-------------------------|
| Low-voltage industrial components (EG000017) / Power contactor, AC switching (EC000066) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Power contactor, AC switching (ecl@ss10.0.1-27-37-10-03 [AAB718015]) | | | |
| Rated control supply voltage Us at AC 50HZ | | V | 110 - 110 |
| Rated control supply voltage Us at AC 60HZ | | V | 120 - 120 |
| Rated control supply voltage Us at DC | | V | 0 - 0 |
| Voltage type for actuating | | | AC |
| Rated operation current Ie at AC-1, 400 V | | A | 45 |
| Rated operation current Ie at AC-3, 400 V | | A | 17 |
| Rated operation power at AC-3, 400 V | | kW | 7.5 |
| Rated operation current Ie at AC-4, 400 V | | A | 10 |
| Rated operation power at AC-4, 400 V | | kW | 4.5 |
| Rated operation power NEMA | | kW | 0 |
| Modular version | | | No |
| Number of auxiliary contacts as normally open contact | | | 1 |
| Number of auxiliary contacts as normally closed contact | | | 1 |
| Type of electrical connection of main circuit | | | Spring clamp connection |
| Number of normally closed contacts as main contact | | | 0 |
| Number of normally open contacts as main contact | | | 3 |

Approvals

| | | |
|-------------------|--|--|
| Product Standards | | IEC/EN 60947-4-1; UL 60947-4-1; CSA - C22.2 No. 60947-4-1-14; CE marking |
| UL File No. | | E29096 |

| | | |
|--------------------------------------|--|--------------------------|
| UL Category Control No. | | NLDX |
| CSA File No. | | 012528 |
| CSA Class No. | | 2411-03, 3211-04 |
| North America Certification | | UL listed, CSA certified |
| Specially designed for North America | | No |

Characteristics

- 1: Overload relay
- 2: Suppressor
- 3: Auxiliary contact modules

Switching conditions for non-motor consumers, 3 pole, 4 pole

Operating characteristics

Non inductive and slightly inductive loads

Electrical characteristics

Switch on: 1 x rated operational current

Switch off: 1 x rated operational current

Utilization category

100 % AC-1

Typical examples of application

Electric heat

Dimensions

Additional product information (links)

| | |
|--|---|
| Motor starters and "Special Purpose Ratings" for the North American market | http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf |
| Switchgear of Power Factor Correction Systems | http://www.moeller.net/binary/ver_techpapers/ver934en.pdf |
| X-Start - Modern Switching Installations Efficiently Fitted and Wired Securely | http://www.moeller.net/binary/ver_techpapers/ver938en.pdf |
| Mirror Contacts for Highly-Reliable Information Relating to Safety-Related Control Functions | http://www.moeller.net/binary/ver_techpapers/ver944en.pdf |
| Effect of the Cable Capacitance of Long Control Cables on the Actuation of Contactors | http://www.moeller.net/binary/ver_techpapers/ver949en.pdf |
| Switchgear for Luminaires | http://www.moeller.net/binary/ver_techpapers/ver955en.pdf |
| Standard Compliant and Functionally Safe Engineering Design with Mechanical Auxiliary Contacts | http://www.moeller.net/binary/ver_techpapers/ver956en.pdf |
| The Interaction of Contactors with PLCs | http://www.moeller.net/binary/ver_techpapers/ver957en.pdf |
| Busbar Component Adapters for modern Industrial control panels | http://www.moeller.net/binary/ver_techpapers/ver960en.pdf |