Trip indicator, 2 x 1 NC, Push in terminals

AGM2-01-PKZ0-PI 199330

Alternate Catalog XTPAXSATRPI02

No

Part no. Catalog No.



Delivery program

Product range	Accessories
Accessories	Trip-indicating auxiliary contacts
	Differential status indication a) General trip indication (overload) b) Short-circuit release Short-circuits indicated locally by means of a red indicator that can be manually reset
Contacts	
N/C = Normally closed	2 x 1 NC
Contact diagram	
Contact sequence	
Connection technique	Push in terminals
For use with	Trip indicator PKZ0(4), PKE
For use with	PKZM0 PKZM4 PKZM0-T PKM0 PKZM01 PKE
Can be combined with auxiliary contact	NHIPKZ0(-PI) NHI-EPI NHI-BPI
Notes Can be fitted to the right of: Motor protective circuit-breaker	

Technical data

Auxiliary contacts

Auxiliary contacts			
Rated impulse withstand voltage	U _{imp}	V AC	6000
Overvoltage category/pollution degree			III/3
Rated operational voltage	U _e	V	
	Ue	V AC	500
	U _e	V DC	250
Safe isolation to EN 61140			
Between auxiliary contacts and main contacts		V AC	690
Rated operational current	l _e	Α	
AC-15			
220 - 240 V	I _e	Α	3.5
380 - 415 V	le	Α	2
440 V 500 V	l _e	Α	1
DC-13 L/R - 100 ms			
24 V	l _e	Α	2
60 V	l _e	Α	1
110 V	l _e	Α	0.5
220 V	I _e	Α	0.25
Lifespan		S	
Lifespan, electrical	Operations	x 10 ⁶	0.05
Control circuit reliability	Failure rate	λ	$<10^{-8}, <$ one failure at 100 million operations (at Ue = 24 V DC, U_{min} = 17 V, I_{min} = 5.4 mA)
interlocked opposing contacts			yes

A gG/gL	10			
mm ²	1 x (0,5 - 2,5) 2 x (0,5 - 2,5)			
mm^2	1 x (0,5 - 2,5) 2 x (0,5 - 2,5)			
mm^2	1 x (0,5 - 1,5) 2 x (0,5 - 1,5)			
AWG	20 - 14			
mm	10			
	3.0 x 0.5			
Rating data for approved types				
	A600			
	mm ² mm ² AWG			

Type

FAZ-B4/1-HI

Pilot Duty		
AC operated		A600
DC operated		Q300
General Use		
AC	V	V 600
AC	А	A 5
DC	V	V 250

Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-25
Operating ambient temperature max.	°C	55

Technical data ETIM 8.0

Short-circuit rating without welding

Fuseless

Low-voltage industrial components (EG000017) / Auxiliary contact block (EC000041)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Auxiliary switch block (ecl@ss10.0.1-27-37-13-02 [AKN342013])

(eci@ss10.0.1-27-37-13-02 [AKN342013])			
Number of contacts as change-over contact			0
Number of contacts as normally open contact			0
Number of contacts as normally closed contact			2
Number of fault-signal switches			1
Rated operation current le at AC-15, 230 V	А	١	3.5
Type of electric connection			Spring clamp connection
Model			Top mounting
Mounting method			Side mounting
Lamp holder			None

Approvals

••	
Product Standards	UL 508; CSA-C22.2 No. 14; IEC60947-4-1; CE marking
UL File No.	E36332
UL Category Control No.	NLRV
CSA File No.	165628
CSA Class No.	3211-05
North America Certification	UL listed, CSA certified
Specially designed for North America	No

Dimensions

Additional product information (links)

Motor starters and "Special Purpose Hatings" for the North American market	http://wwv
Busbar Component Adapters for modern Industrial control panels	http://wwv

ttp://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf
ttp://www.moeller.net/binary/ver_techpapers/ver960en.pdf