SMD Clock Oscillator DX057 Series





Features

- General microprocessor
- Ultra Thin Ceramic Package
- Cost effective
- Surface mount
- HCMOS/TTL output
- · Tri-state option

Specifications

Nominal Frequency Range : 1.5MHz to 23.99MHz

24MHz to 49.99MHz 50MHz to 80MHz

Frequency Toleration : ±50ppm (Options: ±25, ±100ppm)

Operating Temperature Range : 0°C to +70°C

Storage Temperature Range : -40°C to +85°C

Supply Voltage (VDD) : 3.3V or 5V ±10%

Current Consumption (max.) : 25mA; 40mA & 50mA


Output Symmetry at 1/2VDD : 40% to 60% (standard), 45% To 55% tight


Output Load : 15pF HCMOS or 10TTL

Output Level "L" (max.) : 10% VDD HCMOS or +0.4V DC TTL
Output Level "H" (min.) : 90% VDD HCMOS or +2.4VDC TTL


Rise/Fall Time (10%-90% VDD) (max.) : 10ms Start up Time (max.) : 10ms Stand by Function : Tri State

Diagram





Pin	Connection
1	NC or INH
2	Vss
3	Output
4	+VDD



	L	W	Н	L1	P1	P2	L2	W2	P3	P4
Ī	7 ±0.15	5 ±0.15	1.4 ±0.2	5.08±0.15	1.4 ±0.1	1.2 ±0.1	6.4 ±0.15	3.74 ±0.15	2.2 ±0.1	1.4 ±0.1

Dimensions: Millimetres


Quartz crystal oscillators house a small 5x7mm package. Choice of 3.3V and 5V supply versions


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



SMD Clock Oscillator DX057 Series







Specification Table

Part Number	Frequency (MHz)	Freq. Tol (PPM)	Symmetry	Input Voltage	
DXO57-8-50-T-3.3-TS	8				
DXO57-10-50-T-3.3-TS	10				
DXO57-50-50-T-3.3-TS	50	50	Т	3.3	
DXO57-60-50-T-3.3-TS	60				
DXO57-100-50-T-3.3-TS	100				

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

