Audio Adapter Type-C to Hi-Res 3.5mm





RoHS Compliant

Features

- Support USB-C Malex1 (connect Type-C device) Stereo: 3.5mm female
- · Stereo Digital-to-Analog Converter with 93dB SNR for audio output
- Support digital Hi-Res Audio(High Resolution Audio)
- DAC supports 44.1/48/96 Sample Rate, 16/24-bit
- ADC input supports 44.1/48KHz Sample Rate, 16bit
- 4-Pole 3.5mm Audio Jack for Fixed-Type/Global/Universal Audio Jack Design
- · Audio Jack Detection with Auto-Switch
- Support go into standby mode when no music is playing
- · Support voice adjustment function when connected to Apple original headset
- · Plug and play
- · No need to install extra driver
- · USB bus powered
- System Supported: Mac OS 8.6 or above/Linux/Chrome OS/ Win XP/Win 7/8/Win10 Android System

Specifications


Connector	
Connector	Type-C Malex1 6pin Headphone/Microphone connector x1
Channel	Dual-channel 2.0
SNR	93dB
Sampling frequency	96KHz
Warranty	
Limited Warranty	1 Year
Environmental	
Operating Temperature	0°C to +45°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10°C to +70°C
Storage Humidity	5% to 90 % RH (no condensation)
Power Consumption	
Standby power consumption	<5V/2mA
Operating power consumption	<5V/75mA
Certifications	FCC,CE
Power Requirement	
Power Source	USB Bus Power
Accessories Adapter	
User Manual	English Version

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Audio Adapter Type-C to Hi-Res 3.5mm

multicomp PRO



Pin Assignment

<u>P1</u>	P2
L	 4
R ——	 3
SLEEVE	 1
RING2	 2
AGND ——	 5
JACKSN S	 6

Dimensions: Millimetres

No.	Description	Q'ty	Unit
1	USB3.1 Type CM to CM-34AWG-OD: 3.2MM-L=0.4M-Black	1/2	pcs
2	UTC-CA-AL-R-PCBA	1	pcs
3	UTC-CA-AL Aluminum alloy shell	1	pcs
4	UTC-CA-AL Before the file header Black	1	pcs
5	UTC-CA-AL After the file header Black	1	pcs
6	Conductive copper clip	0.025	m
7	Black wire clip	1	pcs
8	45P Black TPE	10	g

Part Number Table

Description	Part Number	
Type-C to Hi-Res 3.5mm Audio Adapter	MP010250	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

