Connector Housing and Contacts Multicomp PRO

WTB, 5.7mm, Double Row

RoHS Compliant




Specifications


Current Rating : 12 to 21A AC/DC Voltage Rating : 600V AC/DC Contact Resistance : $30m\Omega$ Max. Insulation Resistance : $1000M\Omega$ Min. Withstand Voltage : 600V AC /minute Operating Temperature : -40° C to $+105^{\circ}$ C


Materials


Insulator : NY66 (UL94V-0)
Colour : Black

Diagram









Circuits	Dimensions		
	Α	В	
2	8.35		
4	12.05	5.7	
6	17.75	11.4	
8	23.45	17.1	
10	29.15	22.8	
12	34.85	28.5	

Dimensions : Millimetres


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Page <1> 14/07/22 V1.0

Dimensions: Millimetres


Connector Housing and Contacts Multicomp PRO




2X1 PIN




2X2 PIN




2X3 PIN



2X4 PIN



2X5 PIN



2X6 PIN

WTB, 5.7mm Crimp Terminal



Specifications

Materials


Contact : High Performance Alloy Plating : Selective Gold Plated

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Connector Housing and Contacts Multicomp PRO


Diagram





Part Number	Wire apply	INS.O.D.
MP010401	12AWG	4mm ² or 2.5mm ²
MP010402	14AWG to 16AWG	1.5mm²







CONDUCTOR CRIMP 14/16 AWG

Dimensions : Millimetres

Part Number Table

Description	Part Number
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 2 Way	MP010388
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 4 Way	MP010389
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 6 Way	MP010390
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 8 Way	MP010391
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 10 Way	MP010392
WTB Connector Housing, Receptacle, 5.7mm, Double Row, 12 Way	MP010393
WTB Crimp Terminal, Gold Plated, 12 AWG	MP010401
WTB Crimp Terminal, Gold Plated, 14 to 16 AWG	MP010402

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

