## Connector Housing and Contacts Multicomp PRO

### WTB, 5.7mm, Single Row

### RoHS Compliant

### **Specifications**


 $\begin{array}{lll} \mbox{Insulation Resistance} & : 1000 \mbox{M} \mbox{Min.} \\ \mbox{Withstand Voltage} & : 600 \mbox{V AC /minute} \\ \mbox{Operating Temperature} & : -40 \mbox{°C to } +105 \mbox{°C} \\ \end{array}$ 


#### **Materials**


Insulator : NY66 (UL94V-0)


Colour : Black


### Diagram













Circuits	Dimensions		
	Α	В	
2	12.5	5.7	
3	17.75	11.4	
4	23.45	17.1	
5	29.15	22.8	
6	34.85	28.5	
7	40.55	34.2	
8	46.25	39.9	

Dimensions: Millimetres


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Page <1> 14/07/22 V1.0

Dimensions: Millimetres

## Connector Housing and Contacts Multicomp PRO



### WTB, 5.7mm Crimp Terminal



### **Specifications**

**Materials** 


Contact : High Performance Alloy Plating : Selective Gold Plated

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




# Connector Housing and Contacts **Multicomp** PRO


### Diagram






Part Number	Wire apply	INS.O.D.
MP010401	12AWG	4mm <sup>2</sup> or 2.5mm <sup>2</sup>
MP010402	14AWG to 16AWG	1.5mm <sup>2</sup>







Dimensions: Millimetres

### **Part Number Table**

Description	Part Number
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 2 Way	MP010394
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 3 Way	MP010395
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 4 Way	MP010396
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 5 Way	MP010397
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 6 Way	MP010398
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 7 Way	MP010399
WTB Connector Housing, Receptacle, 5.7mm, Single Row, 8 Way	MP010400
WTB Crimp Terminal, Gold Plated, 12 AWG	MP010401
WTB Crimp Terminal, Gold Plated, 14 to 16 AWG	MP010402

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

