



Features

- RoHS Compliant
- Universal 85 305V AC or 120 430V DC Input voltage
- · Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -30°C to +70°C
- Low standby power consumption, high efficiency
- · High I/O isolation test voltage up to 4000VAC
- · Low ripple & noise
- · Output short circuit, over-current, over-voltage protection
- Over-voltage class III (designed to meet EN61558)
- · Operating up to 5000m altitude
- · 3 years warranty

MPM100-23Bxx series is an enclosed AC-DC switching power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, low no load power consumption, high efficiency and high reliability. These converters offer excellent EMC performance and meet IEC/EN61000-4, CISPR32/EN55032, IEC/UL/EN62368, EN60335, GB4943, EN61558 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

Selection Guide							
Part Number	Output Power (W)	Nominal Output Voltage and Current (Vo/Io)	Output Voltage Adjustable Range (V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (µF)		
MPM100-23B05	90	5V/18A	4.5-5.5	85.5	10000		
MPM100-23B12	102	12V/8.5A	10.2-13.8	87	6800		
MPM100-23B15	15	15V/7.0A	13.5-18	87	3300		
MPM100-23B24	108	24V/4.5A	21.6-28.8	89.5	2200		
MPM100-23B36	100.8	36V/2.8A	32.4-39.6	89.5	1000		
MPM100-23B48	110.4	48V/2.3A	43.2-52.8	90.5	470		

Input Specifications	3					
Item	Ope	rating Conditions	Min.	Тур.	Max.	Unit
Innut Voltage Pange	AC input		85		305	V AC
Input Voltage Range	DC input	'	120		430	V DC
Input Voltage Frequency		,	47		63	Hz
January Commons	115V AC				3	
Input Current	230V AC			T	1.5]
Inrush Current	115V AC	Cold start		35		A
inrush Current	230V AC	Cold start		65]
Leakage Current	277V AC			<0.75m	A	
Hot Plug				Unavaila	ble	





Output Specifications

Item	Operating Conditions		Min.	Тур.	Max.	Unit	
Outrot Valtage Assument	Full lood your	5V		±2			
Output Voltage Accuracy	Full load range	12V/15V/24V/36V/48V		±1		1	
Line Regulation	Rated load	•		±0.5			
Load Degulation	00/ 4000/ 1554	5V		±1		%	
Load Regulation	0% - 100% load	12V/15V/24V/36V/48V		±0.5			
		5V		100			
Outset Discula () Naisat	20MHz bandwidth	12V/15V		120			
Output Ripple & Noise*	(peak-peak value)	24V		150		mV	
		36V/48V		200			
Temperature Coefficient				±0.03		%/°C	
Minimum Load			0			%	
0	0001/40	5V/12V/15V/24V			0.3		
Stand-by Power Consumption	230V AC	36V/48V			0.5	W	
Held on Time	115V AC			10		ms	
Hold-up Time	230V AC			55			
Short Circuit Protection	Recovery time < 10s after the short circuit disappear.		Hiccup, continuous, self-recovery				
Over-current Protection			110%-160% lo, self-recovery				
	5V		≤7.5V DC (Output voltage turn off, hiccup or clamp)				
	12V		≤19.2V DC (Output voltage turn off, hiccup or clamp)				
	15V		≤24V DC (Output voltage turn off, hiccup or clamp)				
Over-voltage Protection	24V		≤38.4V DC (Output voltage turn off, hiccup or clamp)				
	36V		≤57.6V DC (Output voltage turn off, hiccup or clamp)				
	48V		≤60V DC (Output voltage turn off, hiccup or clamp)				

Note: *The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.







General S	pecifications							
	Item		Operating Conditions			Тур.	Max.	Unit
	Input - ≟	Electric strength test for 1min., leakage current			2000			V AC
Isolation	Input - output				4000			
	Output - 🖶		TomA					
	Input - 🖶				100			
Insulation Resistance	Input - output	At 500V DC			100			ΜΩ
resistance	Output - 🖶							
Operating Ten	nperature				-30		+70	°C
Storage Temp	erature			-40		+85		
Storage Humi	dity	Non condons	New condension				95	%RH
Operating Hur	nidity	Non-condensing		20		95		
Switching Free	quency					65		kHz
Power Derating		Operating temperature derating	5V output	+45°C to +70°C	16			
			Other output	+50°C to +70°C	2			%/°C
			derating	85VAC-100VAC	1			%/V AC
Safety Standard		Meet IEC/EN/UL623 GB4943 / EN						
Safety Certification				IEC/EN/UL62368/EN60335/ GB4943/EN61558				
Safety Class				CLASS I				
MTBF		MIL-HDBK-217F@25°C			>30,0000 h			

Mechanical Specifications					
Case Material	Metal (AL1100, SGCC)				
Dimensions	129mm × 97mm × 30mm				
Majaht	325g (Typ.)	5V			
Weight	305g (Typ.)	12V/15V/24V/36V/48V			
Cooling Method	Free air convection				


EMC Specifications

	CE	CISPR32/EN55032	CLASS B	
Emissions RE		CISPR32/EN55032	CLASS B	
	Harmonic current	IEC/EN61000-3-2	CLASS A	
	ESD	IEC/EN 61000-4-2	Contact ±6KV/Air ±8KV	perf. Criteria A
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN 61000-4-4	±2KV	perf. Criteria A
Immunity	Surge	IEC/EN 61000-4-5	line to line ±2KV/line to ground ±4KV	perf. Criteria A
	CS	IEC/EN61000-4-6	10 Vr.m.s	perf. Criteria A
	Voltage dip, short interruption and voltage variation	IEC/EN61000-4-11	0%, 70%	perf. Criteria B







Product Characteristic Curve




Note: 1. With an AC input voltage between 85-115VAC and a DC input between 120-163VDC the output power must be derated as per the temperature derating curves;

2. This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.





Dimensions and Recommended Layout







Notes:

- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75% RH with nominal input voltage and rated output load;
- 2. The ambient temperature derating of 5°C/1000m is needed for operating altitude greater than 2000m;
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. The out case needs to be connected to the earth of system when the terminal equipment in operating;
- Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.
- 9. The power supply is considered a component which will be installed into a final equipment. All EMC tests should be confirmed with the final equipment. Please consult our FAE for EMC test operation instructions.

Part Number Table

Description	Part Number		
Enclosed Power Supply, 100W, 5V DC, 18A	MPM100-23B05		
Enclosed Power Supply, 100W, 12V DC, 8.5A	MPM100-23B12		
Enclosed Power Supply, 100W, 15V DC, 7A	MPM100-23B15		
Enclosed Power Supply, 100W, 24V DC, 4.5A	MPM100-23B24		
Enclosed Power Supply, 100W, 36V DC, 2.8A	MPM100-23B36		
Enclosed Power Supply, 100W, 48V DC, 2.3A	MPM100-23B48		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

