

ECN/PCN No.: R0100

For Manufacturer													
<b>Product Description:</b> 5G Sub-6GHz External Whip Antenna		<b>Abrakon Part Number / Part Series:</b> AEBC1101X											
<b>Affected Revision:</b> I.R.		<b>New Revision:</b> Rev A											
		<input type="checkbox"/> Documentation only <input checked="" type="checkbox"/> ECN <input type="checkbox"/> EOL	<input checked="" type="checkbox"/> Series <input type="checkbox"/> Part Number										
		<b>Application:</b> <input type="checkbox"/> Safety <input checked="" type="checkbox"/> Non-Safety											
<b>Prior to Change:</b>  <b>115 x Ø19 mm</b> <b>RoHS/RoHS II Compliant</b> <b>MSL = 3</b>													
		<table border="1"> <thead> <tr> <th>Parameter</th> <th>Specification</th> </tr> </thead> <tbody> <tr> <td>Operating Temperature</td> <td>-30°C to +65°C</td> </tr> <tr> <td>Storage Temperature</td> <td>-30°C to +85°C</td> </tr> <tr> <td>ROHS Complaint</td> <td>Yes RoHS 2011/65/EU with IEC 62321:2008 Method</td> </tr> <tr> <td>MSL Level</td> <td>3</td> </tr> </tbody> </table>	Parameter	Specification	Operating Temperature	-30°C to +65°C	Storage Temperature	-30°C to +85°C	ROHS Complaint	Yes RoHS 2011/65/EU with IEC 62321:2008 Method	MSL Level	3	
Parameter	Specification												
Operating Temperature	-30°C to +65°C												
Storage Temperature	-30°C to +85°C												
ROHS Complaint	Yes RoHS 2011/65/EU with IEC 62321:2008 Method												
MSL Level	3												
<b>After Change:</b>  <b>115 x Ø19 mm</b> <b>RoHS/RoHS II Compliant</b> <b>MSL = N/A</b>													
		<table border="1"> <thead> <tr> <th>Parameter</th> <th>Specification</th> </tr> </thead> <tbody> <tr> <td>Operating Temperature</td> <td>-30°C to +65°C</td> </tr> <tr> <td>Storage Temperature</td> <td>-30°C to +85°C</td> </tr> <tr> <td>ROHS Complaint</td> <td>Yes RoHS 2011/65/EU with IEC 62321:2008 Method</td> </tr> <tr> <td>MSL Level</td> <td>N/A</td> </tr> </tbody> </table>	Parameter	Specification	Operating Temperature	-30°C to +65°C	Storage Temperature	-30°C to +85°C	ROHS Complaint	Yes RoHS 2011/65/EU with IEC 62321:2008 Method	MSL Level	N/A	
Parameter	Specification												
Operating Temperature	-30°C to +65°C												
Storage Temperature	-30°C to +85°C												
ROHS Complaint	Yes RoHS 2011/65/EU with IEC 62321:2008 Method												
MSL Level	N/A												
<b>Cause/Reason for Change:</b> Amend the Moisture Sensitivity Level from MSL 3 to MSL N/A according to the product requirements													
Change Plan													
<b>Effective Date:</b> 6/30/2022		<b>Additional Remarks:</b> N/A											
<b>Change Declaration:</b> Performance, form and size are not affected													
<b>Issued Date:</b> 6/30/2022		<b>Issued By:</b> Evgenii Filatov											
		<b>Issued Department:</b> Engineering											
<b>Approval:</b> Syed Raza VP of Engineering		<b>Approval:</b> Reuben Quintanilla Quality Director											
		<b>Approval:</b> Ying Huang Purchasing Director											
For Abracon EOL only													
<b>Last Time Buy (if applicable):</b>		<b>Alternate Part Number / Part Series:</b>											
<b>Additional Approval:</b>		<b>Additional Approval:</b>											
<b>Customer Approval (If Applicable)</b>													
<b>Qualification Status:</b> <input type="checkbox"/> Approved <input type="checkbox"/> Not accepted <i>Note: It is considered approved if there is no feedback from the customer 1 month after ECN/PCN is released.</i>													
<b>Customer Part Number:</b>		<b>Customer Project:</b>											
<b>Company Name:</b>		<b>Company Representative:</b>											
		<b>Representative Signature:</b>											
<b>Customer Remarks:</b>													

