

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200661042](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18 AWG, Yellow TPE Cable, 9.0m (29.53') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [120066](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Brass
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Region America
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78678880175

Physical

Cable Diameter 6.86mm (.270")
 Cable Length 9.0m (29.53')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 254.510/g
 Orientation Straight to Straight
 Poles 5
 Temperature Range - Operating -20° to +105°C
 Wire Size AWG 18
 Wire/Cable Type PLTC/ITC

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 885030K03M090

Reference - Drawing Numbers

Sales Drawing 1200668165-000, SD-120066-020-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000406200_00_000.pdf

CER_4000410285_00_000.pdf

Search Parts in this Series

[120066 Series](#)

This document was generated on 11/16/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION