CUS250M Series

https://product.tdk.com/en/power/cus-m www.emea.lambda.tdk.com/cus250m

2 x 4" 250W AC-DC Power Supplies















The compact CUS250M is packaged in the industry standard 2x4" footprint. The series can deliver 250W with forced air or conduction cooling in ambient temperatures of up to 50°C. With Medical & ITE certifications, the unit can be used in both Class I & Class II (no ground wire) applications, and meets Class B Conducted and Radiated EMI with generous margins. Options include a 5V standby voltage, remote on/off, DC_OK and AC_Fail signals, with a U channel, cover or top fan mechanical construction.

| Features | Benefits |
|---|--|
| Up to 250W Utilizing Convection and Conduction Cooling | Quiet Operation |
| Operation in Ambient Temperatures of up to 85°C | Suitable for High Ambient Temperature Environments |
| Medical Certifications (2 x MOPP) | Suitable for B and BF Type Medical Equipment |
| Class B Conducted and Radiated EMI with Significant Margins | Easier System EMC Compliance |
| Suitable for Class I and Class II installations | Flexible Utilisation |
| Compact 2 x 4 x 1.56" / 50.8 x 101.6 x 39.5mm Size | Space Saving in End Equipment |
| Enclosure & Cooling Options | Versatile Application |
| EN60335-1 Compliant | Suitable for Household and Similar Electrical Appliances |

| Model Selecto | r | | | | |
|----------------------|----------------------------------|--|----------------------|--------------------------------------|------------------------------------|
| Model | Nominal Output Voltage (V) | Output Adjustment ⁽¹⁾ (V) | Fan Supply (V) | Maximum Current Forced Air (A) | Maximum Power Forced Air (W) |
| CUS250M-12 | 12 | 12 - 13.2 | 11.4 | 20.83 | 250 |
| CUS250M-15 | 15 | 15 - 16.5 | 11.4 | 16.66 | 250 |
| CUS250M-18 | 18 | 18 - 19.8 | 11.4 | 13.88 | 250 |
| CUS250M-24 | 24 | 24 - 26.4 | 11.4 | 10.41 | 250 |
| CUS250M-28 | 28 | 28 - 30.8 | 11.4 | 8.92 | 250 |
| CUS250M-36 | 36 | 36 - 39.6 | 11.4 | 6.94 | 250 |
| CUS250M-48 | 48 | 48 - 52.8 | 11.4 | 5.2 | 250 |

Contact Factory for availability - expected Q2 2023

(2) Subject to Minimum Order Quantities. Please contact Sales

| CUS250M- | 12 | 1 | U | l | | M | | - | | J |
|---|-----------------------|------------|-------------------------------|-------------------|-----------------------|---------------------------|----------------------------|----------------------------|--------------|---------|
| Output voltage 12, 19 | 5, 18, 24, 28, 36, 48 | | | blank M (2) | JST conr Molex typ | nectors be input conne | ctors | | | |
| | | blank U | Open frame (w U channel | ith integral base | eplate) | blank E (2) | Dual fu Single | ises input fuse | e in line | |
| | | A | U channel with U channel, cov | | nted fan | | | blank | No options | |
| | | C | M3 inserts for u | | | | | G | 5V 0.1A stan | 3 11 37 |
| Notes: See website for detailed specifications, test methods and installation manual. | | | | | | 1 | DC_OK, AC_ 5V 0.1A stan | _ | | |
| Specification parameters apply at 25°C ambient temperature unless otherwise stated. (1) Output voltage is user adjustable or can be factory set. Non-standard output versions may be subject to minimum order quantities and variations to specification. For all non-standard output voltage settings please consult Sales. | | | | | | | J | remote on/of DC_OK, AC_ | f (inhibit), | |



| Specifications | | | | |
|---------------------------------------|-----|--|--|--|
| Model | | CUS250M | | |
| Input | | | | |
| Input Voltage range | Vac | 85 - 264 ⁽³⁾ | | |
| Input Frequency | Hz | 47 - 63 ⁽⁴⁾ | | |
| Input Current (100Vac) | Α | 3.2 | | |
| Inrush Current at 230Vac (Cold Start) | Α | <75. Note: the inrush I ² t is significantly below the rating of the internal 5A fast acting fuse, or an external circuit breaker | | |
| Leakage Current | uA | <150 at 264Vac 63Hz | | |
| Touch Current (Enclosure Leakage) | uA | Class I: <10, Class II: <70, at 264Vac 63Hz | | |
| Power Factor (115/230Vac) | - | >0.9 / >0.7 (>20% load) | | |
| Harmonic Compliance | - | Meets IEC61000-3-2 Class A | | |
| No Load Power Consumption | W | <0.5 (230Vac) when output is inhibited | | |
| Hold Up Time | ms | >14 | | |
| Efficiency | % | Up to 94 | | |
| Average Efficiency | % | >91 Measured at 25%, 50%, 75% and 100% load conditions | | |
| Conducted & Radiated EMI | - | EN55032 / EN55011-B (See application notes for conditions) | | |
| Immunity | - | Compliant with EN60601-1-2:2015 (Edition 4), see immunity table | | |
| Insulation Class | - | Construction suitable for Class I or Class II installation | | |
| Safety Certifications and Markings | - | IEC/ES/EN60601-1, IEC/UL/EN62368-1, 60950-1. | | |
| | | Compliant to IEC/EN60335-1 and IEC/EN61010-1, CE Mark and UKCA Mark | | |

⁽³⁾ Derate output power linearly to 225W load from 100 to 90Vac input and to 200W from 90 to 85Vac input (4) For operation at 440Hz please consult Technical Sales.




| Immunity | | | | | | |
|--|--|----------|---|--|--|--|
| Test | Test | UOM | Level & Criteria | | | |
| | Enclosure Port | Lvl | Level 4, Criteria A | | | |
| IEC61000-4-2 (ESD) | AC Port | Lvl | Level 4, Criteria A | | | |
| IEC61000-4-2 (ESD) | CH1 and Standby | Lvl | Level 3, Criteria A | | | |
| | Signal I/O Port (Remote On/Off, AC_FAIL, DC_OK) | Lvl | Level 3, Criteria A | | | |
| IEC61000-4-3 | 80 MHz to 2.7 GHz | V/m | 10 (Level 3, Criteria A) | | | |
| (Radiated Immunity) | 2.7 GHz to 6 GHz | V/m | 10 (Level 3, Criteria A) | | | |
| EN 60601-1-2:2015 | Immunity to RF Wireless Communications Equipment | - | All Criteria, Criteria A | | | |
| (Radiated Immunity) | (Table 9) | | , | | | |
| CISPR 35 | 1.8 GHz to 5 GHz | V/m | 3 (Table 1, condition 1.3 requirements, Criteria A) | | | |
| IEC 61204-3: 2000 | 900 MHz (Keyed Carrier) | V/m | 3 (Criteria A) | | | |
| IEC61000-4-4 | AC Port | kV | 4 (Level 4, Criteria A) | | | |
| 12001000 1 1 | CH1 | kV | 2 (Level 4, Criteria A) | | | |
| (Electrical Fast Transient Burst) | Fan Out, Standby | kV | N/A | | | |
| (Liectical Fast Hallslefft Bulst) | Signal I/O Port (Remote On/Off, AC_FAIL, DC_OK) | kV | 2 (Level 4, Criteria A) | | | |
| | (AC input common mode) | kV | 2 (Level 3, Criteria A) | | | |
| IEC61000-4-5 (Surge) | (AC input common mode) | kV | | | | |
| | , | V | 1 (Level 3, Criteria A) 10 (Level 3, Criteria A) | | | |
| IECC1000 4 C | (AC input common mode) | | , | | | |
| IEC61000-4-6 | (DC output common mode) | V | 10 (Level 3, Criteria A) | | | |
| (Conducted Susceptibility) | (Fan Out, Standby common mode) | V | N/A | | | |
| | (Signal I/O common mode) | V | N/A | | | |
| IEC61000-4-8 (Power Frequency Mag. Field) | | A/m | (Level 4, Criteria A) | | | |
| | When exited factory (Bulk cap life degradation not considered) | - | Class 3 | | | |
| | 0% for 0.5 cycle | Criteria | A | | | |
| IEC61000-4-11 | 0% for 1 cycle | Criteria | A≤175W, B >175W | | | |
| (Voltage dips / Interruption) | 40% for 10/12 cycles | Criteria | 100Vac: A≤50W, B>50W; 220Vac: A | | | |
| (Totago alpo / Intorruption) | 70% for 25/30 cycles | Criteria | 100Vac: A≤150W, B>150W; 220Vac: A | | | |
| | 80% for 250/300 cycles | Criteria | 100Vac: A≤200W, B>200W; 220Vac: A | | | |
| | 0% for 250/300 cycles | Criteria | B | | | |
| | When exited factory (Bulk cap life degradation not considered) | Ontona | | | | |
| IEC60601-1-2 | | Criteria | Δ | | | |
| (Voltage dips / Interruption) | 0% for 0.5 cycle | | A <475W D >475W | | | |
| | 0% for 1 cycle | Criteria | A≤175W, B>175W | | | |
| | 70% for 25/30 cycles | Criteria | 100Vac: A≤150W, B>150W; 220Vac: A | | | |
| JE004000 0 0 | 0% for 250/300 cycles | Criteria | В | | | |
| IEC61000-6-2 | 0% for 1 cycle | Criteria | В | | | |
| (Voltage dips / Interruption) | 40% for 10/12 cycles | Criteria | C | | | |
| | 70% for 25/30 cycles | Criteria | C | | | |
| IEC61204-3 | 0% for 250/300 cycles | Criteria | C | | | |
| (Voltage dips / Interruption) | 30% for 10 ms | Criteria | В | | | |
| , , , | 60% for 100 ms | Criteria | 100Vac: A≤70W, B>70W; 220Vac: A | | | |
| | 95% for 5000 ms | Criteria | C | | | |
| SEMI F47 | 50% for 0.2 s | Criteria | 170Vac: A≤240W, B>240W; 220Vac: A | | | |
| OLIVII F41 | 70% for 0.5 s | Criteria | A | | | |
| | 80% for 1s | Criteria | A | | | |
| IEC61000-4-12 (Ringwave Test) | | - | (Level 3, Criteria A) | | | |
| EN61000-4-14 (Voltage Fluctuations) | | - | Class 3, Criteria A | | | |




| Specifications | | |
|--|---------|---|
| Model | | CUS250M |
| Output | | |
| Line Regulation | % | <0.5 (85 - 264Vac) |
| Load Regulation | % | <1 (0 - 100% load) |
| External Load Capacitance | uF | 12V: 20,830, 15V: 16,660, 18V: 9,440, 24V: 2,290, 28V: 4,460, 36V: 3,470, 48V: 1,300 |
| · | | <1 of nominal output for operating temperatures above 0°C |
| Ripple & Noise | % | 12V model: <2, other voltages: <1.5 at -20°C. <2 in burst mode when the load is <10% of the rated current |
| | | External load capacitance will reduce the amplitude. |
| Temperature Coefficient | %/°C | ±0.02 |
| Minimum Load | - | No minimum load required |
| Overcurrent Protection | % | 110 to 170. Hiccup mode, automatic recovery |
| 0 1 0 1 5 | | 115-140% of standard output voltage |
| Overvoltage Protection | - | Latching (unit shutdown), cycle AC input or use remote on/off to reset |
| Overtemperature Protection | - | Latching, cycle AC or use remote on/off to reset |
| Remote Sense | - | None |
| Remote On/Off | - | Opto-isolated. Inhibit: High = OFF, Low = ON, Enable: High = ON, Low = OFF |
| Standby Voltage | | 5V 0.1A |
| Fan Supply | - | 11.4V 0.5A |
| Parallel Operation | - | Not possible |
| Series Operation | - | Please contact Technical Sales for guidance |
| Environmental | | |
| Operating Temperature (-40°C start-up) | °C | -20 to +85 with system forced air cooling (70 maximum for fan version /F), see derating curves below |
| Storage Temperature | °C | -40 to +85 (70 maximum for fan version /F) |
| Operating Humidity (non condensing) | %RH | 5 - 95 (15 - 90 for /F fan version) |
| Pollution Degree | - | PD2 Material group IIIb |
| Cooling | - | Convection, conduction or forced air cooling. See derating curves below |
| Altitude | m | 5,000 |
| Withstand Voltage (For 1 minute) | Vac | Input to Ground 1,500 (1xMOPP), Input to Output 4,000 (2xMOPP), Output to Ground 1,500 (1xMOPP) |
| Isolation Resistance | MΩ | >100 at 25°C, 70%RH & 500VDC |
| Vibration (non operating) | - | 2G, 10-500Hz for 1 hour |
| Shock (non operating) | - | 30G, 11ms half sine |
| Other | | |
| Weight | g | Open frame: 275, /A: 320, /C: 275, /F: 345, /U: 305 |
| | | Open frame : 50.8 x 101.6 x 39.5 |
| Cizo (Myl yLl) | mm | U channel : 64 x 119.2 x 39.5 |
| Size (WxLxH) | mm | Cover (/A): 64 x 119.2 x 43 |
| | | Fan (/F) : 64 x 119.2 x 60.6 |
| | | Open frame: 2 x 4 x 1.56 |
| Size (WxLxH) | Inches | U channel : 2.52 x 4.69 x 1.56 |
| OIZG (VVALAI I) | IIICIES | Cover (/A): 2.52 x 4.69 x 1.69 |
| | | Fan (/F) : 2.52 x 4.69 x 2.39 |
| Connectors | - | Input: JST B2P3-VH, Output: M3 screw, Fan: Molex 22-05-7025, Signals: Molex 87833-0833 |
| Warranty | yrs | 5 |

Peak Power Rating Curves



Peak Power Rating Curves



Orientation

Horizontal Orientation A




Vertical Orientation B




Notes:

Notes. See website for detailed specifications, test methods and installation manual. Specification parameters apply at 25°C ambient temperature unless otherwise stated.

Output Power vs Ambient Temperature




Output Power vs Ambient Temperature






Output Power vs Ambient Temperature (forced air cooled) all CUS250M voltages



Standby and Fan Output Power vs Ambient Temperature



Notes

- Orientation A (see Application Note), 50mm above surface.
 Standby output is loaded (see derating curves for Standby output), no load on Fan output
- 2: 50mm above surface. Limited by fan specification to 70°C maximum
- 3: Tested with U chassis with airflow direction 1 (see Application Note).


Customer to ensure airflow rate and direction to keep components temperature below the limits.

Standby and Fan output load according to derating curves.


- Measured in wind tunnel with 5mm space on side of U chassis.
- 4: Mounted on natural aluminium plate, 300x300x1mm lifted 50mm above other surfaces Orientation A (see Application Note)
 - Standby output is loaded (see derating curves for Standby output), no load on Fan output



Outline Drawing CUS250M Open Frame Unit (Integral baseplate)




Outline Drawing CUS250M/C Open Frame Unit with inserts (Integral baseplate)






Outline Drawing CUS250M/U (U Channel) Option




Outline Drawing CUS250M/A (U Channel with Cover) Option





Outline Drawing CUS250M/F (U Channel with Cover & Top Mounted Fan) Option







TDK-Lambda France SAS

Tel: +33 1 60 12 71 65 france@fr.tdk-lambda.com www.emea.lambda.tdk.com/fr



Italy Sales Office

Tel: +39 02 61 29 38 63 info.italia@it.tdk-lambda.com www.emea.lambda.tdk.com/it



Netherlands

info@nl.tdk-lambda.com www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Tel: +49 7841 666 0 info@de.tdk-lambda.com www.emea.lambda.tdk.com/de



Austria Sales Office

Tel: +43 2256 655 84 info@at.tdk-lambda.com www.emea.lambda.tdk.com/at



Switzerland Sales Office

Tel: +41 44 850 53 53 info@ch.tdk-lambda.com www.emea.lambda.tdk.com/ch



Nordic Sales Office

Tel: +45 8853 8086 info@dk.tdk-lambda.com www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66 info@uk.tdk-lambda.com www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

Tel: +9 723 902 4333 info@tdk-lambda.co.il emea.lambda.tdk.com/il-en



TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324 tla.powersolutions@tdk.com www.us.lambda.tdk.com



TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599 sales.br@tdk-electronics.tdk.com www.tdk-electronics.tdk.com/en



TDK-Lambda Corporation

Tel: +81-3-6778-1113 www.jp.lambda.tdk.com



TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777 tlc.powersolutions@tdk.com www.lambda.tdk.com.cn



TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211 tls.marketing@tdk.com www.sg.lambda.tdk.com



TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660 mathew.philip@tdk.com www.sg.lambda.tdk.com

