

**RoHS  
Compliant**



## Features


- Euro Plug Top
- DOE Level VI Efficiency
- Overcurrent Protection
- Short Circuit Protection
- 1 Year Warranty
- DC Cable Length: 1500mm

## Specification

Models		MP009259
Output	DC Voltage	5V DC
	Rated Current	2amp
	Current Range	0-2amp
	Rated Power	12 Watt
	Ripple & Noise	200mVp-p max
	Output Regulation	±5%
	Output Connector	2.1 × 5.5 × 12mm C+ve
Input	Voltage Range	90V AC to 264V AC
	Frequency Range	47Hz to 63Hz
	Input Current	1.2amp Max
	Inrush Current	40amp Max
	Standby Power	0.1amp Max
	Leakage Current	0.25amp Max
	Input Connector	UK
Environment	Operating Temp	0°C to 40°C
	Cooling	Convection
	Temperature Coefficient	0.05%/°C
	Humidity	5~95%RH (non-condensing)
	Storage Temp	-20°C to +80°C
Safety & EMC	Safety Standards	CE EN62368-1
	EMC Emissions	EN55032, EN55035, EN61000-3-2 2014, EN61000-3-3 2013

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

## Mechanical Specification



Dimensions : Millimetres

## Part Number Table

Description	Part Number
EU Wall Plug Adapter 12W, 5VDC, 2A Output	MP009259

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.