

GL6G-P4211 G6

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
GL6G-P4211	1059632

Other models and accessories → www.sick.com/G6

Illustration may differ



Detailed technical data

Features

Device type	Photoelectric sensors
Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Dual lens
Sensing range max.	\leq 6 m $^{1)}$
Sensing range	\leq 5 m $^{1)}$
Polarisation filters	Yes
Emitted beam	
Light source	PinPoint LED ²⁾
Type of light	Visible red light
Light spot size (distance)	Ø 8 mm (350 mm)
Key LED figures	
Wave length	650 nm
Adjustment	Potentiometer, 270°
Special applications	Detecting transparent objects

¹⁾ Reflector PL80A.

Safety-related parameters

MTTF _D	1,895 years
DC _{avg}	0 %

 $^{^{2)}}$ Average service life: 100,000 h at T_U = +25 °C.

Electrical data

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	± 10 % ²⁾
Power consumption	30 mA ³⁾
Protection class	III
Digital output	
Туре	PNP
Signal voltage PNP HIGH/LOW	V_S - ($\leq 3 \text{ V}$) / approx. 0 V
Output current I _{max.}	\leq 100 mA $^{4)}$
Response time	< 625 µs ⁵⁾
Switching frequency	1,000 Hz ⁶⁾
Attenuation along light beam	> 20 %
Switching mode	Light/dark switching
Switching mode selector Selectable via light/dark selector	
Circuit protection	A ⁷⁾ B ⁸⁾ D ⁹⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

Mechanical data

Housing	Rectangular
Dimensions (W x H x D)	12 mm x 31.5 mm x 21 mm
Connection	Male connector M8, 4-pin
Material	
Housing	Plastic, ABS/PC
Front screen	Plastic, PMMA
Weight	20 g

Ambient data

Enclosure rating	IP67
Ambient operating temperature	-25 °C +55 °C ¹⁾
Ambient temperature, storage	-40 °C +70 °C
UL File No.	NRKH.E348498 & NRKH7.E348498

 $^{^{1)}}$ Temperature stability following adjustment +/-10 $^{\circ}$ C.

Classifications

ECI@ss 5.0	27270902
------------	----------

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ At Uv > 24 V, IA max. = 50 mA.

⁵⁾ Signal transit time with resistive load.

⁶⁾ With light/dark ratio 1:1.


 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

 $^{^{8)}}$ B = inputs and output reverse-polarity protected.

 $^{^{9)}}$ D = outputs overcurrent and short-circuit protected.

ECI@ss 5.1.4	27270902
ECI@ss 6.0	27270902
ECI@ss 6.2	27270902
ECI@ss 7.0	27270902
ECI@ss 8.0	27270902
ECI@ss 8.1	27270902
ECI@ss 9.0	27270902
ECI@ss 10.0	27270902
ECI@ss 11.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

Connection type




Connection diagram

Cd-066

Characteristic curve

GL6


Operating reserve



- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector P250
- 4 Reflector PL20A
- ⑤ Reflective tape REF-IRF-56


Light spot size

GL6, GL6G



Sensing range diagram


GL6, GL6G



- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector P250
- 4 Reflector PL20A
- ⑤ Reflective tape REF-IRF-56


Adjustments

Adjustment possibility



- 4 LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- Sensitivity control: potentiometer

Dimensional drawing (Dimensions in mm (inch))



- ① Optical axis, receiver
- ② Optical axis, sender
- 3 Mounting holes M3
- 4 LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- 6 Light/ dark rotary switch: L = light switching, D = dark switching

Recommended accessories

Other models and accessories → www.sick.com/G6

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
	Stainless steel (1.4301)	BEF-WN-G6	2062909	
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574	
Plug connecto	Plug connectors and cables			
	Head A: female connector, M8, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF8U14- 050VA3XLEAX	2095889	
	Head A: male connector, M8, 4-pin, straight Head B: - Cable: unshielded	STE-0804-G	6037323	
Reflectors				
	Rectangular, screw connection, 51 mm x 61 mm, PMMA/ABS, Screw-on, 2 hole mounting	P250	5304812	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

