

WT100L-F2241

W100 Laser

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WT100L-F2241	6030704

Included in delivery: BEF-W100-A (1)

Other models and accessories → www.sick.com/W100_Laser

Illustration may differ



Detailed technical data

Features

Sensor/ detection principle	Photoelectric proximity sensor, Energetic
Dimensions (W x H x D)	11 mm x 31 mm x 20 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 mm 450 mm ¹⁾
Sensing range	0 mm 400 mm
Type of light	Visible red light
Light source	Laser ²⁾
Light spot size (distance)	Ø 2 mm (400 mm)
Wave length	650 nm
Laser class	1
Adjustment	Potentiometer, 270°
Special applications	Detecting small objects, Detection of objects moving at high speeds

 $^{^{1)}}$ Object with 90 % reflectance (referred to standard white, DIN 5033).

Mechanics/electronics

Supply voltage	10 V DC 30 V DC ¹⁾
Ripple	± 10 % ²⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ Average service life: 50,000 h at TU = +25 °C.

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ B = inputs and output reverse-polarity protected.

 $^{^{8)}}$ D = outputs overcurrent and short-circuit protected.

Current consumption 30 mA 3) Switching output PNP Switching mode Light/dark switching	
Switching mode Light/dark switching	
Switching mode selector Selectable via light/dark rotary switch	
Signal voltage PNP HIGH/LOW $U_V - 1.8 \text{ V} / \text{ca. } 0 \text{ V}$	
Output current I _{max} . ≤ 100 mA	
Response time < 0.25 ms ⁴⁾	
Switching frequency 2,000 Hz ⁵⁾	
Connection type Male connector M8, 4-pin	
Circuit protection A 60 B 7) D 80	
Weight 10 g	
Housing material Plastic, ABS/PC	
Optics material Plastic, PMMA	
Enclosure rating IP65	
Items supplied Stainless steel mounting bracket (1.4301/304) BEF-W100-A	
Items suppliedStainless steel mounting bracket (1.4301/304) BEF-W100-AAmbient operating temperature-10 °C +50 °C	

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

Safety-related parameters

MTTF _D	416 years
DC _{avg}	0 %

Classifications

ECI@ss 5.0	27270903
ECI@ss 5.1.4	27270903
ECI@ss 6.0	27270903
ECI@ss 6.2	27270903
ECI@ss 7.0	27270903
ECI@ss 8.0	27270903
ECI@ss 8.1	27270903
ECI@ss 9.0	27270903
ECI@ss 10.0	27270904
ECI@ss 11.0	27270904
ETIM 5.0	EC001821

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ B = inputs and output reverse-polarity protected.

⁸⁾ D = outputs overcurrent and short-circuit protected.

WT100L-F2241 | W100 Laser

MINIATURE PHOTOELECTRIC SENSORS


ETIM 6.0	EC001821
ETIM 7.0	EC002719
UNSPSC 16.0901	39121528

Connection diagram

Cd-066

Characteristic curve


WT100L



- ① Sensing range on black, 6% remission
- 3 Sensing range on white, 90% remission

Light spot size


WT100L



All dimensions in mm (inch)

Sensing range diagram


WT100L



- Sensing range Sensing range max.
- ① Sensing range on black, 6% remission
- ② Sensing range on gray, 18 % remission
- ③ Sensing range on white, 90% remission

Adjustments

WT100L, WL100L





- ⑤ Orange LED indicator: switching output active
- 6 LED indicator green: power on
- Sensing range (WT) / sensitivity (WL) adjustment: potentiometer, 270°
- (8) Light/ dark rotary switch: L = light switching, D = dark switching

MINIATURE PHOTOELECTRIC SENSORS

Dimensional drawing (Dimensions in mm (inch))

WT100L, WL100L





- ① Threaded mounting hole M3
- ② Center of optical axis, receiver
- 3 Center of optical axis, sender
- 4 Connection

Recommended accessories

Other models and accessories → www.sick.com/W100_Laser

	Brief description	Туре	Part no.
Plug connectors and cables			
	Head A: female connector, M8, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF8U14- 050VA3XLEAX	2095889
	Head A: female connector, M8, 4-pin, straight Head B: - Cable: unshielded	DOS-0804-G	6009974

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

