

























Features

- 2.06"x1.07"compact size
- · Universal input 85~305VAC
- No load power consumption<0.1W
- · EMI Class B without additional components
- Wide operating temp. range -30~70°C
- · Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- · Isolation Class II
- · Pass LPS
- 3 years warranty

Applications

- Industrial electrical equipment
- Mechanical equipment
- Factory automation equipment
- · Hand-held electronic device

■ GTIN CODE


MW Search: https://www.meanwell.com/serviceGTIN.aspx

Description

IRM-20 is a 20W miniature (52.4*27.2*24mm) AC-DC module-type power supply, ready to be soldered onto the PCB boards of various kinds of electronic instruments or industrial automation equipments. This product allows the universal input voltage range of 85~305VAC. The 94V-0 flame retardant plastic case and the fully-potted silicone enhance the heat dissipation and meet the anti-vibration demand up to 2G; moreover, it provides the fundamental resistance to dust and moisture.

With the high efficiency up to 85% and the extremely low no-load power consumption below 0.1W, IRM-20 series fulfills the worldwide regulation for the low power consumption requirement for electronics. The entire series is a Class II design (no FG pin), incorporating the built-in EMI filtering components, enabling the compliance with BS EN/EN55032 Class B; the supreme EMC features keep the end electronic units from electromagnetic interference.

Model Encoding







MODEL		IRM-20-3.3	IRM-20-5	IRM-20-12	IRM-20-15	IRM-20-24
	DC VOLTAGE	3.3V	5V	12V	15V	24V
OUTPUT	RATED CURRENT	4.5A	4A	1.8A	1.4A	0.9A
	CURRENT RANGE	0 ~ 4.5A	0 ~ 4A	0 ~ 1.8A	0 ~ 1.4A	0 ~ 0.9A
	RATED POWER	14.85W	20W	21.6W	21W	21.6W
	RIPPLE & NOISE (max.) Note.2	200mVp-p	200mVp-p	200mVp-p	200mVp-p	200mVp-p
	VOLTAGE TOLERANCE Note.3	±2.5%	±2.5%	±2.5%	±2.5%	±2.5%
	LINE REGULATION	±0.5%	±0.5%	±0.3%	±0.3%	±0.3%
	LOAD REGULATION	±1%	±1%	±0.5%	±0.5%	±0.5%
	SETUP, RISE TIME	1000ms, 20ms/230VAC 1000ms, 20ms/115VAC at full load				
	HOLD UP TIME (Typ.)	40ms/230VAC 8ms/115VAC at full load				
	VOLTAGE RANGE	85 ~ 305VAC 120 ~ 430VDC				
INPUT	FREQUENCY RANGE	47 ~ 440Hz				
	EFFICIENCY (Typ.)	76%	79%	84%	84%	85%
	, , ,				04 /0	00 /0
	AC CURRENT (Typ.)	0.6A/115VAC				
	INRUSH CURRENT (Typ.)	COLD START 20A/115VAC 40A/230VAC				
	LEAKAGE CURRENT	< 0.25mA/277VAC				
PROTECTION	OVERLOAD	115%~160% rated o	· ·			
		Protection type : Hic	T .			
	OVER VOLTAGE	3.8 ~ 4.46V	5.75 ~ 6.75V	13.8 ~ 16.2V	17.25 ~ 20.25V	27.6 ~ 32.4V
		Protection type : Shut off o/p voltage, clamping by zener diode				
ENVIRONMENT	WORKING TEMP.	-30 ~ +70 $^{\circ}$ C (Refer to "Derating Curve")				
	WORKING HUMIDITY	20 ~ 90% RH non-condensing				
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH				
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)				
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes				
	SOLDERING TEMPERATURE					
	OPERATING ALTITUDE Note.4					
SAFETY & EMC (Note.5)	SAFETY STANDARDS	IEC62368-1, UL62368-1, TUV BS EN/EN62368-1, EAC TP TC 004, BSMI CNS14336-1 approved				
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC				
	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH				
		Parameter Standard Test Level / Note				
	EMC EMISSION	Conducted		32(CISPR32), CNS13438		
		Radiated		32(CISPR32), CNS13438		
		Harmonic Current (Note 5	BS EN/EN610	00-3-2	Class A	
		Voltage Flicker	BS EN/EN610	00-3-3		
	EMC IMMUNITY	BS EN/EN55035, BS EN/EN61000-6-2				
		Parameter	Standard		Test Level /Note	
		ESD	BS EN/EN610	00-4-2	Level 3, 8KV air; Level 2, 4KV contact, criteria A	
		Radiated Susceptibility	BS EN/EN610		Level 3, criteria A	
		EFT/Burest	BS EN/EN610		Level 3, criteria A	
		Surge	BS EN/EN610		Level 4,2KV/L-N, criteria A	
		Conducted	BS EN/EN610		Level 3, criteria A	
		Magnetic Field	BS EN/EN610		Level 4, criteria A >95% dip 0. 5 periods, 30% dip 25 periods,	
		Voltage Dips and interrupti	ions BS EN/EN610	00-4-11	>95% dip 0. 5 periods, 30% dip 25 periods, >95% interruptions 250 periods	
OTHERS	MTBF	10656.2K hrs min. Telcordia SR-332 (Bellcore) ; 970.3K hrs min. MIL-HDBK-217F (25° C)				
	DIMENSION	52.4*27.2*24mm (L*W*H)				
	PACKING	0.05Kg/240pcs/13Kg/0.94CUFT				
NOTE	Ripple & noise are measure Tolerance : includes set up The ambient temperature d The power supply is consider.	to tolerance, line regulation and load regulation. derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500f dered as an independent unit ,but the final equipment still need to re-confirm that the whole system complies with the EMC to to the theorem these EMC tests, please refer to "EMI testing of component power supplies."				
	Tolerance : includes set up The ambient temperature d The power supply is consid directives. For guidance on (as available on http://www.	dered as an independent unit ,but the final equipment still need to re-confirm that the whole system complies with the EMC a how to perform these EMC tests, please refer to "EMI testing of component power supplies."				



